

# CM30-25NPP-EW1

**CAPACITIVE PROXIMITY SENSORS** 





## Ordering information

Туре	Part no.
CM30-25NPP-EW1	6058156

Other models and accessories → www.sick.com/CM

Illustration may differ



#### Detailed technical data

#### **Features**

Housing	Cylindrical thread design
Thread size	M30 1.5
Diameter	Ø 30 mm
Sensing range S <sub>n</sub>	4 mm 25 mm
Safe sensing range S <sub>a</sub>	19.13 mm <sup>1)</sup>
Installation type	Non-flush
Switching frequency	50 Hz
Connection type	Cable, 4-wire, 2 m <sup>2)</sup>
Switching output	PNP
Output function	Complementary
Output characteristic	Wire configurable
Electrical wiring	DC 4-wire
Adjustment	Potentiometer (Sensitivity)
Enclosure rating	IP68, IP69K <sup>3)</sup>
Authorizations	Ecolab, CE-conformity, cULus 4)

 $<sup>^{1)}</sup>$  For flush mounting in electrically conductive materials Sa = 0.8 x Sr at temperatures <0 °C and >60 °C.

 $<sup>^{2)}</sup>$  Do not bend below 0  $^{\circ}\text{C}.$ 

 $<sup>^{3)}\, 1</sup>$  m water depth / 60 min.

<sup>&</sup>lt;sup>4)</sup> P3-topax 19, P3-topax 56, P3-topax 66, P3-topactive DES.

## Mechanics/electronics

Supply voltage	10 V DC 36 V DC
Ripple	≤ 10 % <sup>1)</sup>
Voltage drop	$\leq$ 2 V DC $^{2)}$
Current consumption	$\leq$ 12 mA $^{3)}$
Time delay before availability	≤ 200 ms
Hysteresis	3 % 20 %
Reproducibility	≤ 5 % <sup>4) 5)</sup>
Temperature drift (of S <sub>r</sub> )	± 10 %
ЕМС	According to EN 60947-5-2
Continuous current I <sub>a</sub>	≤ 200 mA
Cable material	PVC
Conductor size	0.34 mm <sup>2</sup>
Cable diameter	Ø 5.2 mm
Short-circuit protection	✓
Reverse polarity protection	✓
Power-up pulse protection	✓
Shock and vibration resistance	According to EN 60068
Ambient operating temperature	-30 °C +85 °C <sup>6)</sup>
Ambient storage temperature	-40 °C +85 °C
Housing material	Plastic, PBT
Housing length	81 mm
Thread length	45.5 mm
Tightening torque, max.	≤ 7.5 Nm
Items supplied	Mounting nuts (plastic)
UL File No.	NRKH.E191603

<sup>&</sup>lt;sup>1)</sup> Of Ub.

#### **Reduction factors**

Note	The values are reference values which may vary
Metal	1
Water	1
PVC	Approx. 0.4
Oil	Approx. 0.25
Glass	0.6
Ceramics	0.5
Alcohol	0.7
Wood	0.2 0.7

<sup>&</sup>lt;sup>2)</sup> At I<sub>a</sub> max.

<sup>3)</sup> Without load.

<sup>&</sup>lt;sup>4)</sup> Of Sr.

<sup>5)</sup> Ub and Ta constant.

 $<sup>^{6)}</sup>$  +120 °C short time, at the front of the sensor.


#### Installation note


Remark	Associated graphic see "Installation"
A	30 mm
В	60 mm
c	30 mm
D	75 mm
E	50 mmln critical distances, the sensor should be tested in the application

#### Classifications

ECI@ss 5.0	27270102
ECI@ss 5.1.4	27270102
ECI@ss 6.0	27270102
ECI@ss 6.2	27270102
ECI@ss 7.0	27270102
ECI@ss 8.0	27270102
ECI@ss 8.1	27270102
ECI@ss 9.0	27270102
ETIM 5.0	EC002715
ETIM 6.0	EC002715
UNSPSC 16.0901	39122230

#### Installation note






# Connection diagram

cd-005


#### Characteristic curve

CM30, Non-flush installation



#### Dimensional drawing (Dimensions in mm (inch))

CM30, non-flush, cable



#### Recommended accessories

Other models and accessories  $\rightarrow$  www.sick.com/CM

	Brief description	Туре	Part no.
Mounting brackets and plates			
	Mounting plate for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WG-M30	5321871
40	Mounting bracket for M30 sensors, steel, zinc coated, without mounting hardware	BEF-WN-M30	5308445

# SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

# **WORLDWIDE PRESENCE:**

Contacts and other locations -www.sick.com

