


**PNP SILICON PLANAR MEDIUM POWER TRANSISTORS**

ISSUE 1 – MARCH 94


**ZTX552  
ZTX553**

**TYPICAL CHARACTERISTICS**



**FEATURES**

- \* 100 Volt  $V_{CEO}$
- \* 1 Amp continuous current
- \*  $P_{tot} = 1$  Watt



**E-Line  
TO92 Compatible**

**ABSOLUTE MAXIMUM RATINGS.**

PARAMETER	SYMBOL	ZTX552	ZTX553	UNIT
Collector-Base Voltage	$V_{CB0}$	-100	-120	V
Collector-Emitter Voltage	$V_{CEO}$	-80	-100	V
Emitter-Base Voltage	$V_{EBO}$	-5	-5	V
Peak Pulse Current	$I_{CM}$	-2	-2	A
Continuous Collector Current	$I_C$	-1	-1	A
Power Dissipation: at $T_{amb} = 25^\circ C$ derate above $25^\circ C$	$P_{tot}$	1	5.7	W
Operating and Storage Temperature Range	$T_j, T_{stg}$	-55 to +200		$^\circ C$

**ELECTRICAL CHARACTERISTICS (at  $T_{amb} = 25^\circ C$ ).**

PARAMETER	SYMBOL	ZTX552		ZTX553		UNIT	CONDITIONS.
		MIN.	MAX.	MIN.	MAX.		
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-100		-120		V	$I_C = -100 \mu A$
Collector-Emitter Sustaining Voltage	$V_{CEO(sus)}$	-80		-100		V	$I_C = -10 mA$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5		-5		V	$I_E = -100 \mu A$
Collector Cut-Off Current	$I_{CBO}$		-0.1		-0.1	$\mu A$	$V_{CB} = -80V$ $V_{CB} = -100V$
Emitter Cut-Off Current	$I_{EBO}$		-0.1		-0.1	$\mu A$	$V_{EB} = -4V$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	-0.25		-0.25		V	$I_C = -150 mA, I_B = -15 mA^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	-1.1		-1.1		V	$I_C = -150 mA, I_B = -15 mA^*$
Base-Emitter Turn-on Voltage	$V_{BE(on)}$	-1.0		-1.0		V	$I_C = -150 mA, V_{CE} = -10V^*$
Static Forward Current Transfer Ratio	$h_{FE}$	40 10	150	40 10	200		$I_C = -150 mA, V_{CE} = -10V^*$ $I_C = -1A, V_{CE} = -10V^*$
Transition Frequency	$f_T$	150		150		MHz	$I_C = -50 mA, V_{CE} = -10V$ $f = 100 MHz$
Output Capacitance	$C_{obo}$	12		12		MHz	$V_{CB} = -10V, f = 1 MHz$

\*Measured under pulsed conditions. Pulse width=300 $\mu s$ . Duty cycle  $\leq 2\%$


**ZTX552  
ZTX553**

**PNP SILICON PLANAR  
MEDIUM POWER TRANSISTORS**

ISSUE 1 – MARCH 94


**ZTX552  
ZTX553**

**TYPICAL CHARACTERISTICS**



**FEATURES**

- \* 100 Volt  $V_{CE0}$
- \* 1 Amp continuous current
- \*  $P_{tot} = 1$  Watt



**E-Line  
TO92 Compatible**

**ABSOLUTE MAXIMUM RATINGS.**

PARAMETER	SYMBOL	ZTX552	ZTX553	UNIT
Collector-Base Voltage	$V_{CBO}$	-100	-120	V
Collector-Emitter Voltage	$V_{CEO}$	-80	-100	V
Emitter-Base Voltage	$V_{EBO}$	-5	-5	V
Peak Pulse Current	$I_{CM}$	-2	-2	A
Continuous Collector Current	$I_C$	-1	-1	A
Power Dissipation: at $T_{amb} = 25^\circ\text{C}$ derate above $25^\circ\text{C}$	$P_{tot}$	1	5.7	W
Operating and Storage Temperature Range	$T_j, T_{stg}$	-55 to +200		$^\circ\text{C}$

**ELECTRICAL CHARACTERISTICS (at  $T_{amb} = 25^\circ\text{C}$ ).**

PARAMETER	SYMBOL	ZTX552		ZTX553		UNIT	CONDITIONS.
		MIN.	MAX.	MIN.	MAX.		
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	-100		-120		V	$I_C = -100\mu\text{A}$
Collector-Emitter Sustaining Voltage	$V_{CEO(sus)}$	-80		-100		V	$I_C = -10\text{mA}$
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	-5		-5		V	$I_E = -100\mu\text{A}$
Collector Cut-Off Current	$I_{CBO}$		-0.1		-0.1	$\mu\text{A}$	$V_{CE} = -80\text{V}$ $V_{CB} = -100\text{V}$
Emitter Cut-Off Current	$I_{EBO}$		-0.1		-0.1	$\mu\text{A}$	$V_{EB} = -4\text{V}$
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	-0.25		-0.25		V	$I_C = -150\text{mA}$ , $I_B = -15\text{mA}^*$
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	-1.1		-1.1		V	$I_C = -150\text{mA}$ , $I_B = -15\text{mA}^*$
Base-Emitter Turn-on Voltage	$V_{BE(on)}$	-1.0		-1.0		V	$I_C = -150\text{mA}$ , $V_{CE} = -10\text{V}^*$
Static Forward Current Transfer Ratio	$h_{FE}$	40 10	150	40 10	200		$I_C = -150\text{mA}$ , $V_{CE} = -10\text{V}^*$ $I_C = -1\text{A}$ , $V_{CE} = -10\text{V}^*$
Transition Frequency	$f_T$	150		150		MHz	$I_C = -50\text{mA}$ , $V_{CE} = -10\text{V}$ $f = 100\text{MHz}$
Output Capacitance	$C_{obo}$		12		12	MHz	$V_{CB} = -10\text{V}$ , $f = 1\text{MHz}$

\*Measured under pulsed conditions. Pulse width=300µs. Duty cycle ≤2%