

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



1-channel contact extension with TBUS interface, 4 N/O contacts, 1 N/C contact, 1 confirmation current path, undelayed, Cat. 4, PL e in accordance with EN ISO 13849, plug-in screw terminal blocks, width: 22.5 mm

Your advantages

- 4 enabling current paths, 1 signaling current path, and 1 confirmation current path
- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with IEC 62061, SIL 3 in accordance with IEC 61508

Commercial Data

Item number	2981677
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DN01
Product Key	DNA231
Catalog Page	Page 233 (C-6-2019)
GTIN	4046356081535
Weight per Piece (including packing)	225.5 g
Weight per Piece (excluding packing)	196.9 g
Customs tariff number	85371098
Country of origin	DE

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Technical Data

Product properties

Product type	Safety relays
Product family	PSRclassic
Application	Extension module
Mechanical service life	approx. 10^7 cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Electrical properties

Maximum power dissipation for nominal condition	1.01 W
Nominal operating mode	100% operating factor

Air clearances and creepage distances between the power circuits

Rated insulation voltage	250 V
Rated surge voltage/insulation	4 kV / basic isolation (safe isolation, reinforced insulation and 6 kV between input circuit/N/C contacts and enabling current paths).

Input data

General

Rated control circuit supply voltage U_S	24 V DC
Voltage range with reference to U_S	0.9 ... 1.1
Rated control supply current I_S	42 mA
Typical response time	10 ms
Typical release time	10 ms
Recovery time	1 s
Protective circuit	Surge protection; Suppressor diode
Status display	Green LED

Output data

Contact switching type	4 enabling current paths
	1 signaling current path
	1 confirmation current path
Contact material	AgSnO ₂
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	15 V AC/DC
Limiting continuous current	6 A (N/O contact, DC1/AC1)
	3 A (N/C contact)
Maximum inrush current	6 A (N/O contact, DC1/AC1)
	3 A (N/C contact)
Inrush current, minimum	25 mA
Sq. Total current	$72 \text{ A}^2 (I_{TH}^2 = I_1^2 + I_2^2 + I_3^2 + I_4^2)$

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Interrupting rating (ohmic load) max.	144 W (24 V DC, $\tau = 0$ ms, N/C contact 61/62: 72 W)
	288 W (48 V DC, $\tau = 0$ ms, N/C contact 61/62: 144 W)
	77 W (110 V DC, $\tau = 0$ ms)
	88 W (220 V DC, $\tau = 0$ ms)
	1500 VA (250 V AC, $\tau = 0$ ms, N/C contact 61/62: 750 VA)
Maximum interrupting rating (inductive load)	48 W (24 V DC, $\tau = 40$ ms)
	40 W (48 V DC, $\tau = 40$ ms)
	35 W (110 V DC, $\tau = 40$ ms)
	33 W (220 V DC, $\tau = 40$ ms)
Switching capacity min.	0.4 W
Switching capacity in accordance with IEC 60947-5-1	5 A (DC13)
	5 A (AC15)
Switching capacity (360/h cycles)	6 A (24 V DC)
	5 A (230 V AC)
Switching capacity (3600/h cycles)	3 A (24 V (DC13))
	3 A (230 V (AC15))
Output fuse	10 A gL/gG NEOZED (N/O contact)
	4 A gL/gG NEOZED (N/C contact)

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Screw connection
Conductor cross section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Stripping length	7 mm
Screw thread	M3

Dimensions

Width	22.5 mm
Height	99 mm
Depth	114.5 mm

Material specifications

Housing material	Polyamide
------------------	-----------

Characteristics

Safety data

Stop category	0
---------------	---

Safety data: EN ISO 13849

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Category	4 (In conjunction with suitable evaluating device)
Performance level (PL)	e (In conjunction with suitable evaluating device)

Safety data: IEC 61508 - High demand

Designation	The data only applies if the safety function is demanded at least once a year.
Safety Integrity Level (SIL)	3 (In conjunction with suitable evaluating device)
Probability of a hazardous failure per hour (PFH _D)	9.7×10^{-11} (In conjunction with suitable evaluating device)
Proof test interval	240 Months
Duration of use	240 Months

Safety data: IEC 61508 - Low demand

Designation	The data is only valid if the demand rate is no more than once a year.
Safety Integrity Level (SIL)	3 (In conjunction with suitable evaluating device)
Probability of a hazardous failure on demand (PFD _{AVG})	1.37×10^{-4} (In conjunction with suitable evaluating device)
Proof test interval	76 Months
Duration of use	240 Months

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	IEC 60947-1
-----------------------	-------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any
Connection method	Screw connection

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module




2981677


<https://www.phoenixcontact.com/us/products/2981677>

Drawings

Circuit diagram



Circuit diagram



PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2981677>



EAC

Approval ID: EAC-Zulassung



EAC

Approval ID: RU C-DE.A*30.B.01082



UL Listed

Approval ID: FILE E 140324



cUL Listed

Approval ID: FILE E 140324



Functional Safety

Approval ID: 968/FSP 1678.00/18



EAC

Approval ID: TR TS_D_01838-19

cULus Listed

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Classifications

ECLASS

ECLASS-11.0	27371819
ECLASS-12.0	27371819
ECLASS-13.0	27371819

ETIM

ETIM 8.0	EC001449
----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
	Hexahydromethylphthalic anhydride
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

Accessories

PSR-TBUS - DIN rail bus connectors

2890425

<https://www.phoenixcontact.com/us/products/2890425>

DIN rail connector for safety switching devices, for supplying/controlling/monitoring (depending on the module)



PSR-TBUS-TP - DIN rail bus connectors

2981716

<https://www.phoenixcontact.com/us/products/2981716>

Blind plug for the PSR-TBUS DIN rail connector used with the modular safety relay system (PSR-SDC4)



PSR-SCP- 24DC/URM4/4X1/2X2/B - Extension module



2981677

<https://www.phoenixcontact.com/us/products/2981677>

PSR-TBUS - 1PCS - DIN rail bus connectors

1326060

<https://www.phoenixcontact.com/us/products/1326060>

DIN rail connector for safety switching devices, for supplying/controlling/monitoring (depending on the module)



Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com