



## Table of Contents

<b>Cleaner Degreasers</b> .....	<b>4-6</b>
<b>Heavy-Duty Degreasers</b> .....	<b>7</b>
<b>Contact Cleaners</b> .....	<b>8-9</b>
<b>Lubricant</b> .....	<b>9</b>
<b>Flux Removers</b> .....	<b>10-13</b>
<b>IPA — Isopropyl Alcohol</b> .....	<b>13</b>
<b>Dusters</b> .....	<b>14-15</b>
<b>Freeze Spray</b> .....	<b>16</b>
<b>Static Dissipative Products</b> .....	<b>17</b>
<b>Desoldering Braid</b> .....	<b>18-19</b>
<b>CircuitWorks® Repair and Prototype Tools</b> ..	<b>20-24</b>
<b>Conformal Coating</b> .....	<b>25-26</b>
<b>Temporary Solder Mask</b> .....	<b>27-28</b>
<b>Presaturated Wipes and Swabs</b> .....	<b>29</b>
<b>Dry Wipes</b> .....	<b>30</b>
<b>Swabs and Applicators</b> .....	<b>31-33</b>
<b>Product Specifications/Callouts</b> .....	<b>34</b>
<b>Part Number Index</b> .....	<b>35</b>

**Additional catalogs are available for specific applications and markets...**




## COVENTRY™

A wide variety of swabs, dry and presaturated wipes for cleanrooms and other critical environments. Ideal products for medical electronics, biotech, semicon and other applications where all contamination must be avoided.



## FOCUS™

Cleaners, cleaning tools, wipes and swabs developed for fiber optic applications. Products are optimized for the wet-dry Combination Cleaning™ process, which is industry recognized as the optimal method of end face cleaning.



## Aviation / Avionics

Cleaners and electronic repair materials that are ideally suited for aircraft maintenance.



# Chemtronics®

Nothing Performs Like Chemtronics



**Tri-V™ – Safer, Nonflammable High Performance nPB Replacement Chemistry**

Cleaning solvent choices are being constrained by regulations, safety concerns and cost. **Chemtronics Tri-V™ High Performance Solvents expand cleaning chemistry options.** These engineered cleaning solutions offer powerful cleaning performance for vapor degreasing, ultrasonic cleaning and immersion cleaning.

- Cost and cleaning performance of n-propyl bromide (nPB), but without the safety concerns.
- Aerosol and bulk packaging available for benchtop cleaning, immersion cleaning, or vapor degreasing.
- Available in Electro-Wash® Tri-V for electronic cleaning, Max-Kleen™ Tri-V™ for heavy-duty cleaning, and Flux-Off® Tri-V™ for removing flux from electronic assemblies.

**Chemtronics offers a wide variety of other high performance solvent cleaners:**



**Delta** – Powerful, nonflammable AK225 replacement chemistry



**Verizane™** – Nonflammable and effective on most sensitive plastics



**Cirozane™** – Nonflammable and safest on sensitive plastics

**Contact Chemtronics today! Application specialists are ready to identify the best choice for you.**

770-424-4888 | 800-645-5244 • [askchemtronics@chemtronics.com](mailto:askchemtronics@chemtronics.com)



## nPB Replacements for Greater Safety

n-propyl bromide (also known as nPB or 1-Bromopropane, CAS 106-94-5) is under close scrutiny by local and national government officials and health and safety managers because of safety concerns.

Studies have shown that exposure to nPB can cause negative neurological and reproductive effects. The National Toxicology Program (NTP) has stated that nPB is "reasonably anticipated to be a human carcinogen", based on increased lung, large intestine and skin cancers observed in animal studies.

OSHA has issued a Hazard Alert detailing worker safety concerns. The American Conference of Governmental Industrial Hygienists (ACGIH) recommends a 10 ppm time-weighted average threshold limit, but has proposed a lower 0.1 ppm (ACGIH 2013). (Source: OSHA Hazard Alert - [https://www.osha.gov/dts/hazardalerts/1bromopropane\\_hazard\\_alert.html](https://www.osha.gov/dts/hazardalerts/1bromopropane_hazard_alert.html))

Safety, regulatory and liability concerns are driving the change from nPB, and Chemtronics® has the ideal replacements with Tri-V™ High Performance Solvents. Electro-Wash® Tri-V, Max-Kleen™ Tri-V, and Flux-Off® Tri-V offer the cost and cleaning performance of nPB, but with much greater safety!





**Electro-Wash® High Purity Solvents** are the most effective products made for critical cleaning and degreasing. Each cleaner is engineered for specific applications — from precision cleaning of sensitive equipment to heavy duty degreasing. Electro-Wash® cleaner degreasers clean a wide variety of oil, grease, oxides and handling contamination from equipment and assemblies.



## Electro-Wash® QD

Fast drying, nonflammable electronics cleaner degreaser

- Nonflammable, no chlorinated compounds
- Excellent material compatibility
- Displaces moisture
- Evaporates fast, minimizes down time
- NSF registered K1 and K2
- All-Way Spray aerosol

**DEL1608B** 12 oz / 340 g BrushClean™ aerosol

## Electro-Wash® VZ

Economical, non-ozone depleting, nonflammable universal cleaner degreaser

- Nonflammable
- One cleaner for all soil types
- Low odor
- Evaporates quickly without leaving residue
- Penetrates to clean hard to reach areas
- Low GWP of <1
- All-Way Spray and BrushClean attachment

**ES6100** 12 oz / 340 g aerosol

**ES6119** 19 oz / 538 g aerosol

**ES6101** 1 gal / 3.7 L liquid

**ES6155** 53 gal / 200 L liquid

## All-Way Spray

Chemtronics aerosol products (where indicated) can spray even when rotated to clean hard-to-reach places.



DEL1608B

ES6100

ES6119





## Electro-Wash® Tri-V

Extra-strength, nonflammable electronics cleaner degreaser for replacing n-propyl bromide

- Nonflammable
- Can be used on energized equipment
- Fast drying
- Does not contain n-propyl bromide, trichloroethylene, or perchloroethylene
- NSF registered K1 and K2



- VV1614** 12 oz / 340 g aerosol
- VV114** 1 gal / 3.7 L liquid
- VV514** 5 gal / 19 L liquid
- VV5514** 53 gallons / 200 L liquid

## Electro-Wash® Delta

Extra-strength, nonflammable electronics cleaner degreaser

- Nonflammable
- Best AK225 replacement chemistry
- Fast drying
- Contains no ozone depleting compounds, low VOC's
- NSF registered K1 and K2
- All-Way Spray aerosol



- DEL1601** 12 oz / 340 g aerosol
- DEL2201** 19 oz / 538 g aerosol
- DEL101** 1 gal / 3.7 L liquid
- DEL5501** 53 gal / 200 L liquid

## Product Selection Guide

Cleaner Degreasers	Features						Cleaning Ability						Cleaning Methods		
	Plastic Safe	Nonflammable	No Ozone Depleting Chemicals	Dries Fast	Dielectric Breakdown (Aerosol)	VOC-EPA (Aerosol / Liquid)	Grease	Oil	Ionic Soils	Aerosol Spray	Vapor Degreasing	Ultrasonics	Hot Immersion	Cold Immersion	
Electro-Wash® Tri-V	✓	✓	✓	✓	21kV	70% / 95%	1	1	2	✓	✓	✓	✓	✓	Strongest Cleaner
Electro-Wash® Delta	✓	✓	✓	✓	31kV	63% / 85%	2	1	2	✓		✓	✓	✓	
Electro-Wash® NXO	✓	✓	✓	✓	15kV	38% / 50%	1	1	2	✓	✓	✓	✓	✓	
Electro-Wash® QD	✓	✓	✓	✓	11kV	0% / NA	3	1	2	✓					
Electro-Wash® VZ	✓	✓	✓	✓	17kV	19% / 45%	3	1	2	✓	✓	✓	✓	✓	
Electro-Wash® PX	✓	✓	✓	✓		75% / 100%	1	1	1	✓				✓	
Electro-Wash® MX	✓	✓	✓	✓		75% / 100%	1	1	1	✓					
Electro-Wash® PR	✓	✓	✓	✓		75% / NA	1	1	-	✓					
Electro-Wash® CZ	✓	✓	✓	✓	17kV	75% / NA	3	2	2	✓					
Electro-Wash® Two Step	✓	✓	✓	✓		NA / 100%	1	1	1			✓	✓	✓	Most Plastic-Safe
<b>Industrial Degreasers</b>															
Max-Kleen™ Tri-V	✓	✓	✓	✓	8kV	70% / 90%	1	1	2	✓	✓	✓	✓	✓	
Max-Kleen™ Citrus	✓	✓	✓	✓	62kV	49% / 49%	2	2	2	✓		✓	✓	✓	
Max-Kleen™ Citrus HF	✓	✓	✓	✓	33kV	50% / 4%	1	1	3	✓					

1 – Excellent    2 – Good    3 – Fair



## Electro-Wash® MX

Extra-strength, plastic safe universal cleaner with moderate evaporation time

- Safe on plastics
- Flammable
- Extra cleaning strength
- Moderate evaporation rate increases cleaning power
- Leaves no residue
- Removes organic and ionic soils
- All-Way Spray aerosol

**ES1621** 10 oz / 283 g aerosol

**CP421** 25 - 8" x 10" / 20.3 cm x 25.4 cm premoistened wipes (9 ml each)

**FW2150** 9 g / 0.32 oz pen

## Electro-Wash® CZ

Non-ozone depleting, nonflammable cleaner degreaser safe for use on plastics

- Safe on plastics
- Nonflammable
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES7100** 12 oz / 340 g aerosol



ES1621

ES7100

## Electro-Wash® NXO

Extra-strength, nonflammable cleaner degreaser

- Nonflammable
- Extra cleaning strength
- Dries fast
- Leaves no residue
- Test on plastics
- All-Way Spray aerosol

**ES1607** 12 oz / 340 g aerosol

**ES107** 1 gal / 3.7 L liquid

## Electro-Wash® PX

Extra-strength universal cleaner and degreaser safe for use on plastics

- Safe on plastics
- Flammable
- Extra cleaning strength
- Dries fast
- Leaves no residue
- Removes organic and ionic soils
- All-Way Spray aerosol

**ES810** 5 oz / 141 g trigger aerosol

**ES1210** 12.5 oz / 354 g aerosol

**ES1210A** 12.5 oz / 354 g trigger aerosol

**ES110** 1 gal / 3.7 L liquid



ES1607

ES810



## Electro-Wash® Two Step

Extra-strength, nonflammable ultrasonic and immersion cleaner

- Nonflammable
- Extra cleaning strength
- Leaves no residue when rinsed with Electro-Wash PX or Electro-Wash CZ
- Increasing temperature increases solvency

**ES125A** 1 gal / 3.7 L liquid

## Electro-Wash® PR

Regular-strength cleaner safe for use on plastics

- Safe on plastics
- Flammable
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES1603** 10 oz / 283 g aerosol



ES125A

ES1603





**Max-Kleen™ Heavy-Duty Degreasers** rise to the challenge of your most difficult jobs. These industrial strength cleaners offer fast, easy removal of grease, tar, asphalt, oil and grime. The extra-strength your toughest degreasing jobs require.

**NEW!**



VV179



VV2279



ES2289



ES2291



## Max-Kleen™ Tri-V™

Extra-strength, nonflammable heavy duty degreaser for replacing n-propyl bromide

- Nonflammable
- Can be used on energized equipment
- Fast drying
- Does not contain n-propyl bromide, trichloroethylene, or perchloroethylene
- NSF registered K1 and K2

<b>VV2279</b>	20 oz / 567 g aerosol
<b>VV179</b>	1 gal / 3.7 L liquid
<b>VV579</b>	5 gal / 19 L liquid
<b>VV5579</b>	53 gallons / 200 L liquid

## Max-Kleen™ Citrus

Citrus-based extra-strength degreaser

- Citrus-based formula
- Engineered for fast removal of oxidized grease, sludge, wax, tar and oil
- Dielectric strength of 62 kV
- Does not contain chlorinated solvents
- Safe on most metals and plastics
- Non-corrosive and nonconductive
- NSF Registered — Nonfood Compounds/Code C1
- All-Way Spray aerosol

<b>ES2289</b>	15 oz / 425 g aerosol
<b>ES589</b>	5 gal / 19 L liquid
<b>ES5589</b>	53 gallons / 200 L liquid

## Max-Kleen™ Citrus HF

High flashpoint citrus-based degreaser for heavy greases

- Citrus-based formula with with a high flash point
- Quickly removes all types of tough soils including oxidized oil and grease
- Safe for use on most metals and plastics
- Flashpoint greater than 140° F
- Non-corrosive and nonconductive
- Low Toxicity
- Leaves no residue
- All-Way Spray aerosol

<b>ES2291</b>	13.5 oz / 383 g aerosol
<b>ES191</b>	1 gal / 3.7 L liquid
<b>ES5591</b>	53 gallons / 200 L liquid

# Contact Cleaners



**Pow-R-Wash™ High Purity Formulations** remove environmental contaminants and protect contacts from corrosion and frictional wear. Contact cleaners restore electrical continuity to all electronic and electrical contacts by penetrating and removing insulating oil and grease, conductive carbon soil, and insulative oxides from contact surfaces. By restoring full circuit continuity, Chemtronics contact cleaners improve the performance of all equipment that rely on electrical contacts.



DEL1681

## Pow-R-Wash™ Delta

Nonflammable cleaner safe for use on powered-up contacts and surrounding plastics

- Nonflammable
- Best AK225 replacement chemistry
- Fast drying
- Dielectric breakdown 30 kV
- Contains no ozone depleting compounds, low VOC's
- All-Way Spray aerosol



**DEL1681** 12 oz / 340 gm aerosol



ES1605

## Pow-R-Wash™ PR

Regular-strength contact cleaner safe for use on plastics

- Safe on plastics
- Flammable
- Dielectric breakdown of 44 kV
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES1605** 10 oz / 283 g aerosol

## Product Selection Guide

Cleaner Degreasers	Features						Benefits and Applications			
	Plastic Safe	Nonflammable	Cleaning Strength	No Ozone Depleting Chemicals	Dries Fast	VOC-EPA (Aerosol / Liquid)	For Use On Live Circuits	Dielectric Breakdown	Lubricates	
Pow-R-Wash® Delta	✓	✓	X	✓	✓	56% / NA		30kV		
Pow-R-Wash® Cable Cleaner	✓		X	✓		50% / NA		62kV		
Pow-R-Wash® VZ		✓	R	✓	✓	16% / 75%	✓	15kV		
Pow-R-Wash® PR	✓		R	✓	✓	75% / NA		44kV		
Tune-O-Wash	✓		R	✓	✓	75% / NA		23kV		
DPL® Deep Penetrating Lubricant	✓		R	✓	NA	0% / NA	✓*	30kV		✓
Pow-R-Wash® CZ	✓	✓	R	✓	✓	7% / NA	✓	31kV		

R – Regular Strength

X – Extra Strength

\* For lubrication only





## Pow-R-Wash™ CZ

Non-ozone depleting, nonflammable contact cleaner safe for use on powered-up contacts and surrounding plastics

- Safe on plastics
- Nonflammable
- Dielectric strength of 31 kV
- Evaporates quickly without leaving residue
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES7300** 12 oz / 340 g aerosol

## Pow-R-Wash™ VZ

Economical non-ozone depleting, nonflammable contact cleaner safe for use on live circuits

- Nonflammable
- Dielectric breakdown of 15 kV
- Noncorrosive
- Evaporates quickly without leaving residue
- Test on plastics
- Ideal AK225 replacement
- All-Way Spray aerosol

**ES6300** 12 oz / 340 g aerosol

**ES6301** 1 gal / 3.7 L liquid

## Pow-R-Wash™ Cable Cleaner

Extra-strength, plastic safe cable and contact cleaner with a moderate evaporation time

- Safe on plastics
- Flammable
- Dielectric breakdown of 63 kV
- Leaves no residue
- All-Way Spray aerosol

**ES2425** 13.5 oz / 385 g aerosol



ES2425

ES2400

## Tun-O-Wash® Cleaner

Universal fast drying cleaner for electro-mechanical and electronic tuners


- Safe on plastics
- Flammable
- Dries fast
- Leaves no residue
- Cleans hard-to-reach areas
- All-Way Spray aerosol

**ES2400** 12.5 oz / 354 g aerosol

## DPL® Deep Penetrating Lubricant

Deep penetrating lubricant to displace moisture and inhibit corrosion



- Restores, rejuvenates, protects and preserves contacts
- Foaming spray penetrates deeply to remove moisture
- Loosens, cleans, lubricates and protects frozen or corroded parts
- Dielectric strength of 30 kV
- Contains no chlorinated solvents or silicone
- Non-corrosive and nonconductive
- Safe on metals and plastics
- NSF Registered — Nonfood Compounds/Code H2
- All-Way Spray aerosol



**ES1626** 11 oz / 322 g aerosol



# Flux Removers



Flux removal is critical to insure reliable circuitry. Not only unsightly, flux residue can promote short circuits and corrosion, degrading or destroying the printed circuit board.

**Flux-Off® Flux Removers** are specially formulated to remove all types of lead-free, rosin (types R, RA and RMA), no-clean, water soluble and synthetic flux.



## Flux-Off® Delta

Extra strength, nonflammable solvent that removes heavy and encrusted flux deposits

- Nonflammable
- Best AK225 replacement chemistry
- Fast drying
- Contains no ozone depleting compounds, low VOC's
- All-Way Spray aerosol

- DEL1692** 12 oz / 340 g aerosol  
**DEL892B** 6 oz / 141 g BrushClean™ System  
**DEL192** 1 gal / 3.7 L liquid  
**DEL592** 5 gal / 18.9 L liquid  
**DEL5592** 53 gal / 200 L liquid



## Flux-Off® Tri-V™

Extra strength, nonflammable flux remover for replacing n-propyl bromide

- Nonflammable
- Can be used on energized equipment
- Fast drying
- Does not contain n-propyl bromide, trichloroethylene or perchloroethylene

- VWV195** 1 gal / 3.7 L liquid  
**VWV595** 5 gal / 18.9 L liquid  
**VWV5595** 53 gal / 200 L liquid



## Product Selection Guide

	Primary Flux Residue Cleaned				Features					Cleaning Methods					
	Rosin Based*	No-Clean SA-Synthetic	Water Soluble	Removes White Residue	Plastic Safe	Nonflammable	Dries Fast	VOC-EPA (Aerosol / Liquid)	Aerosol Spray	BrushClean™ System	Hand Cleaning	Vapor Degreasing	Ultrasonics	Immersion	Benchtop Spray System
Flux-Off® Tri-V	1	1	NR	✓	✓	✓	95% / NA	✓	✓	✓	✓	✓	✓	✓	Strongest Cleaner
Flux-Off® Delta	1	1	NR	✓	✓	✓	39% / 52%	✓	✓	✓	✓	✓	✓	✓	
Flux-Off® Heavy Duty	1	1	2	✓	✓	✓	38% / 50%	✓	✓	✓	✓	✓	✓	✓	
Flux-Off® VZ	1	2	NR		✓	✓	25% / 75%	✓	✓	✓	✓	✓	✓	✓	
Flux-Off® Complete	1	1	NR			✓	42% / 42%	✓	✓		✓	✓			
Flux-Off® Lead-Free	1	2	2			✓	48% / 51%	✓	✓	✓		✓	✓		
Flux-Off® No Clean Plus	1	1	2	✓		✓	48% / 51%	✓	✓	✓		✓	✓		
Flux-Off® Rosin	1	2	2		✓	✓	75% / 100%	✓	✓	✓		✓	✓		
Flux-Off® Water Soluble	1	NR	1		✓	✓	75% / 75%	✓	✓			✓	✓		
Flux-Off® Aqueous	1	2	1	✓	✓	✓	NA / 16%				✓	✓	✓		
Flux-Off® CZ	1	2	NR		✓	✓	22% / NA	✓	✓	✓					Most Plastic-Safe

1 – Excellent    2 – Good    NR – Not Recommended    \*R, RMA, RA, Rosin-based No-Clean

### Flux-Off® VZ

Economical, non-ozone depleting, nonflammable flux remover

- Nonflammable
- Cleans R, RMA, RA, and no-clean flux
- Low odor
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES6200** 12 oz / 340 g aerosol  
**ES6201** 1 gal / 3.7 L liquid  
**ES6255** 53 gal / 200 L liquid



### Flux-Off® CZ

Non-ozone depleting, nonflammable flux remover safe for use on plastics

- Safe on plastics
- Nonflammable
- Cleans R, RMA, RA, and no-clean flux
- Dries fast
- Leaves no residue
- All-Way Spray aerosol

**ES7200** 12 oz / 340 g aerosol  
**ES7208B** 5 oz / 141 g BrushClean™ System



### Flux-Off® Rosin

Plastic safe flux remover for cleaning all rosin and rosin-based no-clean flux

- Safe on plastics
- Flammable
- Evaporates quickly
- Leaves no residue
- All-Way Spray aerosol

**ES1035** 10 oz / 283 g aerosol  
**ES1035B** 10 oz / 283 g BrushClean™ System  
**ES835B** 5 oz / 141 g BrushClean™ System  
**ES135** 1 gal / 3.7 L liquid  
**ES535** 5 gal / 18.5 L liquid  
**ES5535** 55 gal / 208 L liquid



## The BrushClean™ System

Gentle scrubbing action of a brush combined with high performance flux removers



*BrushClean™ System for difficult fluxes*

## The BrushClean™ System

This system increases cleaning efficiency in two ways – minimizing solvent usage by applying solvent only where you need it, and maximizing cleaning with the addition of mechanical scrubbing action.


- Powerful solvents with scrubbing action of a brush
- Brush precisely applies solvent
- For critical defluxing, use Controlwipe™ (C910) between brush and board to absorb dissolved flux residues
- Solvent flow flushes brush clean
- New brush supplied with every can

*Three powerful tools — one convenient package:*

*Spot clean with the brush*

*Flush under SMD's with the extension tube*

*Clean large areas with the spray nozzle*



ES1697

ES897B

ES1631

## Flux-Off® Complete

Powerful, economical flux remover for cleaning no-clean flux

- Cleans R, RMA, RA, and no-clean flux
- Dries fast
- Leaves no residue
- Flammable
- All-Way Spray aerosol

**ES1698** 12 oz / 340 g aerosol

**ES198** 1 gal / 3.7 L liquid

**ES598** 5 gal / 18.9 L liquid

**ES5598** 53 gal / 200 L liquid

## Flux-Off® Lead-Free

Powerful flux remover for high temperature, lead-free flux removal

- Engineered for removing high temperature, lead-free flux
- Can also be used to remove tin/lead fluxes
- Flammable
- Evaporates quickly without leaving residue
- All-Way Spray aerosol

**ES1697** 12 oz / 340 g aerosol

**ES897B** 6 oz / 170 g BrushClean™ System

**ES197** 1 gal / 3.7 L liquid

**ES5597** 55 gal / 208 L liquid

## Flux-Off® Heavy-Duty

Heavy-duty flux remover for removing encrusted no-clean and rosin flux

- Nonflammable
- Dries fast
- Leaves no residue
- Test on plastics
- All-Way Spray aerosol

**ES1631** 12 oz / 340 g aerosol

**ES131** 1 gal / 3.7 L liquid



ES198

ES1698





ES896B

ES1696



ES1530

ES130

## Flux-Off® Aqueous

Aqueous flux remover for use in ultrasonics and in-line cleaning systems

- Water-based saponifier for removing all flux types
- Safe on plastics
- Nonflammable
- Concentrated – dilute to adjust cleaning strength
- Requires a water rinse

**ES132** 1 gal / 3.7 L liquid

## Flux-Off® No Clean Plus

Powerful economical flux remover for cleaning no-clean flux

- Flammable
- Dries fast
- Leaves no residue
- Test on plastics
- All-Way Spray aerosol

**ES1696** 12 oz / 340 g aerosol

**ES896B** 6 oz / 170 g BrushClean™ System

**ES196** 1 gal / 3.7 L liquid

**ES596** 5 gal / 18.5 L liquid

**ES5596** 55 gal / 208 L liquid

## Flux-Off® Water Soluble

Plastic safe flux remover for cleaning water-soluble flux

- Safe on plastics
- Flammable
- Dries fast
- Leaves no residue

**ES1530** 13.5 oz / 383 g aerosol

**ES130** 1 gal / 3.7 L liquid

## IPA - Isopropyl Alcohol



Conveniently packaged and easy to use 99.8% technical grade isopropyl alcohol

- Safe on plastics
- Flammable
- Dries fast
- Leaves no residue
- Cleans hard-to-reach areas
- Meets Fed Spec TT-1-735A

**ES820L** 8 fl oz / 236 ml liquid

**ES105** 1 gal / 3.7 L liquid

**ES505** 5 gal / 18.9 L liquid

**ES5505** 53 gal / 200 L liquid



ES820L



ES105



**Chemtronics® Dusters** are microscopically clean, oil and moisture free sources of "canned air" developed for applications where safe, ultra-pure cleaning is required. Compact and portable, Chemtronics dusters deliver powerful jet action to instantly remove particles from even the most inaccessible areas. Economize solvent usage by removing layers of dry particulate allowing the solvent to work immediately on encrusted soils. Also accelerate surface drying when using slow evaporating cleaners.

## Ultrajet® All-Way

Invertable duster with the BIGGEST blast to clean anything fast

All-Way Spray can be sprayed into hard to reach places without the risk of dispensing a liquid spray that can freeze or damage sensitive surfaces.

- Nonflammable
- Highest powered cleaning strength
- Zero VOC
- Filtered to 0.2 microns
- 100% ultra-pure HFC-134a — leaves no residue
- Safe on plastics

**ES1620** 8 oz / 226 g aerosol

## Ultrajet®

Duster with the BIGGEST blast to clean anything fast

- Nonflammable
- Highest powered cleaning strength
- Zero VOC
- Filtered to 0.2 microns
- 100% ultra-pure HFC-134a — leaves no residue
- Safe on plastics

**ES1020** 10 oz / 283 g aerosol

## Ultrajet® 70

Powerful, economical duster with a BIGGER blast than competitive dusters

- Nonflammable
- High powered cleaning strength
- Bigger Blast than competitive dusters
- Zero VOC
- Filtered to 0.2 microns
- 100% ultra-pure HFC-134a — leaves no residue
- Safe on plastics

**ES1015** 10 oz / 283 g aerosol



ES1620

ES1020

ES1015



## Product Selection Guide

	Blasting Power	Nonflammable	All-Way Spray	Contents	Force Generated*	Internal Pressure	GWP**	Use On Live Circuits
<b>Ultrajet®</b>	XX Strength	✓	No	HFC-134a	1.51 N	71 PSIG	1300	Yes
<b>Ultrajet® All-Way</b>	XX Strength	✓	Yes	HFC-134a	1.78 N	71 PSIG	1300	Yes
<b>Ultrajet® 70</b>	X Strength	✓	No	HFC-134a	1.35 N	71 PSIG	1300	Yes
<b>Duster</b>	Regular Strength	✓	No	HFC-134a	0.94 N	71 PSIG	1300	Yes
<b>152A Blast™</b>	X Strength		No	HFC-152a	1.38 N	63 PSIG	140	No
<b>Typhoon Blast™ 70</b>	X Strength	✓	No	HFO-1234ze	0.93 N	47 PSIG	6	Yes

\* Force generated measured without extension tubes on Shimpo force gauge.

\*\* Global warming potential (GWP) is calculated based on a 100 year time horizon. Carbon dioxide has a GWP of 1.

### Duster

Economical, regular strength duster

- Nonflammable
- Regular cleaning strength
- Zero VOC
- Filtered to 0.2 microns
- 100% ultra-pure HFC-134a
- Leaves no residue
- Safe on plastics

- ES1017** 10 oz / 283 g aerosol  
**ES1217** 8 oz / 226 g aerosol  
**ES1617** 12 oz / 340 g aerosol



ES1617

### 152A Blast™

Economical, extra-strength general purpose duster

- Safe on plastics
- High powered cleaning strength
- Flammable
- Zero VOC
- 100% pure HFC-152a
- 1/10th Global Warming Potential of HFC-134a

#### Applications:

- Cleaning dust and particles from de-energized electronics
- Maintenance and repair of de-energized computers, postage meters, and servers

- ES1029** 10 oz / 283 g aerosol



### Typhoon Blast™ 70 Duster

Powerful and economical, ultra-low GWP duster with the BIGGER blast

- Ultra-Low GWP
- High powered cleaning strength
- Nonflammable
- Zero VOC
- Filtered to 0.2 microns
- 100% HFO-1234ze
- Leaves no residue
- Safe on plastics

- ES1025** 10 oz. / 383 g aerosol



### Ultrajet® Duster System

Reusable duster system with a precision surgical-grade chrome trigger valve

- Nonflammable
- Conductive trigger valve prevents static build-up
- Zero VOC
- Filtered to 0.2 microns
- 100% ultra-pure HFC-134a — leaves no residue
- Safe on plastics

#### Applications:

- Ground valve for cleaning sensitive electronics
- Cleaning inside electrical cabinets

- ES1020K** 10 oz / 283 g aerosol kit  
 Contents: ES1020R and ES710V  
**ES1020R** 10 oz / 283 g aerosol refill  
**ES710V** Chrome Trigger Valve



ES1020K

Chrome trigger can be grounded for static sensitive applications, and fits refill can (ES1020R).

# Freeze Spray



**Chemtronics® Freeze Sprays** are exceptionally pure, nonflammable and provide instantaneous freezing action while leaving no residue. Conveniently packaged and designed for either pin-point or full board application, these non-reactive circuit refrigerants vaporize instantly while cooling targeted areas.

## Freeze-It®

High-performance, pin-point accurate freeze spray for isolating individual components on PC boards

- Pin-point spray isolates individual components without freezing surrounding areas
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1050** 10 oz / 283 g aerosol  
**ES1550** 15 oz / 425 g aerosol

## Freeze-It® Antistat

High-performance, pin-point accurate freeze spray that safely cools individual static-sensitive components



- Pin-point spray isolates individual components without freezing surrounding areas
- Ideal for use on static sensitive components
- Non-frosting
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1051** 10 oz / 283 g aerosol  
**ES1551** 15 oz / 425 g aerosol



## Freeze Spray

Economical, general purpose freeze spray with wide spray for cooling entire PC boards

- Wide spray for cooling entire boards
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1052** 10 oz / 283 g aerosol

## Arctic Blast™

Ultra-low GWP freeze spray with pin-point accuracy for isolating individual components

- Ultra-low Global Warming Potential
- Pin-point spray isolates individual components without freezing surrounding areas
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1054** 10 oz / 283 g aerosol

## Arctic Blast™ Antistat

Ultra-low GWP antistatic freeze spray with pin-point accuracy for isolating individual components



- Ultra-low Global Warming Potential
- Pin-point spray isolates individual components without freezing surrounding areas
- Ideal for use on static sensitive components
- Non-frosting
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1055** 10 oz / 283 g aerosol

## Arctic Storm™

Ultra-low GWP freeze spray with wide spray for cooling entire PC boards

- Ultra-low Global Warming Potential
- Wide spray for cooling an entire board
- Safe on plastics
- Nonflammable
- Filtered to 0.2 microns

**ES1056** 10 oz / 283 g aerosol

## Product Selection Guide

Product	Application	Global Warming Potential*	VOC (EPA)	Frost Formation	Cooling Speed	Cooling Temperature
Arctic Blast™	Pin-point	6	0%	Yes	Fast	-49°F/-45°C
Arctic Blast™ Antistat	Pin-point	6	<1%	No	Fast	-49°F/-45°C
Arctic Storm™	Wide Area	6	0%	Yes	Very Fast	-49°F/-45°C
Freeze-It®	Pin-point	1300	0%	Yes	Fast	-60°F/-51°C
Freeze-It® Antistat	Pin-point	1300	<1%	No	Fast	-60°F/-51°C
Freeze Spray	Wide Area	1300	0%	Yes	Very Fast	-60°F/-51°C

\* Global warming potential (GWP) is calculated based on a 100 year time horizon. Carbon dioxide has a GWP of 1.





## Static Free™ Hand Guard™

Hand lotion formulated to protect against electrostatic discharge

- Special formulation minimizes potential for static damage
- Penetrates deeply to moisten and refresh dry, chapped or chemically irritated skin
- Nongreasy formula contains Aloe Vera and Vitamin E
- Contains no lanolin, silicone or mineral oil that could inhibit solderability of printed circuits or components

**C805** 8 fl oz / 236 ml liquid



Chemtronics Static Free™ products are engineered to protect electronic equipment and work spaces from static buildup while cleaning and reconditioning. These products provide everything required for a comprehensive surface treatment program as recommended by ANSI/ESD S20.20.

## Static Free™ Plast-N-Glas®

Foaming, non-streaking static dissipative cleaner for transparent surfaces

- Controls static, cleans and polishes in one application
- Effectively removes handling oils, finger soils and stains
- Prevents attraction of dust and dirt
- Compatible with plastics, glass and stainless steel
- Foaming spray won't run or drip; ideal for optical surfaces
- Not for use on anti-glare coatings or mesh screens

### Applications:

- Cleaning computer monitors and housings
- Removing handling soils from precision glassware
- Maintaining cleanliness of observation windows on production equipment

**ES1668** 14 oz / 397 g aerosol

## Screen Prep™ Presaturated Wipe

Convenient cleaning and static control for monitors

- Prevents airborne recontamination for up to 7 days
- Safely removes dust, dirt, oil and nicotine
- Controls static-generated contamination
- Wet pad cleans and applies static protection
- Dry wiper polishes screen optically clear

**CSP20** 25 twin packs  
#1 presaturated pad  
#2 polishing wiper

## Static Free™ Mat and Benchtop Reconditioner


Cleans and rejuvenates ESD-safe surfaces

- Cleans and rejuvenates burned or dead spots on ESD mats
- Excellent for extending life of ESD mats
- Will not dry mat surfaces with repeated use
- Long-lasting dissipative protection – up to 30 days
- Effective in relative humidity below 15%
- Chloride and amine free formulation
- Noncorrosive
- Meets static decay criteria of MIL-B-891705C

**ES1664T** 16 fl oz / 472 mL Trigger Spray  
**SIP125P1664** 125 presaturated wipes in pull-up tub  
**NEW!**



# Desoldering Braid



**SW SODER-WICK®**  
Desoldering Braid



**All Soder-Wick meet these specs:**

- MIL-F-14256 F type R flux
- NASA-STD-8739.3 Soldered Electrical Connections
- DOD-STD-883E, Method 2022
- ANSI/IPC J STD-004, Type ROL0

**Soder-Wick® Desoldering Braid**, the world's leading brand of desoldering braid, is the fastest, cleanest and safest braid in the industry. It significantly reduces rework/repair time and minimizes the risk of heat damage to the board.

**Solder-Wick No-Clean and Lead Free wick meet these specs:**

- Meets MIL-STD-883B, Bellcore TR-NWT-000078, ANSI/IPC J SF-818
- Meets parameters tested by the Singapore Institute of Standards and Industrial Research (SISIR) for Solderability
- ANSI/IPC J STD-004, Type ROL0

## Product Selection Guide

Product	Size	Color	5' 1.5m		10' 3.0m		25' 7.5m		100' 30.5m		500' 152.5m		5' / 1.5m VacuPak™	
			5'	1.5m	10'	3.0m	25'	7.5m	100'	30.5m	500'	152.5m	5' / 1.5m	VacuPak™
<b>Soder-Wick® Rosin</b> Fastest wicking action with rosin flux coated desoldering braid	1	.030"/0.8mm	White	80-1-5	80-1-10	50-1-25								SW18015
	2	.060"/1.5mm	Yellow	80-2-5	80-2-10	50-2-25	50-2-100	50-2-500						SW18025
	3	.080"/2.0mm	Green	80-3-5	80-3-10	50-3-25	50-3-100							SW18035
	4	.110"/2.8mm	Blue	80-4-5	80-4-10	50-4-25	50-4-100							SW18045
	5	.145"/3.7mm	Brown	80-5-5	80-5-10	50-5-25								SW18055
	6	.210"/5.3mm	Red	80-6-5		50-6-25								
<b>Soder-Wick® No Clean</b> Cleanest, leaving behind no ionic residue, with no clean flux coated desoldering braid	1	.030"/0.8mm	White	60-1-5	60-1-10									
	2	.060"/1.5mm	Yellow	60-2-5	60-2-10									SW16025
	3	.080"/2.0mm	Green	60-3-5	60-3-10									SW16035
	4	.110"/2.8mm	Blue	60-4-5	60-4-10									SW16045
	5	.145"/3.7mm	Brown	60-5-5	60-5-10									
	6	.210"/5.3mm	Red	60-6-5										
<b>Soder-Wick® Lead-Free</b> Safest on thermally sensitive components, with this specially engineered no clean flux coated desoldering braid	1	.030"/0.8mm	White	40-1-5										
	2	.060"/1.5mm	Yellow	40-2-5	40-2-10									SW14025
	3	.080"/2.0mm	Green	40-3-5	40-3-10									SW14035
	4	.110"/2.8mm	Blue	40-4-5	40-4-10									SW14045

\*Offered in static dissipative (ESD-safe) bobbins:

- DOD Standard 1686C and MIL-HDBK-263B
- Mil-Std-2000A
- Mil-B-81705C Static Decay Rate Provision



### VacuPak™ Resealable Packaging

Guarantees Soder-Wick is as fast as the day it was made. Cans are vacuum sealed with nitrogen-purge to eliminate moisture, which causes oxidation and hurts performance. 10 bobbins/can.

Other 5' and 10' packaged 25 bobbins per nitrogen purged sleeve, all others 1 spool/sleeve.





## Product Selection Guide

Product	Size	Color	⚠️*	
			10' 3.0m	25' 7.5m
<b>Soder-Wick® Unfluxed</b> Unfluxed desoldering braid which can be coated with any flux type	2 .060"/1.5mm	Yellow	75-2-10	70-2-25
	3 .080"/2.0mm	Green	75-3-10	70-3-25
	4 .110"/2.8mm	Blue	75-4-10	

## Desoldering Braid Product Application Guide

<b>#1 White/Gray</b>  .030" (0.8mm)	<b>#2 Yellow</b>  .060" (1.5mm)	<b>#3 Green</b>  .080" (2.0mm)
<b>#4 Blue</b>  .110" (2.8mm)	<b>#5 Brown</b>  .145" (3.7mm)	<b>#6 Red</b>  .210" (5.3mm)

*Wick shown actual size*

Size	Color	Application
1 .030"/0.8mm	White / Gray	SMD, Micro-Circuits
2 .060"/1.5mm	Yellow	Small Pads, SMDs
3 .080"/2.0mm	Green	Medium Pads
4 .110"/2.8mm	Blue	Large Pads
5 .145"/3.7mm	Brown	Terminals
6 .210"/5.3mm	Red	Large Lugs

## Chem-Wik® Desoldering Braid

**Chem-Wik® Desoldering Braid** ensures fast and safe desoldering with ultra-pure, oxygen free copper braid that quickly and completely removes solder from circuit boards and components. Its fast wicking action protects components from harmful heat damage. PermaPak™ Barrier Packaging is nitrogen-purged, which ensures braid freshness and speed by sealing out harmful effects of the environment and protecting against oxidation.

Chem-Wik® Desoldering Braid meets or exceeds industry performance standards:

- MIL-F-14256F Type R
- NASA STD-8739.3 Soldered Electrical Connections
- ANSI/IPC J STD-004, Type ROL0
- DOD-STD-883E, Method 2022



## Product Selection Guide

Product	Size	Color	⚠️*				
			5' 1.5m	25' 7.5m	50' 15.0m	100' 30.5m	500' 152.5m
<b>Chem-Wik® Rosin</b> Fast wicking action with rosin flux coated desoldering braid	1 .030"/0.8mm	Gray	2-5L	2-25L	2-50L		
	2 .050"/1.3mm	Yellow	5-5L	5-25L	5-50L	5-100L	5-500L
	3 .075"/1.9mm	Green	7-5L	7-25L	7-50L	7-100L	7-500L
	4 .100"/2.5mm	Blue	10-5L	10-25L	10-50L	10-100L	10-500L



PermaPak™ Barrier Packaging  
5' packaged 25 bobbins/sleeve, all others 1 spool/sleeve.



**\*Offered in static dissipative (ESD-safe) bobbins:**

- Reduces the risk of damage associated with static electricity
- DOD Standard 1686C and MIL-HDBK-263B
- Mil-Std-2000A
- Mil-B-81705C Static Decay Rate Provision



CircuitWorks® comprehensive line of conveniently packaged and precision dispensing rework and repair products makes circuit board repair and prototyping faster, easier and more accurate. Advanced-formula materials packaged in unique delivery systems ensure superior performance and pinpoint accuracy. The full range of products meets all of the technicians needs for electronics rework and prototyping — repairing, cleaning, protecting, bonding, and restoring electrical conductivity to circuit boards and components.

All CircuitWorks® products are compliant with IPC-7711 Rework of Electronic Assemblies, and ANSI/J-STD-001.

## Conductive Ink

### Conductive Ink Applications:

- Repairs traces
- Links components
- Makes smooth jumpers
- Shields electronics

### CircuitWorks® Conductive Pen

Pen dispenser for drawing highly conductive silver traces, jumpers and shielding with precision and control

- Quickly creates highly conductive silver traces
- Valved pen tip for easy applications
- Solderable at low temperatures
- Dries in minutes at room temperature
- Choice of Micro Tip for fine lines or Standard Tip for wider lines

<b>CW2200STP</b>	Standard Tip	8.5 g / 0.3 oz
<b>CW2200MTP</b>	Micro Tip	8.5 g / 0.3 oz



Standard Tip



Micro Tip

### CircuitWorks® Nickel Conductive Pen

Pen dispenser for economically drawing conductive traces, jumpers and shielding

- Quickly creates conductive nickel traces on most surfaces
- Easy and economical to use
- Valved pen tip for easy applications
- Dries in minutes at room temperature

<b>CW2000</b>	Standard Tip	8.5 g / 0.3 oz
---------------	--------------	----------------



### CircuitWorks® Flex Conductive Pen

Micro-tip pen for drawing conductive traces on flexible and ITO surfaces

- Quickly creates flexible conductive silver traces on flex circuitry
- Micro tip for precise applications
- Dries in minutes at room temperature
- Highly adherent silver-based polymer system

<b>CW2900</b>	Micro Tip	8.5 g / 0.3 oz
---------------	-----------	----------------



### CircuitWorks® Rubber Keypad Repair Kit

Conveniently-sized kit for permanent repair of rubber keypads

- Restores electrical conductivity to worn carbon contacts
- Forms a tough, flexible, wear-resistant surface
- Repairs over 50 rubber button contacts

#### Applications:

- Restores rubber and telephone keypads
- Restores flexible carbon contacts

<b>CW2605</b>	Adhesive	3 g / 0.1 oz
	Curing Agent	0.3 g / 0.01 oz





## Conductive Grease


### CircuitWorks® Silver Conductive Grease

Grease for superior electrical and thermal conductivity, lubrication and protection

- Fills connector gaps to maximize electrical and thermal conductivity
- Protects against moisture and corrosion
- Thermally stable from -70°F/-57°C to 485°F/252°C
- Conductive lubricant containing pure silver
- Controls static discharge
- Grounds circuits

**CW7100** 6.5 g / 0.23 oz

**CW7100KG** 1 KG / 35.27 oz



## Thermal Compounds

For fast, efficient heat transfer between circuit components and heat sinks.



### CircuitWorks® Boron Nitride Heat Sink Grease

Ultra-high efficiency, thermally conductive grease

- Provides maximum thermal conductivity with superior dielectric properties
- Silicone free compound will not harden or dry out
- Electrically insulative; noncorrosive and nonflammable
- Thermally stable from -99.4°F/-73°C to 392°F/200°C
- Exceeds MIL-C-47113 for Thermal Conductivity

**CW7250** 3.4 g / 0.12 oz

### CircuitWorks® Silicone Free Heat Sink Grease

Non-contaminating silicone free heat-sink grease

- Silicone free compound will not harden or dry out
- Excellent thermal conductivity and dielectric properties
- Non-corrosive
- Thermally stable from -99°F/-73°C to 603°F/317°C
- Exceeds MIL-C-47113 for thermal conductivity

**CW7270** 8 g / 0.28 oz

### CircuitWorks® Heat Sink Grease

Silicone compound for heat transfer away from electronics and electrical components

- Excellent thermal and dielectric properties
- Will not dry out, harden, or melt
- Noncorrosive and nonflammable
- Thermally stable from -51°F/-46°C to 400°F/204°C
- Meets MIL-DTL-47113D Type I

**CT40-5** 142 g / 5 oz



## Conductive Epoxies

### Conductive Epoxy Applications:

- Repair traces and temperature sensitive circuits
- Make high-strength solderless conductive connections
- Die attachment
- Thermal dissipation
- Static discharge and grounding



### CircuitWorks® Conductive Epoxy

Epoxy for precision repairs and high-strength conductive bonding

- Conductive silver epoxy provides excellent electrical conductivity
- High strength conductive bond with a five minute work time
- Repairs defective traces and creates jumpers on boards
- Quick solderless electronic connections

**CW2400** Adhesive 7 g / 0.25 oz  
Hardener 7 g / 0.25 oz

### CircuitWorks® 60 Minute Conductive Epoxy

Epoxy system with extended pot life for high strength conductive bonds

- Conductive silver epoxy provides excellent electrical conductivity
- Sixty minute work time provides a high strength conductive bond
- Extended pot life provides increased work time
- Repairs defective traces and creates jumpers on boards
- Quick solderless electronic connections

**CW2460** Adhesive 10 g / 0.35 oz  
Hardener 10 g / 0.35 oz in jars

## Protective Overcoats



CW3300G

### CircuitWorks® Overcoat Pen

Pen dispenser for precise application of a tough protective acrylic conformal coating

- Simple to use, single component system
- Hard, durable coating
- High dielectric strength helps prevent electrical discharge
- Dries quickly at room temperature
- Protects against moisture and abrasion damage
- Meets MIL-I-46058C and IPC-CC-830A

#### Applications:

- Insulates and protects conductive pen traces
- Repairs permanent solder mask
- Prevents shorting and arcing

<b>CW3300C</b>	Clear	4.9 g / 0.16 oz
<b>CW3300G</b>	Green	4.9 g / 0.16 oz
<b>CW3300B</b>	Blue	4.9 g / 0.16 oz
<b>CW3300BLACK</b>	Black	4.9 g / 0.16 oz
<b>CW3300WHITE</b>	White	4.9 g / 0.16 oz



### CircuitWorks® Epoxy Overcoat

Tough, thermally stable, epoxy protective conformal coating

- Provides a hard, durable, protective green coating
- Excellent dielectric properties; help prevent electrical discharge
- Protects against moisture and abrasion
- Ideal for pre-reflow solder resist repair
- Service temperature from -55°F/-48°C to 600°F/315°C
- Meets the requirements of IPC-7721, 2.4.1

#### Applications:

- Ideal for repairing permanent solder mask before reflow applications
- Protects circuits and prevents shorting and arcing

**CW2500** Adhesive Syringe 4 g / 0.14 oz  
Hardener Syringe 3.4 g / 0.12 oz



## Flux / Solder

### CircuitWorks® Flux Dispensing Pens

Pen for applying flux with precision and control

- Chisel tip marker provides exact delivery of flux to surface
- Easily removed with appropriate CircuitWorks® Flux Remover Pen

#### No Clean Flux Dispensing Pen

- Applies a patented noncorrosive, halide free, no clean flux
- Flux meets Bellcore TR-N-NWT-000078 and IPC SF-818 for Surface Insulation Resistance
- Flux meets ANSI/IPC J-STD-004, Type ROL0

**CW8100** 13 g / 0.32 oz

#### Lead-Free Flux Dispensing Pen

- Applies a noncorrosive, halide free, no clean flux for high temperature, lead-free application
- Can also be used for tin/lead solders
- Flux meets Bellcore TR-N-NWT-000078 and IPC SF-818 for Surface Insulation Resistance
- Flux meets ANSI / IPC J-STD-004, Type ROL0
- Easily removed with Lead-Free Flux Remover Pen, or Flux-Off® Lead-Free Flux Remover

**CW8400** 9 g / 0.32 oz

**CW8400BLK50** Box of 50 pens, 9 g each

#### Rosin Flux Dispensing Pen

- Applies a noncorrosive, nonconductive Type R flux
- Flux meets MIL-F-14256 F Type R and ANSI/IPC J-STD-004, Type ROL0

**CW8200** 9 g / 0.32 oz

#### Water Soluble Flux Dispensing Pen

- Applies a neutral pH organic water soluble flux for rapid soldering
- Flux meets ANSI/IPC J-STD-004, ORH1 Classification
- Easily removed with water or Flux-Off® Water Soluble (pg. 13)

**CW8300** 9 g / 0.32 oz




CW8100



CW8200



CW8300



### CircuitWorks® Tacky Flux

Conveniently packaged flux gel formulated for easy SMT rework

- Formulated for No-Clean applications
- Syringe applicator provides exact delivery of flux
- Long tack time, extended shelf life
- No refrigeration required
- Noncorrosive, halide and halogen free
- Meets IPC requirements for ROL0, No Clean
- Conforms to ISO 9454
- Meets Bellcore TR-NWT-000078 requirements
- Meets DIN EN 29454-1 1.1.3.C classification



CW8700



CW8500

#### Lead-Free

**CW8700** 3.5 g / 0.12 oz

#### No-Clean

**CW8500** 3.5 g / 0.12 oz

### CircuitWorks®

#### Lead-Free Pocket Solder

Lead free, high purity pocket sized solder dispenser for convenient rework and repair

- SAC 305 for soldering lead-free applications
- 96.5% Tin (Sn), 3.0% Silver (Ag), 0.5% Copper (Cu)
- Type ROL0 flux per IPC J-STD-004
- Ensures even, reliable solder connections
- Cleans and wets heavily tarnished copper surfaces

**S200** 1.0 mm / 0.04" Diameter,  
3.18 m / 125" Length



## Cleaning and Lubricating Pens



### CircuitWorks® Conformal Coating Remover Pen

Pen for precise removal of silicone, acrylic and urethane coatings from PCBs

- Spot cleans tight tolerance areas on circuit boards
- Marker dispenser provides controlled and exact application
- Evaporates quickly
- Provides low surface tension for superior wetting
- Low VOC content

**CW3500** 9 g / 0.32 oz

### CircuitWorks® Flux Remover Pen

Pen for precise removal of flux from printed circuit boards

- Completely removes flux in seconds
- Spot cleans tight tolerance areas on circuit boards
- Marker dispenser provides controlled spot cleaning
- Dries fast



#### No Clean Flux Remover Pen

**CW9100** 9 g / 0.32 oz



#### Rosin Flux Remover Pen

**CW9200** 8 g / 0.28 oz



#### Lead-Free Flux Remover Pen

**CW9400** 9 g / 0.32 oz

### CircuitWorks® Gold Guard™ Pen

Pen for cleaning and lubricating gold and other noble metal contacts and connectors

- Cleans and leaves protective polyphenyl ether lubricant in one step
- Extends life of noble metal contacts
- Chisel tip marker for exact delivery to the contact
- Safe on plastics

**CW7400** 8.5 g / 0.3 oz



### CircuitWorks® The Mighty Pen®

Powerful universal cleaning pen

- Outstanding cleaning ability
- Marker dispenser provides controlled and exact application
- Mild citrus aroma
- U.S. Patent 6,677,291 and 6,677,292, and foreign patents

#### Applications:

- General purpose cleaning and refurbishing of equipment
- Removes ink stains, label adhesives, and difficult to remove soils

**CW3700** 11 g / 0.39 oz



### Fiber-Wash™ Fiber Optic Cleaning Pens

- Specifically formulated for cleaning all fiber optic connectors
- Removes handling soils, dust, oils and airborne contamination
- Cleans alone or in combination with the SqR™, p-QbE®, QbE®, CCT Cleaning Platforms
- Cleans and eliminates static
- Completely portable; controlled dispensing of cleaning solution



#### Fiber-Wash™ MX Precision Cleaner Pen

Convenient pen with the extra-strength, plastic safe precision cleaner

**FW2150** 9 g / 0.32 oz pen

**FW2150BLK** Box of 24 pens, 9g each



#### Fiber-Wash™ AQ Precision Cleaner Pen

Nonflammable, aqueous fiber optic cleaner

**FW2190** 5 g / 0.2 oz pen

**FW2190BLK** Box of 25 pens, 5 g each




#### Fiber-Wash™ NF Precision Cleaner Pen

Nonflammable, fast drying fiber optic cleaner

**FW2170** 10 g / 0.4 oz pen







**Konform® Conformal Coatings** are used to protect printed circuit boards, components and flex circuitry. These coatings provide excellent electrical insulation and withstand hot and cold operating environments, as well as heat generated by electronic circuitry. Formulated to protect components and circuits in the most demanding of environments, all Konform® conformal coatings contain a UV indicator for easy quality assurance (except Konform® LED). These tough, transparent coatings will not chip or crack, thereby providing excellent protection. All are convenient and ready to use.




## Konform® SR

Silicone coating for maximum flexibility and protection from extreme temperatures and vibration damage

- Silicone coating working temperature from -85°F/-64°C to 390°F/200°C
- High dielectric breakdown of 1100 volts/mil
- Easily removed with Electro-Wash® Two Step, Electro-Wash® NXO, or CircuitWorks® Conformal Coating Remover Pen
- Meets MIL-I-46058C, Type SR
- Compliant to IPC-CC-830A
- Engineered for applications where flexibility and high temperature resistance are required
- Contains UV Tracer for easy quality control
- UL recognized (standard viscosity only)
- Coverage (@1mil dry):  
Aerosol (1 can) 21 ft<sup>2</sup> / 2 m<sup>2</sup>  
Liquid (1 gal.) 251 ft<sup>2</sup> / 23.3 m<sup>2</sup>

- CTSR-12** 10 oz / 283 g aerosol
- CTSR-P** 16 fl oz / 473 ml liquid
- CTSR-1** 1 gal / 3.7 L liquid
- CTSR-5** 5 gal / 19 L liquid



*Konform® SR and Konform® AR conformal coatings contain a UV indicator for improved quality assurance.*

### Medium Viscosity

- Coverage (@1mil dry): 479 ft<sup>2</sup> / 44.5 m<sup>2</sup>

**CTSR-MV5** 5 gal / 19 L liquid

### High Viscosity

- Coverage (@2mil dry): 719 ft<sup>2</sup>

**CTSR-HV1** 1 gal / 3.7 L liquid

## Product Selection Guide

	Resistance					Underwriters Laboratories			Coating Characteristics				Cure Profile				
	Temperature Resistance	Abrasion Resistance	Acid Resistance	Solvent Resistance	Humidity Resistance	Water Submersible Per UL	UL Recognized	UV Traceable System	Viscosity (Liquid)	Flexibility	Solderability	Repairability	Dielectric Breakdown	Working Temperature	Tack Free Time	Full Cure Time	
Konform® SR	1	4	2	2	1	✓	✓	✓	Solvent	40 cps	1	4	3	1100	-85F to 390° (-65°C to 200°)	15 min.	24 hrs. @RT
Konform® SR High Viscosity	1	4	2	2	1	✓		✓	Solvent	120 cps	1	4	3	1100	-85F to 390° (-65°C to 200°)	15 min.	24 hrs. @RT
Konform® AR	2	1	1	3	1		✓	✓	Solvent	70 cps	4	3	4	8300	-75F to 270° (-59°C to 132°)	30 min.	24 hrs. @RT
Konform® LED	1	4	2	2	1				Solvent	65 cps	1	4	3	1100	-85F to 390° (-65°C to 200°)	15 min.	24 hrs. @RT

1 – Outstanding    2 – Excellent    3 – Good    4 – Fair    NA – Not Available



### Konform® AR

Acrylic coating for effective insulation against high voltage arcing and shorts

- Acrylic coating working temperature from -75°F/-59°C to 270°F/132°C
- High dielectric breakdown of 8300 volts/mil
- Meets MIL-I-46058C, Type AR
- Compliant to IPC-CC-830A
- Designed to provide effective insulation against electrical shorts and harsh environments
- Provides excellent acid resistance
- Easily repairable
- Contains UV Tracer for easy quality control
- UL recognized
- Coverage (@1mil dry):  
Aerosol (1 can) 20 ft<sup>2</sup> / 1.9 m<sup>2</sup>  
Liquid (1 gal.) 254 ft<sup>2</sup> / 23.6 m<sup>2</sup>

- CTAR-12 11.5 oz / 326 g aerosol
- CTAR-P 16 fl oz / 473 ml liquid
- CTAR-1 1 gal / 3.7 L liquid
- CTAR-5 5 gal / 19 L liquid




### Konform® LED

Silicone conformal coating designed for light emitting diode (LED) applications

- Silicone coating transparent to visible wavelengths, will not block or change light intensity or wavelength
- Extends component life by protecting against adverse environments
- Good insulation properties help with circuit insulation characteristics, excellent flexibility minimizes thermal stress
- Resists moisture, salt, fungus, corrosive vapors, and severe environments
- Engineered to withstand heat generated by PCB as well as climatic temperature extremes
- Compliant with IPC-CC-830A, MIL-I-46058C (without UV) and RoHS
- Coverage (@1mil dry):  
Liquid (1 gal.) 251 ft<sup>2</sup> / 23.3 m<sup>2</sup>


- CTLED-P 16 fl oz / 473 ml liquid
- CTLED-1 1 gal / 3.7 L liquid
- CTLED-5 5 gal / 18.5 L liquid



Konform® LED is specially formulated to be optically clear.







**Chemask® Temporary Solder Masks** protect PC boards, plated thru-holes, contacts, pins, posts, terminals and gold fingers during reflow and wave soldering. They provide short-term high-temperature protection from molten solder to a minimum of 515°F/268°C. All products are nonflammable, non-contaminating and will not leave ionic or corrosive residue. Use as a protective mask during conformal coating process.

## Chemask® — Peelable

Fast curing, peelable temporary solder masking agent

- Dries tack-free in 15 minutes
- Easy to use — just peel off dried Chemask® masking agent
- Latex material is compatible with all flux systems and stable with cleaning solvents

**CM8** 8 fl oz / 236 ml liquid squeeze bottle  
**CM1** 1 gal / 3.7 L liquid

## Chemask® NA — Non-Ammoniated

High temperature, peelable, temporary mask safe for use on sensitive metals

- Will not affect gold, copper, nickel, silver and OSP finishes
- For lead-free or tin/lead processes
- Stable to 550°F / 288°C
- Phthalate-free, low toxicity and environmentally safe
- Compatible with rosin, no-clean and water soluble flux types
- Dries tack free in 15 minutes
- Can be placed directly into pre-heat oven without waiting
- Removes easily and leaves no residue
- Non-contaminating, non-staining and noncorrosive

**CNA8** 8 fl oz / 236 ml liquid squeeze bottle

## Chemask® LF — Lead-Free

High temperature, peelable temporary mask ideal for lead-free applications

- Formulated for use with lead-free applications
- Can also be used with tin/lead solders
- Usable within five minutes of application with preheat cycles
- Provides short-term high temperature protection up to 550°F / 288°C

**CLF8** 8 fl oz / 236 ml liquid squeeze bottle

**CLF1** 1 gal / 3.7 L liquid



# Temporary Solder Mask

Product Selection Guide	Product Characteristics				Application Methods						Removal Methods
	Safe for Sensitive Metal Surfaces	Tack Free Time @ Room Temperature	Full Cure Time @ Room Temperature	Preheat Activated	Flux Resistance	Solvent Resistance	Automated Dispenser	Stencils	Screens	Peelable	Water Washable Open Loop/Closed Loop
<b>Chemask® Peelable</b>	NR	15 min.	30 min.	NA	All types	All types	Yes	No	No	Yes	No
<b>Chemask® NA Non-Ammoniated</b>	Yes	15 min.	30 min.	Yes; can be placed directly into preheat	All types	All types	Yes	Yes	Yes	Yes	No
<b>Chemask® LF Lead-Free</b>	NR	15 min.	30 min.	Yes; 4 min. full cure	All types	All types	No	No	No	Yes	No
<b>Chemask® HV High Viscosity</b>	Yes	15 min.	30 min.	Yes; 4 min. full cure	All types	All types	No	No	No	Yes	No
<b>Chemask® WF Water Filterable</b>	No	30 min.	60 min.	NA	Not compatible with water-based flux	Remove with water and water-based cleaners	Yes	Yes	Yes	No	Yes

NA – Not Available    NR – Not Recommended    \*Open Loop System Only

## Chemask® WF — Water Filterable

Low-foaming, water filterable temporary solder masking agent


- Easily removed in water cleaning cycles
- Does not coat filtration equipment
- Noncorrosive; safe for sensitive contacts
- Removed with inexpensive filters, increasing the life span of activated carbon/resin beds
- US Patent Number 6,207,265

### Applications:

- Ideal for use with closed loop cleaning systems
- Increases productivity by reducing cleaning system maintenance
- Short-term high-temperature protection from molten solder to 515°F / 268°C

**CWF8** 8 fl oz / 236 ml liquid squeeze bottle

**CWF1** 1 gal / 3.7 L liquid



## Chemask® HV — High Viscosity

High viscosity, peelable temporary solder masking agent

- Usable within five minutes of application with preheat cycle
- More controlled application
- Thicker coating does not seep through thru-holes
- Latex material is compatible with all flux systems and stable with cleaning solvents

**CHV8** 8 fl oz / 236 ml liquid squeeze bottle







**New Package!**



IPA100B



SIP100P



CP421

## IPA Presaturated Wipes

General purpose presaturated wipe in a convenient dispenser

- Ultra pure mixture of IPA and deionized water
- Nonwoven, spunlaced polyester material
- Non-scratching and strong — will not tear or lint
- Ideal for cleaning of semi-automatic printer stencils and touch-up cleaning of automatic printer stencils
- IPA100B wipes are lint free and pre-cut — excellent for cleaning fine pitch stencils

**SIP100P** 100 presaturated wipes in pull-up tub  
70% IPA and 30% deionized water

**SIP125P** 125 presaturated wipes in pull-up tub  
**NEW!** 70% IPA and 30% deionized water

**SIP125P91** 125 presaturated wipes in pull-up tub  
**NEW!** 91% IPA and 9% deionized water

**SIP91P** 100 presaturated wipes in pull-up tub  
91% IPA and 9% deionized water

**IPA100B** 100 c-fold presaturated wipes  
70% IPA and 30% deionized water

## Chempad™ Presaturated Wipe

General purpose, presaturated lint-free cleaning wipe

- Contains ultra pure blend of 91% IPA/9% deionized water
- Highly saturated
- Thick, non-abrasive, wiping pad
- Quickly removes dust, oils and contaminants

**CP400** 50 single pack presaturated wipes

## Electro-Wash® MX Presaturated Wipe

Extra-strength plastic safe universal cleaner with moderate evaporation time

- Cleans all soil types — organic and ionic
- Moderate evaporation rate increases cleaning power
- Leaves no residue
- Presaturated wipe great for toolbox or travel

### Applications:

- Ideal for cleaning fiber optics and fiber optic connectors, cables, hard-line coax cable, cable splices, PC boards, motors, tools and transformers, flooding compounds, control systems, screens and stencils

**CP421** 25 single pack presaturated wipes

*Also available in an aerosol — ES1621. See page 6.*

## Screen Prep™ Presaturated Wipe

Convenient cleaning and static control for monitors



- Cleans and provides a static dissipative treatment
- Prevents airborne recontamination for up to seven days
- Safely removes dust, dirt, oil and nicotine
- Controls static-generated contamination
- Wet pad cleans and applies static protection
- Dry wiper polishes screen optically clear

**CSP20** 25 twin packs  
#1 presaturated pad  
#2 polishing wiper

## Optic Prep™ Presaturated Wipe

Highest quality premoistened lens-grade tissue for cleaning optical surfaces

- Safely cleans and polishes optical surfaces, lenses, photographic equipment, fiber optic connectors and instruments
- Compatible with most plastics, glass and metals
- Mild cleaning solution, nonabrasive wipe
- Quickly removes dust, oils and contaminants connectors and instruments

**CP410** 50 single pack presaturated pads

## Chemswab™ Presaturated Swab

Easy to use swab presaturated with alcohol

- Urethane foam swab (Foamtips™ #120) presaturated with ultra-pure IPA
- Evaporates quickly with no residue or contamination
- Nonabrasive
- Ideal for field service kits

**CS25** 25 presaturated swabs



CP410

CS25



- High absorbency
- Contamination control
- High-purity
- Little or no linting

**Chemtronics® Dry Wipes** are engineered and manufactured clean. They are designed for controlled environments, light industrial, benchtop, laboratory and high absorbency applications.

They are ideal for use with strong solvents and the full range of engineered Chemtronics® cleaners; Electro-Wash® cleaner degreasers, Static Free™ static control products and Flux-Off® flux removers.

## Controlwipes™

Solvent resistant highly absorbent wipe

- Nonwoven, spunlaced polyester cellulose fabric
- General purpose lint-free wipe
- Strong, will not tear, shred, unravel or lint
- High absorbency and liquid retention
- Will not abrade surfaces
- Resistant to most solvents and dilute acids
- For applications requiring contamination control

### Applications:

- Removing contamination from screens and optical glass surfaces
- Cleaning and absorbing solvents from semi-critical work surfaces

**C910** 150 wipes 9" x 9" / 23 cm x 23 cm



## Twillwipes™


Highly absorbent wipe for abrasion-free cleaning and drying of sensitive surfaces, components and equipment

- Strong, textured 100% cotton
- Minimal linting
- Cleanroom Compatible Class 1000 / ISO Class 4
- Resistant to caustic solvents and temperatures up to 302°F/150°C

### Applications:

- Cleaning applications involving high temperature
- Ideal for use with caustic solutions

**C900** 150 wipes 9" x 9" / 23 cm x 23 cm



## Opticwipes™

Soft laboratory-grade cellulose tissue designed for use on optical and other sensitive surfaces

- 100% cellulose
- Highly absorbent; high wet strength
- Noncontaminating
- Solvent resistant
- Low in soluble extractable contamination and particle generation

### Applications:

- Cleaning optical surfaces, photo processing, lab equipment and other precision instrumentation
- Ideal for cleaning optical lenses

**C920** 500 wipes 9" x 9" / 23 cm x 23 cm







**Chemtronics® Swabs and Applicators** are engineered for use in a variety of environments and applications. They are ideal for use with our cleaner degreasers, head cleaners, flux removers and other solvents for fast, precision cleaning. From the innovative no-lint Chamois Tips™ Swab to the general purpose Cottontips™ Swab, Chemtronics® has the right swab or applicator for your job.



## Foamtips™

Highly absorbent precision cleaning swab with a wide variety of head sizes and shapes

- Precision cleaning swabs with 100 ppi polyurethane open cell foam head
- Purest medical grade foam
- Foamtips™ Pro swab (CFP50) has a blue scrubber end and a soft absorbent end
- Available in a variety of head sizes and shapes with various handle lengths

Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
Foamtips™ Pro CFP50	50 swabs	6.75" 17.1 cm	0.20" x 0.13" 4.8 mm x 3.3 mm	<b>white head:</b> 0.75" 19.1 mm	<b>white head:</b> 0.44" 11.1 mm	polypropylene	<b>white side:</b> 100 ppi open cell foam
				<b>blue head:</b> 0.69" 17.5 mm	<b>blue head:</b> 0.28" 17.1 mm		<b>blue side:</b> 75 ppi closed cell



Foamtips™ #100 CF50	50 swabs	6.10" 15.5 cm	0.06" x 0.06" 1.5 mm x 1.5 mm	0.88" 22.4 mm	0.38" 9.7 mm	wood	100 ppi open cell foam over cotton bud
------------------------	----------	------------------	----------------------------------	------------------	-----------------	------	---



Foamtips™ #110 CF1050	50 swabs	5.00" 12.7 cm	0.28" x 0.13" 7.1 mm x 3.3 mm	1.00" 25.4 mm	0.82" 20.8 mm	polypropylene	100 ppi open cell foam
--------------------------	----------	------------------	----------------------------------	------------------	------------------	---------------	------------------------



Foamtips™ #120 CF2050	50 swabs	5.12" 13.0 cm	0.19" x 0.13" 4.8 mm x 3.3 mm	1.00" 25.4 mm	0.46" 11.7 mm	polypropylene	100 ppi open cell foam
--------------------------	----------	------------------	----------------------------------	------------------	------------------	---------------	------------------------



Foamtips™ #130 CF3050	50 swabs	6.00" 15.2 cm	0.13" x 0.13" 3.3 mm x 3.3 mm	0.75" 19.1 mm	0.25" 6.4 mm	polypropylene	100 ppi open cell foam
--------------------------	----------	------------------	----------------------------------	------------------	-----------------	---------------	------------------------



Foamtips™ #140 CF4050	50 swabs	2.87" 7.3 cm	0.10" x 0.10" 2.5 mm x 2.5 mm	0.50" 12.7 mm	0.19" 4.8 mm	polypropylene	100 ppi open cell foam
--------------------------	----------	-----------------	----------------------------------	------------------	-----------------	---------------	------------------------




# Swabs and Applicators

## Flexitips™ & Super Flexitips™

Ideal flexible heads for cleaning optics and small confined areas

- Nonabrasive
- Made without adhesives or glue
- Open cell foam on Flexitips for high absorbency, soil capture and gentle cleaning
- Closed cell foam on Super Flexitips for increased toughness and abrasion resistance



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
<b>Flexitips™ CX50</b>	50 swabs	4.45" 11.3 cm	0.16" x 0.16" 4.1 mm x 4.1 mm	0.81" 20.6 mm	0.25" 6.4 mm	nylon/polypropylene	100 ppi open cell foam

<b>Super Flexitips™ SX50</b>	50 swabs	4.45" 11.3 cm	0.16" x 0.16" 4.1 mm x 4.1 mm	0.81" 20.6 mm	0.25" 6.4 mm	nylon/polypropylene	100 ppi closed cell foam
----------------------------------	----------	------------------	----------------------------------	------------------	-----------------	---------------------	--------------------------



<b>Flexitips™ Mini CXM50</b>	50 swabs	4.13" 10.5 cm	0.16" x 0.16" 4.1 mm x 4.1 mm	0.53" 13.5 mm	0.19" 4.8 mm	nylon/polypropylene	100 ppi open cell foam
----------------------------------	----------	------------------	----------------------------------	------------------	-----------------	---------------------	------------------------

<b>Super Flexitips™ Mini SXM50</b>	50 swabs	4.13" 10.5 cm	0.16" x 0.16" 4.1 mm x 4.1 mm	0.53" 13.5 mm	0.19" 4.8 mm	nylon/polypropylene	100 ppi closed cell foam
--	----------	------------------	----------------------------------	------------------	-----------------	---------------------	--------------------------



## Chamois Tips™

Ideal swab for cleaning magnetic and optical, audio and video heads

- Synthetic chamois cloth head
- Material is free of oils and residues
- Flexible handle bends to clean hard-to-reach areas
- Bonded without adhesives
- Seamless construction
- Effectively cleans excess ink from ink jet cartridges
- Abrasion resistant
- Non-snagging


Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
<b>CC50</b>	50 swabs	3.25" 8.3 cm	0.38" x 0.07" 9.7 mm x 1.8 mm	0.88" 22.4 mm	0.38" 9.7 mm	ABS (acrylonitrile-butadiene-styrene)	synthetic chamois cloth



## Microtips™

Precision applicator for pinpoint solvent, adhesive and lubricant application

- Porous polyvinylidene fluoride-tipped precision applicator and cleaning tool
- Low extractables and particulate levels
- High chemical resistance – compatible with most solvents
- 1.9 mm tapered tip
- Excellent choice for depositing solvents, adhesives and coatings
- Effective as a stylus or pick



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
<b>CM502</b>	50 swabs	6.7" 17.0 cm	0.13" x 0.13" 3.3 mm x 3.3 mm	0.62" 15.7 mm	0.08" 1.93 mm	polypropylene	polyvinylidene fluoride





## Cottontips™ & Cottontips™ Low Lint

Economical swabs designed for general cleaning applications

- 100% pure pharmaceutical grade bleached white cotton head
- Soft and highly absorbent
- Compatible with most solvents
- Available with single or double head
- Rigid wooden handle

### Cottontips™ Low Lint:

- Special low lint cotton fibers used for critical, low particle applications



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
<b>Cottontips™ Single-Head</b>							
<b>CT100</b>	100 swabs	6.00" 15.2 cm	0.08" x 0.08" 2.0 mm x 2.0 mm	0.63" 16 mm	0.19" 4.8 mm	wood	cotton



<b>Cottontips™ Double-Head</b>							
<b>CT200</b>	100 swabs	6.00" 15.2 cm	0.08" x 0.08" 2.0 mm x 2.0 mm	0.63" 16 mm	0.19" 4.8 mm	wood	cotton
<b>CT2000</b>	1000 swabs	6.00" 15.2 cm	0.08" x 0.08" 2.0 mm x 2.0 mm	0.63" 16 mm	0.19" 4.8 mm	wood	cotton




<b>Cottontips™ Low Lint</b>							
<b>CT5000</b>	1000 swabs	6.00" 15.2 cm	0.08" x 0.08" 2.0 mm x 2.0 mm	0.63" 16 mm	0.19" 4.8 mm	wood	cotton



## Cottontips™ MicroPoint

Low particulate, pointed cotton swab, designed for precision applications

- Tightly wrapped head construction
- Small size for delicate precision cleaning
- Extremely Low linting
- High absorbency capacity and rate
- Good solvent compatibility
- Sharp point
- Non-static generating



Product	Pkg Count	Swab Length	Handle Width	Head Length	Head Width	Handle Material	Head Material
<b>Cottontips™ MicroPoint</b>							
<b>CCT2425</b>	25 swabs	3.0" 7.6 cm	0.06" x 0.06" 1.5 mm x 1.5 mm	0.47" 11.9 mm	0.12" 3.0 mm	Paper composite	cotton



# Product Specifications/Call Outs

## U.S. Government National Stock Numbers

Part #	Product Name	Page
0793-00-103-94802	ES1668 Plast-N-Glas®	17
3439-00-009-2334	7-5L Chem-Wik® Rosin	18
3439-01-009-6448	80-5-5 Soder-Wick®	18
3439-01-198-9716	80-4-10 Soder-Wick®	18
3439-01-324-8208	80-2-5 Soder-Wick®	18
3439-01-371-1588	10-5L Chem-Wik®	19
416850-01-514-1372	CW3500 CircuitWorks® Conformal Coating Remover Pen	24
4820-01-314-3601	ES710V Chrome Trigger Valve	15
5836-01-453-8942	CC50 Chamois Tips™	32
5836-01-454-0401	ES820L IPA	13
5836-01-454-0402	CP400 Chempad™	29
5970-01-417-4152	CTSR-12 Konform® SR	25
5970-01-417-4154	CTSR1 Konform® SR	25
5970-01-417-4156	CTAR1 Konform® AR	26
5970-01-417-4158	CTAR-12 Konform® AR	26
6616-00-077-3218	CF4050 Foamtips™ #140	31
6830-01-381-2675	ES1020K Ultrajet® System	15
6830-01-388-6924	ES1020R Ultrajet® Refill	15
6850-00-142-40716	ES1551 Freeze-It® Antistat	16
6850-00-146-38046	ES1217 Duster	15
6850-00-602-2347	ES1631 Flux-Off® Heavy Duty	12
6850-01-224-9211	ES2400 Tun-O-Wash®	9
6850-01-3064	C920 Opticwipes™	30
6850-01-333-1841	ES1550 Freeze-It®	16
6850-01-393-9054	ES1210 Electro-Wash® PX	6
6850-01-406-1356	ES1050 Freeze-It®	16
6850-01-412-0040	ES1020 Ultrajet®	14
6850-01-418-0499	ES1035 Flux-Off® Rosin	11
6850-01-436-4573	ES7300 Pow-R-Wash™ CZ	9
6850-01-436-4578	ES7200 Flux-Off® CZ	11
6850-01-436-4584	ES7100 Electro-Wash® CZ	6
6850-01-436-4585	ES7101 Electro-Wash® CZ	6
6850-01-456-4173	ES835B Flux-Off® Rosin	11
6850-01-463-8043	ES1017 Duster	15
6850-01-463-8046	ES1217 Duster	15
6850-01-475-0987	CW8100 No Clean Flux Dispensing Pen	23
6850-01-484-3064	CP410 Optic Prep™	29
6850-01-506-5662	CW2200MTP Conductive Pen	20
6850-01-560-5804	ES1051 Freeze-It® Antistat	16
7045-01-535-0276	CM502 Microtips™	32
7045-01-548-4966	CT5000 Cottontips™ Low Lint	33
7930-01-467-3289	CFP50 Foamtips™ Pro	31
7930-01-559-5328	CP421 Electro-Wash® MX Presaturated Wipe	6, 29
8030-01-511-6308	CW3300C CircuitWorks® Overcoat Pen	22
8510-01-358-8836	C805 Static Free™ Hand Guard™	17
9150-01-508-9999	CW7100 Conductive Grease	21
9390-01-552-1552	80-3-5 Soder-Wick®	18

Part Number	Product Name	Page	Standard / Specification
ES1020, ES1020R ES1620, ES1015	All Ultrajet®, and Ultrajet® 70	14	Fed Spec A-A-58060, ARI Standard 700, App. C
CM8, CM1	Chemask®	27	MIL-STD-2000A, Para. 5.3.18
CHV8	Chemask® HV High Viscosity	28	MIL-STD-2000A, Para. 5.3.1835,36
CLF8, CLF1	Chemask® LF	27	MIL-STD-2000A, Para. 5.3.18
CNA8, CNA1	Chemask® NA	27	MIL-STD-2000A, Para. 5.3.18
CWF8, CWF1	Chemask® WF	28	MIL-STD-2000A, Para. 5.3.18
All Chem-Wik®	Chem-Wik®	18	MIL-F-14256F, Type R, ANSI/IPC J STD-004, Type ROLO NASA-STD-8739.3
All Chem-Wik®	Chem-Wik®	18	MIL-STD-1686C, MIL-HDBK-263B
All CircuitWorks®	CircuitWorks®	20-24	ANSI/IPC J STD-001, IPC-7711
CW2500	CircuitWorks® Epoxy Overcoat	22	IPC-7721, 2.4.1
CT40-5	CircuitWorks® Heat Sink Grease	21	MIL-DTL-47113D
CW8400	CircuitWorks® Lead-Free Flux Dispensing Pen	23	ANSI / IPC J-STD-004, Type ROLO; Bellcore TR-N-NWT-000078 and IPC SF-818 for Surface Insulation Resistance
CW8100	CircuitWorks® No Clean Flux Dispensing Pen	23	ANSI/IPC SF-818, ANSI/IPC J STD-004, Type ROLO Bellcore TR-NWT-000078
CW3300C, CW3300G	CircuitWorks® Overcoat Pen	22	IPC-CC-830A, MIL-I-46058C, Type AR
CW8200	CircuitWorks® Rosin Flux Dispensing Pen	23	MIL-F-14256F, Type R, ANSI/IPC J STD-004, Type ROLO
CW8500	CircuitWorks® Tacky Flux	23	ISO 9454, Bellcore TR-NWT-000078, DIN EN 29454-1 1.1.3.C classification
CW8300	CircuitWorks® Water Soluble Flux Dispensing Pen	23	ANSI/IPC J-STD-004, ORH1
ES1017, ES1217, ES1617	Duster	15	Fed Spec A-A-58060, ARI Standard 700, App. C
ES7100	Electro-Wash® CZ	6	MIL-PRF-29608A (AS) Class C approved
ES1050, ES1550	Freez-It®	16	Fed Spec A-A-58060, ARI Standard 700, App. C
ES1052	Freeze Spray	16	Fed Spec A-A-58060, ARI Standard 700
CTAR-12, CTAR1	Konform® AR	26	MIL-I-46058C Type AR, IPC-CC-830A, UL Recognized
CTSR-12, CTSR1	Konform® SR	25	MIL-I-46058C Type SR, IPC-CC-830A, UL Recognized
CTSR-HV1	Konform® SR High Viscosity	25	MIL-I-46058C Type SR, IPC-CC-830A
ES7300	Pow-R-Wash™ CZ	9	MIL-PRF-29608A (AS) Class C approv
All Soder-Wick®	Soder-Wick®	18-19	MIL-F-14256F, Type R, ANSI/IPC J STD-004, Type ROLO DOD-STD-883E, Method 2022, NASA-STD-8739.3
60 Series	Soder-Wick®	18	ANSI/IPC J STD-004, Type ROLO, DOD-STD-883E, Method 2022 NASA-STD-8739.3, Bellcore TR-NWT-000078, ANSI/IPC SF-818 Singapore Institute of Standards and Industrial Research (SISR) for Solderability
All Soder-Wick®	Soder-Wick®	18-19	MIL-STD-1686C, MIL-HDBK-263B, MIL-B-81705C, MIL-STD-2000A
Static Dissipative (ESD-Safe)		18-19	MIL-B-81705C, MIL-STD-2000A
C805	Static Free™ Hand Guard™	17	IPC-ESD-20-20, MIL-STD-1686C, MIL-HDBK-263B
ES1664T	Static Free™ Mat and Benchtop Reconditioner	17	IPC-ESD-20-20, MIL-STD-1686C, MIL-HDBK-263B



# Part Number Index

Part #	Page	Part #	Page	Part #	Page	Part #	Page	Part #	Page	Part #	Page
2-5L	19	60-5-5	18	CT100	33	CWF1	28	ES1029	15	ES6201	11
2-25L	19	60-5-10	18	CT200	33	CWF8	28	ES1035	11	ES6255	11
2-50L	19	60-6-5	18	CT2000	33	CX50	32	ES1035B	11	ES6300	9
2-100L	19	70-2-25	19	CT5000	33	CXM50	32	ES1050	16	ES6301	9
5-5L	19	70-3-25	19	CTAR-1	25	DEL101	5	ES1051	16	ES7100	6
5-25L	19	75-2-10	19	CTAR-5	25	DEL192	10	ES1052	16	ES7200	11
5-50L	19	75-3-10	19	CTAR-12	25	DEL592	10	ES1054	16	ES7208B	11
5-100L	19	75-4-10	19	CTLED-1	25	DEL892B	10	ES1055	16	ES7300	9
5-500L	19	80-1-5	18	CTLED-5	25	DEL1601	5	ES1056	16	FW2150	6, 24
7-5L	19	80-1-10	18	CTLED-P	25	DEL1608B	4	ES1210	6	FW2150BLK	24
7-25L	19	80-2-5	18	CTSR-1	25	DEL1681	8	ES1210A	6	FW2170	24
7-50L	19	80-2-10	18	CTSR-5	25	DEL1692	10	ES1217	15	FW2190	24
7-100L	19	80-3-5	18	CTSR-12	25	DEL2201	5	ES1530	13	IPA100B	29
7-500L	19	80-3-10	18	CTSR-HV1	25	DEL5501	5	ES1550	16	S200	23
10-5L	19	80-4-5	18	CTSR-MV5	25	DEL5592	10	ES1551	16	SIP91P	29
10-25L	19	80-4-10	18	CW2000	20	ES105	13	ES1603	6	SIP100P	29
10-50L	19	80-5-5	18	CW2200MTP	20	ES107	6	ES1605	8	SIP125P	29
10-100L	19	80-5-10	18	CW2200STP	20	ES110	6	ES1607	6	SIP125P91	29
10-500L	19	80-6-5	18	CW2400	22	ES125A	6	ES1617	15	SIP125P1664	17
40-1-5	18	C805	16	CW2460	22	ES130	13	ES1620	14	SW14025	18
40-2-5	18	C900	30	CW2500	22	ES131	12	ES1621	6	SW14035	18
40-2-10	18	C910	30	CW2605	20	ES132	13	ES1626	9	SW14045	18
40-3-5	18	C920	30	CW2900	20	ES135	11	ES1631	12	SW16025	18
40-3-10	18	CC50	32	CW3300B	22	ES191	7	ES1664T	17	SW16035	18
40-4-5	18	CCT2425	33	CW3300BLACK	22	ES196	13	ES1668	17	SW16045	18
40-4-10	18	CF50	31	CW3300C	22	ES197	12	ES1696	13	SW18015	18
50-1-25	18	CF1050	31	CW3300G	22	ES198	12	ES1697	12	SW18025	18
50-2-25	18	CF2050	31	CW3300WHITE	22	ES505	13	ES1698	12	SW18035	18
50-2-100	18	CF3050	31	CW3500	24	ES535	11	ES2289	7	SW18045	18
50-2-500	18	CF4050	31	CW3700	24	ES589	7	ES2291	7	SW18055	18
50-3-25	18	CFP50	31	CW7100	21	ES596	13	ES2400	9	SX50	32
50-3-100	18	CHV8	28	CW7100KG	21	ES598	12	ES2425	9	SXM50	32
50-4-25	18	CLF1	27	CW7250	21	ES710V	15	ES5505	13	VV114	5
50-4-100	18	CLF8	27	CW7270	21	ES810	6	ES5535	11	VV179	7
50-5-25	18	CM1	27	CW7400	24	ES820L	13	ES5589	7	VV195	10
50-6-25	18	CM8	27	CW8100	23	ES835B	11	ES5591	7	VV514	5
60-1-5	18	CM502	32	CW8200	23	ES896B	13	ES5596	13	VV579	7
60-1-10	18	CNA8	27	CW8300	23	ES897B	12	ES5597	12	VV595	10
60-2-5	18	CP400	29	CW8400	23	ES1015	14	ES5598	12	VV1614	5
60-2-10	18	CP410	29	CW8500	23	ES1017	15	ES6100	4	VV2279	7
60-3-5	18	CP421	6, 29	CW8700	23	ES1020	14	ES6101	4	VV5514	5
60-3-10	18	CS25	29	CW9100	24	ES1020K	15	ES6119	4	VV5579	7
60-4-5	18	CSP20	17, 29	CW9200	24	ES1020R	15	ES6155	4	VV5595	10
60-4-10	18	CT40-5	21	CW9400	24	ES1025	15	ES6200	11		

The information contained herein is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. Chemtronics does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Ultrajet, Electro-Wash, Kontakt Restorer, Tuner Renu, DPL, Flux-Off, Soder-Wick, Chem-Wik, CircuitWorks, Freez-It, Konform, Chemask, Plast-N-Glas, Tun-O-Wash, QbE and Chemtronics are registered trademarks of Chemtronics. All rights reserved.

Verizane, Cirozane, Pow-R-Wash, Gold Guard, VacuPak, PermaPak, The Mighty Pen, Max-Kleen, Xtreme, Lector-Solv, Static Free, Hand Guard, Head Cleaner, Controlwipes, Opticwipes, Twillwipes, Chemswab, Screen Prep, Optic Prep, Chempad, StencilWorks, Chamois Tips, Microtips, Foamtips, Flexlips, Cottontips, Coventry, Aqua-Prime, Pillow-Tip, Diamond, Econowipes, Cleanroom Chamois, SqR, HD Silicone, Mighty Wash, FSW, Fiberworks, Fiber-Wash and Foccus are trademarks of Chemtronics. All rights reserved.

DuPont™ and Vertrel® are trademarks or registered trademarks of E. I. duPont de Nemours and Company. All other trademarks herein are trademarks or registered trademarks of their respective owners.



**Visit [www.chemtronics.com](http://www.chemtronics.com)**  
for the very latest product information, specs,  
TDS, SDS, COC, videos & more!



## **Chemtronics Cleaning & Coating Application Lab**

Chemtronics combines over 30-years' experience developing high precision cleaners and conformal coatings, giving us a unique perspective of these interrelated processes.

Chemtronics Application Lab offers a state-of-the-art cleaning, coating and analytical services to help customers optimize their processes. Cleaning equipment includes inline, batch, ultrasonic, and vapor degreasing systems. This equipment allows us to better duplicate your production environment for process optimization and troubleshooting.

### **Services Include:**

- Verify cleaning and coating materials meet customer, industry and regulatory requirements
- Optimize cleaning process
- Troubleshoot cleaning and/or coating problems
- Identify most effective cleaner for specific application
- Compatibility testing for sensitive materials

### **Free Qualification Testing**

Call us today to help qualify new cleaning processes, evaluate current processes, or troubleshoot contamination issues.

For more information, contact our

**Technical Hotline at 770-424-4888 ext 154 or [AskChemtronics@chemtronics.com](mailto:AskChemtronics@chemtronics.com).**

*Call 800-645-5244 ext. 154 to schedule an in-house evaluation with a local sales representative.*



8125 Cobb Center Drive • Kennesaw, GA 30152-4386  
Tel: 770-424-4888 • Toll Free: 1-800-645-5244  
Fax: 770-424-4267 • Toll Free Fax: 1-800-243-6003  
[www.chemtronics.com](http://www.chemtronics.com) • [askchemtronics@chemtronics.com](mailto:askchemtronics@chemtronics.com)  
©2018 Chemtronics® all rights reserved.