

STTH812

Ultrafast recovery - 1200 V diode

Main product characteristics

I _{F(AV)}	8 A
V _{RRM}	1200 V
T _j	175° C
V _F (typ)	1.25 V
t _{rr} (typ)	50 ns

Features and benefits


- Ultrafast, soft recovery
- Very low conduction and switching losses
- High frequency and/or high pulsed current operation
- High reverse voltage capability
- High junction temperature
- Insulated packages:
 - TO-220Ins
 Electrical insulation = 2500 V_{RMS}
 Capacitance = 7 pF
 - TO-220FPAC
 Electrical insulation = 2000 V_{RMS}
 Capacitance = 12 pF

Description

The high quality design of this diode has produced a device with low leakage current, regularly reproducible characteristics and intrinsic ruggedness. These characteristics make it ideal for heavy duty applications that demand long term reliability.

Such demanding applications include industrial power supplies, motor control, and similar mission-critical systems that require rectification and freewheeling. These diodes also fit into auxiliary functions such as snubber, bootstrap, and demagnetization applications.

The improved performance in low leakage current, and therefore thermal runaway guard band, is an immediate competitive advantage for this device.



Order codes

Part Number	Marking
STTH812D	STTH812D
STTH812G	STTH812G
STTH812G-TR	STTH812G
STTH812FP	STTH812FP
STTH812DI	STTH812DI

www.st.com

March 2006 Rev 1 1/11

Characteristics STTH812

Characteristics 1

Table 1. Absolute ratings (limiting values at 25° C, unless otherwise specified)

Symbol	Param		Value	Unit	
V _{RRM}	Repetitive peak reverse voltage			1200	V
	RMS forward current	TO-220AC / D ² PAK /	TO-220FPAC	30	Α
I _F (RMS)	nivis iorward current	TO-220AC Ins		20	A
		TO-220AC / D ² PAK	T _c = 140° C		
I _{F(AV)}	$F(AV)$ Average forward current, $\delta = 0.5$	TO-220FPAC	T _c = 75° C	8	Α
		TO-220AC Ins	T _c = 115° C		
I _{FRM}	Repetitive peak forward current	t _p = 5 μs, F = 5 kHz so	quare	100	Α
I _{FSM}	Surge non repetitive forward current $t_p = 10 \text{ ms Sinusoidal}$			80	Α
T _{stg}	Storage temperature range			-65 to + 175	°C
T _j	Maximum operating junction temperature	9		175	°C

Table 2. Thermal parameters

Symbol	Parameter	Value	Unit	
		TO-220AC / D ² PAK	1.9	
R _{th(j-c)}	R _{th(j-c)} Junction to case	TO-220FPAC	5.4	°C/W
		TO-220AC Ins	3.1	

Table 3. Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур	Max.	Unit
I _R ⁽¹⁾	Reverse leakage current	T _j = 25° C	V- - V			8	μA
'R`	IR Proverse leakage current	T _j = 125° C	$V_R = V_{RRM}$		5	50	μΛ
		T _j = 25° C				2.2	
V _F ⁽²⁾	V _F ⁽²⁾ Forward voltage drop	T _j = 125° C	I _F = 8 A		1.30	2.0	V
		T _j = 150° C			1.25	1.9	

^{1.} Pulse test: t_p = 5 ms, δ < 2 %

To evaluate the conduction losses use the following equation: P = 1.5 x $I_{F(AV)}$ + 0.05 $I_{F}^{2}(RMS)$

$$P = 1.5 \times I_{F(AV)} + 0.05 I_{F^2(RMS)}$$

^{2.} Pulse test: t_p = 380 μ s, δ < 2 %

STTH812 Characteristics

Table 4. Dynamic characteristics

Symbol	Parameter	Test conditions	Min.	Тур	Max.	Unit
+	Payorsa racayary tima	$I_F = 1 \text{ A, } dI_F/dt = -50 \text{ A/}\mu\text{s,}$ $V_R = 30 \text{ V, } T_j = 25^{\circ} \text{ C}$			100	ns
t _{rr} Reverse recovery time	$I_F = 1 \text{ A, } dI_F/dt = -100 \text{ A/}\mu\text{s,}$ $V_R = 30 \text{ V, } T_j = 25^{\circ} \text{ C}$		50	70	115	
I _{RM}	Reverse recovery current	$I_F = 8 \text{ A}, dI_F/dt = -200 \text{ A/}\mu\text{s},$ $V_R = 600 \text{ V}, T_j = 125^{\circ} \text{ C}$		14	21	Α
S	Softness factor	$I_F = 8 \text{ A}, dI_F/dt = -200 \text{ A/}\mu\text{s},$ $V_R = 600 \text{ V}, T_j = 125^{\circ} \text{ C}$		2		
t _{fr}	Forward recovery time	$I_F = 8 \text{ A}$ $dI_F/dt = 50 \text{ A/}\mu\text{s}$ $V_{FR} = 1.5 \text{ x } V_{Fmax}, T_j = 25^{\circ} \text{ C}$			400	ns
V _{FP}	Forward recovery voltage	$I_F = 8 \text{ A}, dI_F/dt = 50 \text{ A/}\mu\text{s},$ $T_j = 25^{\circ} \text{ C}$		7		٧

Figure 1. Conduction losses versus average current




Figure 2. Forward voltage drop versus forward current




Figure 3. Relative variation of thermal impedance junction to case versus pulse duration





Figure 4. Relative variation of thermal impedance junction to case versus pulse duration




Characteristics STTH812

Figure 5. Peak reverse recovery current versus dl_F/dt (typical values)




Figure 6. Reverse recovery time versus dI_F/dt (typical values)




t_{rr}(ns) 500 450 400 300 250 200 150 100 dlf/dt(A/µs)

Figure 7. Reverse recovery charges versus dl_F/dt (typical values)


Figure 8. Softness factor versus dI_F/dt (typical values)






Relative variations of dynamic Figure 9. parameters versus junction temperature

Figure 10. Transient peak forward voltage versus dl_F/dt (typical values)





STTH812 Characteristics

Figure 11. Forward recovery time versus dl_F/dt Figure 12. Junction capacitance versus reverse voltage applied (typical values)





Figure 13. Thermal resistance junction to ambient versus copper surface under tab (Epoxy printed circuit board FR4, e_{cu} = 35 μ m)



5//

2 Package mechanical data


Epoxy meets UL94, V0

Cooling method: by conduction (C)

Recommended torque value: 0.55 Nm (TO-220AC)


Maximum torque value: 0.7 Nm (TO-220AC)

Table 5. T0-220AC dimensions




	DIMENSIONS			
REF.	Millin	Millimeters		hes
	Min.	Max.	Min.	Max.
Α	4.40	4.60	0.173	0.181
С	1.23	1.32	0.048	0.051
D	2.40	2.72	0.094	0.107
Е	0.49	0.70	0.019	0.027
F	0.61	0.88	0.024	0.034
F1	1.14	1.70	0.044	0.066
G	4.95	5.15	0.194	0.202
H2	10.00	10.40	0.393	0.409
L2	16.40	0 typ.	0.645 typ.	
L4	13.00	14.00	0.511	0.551
L5	2.65	2.95	0.104	0.116
L6	15.25	15.75	0.600	0.620
L7	6.20	6.60	0.244	0.259
L9	3.50	3.93	0.137	0.154
М	2.6	typ.	0.102	2 typ.
Diam. I	3.75	3.85	0.147	0.151

Table 6. T0-220Ins dimensions




		DIMENSIONS				
REF	Millimete		ers Inches			
	Min.		Max.	Min.		Max.
Α	15.20		15.90	0.598		0.625
a1		3.75			0.147	
a2	13.00		14.00	0.511		0.551
В	10.00		10.40	0.393		0.409
b1	0.61		0.88	0.024		0.034
b2	1.23		1.32	0.048		0.051
С	4.40		4.60	0.173		0.181
c1	0.49		0.70	0.019		0.027
c2	2.40		2.72	0.094		0.107
е	4.80		5.40	0.189		0.212
F	6.20		6.60	0.244		0.259
ØI	3.75		3.85	0.147		0.151
14	15.80	16.40	16.80	0.622	0.646	0.661
L	2.65		2.95	0.104		0.116
12	1.14		1.70	0.044		0.066
М		2.60			0.102	

Table 7. T0-220FPAC dimensions




		DIMEN	SIONS	
REF	Millim	neters	Inc	hes
	Min.	Max.	Min.	Max.
Α	4.4	4.6	0.173	0.181
В	2.5	2.7	0.098	0.106
D	2.5	2.75	0.098	0.108
Е	0.45	0.70	0.018	0.027
F	0.75	1	0.030	0.039
F1	1.15	1.70	0.045	0.067
G	4.95	5.20	0.195	0.205
G1	2.4	2.7	0.094	0.106
Н	10	10.4	0.393	0.409
L2	16	Гур.	0.63	Тур.
L3	28.6	30.6	1.126	1.205
L4	9.8	10.6	0.386	0.417
L5	2.9	3.6	0.114	0.142
L6	15.9	16.4	0.626	0.646
L7	9.00	9.30	0.354	0.366
Dia.	3.00	3.20	0.118	0.126

Table 8. D²PAK dimensions



		DIMEN	SIONS	
REF.	Millimeters		Inc	hes
	Min.	Max	Min.	Max.
Α	4.40	4.60	0.173	0.181
A1	2.49	2.69	0.098	0.106
A2	0.03	0.23	0.001	0.009
В	0.70	0.93	0.027	0.037
B2	1.14	1.70	0.045	0.067
С	0.45	0.60	0.017	0.024
C2	1.23	1.36	0.048	0.054
D	8.95	9.35	0.352	0.368
Е	10.00	10.40	0.393	0.409
G	4.88	5.28	0.192	0.208
L	15.00	15.85	0.590	0.624
L2	1.27	1.40	0.050	0.055
L3	1.40	1.75	0.055	0.069
М	2.40	3.20	0.094	0.126
R	0.40	typ.	0.016	6 typ.
V2	0°	8°	0°	8°

Figure 14. D²PAK footprint (dimensions in mm)



In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect . The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com.

Ordering information STTH812

3 Ordering information

Part Number	Marking	Package	Weight	Base qty	Delivery mode
STTH812D	STTH812D	TO-220AC	1.86 g	50	Tube
STTH812DI	STTH812DI	TO-220Ins	1.86 g	50	Tube
STTH812FP	STTH812FP	TO-220FPAC	2.2 g	50	Tube
STTH812G	STTH812G	D ² PAK	1.48 g	50	Tube
STTH812G-TR	STTH812G	D ² PAK	1.48 g	1000	Tape & reel

4 Revision history

Date	Revision	Description of Changes
02-Mar-2006	1	First issue.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZE REPRESENTATIVE OF ST, ST PRODUCTS ARE NOT DESIGNED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS, WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2006 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

47/