
Item no.: 2002-1204
Product description: 2-Conductor through terminal block suitable for Ex e applications suitable for Ex i applications



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Current intensity EN	32 A
Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm ²]	0.25 - 2.5 mm ²
Cross section [AWG]	22 - 12 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm ²]	0.25 - 4 mm ²
Cross section [AWG]	22 - 12 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Rated voltage EN (Ex e II)	550 V
Nominal current (Ex e II)	22 A
Weight	4.369 g
Color	blue
Wiring type	Front-entry

No. of connection Points	2
No. of potentials	1
Height	33 mm
Height	1.299 in



Width	5.2 mm
Width	0.205 in
Depth	48.5 mm
Depth	1.909 in
Strip length from	10 mm
Strip length to	12 mm
Strip length	0.43 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
2002-1204	ABS	05-HG476175/3-PDA	800	24	0,5-4
2002-1204	AEX	E185892	550	20	22-12
2002-1204	CCA	NL6387	800	24/32	0,2-2,5/4
2002-1204	CSA	154112-1536069	600	20	22-12
2002-1204	DNV	E-10423	800	24	0,5-4
2002-1204	GL	26187-05HH	800	24	0,25-2,5
2002-1204	KEMA	NL2116586.02	800	24	0,5-4
2002-1204	LR	91/20112(E6)	800	24	0,5-4
2002-1204	PRS	TE/1718/880590/08	800	24	0,2-4
2002-1204	PTB	IECExPTB03.0004U	550	22	0,2-4
2002-1204	PTB	PTB03AteX1162U	550	22	0,2-4
2002-1204	RosTest	8189158	550	22	0,2-4
2002-1204	UR	E45172	600	20	22-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected