

Film Capacitors

Metallized Polypropylene Film Capacitors (MKP)

Series/Type: B3277*X/Y/Z
Date: August 2019

© TDK Electronics AG 2019. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without TDK Electronics' prior express consent is prohibited.

B3277*X/Y/Z

MKP DC link

Typical applications

- Frequency converters
- Industrial and high-end power supplies
- Solar Inverters

Climatic

- Max. operating temperature: 105 °C (case)
- Climatic category (IEC 60068-1:2013): 40/105/56

Construction

- Dielectric: Polypropylene (MKP)
- Plastic case (UL 94 V-0)
- Epoxy resin sealing (UL 94 V-0)

Features

- Capacitance value from 1.5 μF up to 170 μF
- High CV product, compact
- Good self-healing properties
- Over-voltage capability
- Low losses with high current capability
- High reliability
- Long useful life
- RoHS-compatible

Terminals

- Parallel wire leads, lead-free tinned
- 2-pin and 4-pin
- Standard lead lengths: 6 –1 mm

Marking

Manufacturer's logo and lot number, date code, rated capacitance (coded), capacitance tolerance (code letter), rated DC voltage

Delivery mode

Bulk (untaped, lead length 6-1 mm)






Dimensional drawings

Number of wires	Lead spacing e ±0.4	Lead diameter d ₁ ±0.05	Туре
2-pin	27.5	0.8	B32774X
2-pin	37.5	1.0	B32776Y
4-pin	37.5	1.2	B32776Z
4-pin	52.5	1.2	B32778Z

Dimensions in mm

Dimensional drawings 2-pin versions

B32774X, B32776Y






	B32774X	B32776Y
Lead spacing e ±0.4:	27.5	37.5
Lead diameter d₁:	0.8	1.0

Dimensions in mm

B32776Y (low profile)



	N N N N N N N N N N N N N N N N N N N	
37.5		

Lead spacing e ±0.4:	37.5
Lead diameter d₁:	1.0

Dimensions in mm






B3277*X/Y/Z

MKP DC link

Dimensional drawings 4-pin versions

B32776Z, B32778Z





	B32776Z	B32778Z
Lead spacing <i>e</i> ±0.4:	37.5	52.5
Lead diameter d₁:	1.2	1.2

Dimensions in mm







Overview of available types

Lead spacing	27.5 mm						
Туре	B32774X						
Page	8						
V _R (V DC)	500	600	800	900	1000	1100	1200
C _R (μF)							
1.5							
1.8							
2.0							
2.5							
3.0							
4.0							
4.5							
5.0							
6.0							
6.5							
7.0							
8.0							
9.0							
10							
12							
13							
15							
16							
22							





B3277*X/Y/Z

MKP DC link

Lead spacing	37.5 mm	า					
Туре	B32776	Y/Z					
Page	11						
V _R (V DC)	500	600	800	900	1000	1100	1200
C _R (µF)							
2.7							
3.5							
3.9							
4.5							
5.0							
6.0							
6.8							
7.5							
8.0							
8.5							
10							
12							
13							
14							
15							
16							
20							
22							
25							
30							
35							
40							
45							
50							
60							
65							



B3277*X/Y/Z

MKP DC link



Lead spacing	52.5 mm	1					
Туре	B327782	7					
Page	15						
V _R (V DC)	500	600	800	900	1000	1100	1200
C _R (μF)							
14							
16							
20							
22							
25							
27							
28							
30							
33							
35							
40							
45							
50							
55							
58							
60							
70							
75							
80							
90							
95							
100							
110							
120							
130							
170							





Ordering codes and packing units (lead spacing 27.5 mm)

C _R ¹⁾	Max. dimensions	Ordering code	I _{RMS,max} ²⁾	ESR _{typ}	ESL _{typ} ³⁾	$tan \delta$	tan δ	Un-
	$w \times h \times I$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	
μF	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
V _{R,85} ° _C	= 500 V DC							
5.0	$11.0 \times 21.0 \times 31.5$	B32774X4505+000	5.0	21.1	19.0	1.2	10.7	2352
6.0	$12.5 \times 21.5 \times 31.5$	B32774X4605+000	5.8	17.0	20.0	1.2	10.7	2100
7.0	$13.5 \times 23.0 \times 31.5$	B32774X4705+000	6.6	14.5	21.0	1.2	10.8	1932
8.0	$14.5 \times 24.5 \times 31.5$	B32774X4805+000	7.3	12.5	22.5	1.2	10.8	1848
10.0	$15.0 \times 24.5 \times 31.5$	B32774X4106K000	8.0	10.9	24.0	1.2	11.0	1680
12.0	$18.0 \times 27.5 \times 31.5$	B32774X4126+000	10.0	9.5	26.5	1.2	11.0	1064
13.0	$18.0 \times 27.5 \times 31.5$	B32774X4136+000	10.5	8.0	27.0	1.2	11.2	1064
15.0	$21.0 \times 31.0 \times 31.5$	B32774X4156+000	11.2	7.5	28.0	1.2	11.2	952
16.0	$21.0 \times 31.0 \times 31.5$	B32774X4166+000	11.7	7.0	29.0	1.2	11.2	952
22.0	$22.0\times36.5\times31.5$	B32774X4226+000	14.5	5.4	30.0	1.3	12.1	784
V _{R,85} °C	= 600 V DC							
4.0	$11.0 \times 21.0 \times 31.5$	B32774X5405+000	4.8	22.0	19.5	1.1	10.0	2352
4.5	$12.5 \times 21.5 \times 31.5$	B32774X5455+000	5.1	19.5	20.5	1.1	10.0	2100
5.0	$13.5 \times 23.0 \times 31.5$	B32774X5505+000	5.5	17.0	21.5	1.1	10.1	1932
6.0	$14.5 \times 24.5 \times 31.5$	B32774X5605+000	6.8	14.5	23.0	1.1	10.1	1848
6.5	$15.0 \times 24.5 \times 31.5$	B32774X5655+000	7.2	13.5	22.5	1.2	10.1	1680
8.0	$18.0 \times 27.5 \times 31.5$	B32774X5805+000	8.8	11.0	25.0	1.2	10.2	1064
9.0	$18.0 \times 27.5 \times 31.5$	B32774X5905+000	9.4	10.0	27.5	1.2	10.2	1064
10.0	$21.0 \times 31.0 \times 31.5$	B32774X5106+000	10.2	8.5	29.5	1.2	10.3	952
16.0	$22.0\times36.5\times31.5$	B32774X5166+000	13.5	6.2	32.0	1.2	10.5	784

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

000 = untaped (lead length 6 - 1 mm)

Other lead lengths available upon request

¹⁾ Capacitance value measured at 1 kHz

²⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a ΔT ≤20 °C when $\Delta ESR_{typ} \leq \pm 5\%$

³⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)



B32774X

MKP DC link



Ordering codes and packing units (lead spacing 27.5 mm)

$C_R^{4)}$	Max. dimensions	Ordering code	I _{RMS,max} 5)	ESR _{typ}	ESL _{typ} ⁶⁾	tan δ	tan δ	Un-
	$w \times h \times I$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	
μF	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
V _{R,85} ° _C	= 800 V DC							
3.0	$11.0 \times 21.0 \times 31.5$	B32774X8305+000	4.5	24.8	19.0	0.9	7.6	2352
4.0	$13.5 \times 23.0 \times 31.5$	B32774X8405+000	5.6	18.5	21.0	0.9	7.6	1932
5.0	$14.5 \times 24.5 \times 31.5$	B32774X8505+000	6.5	15.3	23.0	0.9	7.7	1848
6.0	$18.0 \times 27.5 \times 31.5$	B32774X8605+000	8.0	12.6	24.5	0.9	7.7	1064
7.0	$18.0 \times 27.5 \times 31.5$	B32774X8705+000	8.7	11.0	28.0	0.9	7.8	1064
8.0	$21.0 \times 31.0 \times 31.5$	B32774X8805+000	9.6	9.6	29.0	0.9	7.9	952
9.0	$21.0 \times 31.0 \times 31.5$	B32774X8905+000	10.3	8.7	30.0	1.0	8.0	952
10.0	$22.0 \times 36.5 \times 31.5$	B32774X8106+000	10.0	8.0	32.0	1.0	8.2	784
12.0	$22.0 \times 36.5 \times 31.5$	B32774X8126+000	13.0	6.8	34.0	1.0	8.3	784
V _{R,85} ° _C	= 900 V DC							
2.5	$12.5 \times 21.5 \times 31.5$	B32774X9255+000	4.5	26.0	21.0	8.0	7.2	2100
3.0	$13.5 \times 23.0 \times 31.5$	B32774X9305+000	5.2	22.0	21.5	8.0	7.2	1932
4.0	$15.0 \times 24.5 \times 31.5$	B32774X9405+000	6.3	17.5	22.8	8.0	7.2	1680
5.0	$18.0 \times 27.5 \times 31.5$	B32774X9505+000	8.0	13.5	26.0	8.0	7.2	1064
6.0	$18.0 \times 27.5 \times 31.5$	B32774X9605+000	8.7	11.5	29.5	8.0	7.3	1064
7.0	$21.0 \times 31.0 \times 31.5$	B32774X9705+000	9.7	10.0	30.0	8.0	7.3	952
10.0	$22.0 \times 36.5 \times 31.5$	B32774X9106+000	12.5	7.5	33.8	8.0	7.3	784

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

J = ±5%

Packing code:

000 = untaped (lead length 6 - 1 mm)


Other lead lengths available upon request

⁴⁾ Capacitance value measured at 1 kHz

⁵⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le$ 20 °C when $\Delta ESR_{typ} \le \pm 5\%$

⁶⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)





Ordering codes and packing units (lead spacing 27.5 mm)

$C_R^{7)}$	Max. dimensions	Ordering code	I _{RMS,max} 8)	ESR _{typ}	ESL _{typ} ⁹⁾	$tan \ \delta$	tan δ	Un-
	$w \times h \times l$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	
μF	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
V _{R,85} ° _C	= 1000 V DC							
2.0	$12.5 \times 21.5 \times 31.5$	B32774X0205+000	4.5	26.3	19.0	0.7	5.3	2100
2.5	$14.5 \times 24.5 \times 31.5$	B32774X0255+000	5.7	20.8	21.8	0.7	5.3	1848
3.0	$18.0 \times 27.5 \times 31.5$	B32774X0305+000	7.0	17.8	23.0	0.7	5.4	1064
4.0	$18.0 \times 27.5 \times 31.5$	B32774X0405+000	7.9	13.4	27.9	0.7	5.5	1064
5.0	$21.0 \times 31.0 \times 31.5$	B32774X0505+000	9.0	10.8	29.7	0.7	5.5	952
7.0	$22.0\times36.5\times31.5$	B32774X0507+000	12.0	8.1	30.0	0.7	5.8	784
V _{R,85} ° _C	= 1100 V DC							
1.8	$13.5 \times 23.0 \times 31.5$	B32774X7185+000	4.8	26.5	20.8	0.7	4.9	1932
2.0	$15.0 \times 24.5 \times 31.5$	B32774X7205+000	5.2	23.7	21.5	0.7	4.9	1680
3.0	$18.0 \times 27.5 \times 31.5$	B32774X7305+000	7.2	16.3	26.0	0.7	5.0	1064
4.0	$21.0 \times 31.0 \times 31.5$	B32774X7405+000	8.5	12.5	29.5	0.7	5.0	1064
5.0	$22.0 \times 36.5 \times 31.5$	B32774X7505+000	9.5	10.1	31.8	0.7	5.1	952
6.0	$22.0\times36.5\times31.5$	B32774X7605+000	11.3	8.5	33.8	0.7	5.2	784
V _{R,85} ° _C	= 1200 V DC							
1.5	$12.5 \times 21.5 \times 31.5$	B32774X1155K000	4.4	31.3	20.0	0.6	4.8	2100
2.0	$21.0 \times 31.0 \times 31.5$	B32774X1205+000	6.1	22.0	22.8	0.6	4.8	1428
3.0	$21.0 \times 31.0 \times 31.5$	B32774X1305K000	7.1	16.0	24.0	0.6	4.9	1428
4.0	$22.0 \times 36.5 \times 31.5$	B32774X1405+000	9.4	11.5	29.0	0.7	5.1	784
5.0	$22.0 \times 36.5 \times 31.5$	B32774X1505+000	10.5	9.5	33.0	0.7	5.1	784

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

⁷⁾ Capacitance value measured at 1 kHz

⁸⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a ΔT $\leq\!\!20$ °C when $\Delta ESR_{typ}\!\leq\!\pm5\%$

⁹⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)



MKP DC link



Ordering codes and packing units (lead spacing 37.5 mm)

$C_R^{1)}$	Max. dimensions	P ₁	Ordering code	I _{RMS,max} ²⁾	ESR _{typ}	ESL _{typ} ³⁾	$tan \delta$	tan δ	Un-
	$w \times h \times l$		(composition see	70 °C	70 °C	70 °C	max.	max.	taped
			below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
$V_{R,85}$	_{°C} = 500 V DC								
12.0	$24.0 \times 15.0 \times 42.0$	_	B32776Y4126K000	7.0	17.1	19.0	2.2	21.0	1040
16.0	$24.0 \times 19.0 \times 42.0$	_	B32776Y4166K000	8.0	13.0	18.0	2.3	21.2	780
30.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z4306+000	14.0	7.0	11.0	2.3	21.3	640
30.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y4306+000	14.0	7.3	28.0	2.4	22.3	640
35.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z4356+000	16.5	6.0	10.0	2.3	21.4	440
35.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y4356+000	16.0	6.4	24.0	2.4	22.6	440
40.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z4406+000	17.5	5.3	11.0	2.3	21.4	440
40.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y4406+000	17.0	5.6	26.0	2.4	22.7	440
50.0	$28.0 \times 42.5 \times 42.0$	20.3	B32776Z4506+000	20.0	4.3	12.0	2.3	21.7	440
50.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y4506+000	19.0	4.7	30.0	2.5	23.8	440
60.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z4606+000	23.5	3.6	14.0	2.4	22.3	400
60.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y4606+000	22.0	4.0	32.0	2.5	24.2	400
65.0	$33.0 \times 48.0 \times 42.0$	20.3	B32776Z4656+000	25.5	3.3	14.0	2.3	22.2	180
$V_{R,85}$	_{°C} = 600 V DC								
8.5	$24.0 \times 15.0 \times 42$	_	B32776Y5585+000	6.5	19.9	19.0	1.9	17.2	1040
12.0	$24.0 \times 19.0 \times 42.0$	_	B32776Y5126K000	8.0	14.4	18.0	1.9	17.4	780
25.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z5256K000	14.0	7.0	12.0	1.9	17.5	640
25.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y5256K000	13.5	7.4	28.0	2.0	18.3	640
30.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z5306K000	16.5	5.8	11.0	1.9	17.6	440
30.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y5306K000	16.5	6.1	26.0	2.0	17.6	440
35.0	$28.0 \times 42.5 \times 42.0$	10.2	B32776Z5356+000	19.0	5.0	12.0	1.9	17.8	440
35.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y5356+000	18.0	5.3	29.0	2.0	19.0	440
45.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z5456K000	22.0	4.0	13.0	1.9	17.9	400
45.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y5456K000	21.0	4.4	32.0	2.1	19.7	400
50.0	$33.0\times48.0\times42.0$	20.3	B32776Z5506K000	25.0	3.5	14.0	2.0	18.1	180

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

000 = untaped (lead length 6 - 1 mm)

Other lead lengths available upon request

¹⁾ Capacitance value measured at 1 kHz

²⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le 20$ °C when $\Delta ESR_{typ} \le \pm 5\%$

³⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)





MKP DC link

Ordering codes and packing units (lead spacing 37.5 mm)

$C_R^{4)}$	Max. dimensions	P ₁	Ordering code	I _{RMS,max} 5)	ESR _{typ}	ESL _{typ} ⁶⁾	tan δ	tan δ	Un-
	$w \times h \times I$		(composition see	70 °C	70 °C	70 °C	max.	max.	taped
			below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm	mm		Α	$m\Omega$	nH	10-3	10 ⁻³	MOQ
V _{R,85}	_{°C} = 800 V DC								
6.8	$24.0 \times 15.0 \times 42.0$	_	B32776Y8685+000	6.0	22.1	18.0	1.7	15.1	1040
8.5	$24.0 \times 19.0 \times 42.0$	_	B32776Y8855+000	7.5	17.8	18.0	1.7	15.1	780
13.0	$18.0 \times 32.5 \times 42.0$	_	B32776Y8146+000	10.0	11.5	23.0	1.8	16.3	720
15.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z8156+000	12.0	9.6	10.0	1.7	15.2	640
15.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y8156+000	11.5	10.3	24.0	1.7	15.7	640
20.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z8206+000	14.5	7.5	10.0	1.7	15.3	440
20.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y8206+000	14.5	7.8	24.0	1.7	15.9	440
22.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z8226+000	15.5	6.8	11.0	1.7	15.3	440
22.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y8226+000	15.0	7.1	25.0	1.7	16.0	440
25.0	$28.0 \times 42.5 \times 42.0$	20.3	B32776Z8256+000	17.0	6.1	11.0	1.7	15.4	440
25.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y8256+000	16.5	6.4	28.0	1.8	16.3	440
30.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z8306+000	19.5	5.1	12.0	1.7	15.6	400
30.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y8306+000	19.0	5.5	30.0	1.8	16.7	400
35.0	$33.0\times48.0\times42.0$	20.3	B32776Z8356+000	22.0	4.3	14.0	1.7	15.7	180
$V_{R,85}$	_{°C} = 900 V DC								
5.0	$24.0 \times 15.0 \times 42.0$	_	B32776Y9505+000	5.5	26.1	19.0	1.5	13.4	1040
7.5	$24.0 \times 19.0 \times 42.0$	_	B32776Y9755K000	7.5	17.8	18.0	1.5	13.5	780
15.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z9156K000	12.5	9.1	12.0	1.5	13.6	640
15.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y9156K000	12.0	9.4	28.0	1.5	14.1	640
20.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z9206K000	15.0	7.0	11.0	1.5	13.6	440
20.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y9206K000	15.0	7.3	26.0	1.5	14.2	440
22.0	$28.0 \times 42.5 \times 42.0$	10.2	B32776Z9226K000	17.0	6.3	12.0	1.5	13.7	440
22.0	$28.0\times42.5\times42.0$	_	B32776Y9226K000	16.5	6.6	29.0	1.5	14.5	440
25.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z9256+000	19.0	5.5	13.0	1.5	13.8	400
25.0	$30.0 \times 45.0 \times 42.0$	_	B32776Z9256+000	18.5	5.9	32.0	1.5	14.7	400
30.0	$33.0\times48.0\times42.0$	20.3	B32776Z9306+000	21.5	4.7	14.0	1.5	13.9	180

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$ $J = \pm 5\%$ Packing code:

⁴⁾ Capacitance value measured at 1 kHz

⁵⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le 20$ °C when $\Delta ESR_{typ} \le \pm 5\%$

⁶⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)







Ordering codes and packing units (lead spacing 37.5 mm)

$C_R^{7)}$	Max. dimensions	P ₁	Ordering code	I _{RMS,max} 8)	ESR _{typ}	ESL _{typ} ⁹⁾	tan δ	tan δ	Un-
	$w \times h \times l$		(composition see	70 °C	70 °C	70 °C	max.	max.	taped
			below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
$V_{R,85}$	_{°C} = 1000 V DC								
3.9	$24.0 \times 15.0 \times 42.0$	_	B32776Y0395+000	5.0	30.5	18.0	1.4	12.1	1040
5.0	$24.0 \times 19.0 \times 42.0$	_	B32776Y0505+000	6.5	23.6	18.0	1.4	12.1	780
12.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z0126+000	12.0	10.2	12.0	1.4	12.2	640
12.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y0126+000	11.5	10.5	28.0	1.4	12.6	640
14.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z0146+000	13.5	8.7	12.0	1.4	12.2	440
14.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y0146+000	13.5	9.0	25.0	1.4	12.6	440
16.0	$28.0 \times 42.5 \times 42.0$	10.2	B32776Z0166+000	15.5	7.4	12.0	1.4	12.3	440
16.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y0166+000	15.0	7.8	30.0	1.4	12.9	440
20.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z0206+000	18.0	6.0	14.0	1.4	12.4	400
20.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y0206+000	17.5	6.5	32.0	1.4	13.1	400
22.0	$33.0 \times 48.0 \times 42.0$	20.3	B32776Z0226+000	21.0	4.9	15.0	1.3	11.4	180
$V_{R,85}$	° _C = 1100 V DC								
3.5	$24.0 \times 15.0 \times 42.0$	_	B32776Y7355+000	5.2	30.5	19.2	1.3	11.8	1040
4.5	$24.0 \times 19.0 \times 42.0$	_	B32776Y7455+000	5.6	29.5	20.0	1.3	11.8	780
6.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z7605+000	8.0	17.1	12.0	1.3	11.8	640
6.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y7605+000	8.0	17.2	23.8	1.3	11.8	640
10.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z7106+000	12.0	10.0	12.0	1.3	11.7	440
10.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y7106+000	12.0	10.5	25.6	1.3	11.7	440
12.0	$28.0 \times 42.5 \times 42.0$	10.2	B32776Z7126+000	13.3	8.5	12.9	1.3	11.6	440
12.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y7126+000	14.0	8.9	27.6	1.3	11.6	440
16.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z7166+000	17.0	6.4	13.5	1.3	11.6	400
16.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y7166+000	16.0	6.8	33.8	1.3	11.5	400
20.0	$33.0\times48.0\times42.0$	20.3	B32776Z7206+000	19.0	5.2	14.4	1.3	11.5	180

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

000 = untaped (lead length 6 - 1 mm)

Other lead lengths available upon request

⁷⁾ Capacitance value measured at 1 kHz

⁸⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le$ 20 °C when $\Delta ESR_{typ} \le \pm 5\%$

⁹⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)





MKP DC link

Ordering codes and packing units (lead spacing 37.5 mm)

$C_R^{10)}$	Max. dimensions	P ₁	Ordering code	I _{RMS,max} 11	ESR _{typ}	ESL _{typ} ¹²⁾	$tan \delta$	tan δ	Un-
	$w \times h \times l$		(composition see	70 °C	70 °C	70 °C	max.	max.	taped
			below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
$V_{R,85}$	_{°C} = 1200 V DC								
2.7	$24.0 \times 15.0 \times 42.0$	_	B32776Y1275+000	5.0	34.7	19.0	1.1	9.6	1040
3.5	$24.0 \times 19.0 \times 42.0$	_	B32776Y1355+000	6.0	27.4	18.0	1.1	9.7	780
8.0	$20.0 \times 39.5 \times 42.0$	10.2	B32776Z1805+000	11.0	12.1	12.0	1.1	9.7	640
8.0	$20.0 \times 39.5 \times 42.0$	_	B32776Y1805+000	10.5	12.4	24.0	1.1	10.0	640
10.0	$28.0 \times 37.0 \times 42.0$	10.2	B32776Z1106+000	13.0	9.6	11.0	1.1	9.7	440
10.0	$28.0 \times 37.0 \times 42.0$	_	B32776Y1106+000	12.5	9.9	26.0	1.2	10.0	440
12.0	$28.0 \times 42.5 \times 42.0$	10.2	B32776Z1126+000	14.5	8.1	12.0	1.1	9.8	440
12.0	$28.0 \times 42.5 \times 42.0$	_	B32776Y1126+000	14.0	8.5	28.0	1.2	10.1	440
14.0	$30.0 \times 45.0 \times 42.0$	20.3	B32776Z1146+000	17.0	6.8	14.0	1.1	10.1	400
14.0	$30.0 \times 45.0 \times 42.0$	_	B32776Y1146+000	16.5	7.3	32.0	1.2	10.4	400
16.0	$33.0 \times 48.0 \times 42.0$	20.3	B32776Z1166+000	19.0	6.0	15.0	1.1	9.9	180

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$ $J = \pm 5\%$ Packing code:

¹⁰⁾ Capacitance value measured at 1 kHz

¹¹⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \leq\!\! 20$ °C when $\Delta ESR_{typ} \leq\! \pm 5\%$

¹²⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)



MKP DC link



Ordering codes and packing units (lead spacing 52.5 mm, P_1 = 20.3 mm)

$C_R^{1)}$	Max. dimensions	Ordering code	I _{RMS,max} ²⁾	ESR _{typ}	ESL _{typ} ³⁾	$tan \ \delta$	tan δ	Un-
	$w \times h \times l$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm		Α	mΩ	nH	10 ⁻³	10 ⁻³	MOQ
V _{R,85 °C}	= 500 V DC							
55.0	$43.0 \times 24.0 \times 57.5$	B32778Z4556+000	16.5	7.2	13.0	4.3	41.7	420
75.0	$30.0 \times 45.0 \times 57.5$	B32778Z4756+000	21.0	5.6	12.0	4.4	42.6	280
80.0	$30.0 \times 45.0 \times 57.5$	B32778Z4806+000	21.5	5.3	13.0	4.4	42.7	280
100.0	$35.0 \times 50.0 \times 57.5$	B32778Z4107+000	26.0	4.3	14.0	4.5	43.3	108
110.0	$35.0 \times 50.0 \times 57.5$	B32778Z4117K000	27.0	3.9	15.0	4.5	43.6	108
130.0	$38.0 \times 57.5 \times 57.5$	B32778Z4137+000	28.0	3.5	16.0	4.6	45.0	96
170.0	$45.0\times57.0\times57.5$	B32778Z4177+000	36.5	2.6	17.0	4.6	45.7	140
V _{R,85} ° _C	= 600 V DC							
40.0	$43.0 \times 24.0 \times 57.5$	B32778Z5406+000	15.5	8.5	13.0	3.6	34.5	420
55.0	$30.0 \times 45.0 \times 57.5$	B32778Z5556+000	19.5	6.5	12.0	3.7	35.0	280
60.0	$30.0 \times 45.0 \times 57.5$	B32778Z5606+000	20.5	5.8	13.0	3.7	35.3	280
75.0	$35.0 \times 50.0 \times 57.5$	B32778Z5756+000	24.0	4.9	14.0	3.7	35.8	108
80.0	$35.0 \times 50.0 \times 57.5$	B32778Z5806+000	25.5	4.4	15.0	3.7	36.0	108
90.0	$38.0 \times 57.5 \times 57.5$	B32778Z5906+000	27.0	4.0	16.0	3.9	37.0	96
95.0	$38.0\times57.5\times57.5$	B32778Z5956+000	28.0	3.5	17.0	3.9	37.3	96
120.0	$45.0 \times 57.0 \times 57.5$	B32778Z5127+000	34.5	3.1	18.0	3.9	37.5	140
V _{R,85} ° _C	= 800 V DC							
30.0	$43.0 \times 24.0 \times 57.5$	B32778Z8306+000	14.5	9.8	14.0	3.2	30.2	420
45.0	$30.0 \times 45.0 \times 57.5$	B32778Z8456+000	19.5	6.6	14.0	3.2	30.9	280
50.0	$30.0 \times 45.0 \times 57.5$	B32778Z8506K000	20.0	6.3	14.0	3.2	30.9	280
55.0	$35.0 \times 50.0 \times 57.5$	B32778Z8556+000	23.0	5.6	14.0	3.2	31.1	108
60.0	$35.0 \times 50.0 \times 57.5$	B32778Z8606+000	23.5	5.1	15.0	3.3	31.2	108
70.0	$38.0\times57.5\times57.5$	B32778Z8706+000	25.0	4.6	16.0	3.4	32.2	96
75.0	$38.0\times57.5\times57.5$	B32778Z8756+000	26.0	4.3	17.0	3.4	32.4	96
90.0	$45.0 \times 57.0 \times 57.5$	B32778Z8906+000	32.5	3.5	18.0	3.4	32.5	140

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

¹⁾ Capacitance value measured at 1 kHz

²⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le 20$ °C when $\Delta ESR_{typ} \le \pm 5\%$

³⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)





MKP DC link

Ordering codes and packing units (lead spacing 52.5 mm, P_1 = 20.3 mm)

$C_R^{4)}$	Max. dimensions	Ordering code	I _{RMS,max} ⁵⁾	ESR _{typ}	ESL _{typ} 6)	$tan \ \delta$	tan δ	Un-
	$w \times h \times l$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm		Α	$m\Omega$	nΗ	10 ⁻³	10 ⁻³	MOQ
V _{R,85} °C	= 900 V DC							
25.0	$43.0 \times 24.0 \times 57.5$	B32778Z9256+000	13.5	10.7	13.0	2.8	26.8	420
35.0	$30.0 \times 45.0 \times 57.5$	B32778Z9356+000	18.0	7.7	13.0	2.9	27.3	280
45.0	$35.0 \times 50.0 \times 57.5$	B32778Z9456+000	19.0	7.0	13.0	2.9	27.5	108
50.0	$35.0 \times 50.0 \times 57.5$	B32778Z9506K000	22.5	5.6	15.0	2.9	27.7	108
55.0	$38.0 \times 57.5 \times 57.5$	B32778Z9556+000	23.5	5.2	16.0	3.0	28.2	96
60.0	$38.0 \times 57.5 \times 57.5$	B32778Z9606+000	24.5	4.9	17.0	3.0	28.4	96
70.0	$45.0 \times 57.0 \times 57.5$	B32778Z9706+000	31.0	3.8	18.0	3.0	28.5	140
V _{R,85 °C}	= 1000 V DC							
20.0	$43.0 \times 24.0 \times 57.5$	B32778Z0206+000	13.0	11.9	13.0	2.6	24.1	420
25.0	$30.0 \times 45.0 \times 57.5$	B32778Z0256+000	16.0	8.9	13.0	2.6	24.5	280
30.0	$30.0 \times 45.0 \times 57.5$	B32778Z0306K000	17.5	8.2	13.0	2.6	24.6	280
35.0	$35.0 \times 50.0 \times 57.5$	B32778Z0356+000	19.5	7.2	14.0	2.7	25.1	108
40.0	$35.0 \times 50.0 \times 57.5$	B32778Z0406+000	21.5	6.2	15.0	2.7	25.5	108
45.0	$38.0 \times 57.5 \times 57.5$	B32778Z0456+000	22.5	5.6	16.0	2.7	25.6	108
50.0	$38.0 \times 57.5 \times 57.5$	B32778Z0506+000	23.5	5.3	17.0	2.7	25.8	96
58.0	$45.0 \times 57.0 \times 57.5$	B32778Z0586+000	29.0	4.3	18.0	2.7	26.0	140
V _{R,85} ° _C	= 1100 V DC							
16.0	$43.0 \times 24.0 \times 57.5$	B32778Z7166+000	12.5	13.5	13.0	2.4	23.0	420
22.0	$30.0 \times 45.0 \times 57.5$	B32778Z7206+000	16.0	9.0	13.8	2.4	23.5	280
25.0	$30.0 \times 45.0 \times 57.5$	B32778Z7226K000	16.5	8.7	14.2	2.4	23.5	280
28.0	$35.0 \times 50.0 \times 57.5$	B32778Z7256+000	20.0	7.0	15.3	2.5	23.5	108
30.0	$35.0 \times 50.0 \times 57.5$	B32778Z7276+000	20.5	6.8	15.8	2.5	24.2	108
35.0	$38.0 \times 57.5 \times 57.5$	B32778Z7306+000	23.0	5.7	17.4	2.5	24.2	96
45.0	$45.0 \times 57.0 \times 57.5$	B32778Z7456+000	27.5	4.8	18.0	2.5	24.5	140

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

⁴⁾ Capacitance value measured at 1 kHz

⁵⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a $\Delta T \le 20$ °C when $\Delta ESR_{typ} \le \pm 5\%$

⁶⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)



MKP DC link



Ordering codes and packing units (lead spacing 52.5 mm, P_1 = 20.3 mm)

$C_R^{7)}$	Max. dimensions	Ordering code	I _{RMS,max} 8)	ESR _{typ}	ESL _{typ} 9)	tan δ	tan δ	Un-
	$w \times h \times l$	(composition see	70 °C	70 °C	70 °C	max.	max.	taped
		below)	10 kHz	10 kHz		1 kHz	10 kHz	pcs./
μF	mm		Α	mΩ	nH	10-3	10 ⁻³	MOQ
V _{R,85} ° _C	= 1200 V DC							
14.0	$43.0 \times 24.0 \times 57.5$	B32778Z1146+000	12.0	13.8	13.0	2.1	19.5	420
20.0	$30.0\times45.0\times57.5$	B32778Z1206+000	16.0	9.7	13.0	2.1	19.8	280
22.0	$30.0\times45.0\times57.5$	B32778Z1226+000	16.5	9.3	14.0	2.1	19.9	280
25.0	$35.0\times50.0\times57.5$	B32778Z1256+000	19.0	7.8	15.0	2.1	19.9	108
27.0	$35.0 \times 50.0 \times 57.5$	B32778Z1276K000	19.5	7.3	15.0	2.1	20.0	108
30.0	$38.0\times57.5\times57.5$	B32778Z1306+000	21.0	6.8	16.0	2.2	20.2	96
33.0	$38.0\times57.5\times57.5$	B32778Z1336+000	22.0	6.0	17.0	2.2	20.2	96

MOQ = Minimum Order Quantity, consisting of 4 packing units. Intermediate capacitance values are available on request.

Composition of ordering code

+ = Capacitance tolerance code:

 $K = \pm 10\%$

 $J = \pm 5\%$

Packing code:

⁷⁾ Capacitance value measured at 1 kHz

⁸⁾ Max. ripple current I_{RMS} at 70 °C at 10 kHz for a ΔT ≤20 °C when $\Delta ESR_{typ} \leq \pm 5\%$

⁹⁾ ESL value measured at resonance frequency (see specific graphs of Z versus frequency)





B3277*X/Y/Z


MKP DC link

Technical data

Reference standard: IEC 61071. All data given at T = 20 °C, unless otherwise specified.

ricicio standard. 120 01071. 7th data given at		o, am	000 0		ороон	ou.	
Rated temperature T _R	+85 °	С					
Operating temperature range (case)	Max.	operati	ng tem	oeratur	e, T _{op,m}	ax +	105 °C
	Uppe	r catego	ory tem	peratu	re T _{max}	+	105 °C
	Lowe	r catego	ory tem	peratu	re T _{min}	_	-40 °C
Insulation resistance R _{ins} given as time	$\tau > 10$	0000 s (after 1	min)			
constant $\tau = C_R \cdot R_{ins}$, rel. humidity $\leq 65\%$	for V _R	≥ 500	V DC n	neasur	ed at 50	00 V D	C
(minimum as-delivered values)							
DC voltage test between terminals (10 s)	1.5 · `	V_R					
Voltage test terminal to case (10 s)	2110	V AC, 5	50 Hz				
Pulse handling capability (V/μs)	I _P (A)	/ C (μF)				
V _R (V DC) at 85 °C	500	600	800	900	1000	1100	1200
Continuous operating voltage (V_{op}) at T_{op} of 85 °C	500	600	800	900	1000	1100	1200
For temperatures between 85 °C and 105 °C	1.33%	%/°C of	V _{op} der	ating c	ompare	ed to	
	V_{op} at	85 °C					
Reliability:							
Failure rate λ	10 fit	(≤1 ⋅ 1	0 ⁻⁹ h) a	t 0.5 ·	V _R , 40	°C	
Service life t _{SL}	50 000 h at V _R , 85 °C						
	For conversion to other operating conditions and temperatures, refer to chapter "Quality, 2 Reliability".						

Typical waveforms



Restrictions:

 V_R : Maximum operating peak voltage of either polarity but of a non-reversing waveform, for which the capacitor has been designed for continuous operation.





 $\hat{u}_{AC} \leq 0.2 \cdot V_{R}$

Overvoltage	Maximum duration within one day	Observation
1.1 · V _R	30% of on-load duration	System regulation
1.15 · V _R	30 min.	System regulation
$1.2 \cdot V_R$	5 min.	System regulation
$1.3 \cdot V_R$	1 min.	System regulation

NOTE 1 An overvoltage equal to $1.5 \cdot V_R$ for 30 ms is permitted 1000 times during the life of the capacitor.

The amplitudes of the overvoltages that may be tolerated without significant reduction in the life time of the capacitor depend on their duration, the number of application and the capacitor temperature.

In addition these values assume that the overvoltages may appear when the internal temperature of the capacitor is less than 0 °C but within the temperature category.

NOTE 2 The average applied voltage must not be higher than the specified voltage.

Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/μs.

Note:

The values of dV/dt provided below must not be exceeded in order to avoid damaging the capacitor.

dV/dt values

Lead spacing	27.5 mm						
Туре	B32774X						
V _R (V DC)	500	600	800	900	1000	1100	1200
dV/dt in V/μs	30	35	40	50	75	85	100
	·						
Lead spacing	37.5 mm						
Туре	B32776YZ						
V _R (V DC)	500	600	800	900	1000	1100	1200
dV/dt in V/μs	21	22	22	35	54	60	73
Lead spacing	52.5 mm						
Type	B32778Z						
V _R (V DC)	500	600	800	900	1000	1100	1200
dV/dt in V/μs	14	14	15	22	35	40	50





Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm

500 V DC




ESR versus frequency f

(typical values)

Lead spacing 27.5 mm

500 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm


600 V DC



ESR versus frequency f

(typical values)

Lead spacing 27.5 mm





B32774X

MKP DC link



Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm

800 V DC




ESR versus frequency f

(typical values)

Lead spacing 27.5 mm

800 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm


900 V DC



ESR versus frequency f

(typical values)

Lead spacing 27.5 mm







Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm

1000 V DC




ESR versus frequency f

(typical values)

Lead spacing 27.5 mm

1000 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm


1100 V DC



ESR versus frequency f

(typical values)

Lead spacing 27.5 mm





B32774X





Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 27.5 mm


1200 V DC



ESR versus frequency f

(typical values)

Lead spacing 27.5 mm







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

500 V DC




ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

500 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)


500 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)





B32776Y/Z MKP DC link




Characteristics curves

Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f (typical values)

Lead spacing 37.5 mm (2-pin version)


600 V DC



ESR versus frequency f (typical values)

Lead spacing 37.5 mm (2-pin version)


600 V DC



Impedance Z versus frequency f (typical values)

Lead spacing 37.5 mm (4-pin version)


600 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

800 V DC




ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

800 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)


800 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)





MKP DC link



Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

900 V DC




ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

900 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)


900 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

1000 V DC




ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

1000 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)


1000 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)





B32776Y/Z MKP DC link




Characteristics curves

Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f (typical values)

Lead spacing 37.5 mm (2-pin version)


1100 V DC



ESR versus frequency f (typical values)

Lead spacing 37.5 mm (2-pin version)


1100 V DC



Impedance Z versus frequency f (typical values)

Lead spacing 37.5 mm (4-pin version)


1100 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

1200 V DC




ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (2-pin version)

1200 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)


1200 V DC



ESR versus frequency f

(typical values)

Lead spacing 37.5 mm (4-pin version)





MKP DC link



Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm

500 V DC




ESR versus frequency f

(typical values)

Lead spacing 52.5 mm

500 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm


600 V DC



ESR versus frequency f

(typical values)

Lead spacing 52.5 mm







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm

800 V DC




ESR versus frequency f

(typical values)

Lead spacing 52.5 mm

800 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm


900 V DC



ESR versus frequency f

(typical values)

Lead spacing 52.5 mm





MKP DC link



Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm

1000 V DC




ESR versus frequency f

(typical values)

Lead spacing 52.5 mm

1000 V DC




Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm


1100 V DC



ESR versus frequency f

(typical values)

Lead spacing 52.5 mm







MKP DC link

Characteristics curves


Additional technical information can be found under "Design support" on www.epcos.com.

Impedance Z versus frequency f

(typical values)

Lead spacing 52.5 mm


1200 V DC



ESR versus frequency f

(typical values)

Lead spacing 52.5 mm













Characteristics curves

Permissible current I_{RMS} versus frequency f at $\leq\!70~^{\circ}\text{C}$

Lead spacing 27.5 mm

500 V DC











Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C

Lead spacing 27.5 mm

800 V DC















Characteristics curves

Permissible current I_{RMS} versus frequency f at $\leq\!70~^{\circ}\text{C}$

Lead spacing 27.5 mm

1000 V DC










Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 $^{\circ}$ C

Lead spacing 27.5 mm







MKP DC link





Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 °C)

Lead spacing 37.5 mm

500 V DC (2-pin version)









B32776Y/Z


MKP DC link


Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C)

Lead spacing 37.5 mm

600 V DC (2-pin version)









MKP DC link





Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 °C)

Lead spacing 37.5 mm

800 V DC (2-pin version)









B32776Y/Z


MKP DC link


Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C)

Lead spacing 37.5 mm

900 V DC (2-pin version)









MKP DC link





Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 °C)

Lead spacing 37.5 mm

1000 V DC (2-pin version)









B32776Y/Z


MKP DC link


Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C)

Lead spacing 37.5 mm

1100 V DC (2-pin version)









MKP DC link





Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 °C)

Lead spacing 37.5 mm

1200 V DC (2-pin version)










MKP DC link


Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C

Lead spacing 52.5 mm

500 V DC







MKP DC link





Characteristics curves

Permissible current I_{RMS} versus frequency f at $\leq\!70~^{\circ}\text{C}$

Lead spacing 52.5 mm

800 V DC










MKP DC link


Characteristics curves

Permissible current I_{RMS} versus frequency f at ≤70 °C

Lead spacing 52.5 mm

1000 V DC








MKP DC link



Characteristics curves

Permissible current I_{RMS} versus frequency f at \leq 70 $^{\circ}$ C

Lead spacing 52.5 mm








MKP DC link

Curves characteristics (I_{RMS} derating versus temperature)




Maximum I_{RMS} current as function of the ambient temperature: I_{RMS} (T_A) = $F_T \times I_{RMS}$ (70 °C)







Heat transference for self heating calculation



Box dimensions			Equivalent heat coefficient
w (mm)	h (mm)	I (mm)	G (mW/°C)
11.0	19.0	31.5	25
11.0	21.0	31.5	28
12.5	21.5	31.5	30
13.5	23.0	31.5	32
14.0	24.5	31.5	35
15.0	24.5	31.5	36
16.0	32.0	31.5	45
18.0	27.5	31.5	44
18.0	33.0	31.5	48
19.0	30.0	31.5	48
21.0	31.0	31.5	51
22.0	36.5	31.5	58
12.0	22.0	42.0	70
14.0	25.0	42.0	43
16.0	28.5	42.0	50
18.0	32.5	42.0	59
20.0	39.5	42.0	72
24.0	19.0	42.0	50
24.0	15.0	42.0	44
28.0	37.0	42.0	83
28.0	42.5	42.0	90
30.0	45.0	42.0	100
33.0	48.0	42.0	110
30.0	45.0	57.5	125
35.0	50.0	57.5	145
38.0	57.5	57.5	165

The equivalent heat coefficient "**G** (**mW**/**°C**)" is given for measuring the temperature on the lateral surface of the plastic box as figure 1 shows. By using a thermocouple and avoiding effect of radiation and convection the temperature measured during operation conditions should be a result of the dissipated power divided by the equivalent heat coefficient.





MKP DC link

Self heating by power dissipation and equivalent heat coefficient

The I_{RMS} and consequently the power dissipation must be limited during operation in order to not exceed the maximum limit of ΔT allowed for this series. ΔT_{max} given for this series is equal or lower than 15 °C at rated temperature (70 °C), for higher ambient temperatures ΔT_{max} (T) will have the same derating factor than I_{RMS} versus temperature and then an equivalent derating as per:

$$\Delta T_{\text{max}}$$
 (T) = (Factor)² × ΔT (70 °C).

For any particular I_{RMS} the ΔT may be calculated by:

$$\Delta T$$
 (°C) = P_{dis} (mW) / G(mW/°C).

Where ΔT (°C) is the difference between the temperature measured on the box (see figure 1) and the ambient temperature when capacitor is working during normal operation;

$$\Delta T$$
 (°C) = T_{op} (°C) - T_{A} (°C).

It represents the increasing of temperature provoked by the I_{RMS} during operation.

G (mW/°C) is the equivalent heat coefficient described above and P_{dis} (mW) is the dissipated power defined by: P_{dis} (mW) = ESR_{tvp} (m Ω) × I_{RMS}^2 (A_{RMS}).

Example for thermal calculation:

We will take as reference B32778Z0306K (30 μ F/1000 V DC) type for thermal calculation. Considering the following load and capacitor characteristics:

 I_{RMS} : 12 A_{RMS} at 20 kHz

T_A: 85 ^oC

 $35 \times 45 \times 57.5$ box

G (mW/ºC): 125

Then we have to find the ESR_{tvp} at 20 kHz what is approximately 8.2 m Ω .

So according to P_{dis} (mW) = ESR_{tvp} (m Ω) × I_{RMS} ² (A_{RMS})

we have the following: P_{dis} (mW) = 8.2 m $\Omega \times 12$ $A_{RMS}^2 = 1181$ mW.

And as per ΔT (°C) = P_{dis} (mW) / G (mW/°C)

we have the following: ΔT (°C) = 1181 (mW) / 125 (mW/°C) = 9.5 °C.

What is below of the ΔT_{max} (85 °C) = (Factor)² × ΔT (70 °C) = (0.7)² × 20 °C = 9.8 °C.

On the other hand we may confirm according to page 33 that max. I_{RMS} at 20 kHz at 70 °C = 17.5 A_{RMS} .

And then max I_{RMS} for 85 °C of ambient temperature is defined as follows:

$$I_{RMS}$$
 (85 °C) = Factor × I_{RMS} (70 °C) = 0.7 × 17.5 A_{RMS} = 12.3 A_{RMS} .

What confirms once again that I_{RMS} (12 A_{RMS} at 20 kHz at 100 °C) is below the max specified for such frequency and ambient temperature.








Service life

Life time expectancy – typical curve

B3277*-X/Y4/5/8/9/0/7/1

(500 V DC, 600 V DC, 800 V DC, 900 V DC, 1000 V DC, 1100 V DC, 1200 V DC)



Note:

Confidence level of 95%





MKP DC link

Testing and Standards

Test	Reference	Conditions of test		Performance requirements
Electrical para-	IEC61071:2007	Voltage between terminals, 1.5 V _R , during 10 s		Within specified limits
meters (Routine		Insulation resistance, if $V_R < 500 \text{ V}$ or 500 V	****	
test)		Capacitance, C at 1 k (room temperature)	KHz	
		Dissipation factor, tar (room temperature)	n δ at 1/10 kHz	
Robust- ness of termina-	IEC 60068-2-21:2006	Tensile strength (test Wire diameter $0.5 < d_1 \le 0.8 \text{ mm}$	Ua1) Tensile force 10 N	Capacitance and tan δ within specified limits
tions (Type test)		$0.8 < d_1 \le 1.25 \text{ mm}$	20 N	
Resis- tance to soldering heat (Type test)	tance to 60068-2-20:2008, immersion for 10 seconds soldering heat method 1A		•	$ \Delta C/C_0 \le 2\%$ $ \Delta \tan \delta \le 0.002$ Mechanical: No visible damage
Rapid change of temperature (Type test)	Rapid IEC 61071:2007 TA = lower category temperature TB = upper category temperature Five cycles, duration t = 30 min.		temperature	$\begin{split} \Delta C/C_0 &\leq 2\% \\ \Delta \tan \delta &\leq 0.002 \\ \text{Mechanical:} \\ \text{No visible damage} \end{split}$
Vibration and shocks (Type test)	IEC 61071:2007	In accordance with IEC 60068-2-6 f = 10 Hz to 55 Hz a = ±0.35 mm Test duration per axis = 10 frequency cycles (3 axes offset from each other by 90°),		Electrical: $ \Delta C/C_0 \le 0.5\%$ at 1 kHz Mechanical: No visible damage
		1 octave/min. Mounting conditions: The capacitor shall be and the body must be	e fixed by the leads	







Test	Reference	Conditions of test	Performance
			requirements
Climatic	IEC	Dry heat Tb / 16 h	No visible damage
sequence	60384-16:2005	Damp heat cyclic, 1st cycle	$ \Delta C/C_0 \leq 3\%$
(Type test)		+55 °C / 24 h / 95% 100% RH	$ \Delta \tan \delta \le 0.001$
		Cold Ta / 2 h	$R_{ins} \ge 50\%$ of initial limit
		Damp heat cyclic, 5 cycles	
		+55 °C / 24 h / 95% 100% RH	
Damp	IEC	Test Ca	No visible damage
Heat	60384-16:2005	40 °C / 93% RH / 56 days	$ \Delta C/C_0 \leq 5\%$
Steady			$ \Delta \tan \delta \le 0.005 \text{ (1kHz)}$
State			$R_{ins} \ge 50\%$ of initial limit
(Type test)			
Endur-	IEC	+85 °C / 1.3 V _R / 500 hours and	No visible damage
ance	60384-16:2005	1000 discharges at 1.4 I _R	$ \Delta C/C_0 \leq 3\%$
(Type test)			$ \Delta \tan \delta \le 0.015$
, ,,			$R_{ins} \ge 50\%$ of initial limit
			Mechanical:
			No visible damage

Mounting guidelines

1 Soldering

1.1 Solderability of leads

The solderability of terminal leads is tested to IEC 60068-2-20, test Ta, method 1.

Before a solderability test is carried out, terminals are subjected to accelerated ageing (to IEC 60068-2-2, test Ba: 4 h exposure to dry heat at 155 °C). Since the ageing temperature is far higher than the upper category temperature of the capacitors, the terminal wires should be cut off from the capacitor before the ageing procedure to prevent the solderability being impaired by the products of any capacitor decomposition that might occur.

Solder bath temperature	235 ±5 °C
Soldering time	2.0 ±0.5 s
Immersion depth	2.0 +0/-0.5 mm from capacitor body or seating plane
Evaluation criteria:	
Visual inspection	Wetting of wire surface by new solder ≥90%, free-flowing solder






MKP DC link

1.2 Resistance to soldering heat

Resistance to soldering heat is tested to IEC 60068-2-20, test Tb, method 1. Conditions:

Series		Solder bath temperature	Soldering time
MKT	boxed (except $2.5 \times 6.5 \times 7.2$ mm) coated uncoated (lead spacing >10 mm)	260 ±5 °C	10 ±1 s
MFP	anocaroa (read spaonig) is imin,		
MKP	(lead spacing >7.5 mm)		
MKT	boxed (case $2.5 \times 6.5 \times 7.2$ mm)		5 ±1 s
MKP	(lead spacing ≤7.5 mm)		<4 s
MKT	uncoated (lead spacing ≤10 mm) insulated (B32559)		recommended soldering profile for MKT uncoated (lead spacing ≤ 10 mm) and insulated (B32559)



Immersion depth	2.0 +0/-0.5 mm from capacitor body or seating plane
Shield	Heat-absorbing board, (1.5 ±0.5) mm thick, between
	capacitor body and liquid solder
Evaluation criteria:	
Visual inspection	No visible damage
$\Delta C/C_0$	2% for MKT/MKP/MFP
$\Delta O/O_0$	5% for EMI suppression capacitors
$tan \delta$	As specified in sectional specification





1.3 General notes on soldering


Permissible heat exposure loads on film capacitors are primarily characterized by the upper category temperature T_{max} . Long exposure to temperatures above this type-related temperature limit can lead to changes in the plastic dielectric and thus change irreversibly a capacitor's electrical characteristics. For short exposures (as in practical soldering processes) the heat load (and thus the possible effects on a capacitor) will also depend on other factors like:

- Pre-heating temperature and time
- Forced cooling immediately after soldering
- Terminal characteristics: diameter, length, thermal resistance, special configurations (e.g. crimping)
- Height of capacitor above solder bath
- Shadowing by neighboring components
- Additional heating due to heat dissipation by neighboring components
- Use of solder-resist coatings

The overheating associated with some of these factors can usually be reduced by suitable countermeasures. For example, if a pre-heating step cannot be avoided, an additional or reinforced cooling process may possibly have to be included.

Recommendations

As a reference, the recommended wave soldering profile for our film capacitors is as follows:



T_s: Capacitor body maximum temperature at wave soldering


T_p: Capacitor body maximum temperature at pre-heating

KMK1745-A-E





MKP DC link



Body temperature should follow the description below:

MKP capacitor

During pre-heating: T_p ≤110 °C

During soldering: T_s ≤120 °C, t_s ≤45 s

MKT capacitor

During pre-heating: T_p ≤125 °C

During soldering: T_s ≤160 °C, t_s ≤45 s

When SMD components are used together with leaded ones, the film capacitors should not pass into the SMD adhesive curing oven. The leaded components should be assembled after the SMD curing step.

Leaded film capacitors are not suitable for reflow soldering.

In order to ensure proper conditions for manual or selective soldering, the body temperature of the capacitor (T_s) must be ≤ 120 °C.

One recommended condition for manual soldering is that the tip of the soldering iron should be <360 °C and the soldering contact time should be no longer than 3 seconds.

For uncoated MKT capacitors with lead spacings ≤10 mm (B32560/B32561) the following measures are recommended:

- pre-heating to not more than 110 °C in the preheater phase
- rapid cooling after soldering

Please refer to our Film Capacitors Data Book in case more details are needed.





Cautions and warnings

- Do not exceed the upper category temperature (UCT).
- Do not apply any mechanical stress to the capacitor terminals.
- Avoid any compressive, tensile or flexural stress.
- Do not move the capacitor after it has been soldered to the PC board.
- Do not pick up the PC board by the soldered capacitor.
- Do not place the capacitor on a PC board whose PTH hole spacing differs from the specified lead spacing.
- Do not exceed the specified time or temperature limits during soldering.
- Avoid external energy inputs, such as fire or electricity.
- Avoid overload of the capacitors.
- Consult us if application is with severe temperature and humidity condition.
- There are no serviceable or repairable parts inside the capacitor. Opening the capacitor or any attempts to open or repair the capacitor will void the warranty and liability of TDK Electronics.
- Please note that the standards referred to in this publication may have been revised in the meantime.

The table below summarizes the safety instructions that must always be observed. A detailed description can be found in the relevant sections of the chapters "General technical information" and "Mounting guidelines".

Topic	Safety information	Reference chapter "General technical information"
Storage conditions	Make sure that capacitors are stored within the specified range of time, temperature and humidity	4.5 "Storage conditions"
	conditions.	Storage containents
Flammability	Avoid external energy, such as fire or electricity (passive flammability), avoid overload of the capacitors (active flammability) and consider the flammability of materials.	5.3 "Flammability"
Resistance to vibration	Do not exceed the tested ability to withstand vibration. The capacitors are tested to IEC 60068-2-6:2007. TDK Electronics offers film capacitors specially designed for operation under more severe vibration regimes such as those found in automotive applications. Consult our catalog "Film Capacitors for Automotive Electronics".	5.2 "Resistance to vibration"





MKP DC link

Topic	Safety information	Reference chapter "Mounting guidelines"
Soldering	Do not exceed the specified time or temperature limits during soldering.	1 "Soldering"
Cleaning	Use only suitable solvents for cleaning capacitors.	2 "Cleaning"
Embedding of capacitors in finished assemblies	When embedding finished circuit assemblies in plastic resins, chemical and thermal influences must be taken into account. Caution: Consult us first, if you also wish to embed other uncoated component types!	3 "Embedding of capacitors in finished assemblies"

Display of ordering codes for TDK Electronics products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications, on the company website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.

Detailed information can be found on the Internet under www.tdk-electronics.tdk.com/orderingcodes.







Symbols and terms

Symbol	English	German
α	Heat transfer coefficient	Wärmeübergangszahl
α_{C}	Temperature coefficient of capacitance	Temperaturkoeffizient der Kapazität
Α	Capacitor surface area	Kondensatoroberfläche
β_{C}	Humidity coefficient of capacitance	Feuchtekoeffizient der Kapazität
С	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
ΔC	Absolute capacitance change	Absolute Kapazitätsänderung
ΔC/C	Relative capacitance change (relative deviation of actual value)	Relative Kapazitätsänderung (relative Abweichung vom Ist-Wert)
$\Delta C/C_R$	Capacitance tolerance (relative deviation from rated capacitance)	Kapazitätstoleranz (relative Abweichung vom Nennwert)
dt	Time differential	Differentielle Zeit
Δt	Time interval	Zeitintervall
ΔΤ	Absolute temperature change (self-heating)	Absolute Temperaturänderung (Selbsterwärmung)
∆tan δ	Absolute change of dissipation factor	Absolute Änderung des Verlustfaktors
ΔV	Absolute voltage change	Absolute Spannungsänderung
dV/dt	Time differential of voltage function (rate of voltage rise)	Differentielle Spannungsänderung (Spannungsflankensteilheit)
$\Delta V/\Delta t$	Voltage change per time interval	Spannungsänderung pro Zeitintervall
E	Activation energy for diffusion	Aktivierungsenergie zur Diffusion
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatz-Serienwiderstand
f	Frequency	Frequenz
f ₁	Frequency limit for reducing permissible AC voltage due to thermal limits	Grenzfrequenz für thermisch bedingte Reduzierung der zulässigen Wechselspannung
f_2	Frequency limit for reducing permissible AC voltage due to current limit	Grenzfrequenz für strombedingte Reduzierung der zulässigen Wechselspannung
f _r	Resonant frequency	Resonanzfrequenz
$F_{\mathtt{D}}$	Thermal acceleration factor for diffusion	Therm. Beschleunigungsfaktor zur Diffusion
F _T	Derating factor	Deratingfaktor
i	Current (peak)	Stromspitze
I _C	Category current (max. continuous current)	Kategoriestrom (max. Dauerstrom)





MKP DC link

Symbol	English	German
I _{RMS}	(Sinusoidal) alternating current,	(Sinusförmiger) Wechselstrom
	root-mean-square value	
i _z	Capacitance drift	Inkonstanz der Kapazität
k_0	Pulse characteristic	Impulskennwert
L _S	Series inductance	Serieninduktivität
λ	Failure rate	Ausfallrate
λ_0	Constant failure rate during useful	Konstante Ausfallrate in der
	service life	Nutzungsphase
λ_{test}	Failure rate, determined by tests	Experimentell ermittelte Ausfallrate
P_{diss}	Dissipated power	Abgegebene Verlustleistung
P_{gen}	Generated power	Erzeugte Verlustleistung
Q	Heat energy	Wärmeenergie
ρ	Density of water vapor in air	Dichte von Wasserdampf in Luft
R	Universal molar constant for gases	Allg. Molarkonstante für Gas
R	Ohmic resistance of discharge circuit	Ohmscher Widerstand des
		Entladekreises
R_{i}	Internal resistance	Innenwiderstand
R _{ins}	Insulation resistance	Isolationswiderstand
R_P	Parallel resistance	Parallelwiderstand
R_s	Series resistance	Serienwiderstand
S	severity (humidity test)	Schärfegrad (Feuchtetest)
t	Time	Zeit
Т	Temperature	Temperatur
τ	Time constant	Zeitkonstante
tan δ	Dissipation factor	Verlustfaktor
$tan \; \delta_{\scriptscriptstyle D}$	Dielectric component of dissipation factor	Dielektrischer Anteil des Verlustfaktors
tan δ_P	Parallel component of dissipation factor	Parallelanteil des Verlfustfaktors
tan δ_{s}	Series component of dissipation factor	Serienanteil des Verlustfaktors
T _A	Temperature of the air surrounding the component	Temperatur der Luft, die das Bauteil umgibt
T_{max}	Upper category temperature	Obere Kategorietemperatur
T _{min}	Lower category temperature	Untere Kategorietemperatur
t _{OL}	Operating life at operating temperature	Betriebszeit bei Betriebstemperatur und
	and voltage	-spannung
T _{op}	Operating temperature, $T_A + \Delta T$	Beriebstemperatur, $T_A + \Delta T$
T _R	Rated temperature	Nenntemperatur
T _{ref}	Reference temperature	Referenztemperatur
t _{SL}	Reference service life	Referenz-Lebensdauer





MKP DC link



Symbol	English	German
V_{AC}	AC voltage	Wechselspannung
V_{C}	Category voltage	Kategoriespannung
$V_{\text{C,RMS}}$	Category AC voltage	(Sinusförmige)
		Kategorie-Wechselspannung
V_{CD}	Corona-discharge onset voltage	Teilentlade-Einsatzspannung
V_{ch}	Charging voltage	Ladespannung
V_{DC}	DC voltage	Gleichspannung
V_{FB}	Fly-back capacitor voltage	Spannung (Flyback)
V_{i}	Input voltage	Eingangsspannung
V_{o}	Output voltage	Ausgangssspannung
V_{op}	Operating voltage	Betriebsspannung
V_p	Peak pulse voltage	Impuls-Spitzenspannung
V_{pp}	Peak-to-peak voltage Impedance	Spannungshub
V_R	Rated voltage	Nennspannung
Ŷ _R	Amplitude of rated AC voltage	Amplitude der Nenn-Wechselspannung
V_{RMS}	(Sinusoidal) alternating voltage,	(Sinusförmige) Wechselspannung
	root-mean-square value	
V_{SC}	S-correction voltage	Spannung bei Anwendung "S-correction"
V_{sn}	Snubber capacitor voltage	Spannung bei Anwendung
		"Beschaltung"
Z	Impedance	Scheinwiderstand
е	Lead spacing	Rastermaß



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to our General Terms and Conditions of Supply.



Important notes

- 7. Our manufacturing sites serving the automotive business apply the IATF 16949 standard. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that only requirements mutually agreed upon can and will be implemented in our Quality Management System. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.
- 8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10