F98 Series Resin-Molded Chip, High CV Undertab





CASE DIMENSIONS: millimeters (inches)

FEATURES

- Compliant to the RoHS2 directive 2011/65/EU
- SMD face down design
- Small and low profile

APPLICATIONS


- Smartphone
- Mobile phone
- Wireless module
- Hearing aid





Code EIA Code EIA Metric W₁ L W_2 н S₁ S₂ **1.60** +0.20 -0.10 0.85 +0.20 0.65±0.10 0.80±0.10*3 0.50±0.10 0.60±0.10 Μ 0603 1608-09 (0.063 +0.008) (0.033 +0.008) (0.026 ± 0.004) (0.031 ± 0.004) (0.020 ± 0.004) (0.024 ± 0.004) 2.00 +0.20 1.25 +0.20 -0.10 0.90±0.10 0.80±0.10 0.50±0.10 1.00±0.10 s 0805 2012-09 (0.079 +0.008) (0.049 +0.008) (0.035±0.004) (0.031 ± 0.004) (0.020±0.004) (0.039±0.004) 1.10±0.05 0.60 ± 0.05 0.35 ± 0.05 0.55±0.05 0.30 ± 0.05 0.50 ± 0.05 U 0402 1106-06 (0.043±0.002) (0.024 ± 0.002) (0.014 ± 0.002) (0.022 ± 0.002) (0.012 ± 0.002) (0.020 ± 0.002)

*3 F980J107MMAAXE: 1.0mm Max.



TECHNICAL SPECIFICATIONS

Category Temperature Range:	-55 to +125°C
Rated Temperature:	+85°C
Capacitance Tolerance:	±20% at 120Hz
Dissipation Factor:	Refer to next page
ESR 100kHz:	Refer to next page
Leakage Current:	Refer to next page
	Provided that:
	After 5 minute's application of rated voltage, leakage current at 85°C
	10 times or less than 20°C specified value.
	After 5 minute's application of rated voltage, leakage current at 125°C
	12.5 times or less than 20°C specified value.





Resin-Molded Chip, High CV Undertab

CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capac	citance	Rated Voltage						*Cap		
μF	Code	2.5 (0e)	4V (0G)	6.3V (0J)	10V (1A)	16V (1C)	20V (1D)	25V (1E)	35V (1V)	Code
0.47	474					U				N
1.0	105					М	М	М	S	A
2.2	225				M/U	М				J
4.7	475		U	M/U	M/U**	М				S
10	106		U	M/U**	М	S				а
15	156		U							е
22	226		M/U**	M	M**/S					J
33	336		М	M	M**/S					n
47	476	М	М	S	S					S
68	686		M/S							W
100	107		M/S	M*4/S						A
220	227		S							J

Released ratings

*4 Rated temperature 60°C and H dimension 1.0mm Max only. Please contact AVX when you need detail spec.

**Rated temperature 60°C only. Please contact AVX when you need detail spec.

RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	*2 DCL (μA)	DF @ 120Hz (%)	ESR @ 100kHz (Ω)	*1 ∆C/C (%)	MSL
2.5 Volt								
F980E476MMA	М	47	2.5	1.2	30	4	±30	3
4 Volt								
F980G475MUA	U	4.7	4	0.5	20	20	±30	3
F980G106MUA	U	10	4	0.8	25	20	±30	3
F980G156MUA	U	15	4	9.0	40	25	±30	3
F980G226MMA	Μ	22	4	0.9	15	7.5	±30	3
F980G226MUALZT	U	22	4	25.0	40	20	±30	3
F980G336MMA	Μ	33	4	1.3	30	4	±30	3
F980G476MMA	М	47	4	1.9	40	8	±30	3
F980G686MMA	Μ	68	4	27.2	50	10	±30	3
F980G686MSA	S	68	4	2.7	30	4	±30	3
F980G107MMA	Μ	100	4	80.0	60	10	±30	3
F980G107MSA	S	100	4	4.0	35	4	±30	3
F980G227MSA	S	220	4	132	80	5	±30	3
6.3 Volt								
F980J475MMA	М	4.7	6.3	0.5	20	7.5	±30	3
F980J475MUA	U	4.7	6.3	0.6	20	20	±30	3
F980J106MMA	М	10	6.3	0.6	8	6	±30	3
F980J106MUALZT	U	10	6.3	6.3	30	30	±30	3
F980J226MMA	М	22	6.3	1.4	20	6	±30	3
F980J336MMA	Μ	33	6.3	4.2	35	8	±30	3
F980J476MMA	Μ	47	6.3	29.6	45	10	±30	3
F980J476MSA	S	47	6.3	3.0	25	6	±30	3
F980J107MMAAXE	Μ	100	6.3	126	80	10	±30	3
F980J107MSA	S	100	6.3	63.0	50	8	±30	3

Rated *2 DF ESR *1 Case Capacitance AVX MSL DCL @ 120Hz ∆C/C Voltage @ 100kHz Part No. Size (µF) (μA) (Ω) (V) (%) (%) 10 Volt ±30 F981A225MMA Μ 2.2 10 0.5 6 7.5 F981A225MUA U 2.2 10 0.5 15 15 ±30 F981A475MMA М 4. 10 0.5 6 6 ±30 25 20 30 F981A475MUALZT U 4.7 10 4.7 25 ±30 F981A106MMA F981A226MMALZT 1.0 Μ 10 10 ±30 7.5 M 10 11.0 22 ±30 8 F981A226MSA S 22 10 2.2 20 4 ±30 F981A336MMALZT Μ 10 33.0 8 ±30 45 3 S S 33 3.3 30 F981A336MSA 10 ±30 6 F981A476MSA 47 10 9.4 35 5 +3016 Volt F981C474MUA U 0.47 0.5 25 ±20 <u>±30</u> F981C105MMA Μ 10 16 0.5 6 0.5 F981C225MMA М 2.2 16 6 10 ±30 3 F981C475MMA F981C106MSA M S 12 18 ±30 ±30 4.7 16 0.8 12 16 1.6 4 2 20 Volt F981D105MMA M 0.5 6 10 ±30 3 20 25 Volt F981E105MMA M 0.5 10 ±30 8 3 - 2 35 Volt F981V105MSA S 1 35 0.7 20 8 ±30 3

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

We can consider the type of compliance to AEC-Q200.

are being designed in your application.

Please contact to your local AVX sales office when these series

*2: Leakage Current

After 5 minute's application of rated voltage, leakage current at 20°C.



F98 Series

Resin-Molded Chip, High CV Undertab

QUALIFICATION TABLE

TEST	F98 series (Temperature range -55°C to +125°C)							
IESI	Condition							
Damp Heat	At 40°C, 90 to 95% R.H., 500 hours (No voltage applied) Capacitance Change							
(Steady State)	Dissipation Factor							
Temperature Cycles	-55°C / +125°C, 30 minutes each, 5 cycles Capacitance Change							
Resistance to Soldering Heat	10 seconds reflow at 260°C, 5 seconds immersion at 260°C. Capacitance Change							
Surge	After application of surge in series with a 1kΩ resistor at the rate of 30 seconds ON, 30 seconds OFF, for 1000 successive test cycles at 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change							
Endurance	After 1000 hours' application of rated voltage in series with a 3Ω resistor at 85°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change							
Shear Test	After applying the pressure load of 5N for 10±1 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode.							
Terminal Strength	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of substrate so that the substrate may bend by 1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.							




F98 Series




Resin-Molded Chip, High CV Undertab

AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP



Five Capacitor Construction Styles



SERIES LINE UP: CONVENTIONAL SMD MnO₂

