# A798 High Humidity and High Temperature Polymer Aluminum



#### **Overview**

The KEMET A798 Aluminum Organic Capacitor (AO-CAP) is a solid state aluminum capacitor. The cathode is a conductive organic polymer, which results in very low ESR and improved capacitance retention at high frequency. AO-CAPs may be operated at steady state voltages up to 100% of rated voltage without the need to de-rate.


Since there is no liquid electrolyte, the A798 offers long operational lifetimes, low ESR, and high operational temperatures. The inherent low ESR renders the A798 suitable for high ripple current handling. The small

package size, high ripple current capability, high operating temperature, low parasistics, and capacitance stability over life span makes the A798 ideal for demand applications.

The A798 High Humidity and High Temperature Aluminium Polymer capacitors deliver higher capacitance and ESR stability under harsh environmental conditions. Enhancements to the design and selected material upgrades were introduced to deliver 1,000 hours at 85°C/85% RH rated voltage and 125°C Endurance Life and Storage.

#### **Benefits**

- ESR: 9 mΩ
- · Polymer cathode technology
- · High frequency capacitance retention
- · Non-ignition failure mode
- 100% accelerated steady state aging
- 100% surge current tested
- · Volumetric efficiency
- Self-healing mechanism
- · EIA standard case sizes



## **Applications**

Typical applications include DC/DC converters, notebook PCs, telecommunications, displays, and industrial applications with harsh humidity and temperature requirements.

## **Environmental Compliance**

- RoHS compliant (6/6) according to Directive 2002/95/EC when ordered with 100% Sn solder.
- · Halogen-free
- Epoxy compliant with UL 94 V-0
- Molded Epoxy complies for outgassing testing under ASTM E 595.



#### K-SIM

For a detailed analysis of specific part numbers, please visit ksim.kemet.com to access KEMET's K-SIM software. KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels.

## **Ordering Information**

A	798	D	477	M	002	A	Т	E009	
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	ESR	Packaging (C-Spec)
A = Aluminum	798 = High Humidity/ High Temperature Aluminum Polymer	D	First two digits represent significant figures. Third digit specifies number of zeros.		002 = 2 2R5 = 2.5	A = N/A	T = 100% Matte Tin (Sn)-plated	E = ESR Last three digits specify ESR in mΩ (009 = 9 mΩ)	Blank = 7" Reel 7280 = 13" Reel

#### **Performance Characteristics**

ltem	Performance Characteristics
Operating Temperature	-55°C to 125°C
Rated Capacitance Range	470 μF at 120 Hz/25°C
Capacitance Tolerance	M Tolerance (20%)
Rated Voltage Range	2 - 2.5 V
DF (120 Hz)	6%
ESR (100 kHz)	Refer to Part Number Electrical Specification Table
Leakage Current	$ \leq 2.5 \text{ V Rating:} \leq 0.1 \text{ CV } (\mu\text{A}) \text{ at rated voltage after 5 minutes} $ If there is any concern about leakage current, please perform pre-conditioning to the part following below conditions: $ \text{ Temperature: } 105^{\circ}\text{C maximum} $ $ \text{ Voltage: Rated Voltage } $ $ \text{ Series Resistor: } 1,000 \Omega $ $ \text{ Charge Time: 1 hour minimum} $ $ \text{ Measuring: Discharge the capacitor(s), store them for 4 to 24 hours at room temperature and RH } \leq 60\% $



# Qualification


Test	Condition			Characteristics				
						)		
Endurance Endurance	125°C at rotad valtage 1 000 bears		DF	≤ initial lim	≤ initial limit			
Endurance	125°C at rated voltage, 1,000 hours		DCL	Within 1.25	x initial limit			
			ESR	Within 2.0	x initial limit			
			Δ C/C	Within ±20°	% of initial value	9		
Ctorono Life	105°0 at 0 Valta 1 000 haves		DF	Within initia	al limits			
Storage Life	125°C at 0 Volts, 1,000 hours		DCL	Within 1.25	x initial limit			
			ESR	Within 2.0	x initial limit			
			Δ C/C	Within −20/+70% of initial value				
I I	05°0 05% DIL lead 1000 baura	DF	Within 2.0 x initial limit					
Humidity	85°C, 85% RH, load, 1,000 hours	DCL	Within 5.0	Within 5.0 x initial limit				
			ESR	Within 2.0 x initial limit				
			+25°C	-55°C	+85°C	+125°C		
Town anatoma Otabilito	Extreme temperature exposure at a succession of continuous steps at -55°C, +25°C, +85°C, +125°C	Δ C/C	IL*1	±15%	±15%	±20%		
Temperature Stability		DF	IL	IL	1.2 x IL	1.5 x IL		
		DCL	IL	N/A	10 x IL	10 x IL		
			Δ C/C	Within ±20°	Within ±20% of initial value			
Curre Veltere	125°C, 1.32 x rated voltage, 33 Ω resistance,	125°C. 1.32 x rated voltage. 33 Ω resistance.						
Surge Voltage	1,000 cycles		DCL	Within initial limits				
			ESR	Within initial limits				
	MIL-STD-202, Method 213, Condition I, 100	G neak	Δ C/C	Within ±109	% of initial value	!		
Mechanical Shock/ Vibration	MIL-STD-202, Method 204, Condition D,	DF	Within initial limits					
Y ISTUTION	10 Hz to 2,000 Hz, 20 G peak		DCL	Within initial limits				

<sup>\*1</sup> IL = Initial Limit




#### **Electrical Characteristics**

ESR vs. Frequency




#### Capacitance vs. Frequency



# **Dimensions - Millimeters (Inches)**

Metric will govern



<sup>\*</sup>Glue pad shape is at KEMET's option

Cas	e Size		(	Component	Typical Weight		
KEMET	EIA	L	W	Н	F ±0.1 ±(0.004)	S ±0.3 ±(0.012)	(mg)
D	7343-31	7.3±0.3 (0.287±0.012)	4.3±0.3 (0.169±0.012)	2.8±0.3 (0.110±0.012)	2.4 (0.094)	1.3 (0.051)	196.58

Notes: (Ref) - Dimensions provided for reference only.



## **Table 1 - Ratings & Part Number Reference**

Rated Voltage	Rated Capacitance	Case Code/ Case Size	KEMET Part Number	DC Leakage	DF	ESR	Maximum Allowable Ripple Current	Maximum Allowable Ripple Current	Maximum Allowable Ripple Current	MSL	Maximum Operating Temp.
(V) at 125°C	μF	KEMET/EIA		µA at +25°C Maximum/ 5 Minutes	% at +25°C 120 Hz Maximum	100 kHz	(mA 85°C 100 kHz)	(mA 105°C 100 kHz)	(mA 125°C 100 kHz)	Reflow Temp ≤ 260°C	°C
2 2.5	470 470	D/7343-31 D/7343-31	A798D477M002ATE009 A798D477M2R5ATE009	94 118	6 6	9 q	5,270 5.270	3,690 3.690	1,320 1.320	3	125 125
Rated Voltage	Rated Capacitance	Case Code/ Case Size	KEMET Part Number	DC Leakage	DF	ESR	Ripple Current (mA 85°C)	Ripple Current (mA 105°C)	Ripple Current (mA 125°C)	MSL	Maximum Operating Temp.

# **Derating Guidelines**

Voltage Rating	Rated Voltage	Maximum Recommended Application Voltage
	-55°C t	o 125°C
2 - 25 V	V <sub>R</sub>	$V_{_{\mathrm{R}}}$

 $V_R$  = Rated Voltage



#### **Ripple Current/Ripple Voltage**

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria

- 1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.
- 2. The negative peak AC voltage, in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits

Power capability is determined based on a 20°C temperature rise. A higher temperature rise and therefore higher power capability is allowable as long as the ambient temperature, plus, temperature rise due to ripple current, does not exceed the rated temperature of the part.

The maximum power dissipation by case size can be determined using the below table.

KEMET Series and Case Code	EIA Case Code	Maximum Power Dissipation (Pmax) mWatts at 25°C with +20°C Rise
A700D	7343-31	250

Using the Pmax of the device, the maximum allowable rms ripple current or voltage may be determined.

 $I(max) = \sqrt{Pmax/R}$  $E(max) = Z \sqrt{Pmax/R}$ 

I = rms ripple current (amperes)

E = rms ripple voltage (volts)

Pmax = maximum power dissipation(watts)

R = ESR at specified frequency (ohms)

Z = Impedance at specified frequency (Ohms)

Refer to part number listings for permittable Arms limits.

· ·	Temperature Compensation Multipliers for Maximum Ripple Current								
T ≤ 85°C									
1.00 0.70 0.25									

*T = Environmental Temperature* 



#### **Reverse Voltage**

Polymer aluminum capacitors are polar devices and may be permanently damaged or destroyed if connected in the wrong polarity. These devices will withstand a certain degree of transient voltage reversal for short periods as shown in the below table. Please note that these parts may not be operated continuously in reverse, even within these limits.

Temperature	Permissible Transient Reverse Voltage
25°C	60% of Rated Voltage
55°C	50% of Rated Voltage
85°C	40% of Rated Voltage
125°C	30% of Rated Voltage


#### **Table 2 - Land Dimensions/Courtyard**

KEMET	Metric Size Code	Density Level A: Maximum (Most) Land Protrusion (mm)			Density Level B: Median (Nominal) Land Protrusion (mm)				Density Level C: Minimum (Least) Land Protrusion (mm)							
Case	EIA	W	L	S	<b>V</b> 1	V2	W	L	S	<b>V</b> 1	V2	W	L	S	<b>V</b> 1	V2
D	7343-31	2.55	2.77	3.67	10.22	5.60	2.43	2.37	3.87	9.12	5.10	2.33	1.99	4.03	8.26	4.84

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC standard 7351 (IPC-7351).

<sup>&</sup>lt;sup>2</sup> Land pattern geometry is too small for silkscreen outline.



<sup>&</sup>lt;sup>1</sup> Height of these chips may create problems in wave soldering.



#### **Soldering Process**

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR, or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.


Please note that although the X/7343-43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.

Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurs, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

<b>Profile Feature</b>	SnPb Assembly	Pb-Free Assembly
Preheat/Soak		
Temperature Minimum (T <sub>our</sub> )	100°C	150°C
Temperature Maximum (T)	150°C	200°C
Time $(t_s)$ from $T_{smin}$ to $T_{smax}$	60 - 120 seconds	60 – 120 seconds
Ramp-up Rate $(T_L \text{ to } T_P)$	3°C/seconds maximum	3°C/seconds maximum
Liquidous Temperature $(T_L)$	183°C	217°C
Time Above Liquidous (t <sub>L</sub> )	60 - 150 seconds	60 - 150 seconds
Peak Temperature (T <sub>P</sub> )	220°C* 235°C**	250°C* 260°C**
Time within 5°C of Maximum Peak Temperature (t <sub>a</sub> )	20 seconds maximum	30 seconds maximum
Ramp-down Rate $(T_p \text{ to } T_L)$	6°C/seconds maximum	6°C/seconds maximum
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum

Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow.

<sup>\*\*</sup> For Case Size height ≤ 2.5 mm



#### **Storage**

All AO-CAP Series are shipped in moisture barrier bags (MBBs) with desiccant and humidity indicator card (HIC). These parts are classified as MSL3 (Moisture Sensitivity Level 3) per IPC/JEDEC J-STD-020 and packaged per IPC/JEDEC J-STD-033. MSL3 specifies a floor time of 168H at 30°C maximum temperature and 60% relative humidity. Unused capacitors should be sealed in a MBB with fresh desiccant.


The calculated shelf life in a sealed bag would be 12 months from a bag seal date in a storage environment of < 40°C and humidity < 90% RH. It should be 24 months from a bag seal date in a storage environment of < 30°C and humidity < 70% RH.

If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure.


<sup>\*</sup> For Case Size height > 2.5 mm



#### Construction



# **Capacitor Marking**




\* 103 = 3<sup>rd</sup> week of 2021

Date Code *								
1st digit = Last number of Year	8 = 2018							
	9 = 2019							
	0 = 2020							
	1 = 2021							
2 <sup>nd</sup> and 3 <sup>rd</sup> digit = Week of the Year	01 = 1 <sup>st</sup> week of the Year to $52 = 52$ <sup>nd</sup> week of the Year							



#### **Tape & Reel Packaging Information**

KEMET's molded chip capacitor families are packaged in 8 and 12 mm plastic tape on 7" and 13" reels in accordance with *EIA Standard 481*: Embossed Carrier Taping of Surface Mount Components for Automatic Handling. This packaging system is compatible with all tape-fed automatic pick-and-place systems.




**Table 3 - Packaging Quantity** 

Case Code		Tape Width (mm)	7" Reel*	13" Reel*	
KEMET	EIA				
D	7343-31	12	500	2,500	

<sup>\*</sup> No C-Spec required for 7" reel packaging. C-7280 required for 13" reel packaging.



#### Figure 1 – Embossed (Plastic) Carrier Tape Dimensions



**Table 4 - Embossed (Plastic) Carrier Tape Dimensions** 

Metric will govern

Constant Dimensions — Millimeters (Inches)									
Tape Size	D <sub>0</sub>	D <sub>1</sub> Minimum Note 1	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	R Reference Note 2	S <sub>1</sub> Minimum Note 3	T Maximum	T <sub>1</sub> Maximum
8 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.0 (0.039)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	25.0 (0.984)	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)
12 mm		1.5 (0.059)				30 (1.181)			

Variable Dimensions — Millimeters (Inches)								
Tape Size	Pitch	B <sub>1</sub> Maximum Note 4	E <sub>2</sub> Minimum	F	P <sub>1</sub>	T <sub>2</sub> Maximum	W Maximum	A <sub>0</sub> , B <sub>0</sub> & K <sub>0</sub>
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	2.0 ±0.05 or 4.0 ±0.10 (0.079 ±0.002 or 0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)	
12 mm	Single (4 mm) and Double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	2.0 ±0.05 (0.079 ±0.002) or 4.0 ±0.10 (0.157 ±0.004) or 8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Note 5

- 1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.
- 2. The tape, with or without components, shall pass around R without damage (see Figure 4).
- 3. If S<sub>1</sub> < 1.0 mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481–D, paragraph 4.3, section b).
- 4.  $B_1$  dimension is a reference dimension for tape feeder clearance only.
- 5. The cavity defined by  $A_{o}$ ,  $B_{o}$  and  $K_{o}$  shall surround the component with sufficient clearance that:
  - (a) the component does not protrude above the top surface of the carrier tape.
  - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
  - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes (see Figure 2).
  - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 mm and 12 mm wide tape (see Figure 3).
  - (e) see Addendum in EIA Standard 481-D for standards relating to more precise taping requirements.



#### **Packaging Information Performance Notes**

1. Cover tape break force: 1.0 kg minimum.


2. Cover tape peel strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength		
8 mm	0.1 to 1.0 newton (10 to 100 gf)		
12 mm	0.1 to 1.3 newton (10 to 130 gf)		

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

**3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.

#### Figure 2 - Maximum Component Rotation






Figure 3 – Maximum Lateral Movement




Figure 4 - Bending Radius







Figure 5 - Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.


**Table 5 - Reel Dimensions** 

Metric will govern


Constant Dimensions — Millimeters (Inches)									
Tape Size	A	B Minimum	С	D Minimum					
8 mm	178 ±0.20 (7.008 ±0.008)			20.2 (0.795)					
12 mm	or 330 ±0.20 (13.000 ±0.008)	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)						
	Variable Dimensions — Millimeters (Inches)								
Tape Size	N Minimum	W <sub>1</sub>	W <sub>2</sub> Maximum	W <sub>3</sub>					
8 mm	50	8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)	Shall accommodate tape					
12 mm	(1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	width without interference					



## Figure 6 - Tape Leader & Trailer Dimensions



## Figure 7 - Maximum Camber





#### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.