




**1821**  
**STRAIGHT MALE BSP**  
**EQUAL/UNEQUAL ADAPTOR**  
**BSPT/NPT**

1821

Specifications

<b>maximum working pressure</b>	<b>bar</b> 150	<b>MPa</b> 15,0	<b>psi</b> 2176
<b>working temperature</b>	<b>°C</b> <b>(Celsius)</b> From -20 to 180	<b>F</b> <b>(Fahrenheit)</b> From -4 to 356	<b>K</b> <b>(Kelvin)</b> From 253 to 453
<b>body</b>	stainless steel 316L		





**1821**  
**STRAIGHT MALE BSP**  
**EQUAL/UNEQUAL ADAPTOR**  
**BSPT/NPT**

1821

Dimensions

convert weight : kg | oz  
 convert dimensions : mm | inch

		C	C1	C2	F (mm)	L (mm)	 (kg)
1821 10 10			R1/8	R1/8	12,0	19,0	0,008
1821 11 11		NPT1/8			12,0	23,0	0,011
1821 13 10			R1/4	R1/8	14,0	23,5	0,015
1821 13 13			R1/4	R1/4	14,0	27,0	0,019
1821 14 14		NPT1/4			14,0	32,0	0,023
1821 17 13			R3/8	R1/4	17,0	27,5	0,024
1821 17 17			R3/8	R3/8	17,0	28,0	0,024
1821 18 18		NPT3/8			19,0	33,0	0,031
1821 21 17			R1/2	R3/8	22,0	32,5	0,042
1821 21 21			R1/2	R1/2	22,0	36,0	0,048
1821 22 22		NPT1/2			22,0	42,0	0,056
1821 27 21			R3/4	R1/2	27,0	42,0	0,000
1821 27 27			R3/4	R3/4	27,0	42,0	0,000
1821 28 28		R3/4			27,0	40,0	0,000
1821 34 27			R1	R3/4	22,0	48,0	0,000
1821 34 34			R1	R1	36,0	46,0	0,000
1821 35 35		R1			36,0	46,0	0,000