
KEMET Part Number: C0603C102K3RACTU

(C0603C102K3RAC7867, C0603C102K3RACTR, 0603C102K3RACTU)



Ceramic, Commercial Grade, KEMET, Commercial-(CxxxxC), 1000 pF, 10%, 25 V, 0603, X7R, SMD, MLCC, Temperature Stable, Class II



| Dimensions | | |
|------------|------------------|--|
| L | 1.6mm +/-0.15mm | |
| W | 0.8mm +/-0.15mm | |
| Т | 0.8mm +/-0.07mm | |
| S | 0.7mm MIN | |
| В | 0.35mm +/-0.15mm | |

| Packaging Specifications | | |
|--------------------------|------------------------|--|
| Packaging: | T&R, 180mm, Paper Tape | |
| Packaging Quantity: | 4000 | |

| General Information | |
|---------------------|--|
| Style: | SMD Chip |
| Supplier: | KEMET |
| Series: | Commercial-(CxxxxC) |
| Chip Size: | 0603 |
| Description: | SMD, MLCC, Temperature Stable, Class II |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 48 hours |

| Specifications | | |
|--------------------------|---------------------|--|
| Capacitance: | 1000 pF | |
| Capacitance Tolerance: | 10% | |
| Voltage DC: | 25 VDC | |
| Temperature Range: | -55/+125C | |
| Temperature Coefficient: | X7R | |
| Dissipation Factor: | 3.5% | |
| Aging Rate: | 3% Loss/Decade Hour | |
| Dielectric Strength: | 62.5 V | |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

