BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD



ATS Part#:

ATS-50190P-C1-R0

Description:

19.00 x 19.00 x 17.50 mm BGA Heat Sink - High Performance maxiFLOW/maxiGRIP-STD

Heat Sink Type: maxiFLOW Heat Sink Attachment: maxiGRIP Equivalent Part Number: ATS-50190P-C2-R0 Discontinued

*Image above is for illustration purpose only.

Features & Benefits

- maxiFLOW[™] design features a low profile, spread fin array that maximizes surface area for more effective convection (air) cooling
- maxiGRIP™ attachment applies steady, even pressure to the component and does not require holes in the PCB
- Meets Telcordia GR-63-Core Office Vibration; ETSI 300 019 Transportation Vibration; and MIL-STD-810 Shock and Unpackaged Drop Testing standards
- Comes preassembled with high performance, phase changing, thermal interface material .
- Designed for standard height components from 3 to 4.5mm .

Thermal Performance

AIR VELOCITY		@200 LFM 1.0 M/S	@300 LFM 1.5 M/S	@400 LFM 2.0 M/S	@500 LFM 2.5 M/S	@600 LFM 3.0 M/S	@700 LFM 3.5 M/S	@800 LFM 4.0 M/S
THERMAL RESISTANCE	Unducted Flow	7.7 °C/W	6.3 °C/W	5.6 °C/W	5 °C/W	4.6 °C/W	4.3 °C/W	4 °C/W
	Ducted Flow	6.4	N/A	N/A	N/A	N/A	N/A	N/A

Product Detail

Schematic Image	Dimension A	Dimension B	Dimension C	Dimension D	ТІМ	Finish
	19.00 mm	19.00 mm	17.50 mm	34.7 mm	T766	BLUE-ANODIZED
Image above is for illustration purpose only.	ffective 12 rmance n	nterface material				

For more information, to find a distributor or to place an order, please contact us at 781-769-2800 (North America), sales@qats.com or www.qats.com.



© 2013 Advanced Thermal Solutions, Inc. | 89-27 Access Road | Norwood MA | 02062 | USA

Rev - 011018

