

74V1T04


SINGLE INVERTER

- HIGH SPEED: t_{PD} = 4.7ns (TYP.) at V_{CC} = 5V
- LOW POWER DISSIPATION: I_{CC} = 1μA(MAX.) at T_A=25°C
- COMPATIBLE WITH TTL OUTPUTS: V_{IH} = 2V (MIN), V_{IL} = 0.8V (MAX)
- POWER DOWN PROTECTION ON INPUT
- SYMMETRICAL OUTPUT IMPEDANCE: |I_{OH}| = I_{OL} = 8mA (MIN) at V_{CC} = 4.5V
- BALANCED PROPAGATION DELAYS: t_{PLH} ≅ t_{PHL}
- OPERATING VOLTAGE RANGE: V_{CC}(OPR) = 4.5V to 5.5V
- IMPROVED LATCH-UP IMMUNITY

DESCRIPTION

The 74V1T04 is an advanced high-speed CMOS SINGLE INVERTER fabricated with sub-micron silicon gate and double-layer metal wiring C^2MOS technology.

The internal circuit is composed of 3 stages including buffer output, which provide high noise immunity and stable output.




ORDER CODES


PACKAGE	T & R
SOT23-5L	74V1T04STR
SOT323-5L	74V1T04CTR

Power down protection is provided on input and 0 to 7V can be accepted on input with no regard to the supply voltage. This device can be used to interface 5V to 3V.

PIN CONNECTION AND IEC LOGIC SYMBOLS



INPUT EQUIVALENT CIRCUIT



PIN DESCRIPTION

PIN N°	SYMBOL	NAME AND FUNCTION
1	NC	Not Connected
2	1A	Data Input
4	1Y	Data Output
3	GND	Ground (0V)
5	V _{CC}	Positive Supply Voltage

TRUTH TABLE

A	Y
L	Н
Н	L

57

ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit			
V _{CC}	Supply Voltage	-0.5 to +7.0	V			
VI	DC Input Voltage	-0.5 to +7.0	V			
Vo	DC Output Voltage	-0.5 to V _{CC} + 0.5	V			
I _{IK}	DC Input Diode Current	- 20 m				
I _{OK}	DC Output Diode Current	± 20	mA			
Ι _Ο	DC Output Current	± 25	mA			
I _{CC} or I _{GND}	DC V _{CC} or Ground Current	± 50	mA			
T _{stg}	Storage Temperature	-65 to +150	°C			
TL	Lead Temperature (10 sec)	300	°C			

Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these conditions is not implied

RECOMMENDED OPERATING CONDITIONS

Symbol	Parameter	Value	Unit
V _{CC}	Supply Voltage	4.5 to 5.5	V
VI	Input Voltage	0 to 5.5	V
Vo	Output Voltage	0 to V _{CC}	V
T _{op}	Operating Temperature	-55 to 125	°C
dt/dv	Input Rise and Fall Time (note 1) (V $_{\rm CC}$ = 5.0 \pm 0.5V)	0 to 20	ns/V

1) V_{IN} from 0.8V to 2V

DC SPECIFICATIONS

		Г	est Condition	Value							
Symbol	Parameter	v _{cc}		т	T _A = 25°C			-40 to 85°C		-55 to 125°C	
	(V)		Min.	Тур.	Max.	Min.	Max.	Min.	Max.		
V _{IH}	High Level Input Voltage	4.5 to 5.5		2			2		2		V
V _{IL}	Low Level Input Voltage	4.5 to 5.5				0.8		0.8		0.8	V
V _{OH}	High Level Output	4.5	I _O =-50 μA	4.4	4.5		4.4		4.4		V
	Voltage	4.5	I _O =-8 mA	3.94			3.8		3.7		
V _{OL}	Low Level Output	4.5	I _O =50 μA		0.0	0.1		0.1		0.1	V
	Voltage	4.5	I _O =8 mA			0.36		0.44		0.55	
Ι _Ι	Input Leakage Current	0 to 5.5	$V_{I} = 5.5V \text{ or GND}$			± 0.1		± 1.0		± 1.0	μΑ
Icc	Quiescent Supply Current	5.5	$V_I = V_{CC}$ or GND			1		10		20	μΑ
+lcc	Additional Worst Case Supply Current	5.5	One Input at 3.4V, other input at V _{CC} or GND			1.35		1.5		1.5	mA

AC ELECTRICAL CHARACTERISTICS (Input $t_r = t_f = 3ns$)

Symbol	Parameter	Test Condition		Value								
			CL	T _A = 25°C			-40 to 85°C		-55 to 125°C		Unit	
			(pF)		Min.	Тур.	Max.	Min.	Max.	Min.	Max.	
t _{PLH}	Propagation Delay	5.0 (*)	15			4.7	6.7	1.0	7.5	1.0	8.5	
t _{PHL}	t _{PHL} Time	5.0 (*)	50			5.5	7.7	1.0	8.5	1.0	9.5	ns

(*) Voltage range is $5.0V \pm 0.5V$

CAPACITIVE CHARACTERISTICS


		Test Condition		Value						
Symbol	Parameter		Т	T _A = 25°C		-40 to 85°C		-55 to 125°C		Unit
			Min.	Тур.	Max.	Min.	Max.	Min.	Max.	
C _{IN}	Input Capacitance			4	10		10		10	рF
C _{PD}	Power Dissipation Capacitance (note 1)			16						pF

1) C_{PD} is defined as the value of the IC's internal equivalent capacitance which is calculated from the operating current consumption without load. (Refer to Test Circuit). Average operating current can be obtained by the following equation. $I_{CC(opr)} = C_{PD} \times V_{CC} \times f_{IN} + I_{CC}$




74V1T04

TEST CIRCUIT



 C_L =15/50pF or equivalent (includes jig and probe capacitance) R_T = Z_{OUT} of pulse generator (typically 50 Ω)


WAVEFORM: PROPAGATION DELAY (f=1MHz; 50% duty cycle)



57


DIM.		mm.			mils		
Dilwi.	MIN.	ТҮР	MAX.	MIN.	TYP.	MAX.	
А	0.90		1.45	35.4		57.1	
A1	0.00		0.10	0.0		3.9	
A2	0.90		1.30	35.4		51.2	
b	0.35		0.50	13.7		19.7	
С	0.09		0.20	3.5		7.8	
D	2.80		3.00	110.2		118.1	
Е	1.50		1.75	59.0		68.8	
е		0.95			37.4		
Н	2.60		3.00	102.3		118.1	
L	0.10		0.60	3.9		23.6	





Г


	SOT323-5L MECHANICAL DATA								
DIM.		mm.			mils				
	MIN.	ТҮР	MAX.	MIN.	TYP.	MAX.			
А	0.80		1.10	31.5		43.3			
A1	0.00		0.10	0.0		3.9			
A2	0.80		1.00	31.5		39.4			
b	0.15		0.30	5.9		11.8			
С	0.10		0.18	3.9		7.1			
D	1.80		2.20	70.9		86.6			
Е	1.80		2.40	70.9		94.5			
E1	1.15		1.35	45.3		53.1			
е		0.65			25.6				
e1		1.3			51.2				
L	0.10		0.30	3.9		11.8			




٦


		mm.			inch			
DIM.	MIN.	ТҮР	MAX.	MIN.	TYP.	MAX.		
А			180			7.086		
С	12.8	13.0	13.2	0.504	0.512	0.519		
D	20.2			0.795				
Ν	60			2.362				
Т			14.4			0.567		
Ao	3.13	3.23	3.33	0.123	0.127	0.131		
Во	3.07	3.17	3.27	0.120	0.124	0.128		
Ko	1.27	1.37	1.47	0.050	0.054	0.0.58		
Po	3.9	4.0	4.1	0.153	0.157	0.161		
Р	3.9	4.0	4.1	0.153	0.157	0.161		

Tape & Reel SOT23-xL MECHANICAL DATA



	Tape & Reel SOT323-xL MECHANICAL DATA								
DIM		mm.			inch				
DIM.	MIN.	ТҮР	MAX.	MIN.	TYP.	MAX.			
А	175	180	185	6.889	7.086	7.283			
С	12.8	13	13.2	0.504	0.512	0.519			
D	20.2			0.795					
Ν	59.5	60	60.5		2.362				
Т			14.4			0.567			
Ao		2.25			0.088				
Во		2.7			0.106				
Ko		1.2			0.047				
Po	3.9	4	4.1	0.153	0.157	0.161			
Р	3.8	4	4.2	0.149	0.157	0.165			





\$7**/**

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics All other names are the property of their respective owners

© 2004 STMicroelectronics - All Rights Reserved STMicroelectronics GROUP OF COMPANIES

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States. http://www.st.com

