

## Dual-Cell Li-Ion/Li-Polymer Battery Charge Management Controller with Input Overvoltage Protection

### **Features**

- · Complete Linear Charge Management Controller:
  - Integrated Input Overvoltage Protection
  - Integrated Pass Transistor
  - Integrated Current Sense
  - Integrated Reverse Discharge Protection
- Constant Current/Constant Voltage Operation with Thermal Regulation
- 4.15V Undervoltage Lockout (UVLO)
- · 13V Input Overvoltage Protection
- High Accuracy Preset Voltage Regulation through Full Temperature Range (–5°C to +55°C ±0.6%)
- · Battery Charge Voltage Options:
  - 8.20V, 8.40V, 8.7V or 8.8V
- · Resistor Programmable Fast Charge Current:
  - 130 mA-1100 mA
- · Preconditioning of Deeply Depleted Cells:
  - Available Options: 10% or Disable
- Integrated Precondition Timer:
  - 32 Minutes or Disable
- · Automatic End-of-Charge Control:
  - Selectable Minimum Current Ratio: 5%, 7.5%, 10% or 20%
  - Elapse Safety Timer: 4 hr., 6 hr., 8 hr. or Disable
- · Automatic Recharge:
  - Available Options: 95% or Disable
- · Factory Preset Charge Status Output:
  - On/Off or Flashing
- · Soft Start
- Temperature Range: -40°C to +85°C
- Packaging: DFN-10 (3 mm x 3 mm)

### **Applications**

- · Digital Camcorders
- Portable Media Players
- · Ultra Mobile Personal Computers
- · Netbook Computers
- · Handheld Devices
- · Walkie-Talkie
- Low-Cost 2-Cell Li-Ion/Li-Poly Chargers/Cradles

### Description


The MCP73213 is a highly integrated Li-Ion battery charge management controller for use in space-limited and cost-sensitive applications. The MCP73213 provides specific charge algorithms for dual-cell Li-Ion/Li-Polymer batteries to achieve optimal capacity and safety in the shortest charging time possible. Along with its small physical size, the low number of external components makes the MCP73213 ideally suitable for portable applications. The absolute maximum voltage, up to 18V, allows the use of MCP73213 in harsh environments, such as low-cost wall wart or voltage spikes from plug/unplug.

The MCP73213 employs a constant current/constant voltage charge algorithm. The various charging voltage regulations provide design engineers flexibility to use in different applications. The fast charge, constant current value is set with one external resistor from 130 mA to 1100 mA. The MCP73213 limits the charge current based on die temperature during high-power or high-ambient conditions. This thermal regulation optimizes the charge cycle time while maintaining device reliability.

The PROG pin of the MCP73213 also serves as enable pin. When high impedance is applied, the MCP73213 will be in Standby mode.

The MCP73213 is fully specified over the ambient temperature range of -40°C to +85°C. The MCP73213 is available in a 10-lead DFN package.

### Package Types (Top View)



### **Typical Application**




TABLE 1:	AVAIL	AVAILABLE FACTORY PRESET OPTIONS	RESET OPTIONS					
Charge Voltage	OVP	Preconditioning Charge Current	Preconditioning Threshold	Precondition Timer	Elapse Timer	End-of-Charge Control	Automatic Recharge	Output Status
	13V	Disable/10%	66.5%/71.5%	Disable/ 32 Minimum	Disable/4 hr/ 6 hr/8 hr	5%/7.5%/ 10%/20%	No/ Yes	Type 1/ Type 2
	13V	Disable/10%	66.5%/71.5%	Disable/ 32 Minimum	Disable/4 hr/ 6 hr/8 hr	5%/7.5%/ 10%/20%	No/ Yes	Type 1/ Type 2
	13V	Disable/10%	66.5%/71.5%	Disable/ 32 Minimum	Disable/4 hr/ 6 hr/8 hr	5%/7.5%/ 10%/20%	No/ Yes	Type 1/ Type 2
8.8V	13V	Disable/10%	%5'.14'%5'99	Disable/ 32 Minimum	Disable/4 hr/ 6 hr/8 hr	5%/7.5%/ 10%/20%	No/ Yes	Type 1/ Type 2

I<sub>REG</sub>: Regulated fast charge current. Note 1:

V<sub>REG</sub>: Regulated charge voltage.

IPREG/IREG: Preconditioning charge current; ratio of regulated fast charge current.

TERM/IREG: End-of-Charge control; ratio of regulated fast charge current.

4. 5:

.:

VRTH/VREG: Recharge threshold; ratio of regulated battery voltage.

V<sub>PTH</sub>/V<sub>REG</sub>: Preconditioning threshold voltage.


Type 1: On/Off; Type 2: Flashing. Please refer to Table 5-2. :9

# STANDARD SAMPLE OPTIONS TABIF 2.

Part Number	VREG	OVP	IPREG/IREG	Precharge Timer	Elapse Timer	lterm <sup>//</sup> reg	V <sub>RTH</sub> /V <sub>REG</sub>	V <sub>PTH</sub> /V <sub>REG</sub>	Output Status
MCP73213-B6S/MF	8.20V	13V	10%	32 Minimum	6 hr	10%	%56	71.5%	Type 1
MCP73213-A6S/MF	8.40V	13V	10%	32 Minimum	6 hr	10%	%56	71.5%	Type 1

able to help customers. A listing of sales offices and locations is included at the back of this document. Technical support is available through the web site Customers should contact their distributor, representatives or field application engineer (FAE) for support and sample. Local sales offices are also availat: http://www.microchip.com/support Note 1:

### **Functional Block Diagram**



# 1.0 ELECTRICAL CHARACTERISTICS

### **Absolute Maximum Ratings†**

V <sub>DD</sub>	18.0V
V <sub>PROG</sub>	6.0V
All Inputs and Outputs w.r.t. V <sub>SS</sub>	0.3 to (V <sub>DD</sub> +0.3)V
Maximum Junction Temperature, T	J . Internally Limited
Storage Temperature	–65°C to +150°C
ESD Protection on All Pins	≥ 4 kV HBM
ESD Protection on All Pins	> 300V MM

† Notice: Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational listings of this specification is not implied. Exposure to maximum rating conditions for extended periods may affect device reliability.

### **DC CHARACTERISTICS**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Supply Input						
Input Voltage Range	$V_{DD}$	4	_	16	V	
Operating Supply Voltage	$V_{DD}$	4.2	_	13	V	
Supply Current	I <sub>SS</sub>	_	4	5.5	μA	Shutdown (V <sub>DD</sub> ≤ V <sub>BAT</sub> – 150 mV)
		_	700	1500	μA	Charging
		_	50	125	μA	Standby (PROG Floating)
		_	50	150	μА	Charge Complete; No Battery; V <sub>DD</sub> < V <sub>STOP</sub>
Battery Discharge Curren	t				'	
Output Reverse Leakage	I <sub>DISCHARGE</sub>	_	0.5	2	μA	Standby (PROG Floating)
Current		_	0.5	2	μA	Shutdown ( $V_{DD} \le V_{BAT}$ or $V_{DD} < V_{STOP}$ )
		_	10	17	μA	Charge Complete; V <sub>DD</sub> is present
Undervoltage Lockout						
UVLO Start Threshold	$V_{START}$	4.10	4.15	4.25	V	
UVLO Stop Threshold	V <sub>STOP</sub>	4.00	4.05	4.10	V	
UVLO Hysteresis	V <sub>HYS</sub>	_	100	_	mV	
Overvoltage Protection					-	
OVP Start Threshold	$V_{OVP}$	12.8	13	13.2	V	
OVP Hysteresis	V <sub>OVPHYS</sub>	_	150	_	mV	
Voltage Regulation (Cons	tant Voltage M	lode)				
Regulated Output Voltage	V <sub>REG</sub>	8.15	8.20	8.25	V	T <sub>A</sub> = -5°C to +55°C
O 1:			1			1,, ,, ,, ,, ,,

8.40

8.70

8.80

0.05

0.05

8.45

8.75

8.85

0.6

0.20

0.20

V

V %

%/V

%

8.35

8.65

8.75

-0.6

**Electrical Specifications:** Unless otherwise indicated, all limits apply for  $V_{DD} = [V_{REG}(Typical) + 0.3V]$  to 12V,

Note 1: Not production tested. Ensured by design.

 $V_{RTOL}$ 

 $|(\Delta V_{BAT}/$ 

 $V_{BAT}$ )/ $\Delta V_{DD}$ 

 $|\Delta V_{BAT}/V_{BAT}|$ 

**Output Voltage Tolerance** 

Line Regulation

Load Regulation

 $V_{DD} = [V_{REG}(Typical)+1V]$ 

 $I_{OUT} = 50 \text{ mA} - 150 \text{ mA}$ 

 $V_{DD} = [V_{REG}(Typical) + 1V]$ 

 $V_{DD} = [V_{REG}(Typical)+1V]$  to 12V

 $I_{OUT} = 50 \text{ mA}$ 

 $I_{OUT} = 50 \text{ mA}$ 

Options

### **DC CHARACTERISTICS (CONTINUED)**

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Supply Ripple Attenuation	PSRR	_	-46	_	dB	I <sub>OUT</sub> = 20 mA, 10 Hz to 1 kHz
		_	-30	_	dB	I <sub>OUT</sub> = 20 mA, 10 Hz to 10 kHz
Battery Short Protection	L	1				1-001
BSP Start Threshold	V <sub>SHORT</sub>	I _	3.4		V	
BSP Hysteresis	V <sub>BSPHYS</sub>	_	150	_	mV	
BSP Regulation Current	I <sub>SHORT</sub>	_	25	_	mA	
Current Regulation (Fast		⊥ tant-Curre				
Fast Charge Current	I <sub>REG</sub>	130	_	1100	mA	$T_A = -5^{\circ}C$ to +55°C
Regulation	REG	117	130	143	mA	PROG = 10 kΩ
		900	1000	1100	mA	PROG = 1.1 kΩ
Preconditioning Current	∟ Regulation (Tr				1	
Precondition Current Ratio	I <sub>PREG</sub> /I <sub>REG</sub>	_	10	_	%	PROG = 1 kΩ to 10 kΩ $T_A=-5^{\circ}\text{C to } +55^{\circ}\text{C}$
ratio			100	_	%	No Preconditioning
Precondition Voltage	V <sub>PTH</sub> /V <sub>REG</sub>	64	66.5	69	%	V <sub>BAT</sub> Low-to-High
Threshold Ratio	YPIH/YREG	69	71.5	74	%	V <sub>BAT</sub> Low-to-High
Precondition Hysteresis	V <sub>PHYS</sub>	_	100	_	mV	V <sub>BAT</sub> High-to-Low (Note 1)
Charge Termination	PHYS		100		1117	VBAI Tiigii to Low (Note 1)
Charge Termination	I <sub>TERM</sub> /I <sub>REG</sub>	3.7	5	6.3	%	PROG = 1 kΩ to 10 kΩ
Current Ratio	TERMTREG	5.6	7.5	9.4	%	$T_A = -5^{\circ}C$ to $+55^{\circ}C$
		7.5	10	12.5	%	
		15	20	25	%	
Automatic Recharge		1			,,,	
Recharge Voltage Threshold Ratio	V <sub>RTH</sub> /V <sub>REG</sub>	93	95.0	97	%	V <sub>BAT</sub> High-to-Low
Through Radio			0	_	%	No Automatic Recharge
Pass Transistor ON-Resis	stance				,,,	Tro / tatomatic / toonarge
ON-Resistance	R <sub>DSON</sub>	T _	350		mΩ	V <sub>DD</sub> = 4.5V, T <sub>J</sub> = 105°C (Note 1
Status Indicator - STAT	I DSON					1 DD 110 1, 1 J 100 0 (110 0 1
Sink Current	I <sub>SINK</sub>	_	20	35	mA	
Low Output Voltage	V <sub>OL</sub>	_	0.2	0.5	V	I <sub>SINK</sub> = 4 mA
Input Leakage Current	I <sub>LK</sub>	_	0.001	1	μA	High Impedance, V <sub>DD</sub> on pin
PROG Input	LK		1 21221		ļ ļ	тэн трезаное, грв стр.
Charge Impedance Range	R <sub>PROG</sub>	1	_	22	kΩ	
Shutdown Impedance	R <sub>PROG</sub>	_	200	_	kΩ	Impedance for Shutdown
Automatic Power-Down		·	1		'	ı
Automatic Power-Down Entry Threshold	V <sub>PDENTRY</sub>	V <sub>BAT</sub> + 10 mV	V <sub>BAT</sub> + 50 mV	_	V	V <sub>DD</sub> Falling
Automatic Power-Down	V <sub>PDEXIT</sub>	_	V <sub>BAT</sub> + 150	V <sub>BAT</sub> + 250	V	V <sub>DD</sub> Rising

Note 1: Not production tested. Ensured by design.

### DC CHARACTERISTICS (CONTINUED)

Electrical Specifications: Unless otherwise indicated, all limits apply for V<sub>DD</sub>= [V<sub>REG</sub>(Typical) + 0.3V] to 12V,
T<sub>A</sub> = -40°C to +85°C. Typical values are at +25°C, V<sub>DD</sub> = [V<sub>REG</sub> (Typical) + 1.0V]

Parameters Sym. Min. Typ. Max. Units Conditions

Thermal Shutdown

Parameters	Sym.	Min.	Тур.	Max.	Units	Conditions
Thermal Shutdown						
Die Temperature	T <sub>SD</sub>	_	150	_	°C	
Die Temperature Hysteresis	T <sub>SDHYS</sub>	_	10	_	°C	

Note 1: Not production tested. Ensured by design.

### **AC CHARACTERISTICS**

Electrical Specifications: Unless otherwise specified, all limits apply for V<sub>DD</sub>= [V<sub>REG</sub>(Typical)+0.3V] to 12V,  $T_A = -40$ °C to +85°C. Typical values are at +25°C,  $V_{DD} = [V_{REG}(Typical) + 1.0V]$ Min. Svm. Max. Units Conditions **Parameters** Typ. **Elapsed Timer Elapsed Timer Period** Hours Timer Disabled 0  $t_{EL-}$ **APSED** 4.0 4.4 Hours 3.6 5.4 6.0 6.6 Hours 7.2 8.0 8.8 Hours **Preconditioning Timer Disabled Timer** Preconditioning Timer Period 0 Hours **t**PRECHG 0.4 0.5 0.6 Hours **Status Indicator** Status Output Turn-Off  $I_{SINK}$  = 1 mA to 0 mA 500 toff μs (Note 1) Status Output Turn-On 500  $I_{SINK} = 0 \text{ mA to } 1 \text{ mA}$ μs  $t_{ON}$ (Note 1)

Note 1: Not production tested. Ensured by design.


### TEMPERATURE SPECIFICATIONS

**Electrical Specifications:** Unless otherwise indicated, all limits apply for  $V_{DD} = [V_{RFG} \text{ (Typical)} + 0.3V] \text{ to 6V}.$ Typical values are at +25°C,  $V_{DD} = [V_{REG} (Typical) + 1.0V]$ Units **Parameters** Sym. Min. Typ. Max. **Conditions Temperature Ranges** Specified Temperature Range  $T_A$ -40 +85 °C +125 °C Operating Temperature Range -40  $T_{J}$ °C Storage Temperature Range  $T_A$ -65+150 **Thermal Package Resistances** Thermal Resistance, DFN-10LD °C/W 4-Layer JC51-7 Standard  $\theta_{JA}$ 62 (3x3)Board, Natural Convection °C/W 20.5  $\theta_{JC}$ 


### 2.0 TYPICAL PERFORMANCE CURVES

**Note:** The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.


**Note:** Unless otherwise indicated,  $V_{DD} = [V_{REG}(Typical) + 1V]$ ,  $T_A = +25$ °C, Constant Voltage mode.




**FIGURE 2-1:** Battery Regulation Voltage (V<sub>BAT</sub>) vs. Supply Voltage (V<sub>DD</sub>).




**FIGURE 2-2:** Battery Regulation Voltage (V<sub>BAT</sub>) vs. Supply Voltage (V<sub>DD</sub>).




**FIGURE 2-3:** Battery Regulation Voltage  $(V_{BAT})$  vs. Ambient Temperature  $(T_A)$ .



**FIGURE 2-4:** Battery Regulation Voltage  $(V_{BAT})$  vs. Ambient Temperature  $(T_A)$ .




**FIGURE 2-5:** Charge Current ( $I_{OUT}$ ) vs. Programming Resistor ( $R_{PROG}$ ).




**FIGURE 2-6:** Charge Current  $(I_{OUT})$  vs. Supply Voltage  $(V_{DD})$ .

### TYPICAL PERFORMANCE CURVES (CONTINUED)


**Note:** Unless otherwise indicated,  $V_{DD} = [V_{REG}(Typical) + 1V]$ ,  $T_A = +25$ °C, Constant-voltage mode.




**FIGURE 2-7:** Charge Current ( $I_{OUT}$ ) vs. Supply Voltage ( $V_{DD}$ ).




**FIGURE 2-8:** Charge Current  $(I_{OUT})$  vs. Supply Voltage  $(V_{DD})$ .




**FIGURE 2-9:** Charge Current  $(I_{OUT})$  vs. Ambient Temperature  $(T_A)$ .



**FIGURE 2-10:** Charge Current  $(I_{OUT})$  vs. Ambient Temperature  $(T_A)$ .




**FIGURE 2-11:** Battery Short Protection Regulation Current ( $I_{SHORT}$ ) vs. Ambient Temperature ( $T_{\Delta}$ ).




**FIGURE 2-12:** Output Leakage Current  $(I_{DISCHARGE})$  vs. Ambient Temperature  $(T_A)$ .

### TYPICAL PERFORMANCE CURVES (CONTINUED)

**Note:** Unless otherwise indicated,  $V_{DD} = [V_{REG}(Typical) + 1V]$ ,  $T_A = +25$ °C, Constant-voltage mode.



**FIGURE 2-13:** Battery Voltage Accuracy  $(V_{RTOL})$  vs. Supply Voltage  $(V_{DD})$ .



**FIGURE 2-14:** Load Transient Response  $(I_{LOAD} = 50 \text{ mA/Div}, \text{ Output: } 100 \text{ mV/Div}, \text{ Time: } 100 \text{ µs/Div}).$ 




FIGURE 2-15: Complete Charge Cycle.






FIGURE 2-16:

Input Overvoltage Protection

( $\rm V_{IN}$ = 5V/Div,  $\rm V_{BAT}$ = 2V/Div,  $\rm I_{LOAD}$ = 200 mA/Div, Time: 200 ms/Div)



**FIGURE 2-17:** Line Transient Response  $(I_{LOAD} = 10 \text{ mA}, V_{IN} = 1 \text{V/Div}, V_{OUT} = 100 \text{ mV/Div}, Time: 100 µs/Div).$ 



**FIGURE 2-18:** Line Transient Response  $(I_{LOAD} = 100 \text{ mA}, V_{IN} = 1V/\text{Div}, V_{OUT} = 100 \text{ mV/Div}, Time:100 <math>\mu$ s/Div).

### 3.0 PIN DESCRIPTION

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1: PIN FUNCTION TABLE

MCP73213	Symbol	I/O	Deparintion
DFN-10	Symbol	1/0	Description
1, 2	$V_{DD}$	I	Battery Management Input Supply Pin
3, 4	$V_{BAT}$	I/O	Battery Charge Control Output Pin
5, 6	NC	_	No Connection Pin
7	STAT	0	Battery Charge Status Output Pin
8, 9	V <sub>SS</sub>	_	Battery Management 0V Reference Pin
10	PROG	I/O	Battery Charge Current Regulation Program and Charge Control Enable Pin
11	EP	_	Exposed Pad Pin

# 3.1 Battery Management Input Supply (V<sub>DD</sub>)

A supply voltage of [V<sub>REG</sub> (Typical) + 0.3V] to 13.0V is recommended. Bypass to V<sub>SS</sub> with a minimum of 1  $\mu\text{F}.$  The V<sub>DD</sub> pin is rated 18V absolute maximum to prevent a sudden rise in input voltage from spikes or low-cost AC-DC wall adapters from causing an over-voltage condition and damaging the device.

# 3.2 Battery Charge Control Output (V<sub>RAT</sub>)

Connect to the positive terminal of the battery. Bypass to  $V_{SS}$  with a minimum of 1  $\mu F$  to ensure loop stability when the battery is disconnected.

### 3.3 No Connection (NC)

No connection.

### 3.4 Status Output (STAT)

STAT is an open-drain logic output for connection to an LED for charge status indication in stand-alone applications. Alternatively, a pull-up resistor can be applied for interfacing to a host microcontroller. Refer to Table 5-2 for a summary of the status output during a charge cycle.

# 3.5 Battery Management 0V Reference (V<sub>SS</sub>)

Connect to the negative terminal of the battery and input supply.

### 3.6 Current Regulation Set (PROG)

The fast charge current is set by placing a resistor from PROG to  $V_{SS}$  during constant current (CC) mode. PROG pin also serves as charge control enable. When a typical 200 k $\Omega$  impedance is applied to the PROG pin, the MCP73213 will go into standby mode until the high impedance is removed. Refer to **Section 5.5** "Constant-Current Mode - Fast Charge" for details.

### 3.7 Exposed Pad (EP)

Connect the Exposed Thermal Pad (EP) to the exposed copper area on the Printed Circuit Board (PCB) for thermal enhancement. Additional vias in the copper area under the MCP73213 device can improve heat dissipation performance and simplify the assembly process.

### 4.0 DEVICE OVERVIEW

The MCP73213 are simple, but fully integrated linear charge management controllers. Figure 4-1 depicts the operational flow algorithm.




FIGURE 4-1: The MCP73213 Flow Chart.

### 5.0 DETAILED DESCRIPTION

### 5.1 Undervoltage Lockout (UVLO)

An internal undervoltage lockout (UVLO) circuit monitors the input voltage and keeps the charger in shutdown mode until the input supply rises above the UVLO threshold. In the event a battery is present when the input power is applied, the input supply must rise approximately 150 mV above the battery voltage before the MCP73213 device becomes operational.

The UVLO circuit places the device in shutdown mode if the input supply falls to approximately 150 mV above the battery voltage. The UVLO circuit is always active. Any time the input supply is below the UVLO threshold or approximately 150 mV of the voltage at the  $V_{BAT}$  pin, the MCP73213 device is placed in a shutdown mode.

### 5.2 Overvoltage Protection (OVP)

An internal overvoltage protection (OVP) circuit monitors the input voltage and keeps the charger in shutdown mode when the input supply rises above the typical 13V OVP threshold. The OVP hysteresis is approximately 150 mV for the MCP73213 device.

The MCP73213 device is operational between UVLO and OVP thresholds. The OVP circuit is also recognized as overvoltage lockout (OVLO).

### 5.3 Charge Qualification

When the input power is applied, the input supply must rise 150 mV above the battery voltage before the MCP73213 becomes operational.

The automatic power-down circuit places the device in a shutdown mode if the input supply falls to within +50 mV of the battery voltage.

The automatic circuit is always active. At any time the input supply is within +50 mV of the voltage at the  $V_{BAT}$  pin, the MCP73213 is placed in a shutdown mode.

For a charge cycle to begin, the automatic power-down conditions must be met and the charge enable input must be above the input high threshold.

# 5.3.1 BATTERY MANAGEMENT INPUT SUPPLY (V<sub>DD</sub>)

The  $V_{DD}$  input is the input supply to the MCP73213. The MCP73213 automatically enters a power-down mode if the voltage on the  $V_{DD}$  input falls to within +50 mV of the battery voltage. This feature prevents draining the battery pack when the  $V_{DD}$  supply is not present.

# 5.3.2 BATTERY CHARGE CONTROL OUTPUT (V<sub>BAT</sub>)

The battery charge control output is the drain terminal of an internal P-channel MOSFET. The MCP73213 provides constant current and voltage regulation to the battery pack by controlling this MOSFET in the linear region. The battery charge control output should be connected to the positive terminal of the battery pack.

### 5.3.3 BATTERY DETECTION

The MCP73213 detects the battery presence with charging of the output capacitor. The charge flow will initiate when the voltage on  $V_{BAT}$  is pulled below the  $V_{RECHARGE}$  threshold. Refer to **Section 1.0** "**Electrical Characteristics**" for  $V_{RECHARGE}$  values. The value will be the same for nonrechargeable devices.

When  $V_{BAT} > V_{REG}$  + Hysteresis, the charge will be suspended (or not started, depending on the condition) to prevent overcharging.

### 5.4 Preconditioning

If the voltage at the  $V_{BAT}$  pin is less than the preconditioning threshold, the MCP73213 device enters a preconditioning mode. The preconditioning threshold is factory set. Refer to **Section 1.0** "Electrical Characteristics" for preconditioning threshold options.

In this mode, the MCP73213 device supplies 10% of the fast charge current (established with the value of the resistor connected to the PROG pin) to the battery.

When the voltage at the  $V_{BAT}$  pin rises above the preconditioning threshold, the MCP73213 device enters the Constant Current (Fast Charge) mode.

Note:	The MCP73213 device also offers options
	with no preconditioning.

# 5.4.1 TIMER EXPIRED DURING PRECONDITIONING MODE

If the internal timer expires before the voltage threshold is reached for Fast Charge mode, a timer fault is indicated and the charge cycle terminates. The MCP73213 device remains in this condition until the battery is removed or input power is cycled. If the battery is removed, the MCP73213 device enters the Standby mode, where it remains until a battery is reinserted.

Note:	The	typica	l pre	conditi	oning	timer	for
	MCP7	73213	is	32	minut	es.	The
	MCP7	73213	also	offers	options	s with	no no
	preco	ndition	ing ti	mer.			

# 5.5 Constant-Current Mode - Fast Charge

During Constant-Current mode, the programmed charge current is supplied to the battery or load.

The charge current is established using a single resistor from PROG to  $V_{SS}$ . The program resistor and the charge current are calculated using the following equation:

### **EQUATION 5-1:**

$$I_{REG} = 1104 \times R_{PROG}^{\phantom{PROG}-0.93} \label{eq:region}$$
 Where:

 $R_{PROG}$  = kilohm (k $\Omega$ )  $I_{REG}$  = milliampere (mA)

### **EQUATION 5-2:**

$$R_{PROG} = 10^{\left(log\left(rac{I_{REG}}{I104}
ight)/(-0.93)}$$
 Where: 
$$R_{PROG} = \text{kilohm (k}\Omega)$$
 
$$I_{REG} = \text{milliampere (mA)}$$

Table 5-1 provides commonly seen E96 (1%) and E24 (5%) resistors for various charge current to reduce design time.

TABLE 5-1: RESISTOR LOOKUP TABLE

Charge Current (mA)	Recommended E96 Resistor ( $\Omega$ )	Recommended E24 Resistor ( $\Omega$ )
130	10k	10k
150	8.45k	8.20k
200	6.20k	6.20k
250	4.99k	5.10k
300	4.02k	3.90k
350	3.40k	3.30k
400	3.00k	3.00k
450	2.61k	2.70k
500	2.32k	2.37k
550	2.10k	2.20k
600	1.91k	2.00k
650	1.78k	1.80k
700	1.62k	1.60k
750	1.50k	1.50k
800	1.40k	1.50k
850	1.33k	1.30k
900	1.24k	1.20k
950	1.18k	1.20k
1000	1.10k	1.10k
1100	1.00k	1.00k

Constant-Current mode is maintained until the voltage at the  $V_{BAT}$  pin reaches the regulation voltage,  $V_{REG}$ . When Constant Current mode is invoked, the internal timer is reset.

# 5.5.1 TIMER EXPIRED DURING CONSTANT-CURRENT - FAST CHARGE MODE

If the internal timer expires before the recharge voltage threshold is reached, a timer fault is indicated and the charge cycle terminates. The MCP73213 device remains in this condition until the battery is removed. If the battery is removed or input power is cycled, the MCP73213 device enters the Standby mode where it remains until a battery is reinserted.

### 5.6 Constant-Voltage Mode

When the voltage at the  $V_{BAT}$  pin reaches the regulation voltage,  $V_{REG}$ , constant voltage regulation begins. The regulation voltage is factory set to 8.2V, 8.4V, 8.7V or 8.8V with a tolerance of  $\pm$  0.5%.

### 5.7 Charge Termination

The charge cycle is terminated when, during Constant-Voltage mode, the average charge current diminishes below a threshold established with the value of 5%, 7.5%, 10% or 20% of fast charge current or the internal timer expires. A 1 ms filter time on the termination comparator ensures that transient load conditions do not result in premature charge cycle termination. The timer period is factory set and can be disabled. Refer to **Section 1.0** "**Electrical Characteristics**" for timer period options.

### 5.8 Automatic Recharge

The MCP73213 device continuously monitors the voltage at the  $V_{BAT}$  pin in the charge complete mode. If the voltage drops below the recharge threshold, another charge cycle begins and current is once again supplied to the battery or load. The recharge threshold is factory set. Refer to Section 1.0 "Electrical Characteristics" for recharge threshold options.

**Note:** The MCP73213 also offers options with no automatic recharge.

For the MCP73213 device with no recharge option, the MCP73213 will go into Standby mode when the termination condition is met. The charge will not restart until the following conditions have been met:

- Battery is removed from the system and inserted again
- V<sub>DD</sub> is removed and plugged in again
- R<sub>PROG</sub> is disconnected (or high-impedance) and reconnected

### 5.9 Thermal Regulation

The MCP73213 shall limit the charge current based on the die temperature. The thermal regulation optimizes the charge cycle time while maintaining device reliability. Figure 5-1 depicts the thermal regulation for the MCP73213 device. Refer to Section 1.0 "Electrical Characteristics" for thermal package resistances and Section 6.1.1.2 "Thermal Considerations" for calculating power dissipation.




FIGURE 5-1: Thermal Regulation.

### 5.10 Thermal Shutdown

The MCP73213 suspends charge if the die temperature exceeds +150°C. Charging will resume when the die temperature has cooled by approximately 10°C. The thermal shutdown is a secondary safety feature in the event that there is a failure within the thermal regulation circuitry.

### 5.11 Status Indicator

The charge status outputs are open-drain outputs with two different states: Low (L), and High-Impedance (High Z). The charge status outputs can be used to illuminate LEDs. Optionally, the charge status outputs can be used as an interface to a host microcontroller. Table 5-2 summarizes the state of the status outputs during a charge cycle.

TABLE 5-2: STATUS OUTPUTS

CHARGE CYCLE STATE	STAT
Shutdown	High Z
Standby	High Z
Preconditioning	L
Constant Current Fast Charge	L
Constant Voltage	L
Charge Complete - Standby	High Z
Temperature Fault	1.6 second 50% D.C. Flashing (Type 2) High Z (Type 1)
Timer Fault	1.6 second 50% D.C. Flashing (Type 2) High Z (Type 1)
Preconditioning Timer Fault	1.6 second 50% D.C. Flashing (Type 2) High Z (Type 1)

### 5.12 Battery Short Protection

Once a single-cell Li-lon battery is detected, an internal battery short protection (BSP) circuit starts monitoring the battery voltage. When  $V_{BAT}$  falls below a typical 1.7V battery short protection threshold voltage, the charging behavior is postponed. A typical 25 mA detection current is supplied for recovering from the battery short condition.

Preconditioning mode resumes when  $V_{BAT}$  raises above the battery short protection threshold. The battery voltage must rise approximately 150 mV above the battery short protection voltage before the MCP73213 device becomes operational.

### 6.0 APPLICATIONS

The MCP73213 is designed to operate in conjunction with a host microcontroller or in stand-alone applications. The MCP73213 provides the preferred charge algorithm for dual Lithium-lon or Lithium-Polymer cells: Constant Current followed by Constant Voltage. Figure 6-1 depicts a typical stand-alone application circuit, while Figure 6-2 depicts the accompanying charge profile.





FIGURE 6-1: Typical Application Circuit.



**FIGURE 6-2:** Typical Charge Profile (875 mAh Li-Ion Battery).

### 6.1 Application Circuit Design

Due to the low efficiency of linear charging, the most important factors are thermal design and cost, which are a direct function of the input voltage, output current and thermal impedance between the battery charger and the ambient cooling air. The worst-case situation is when the device has transitioned from the Preconditioning mode to the Constant Current mode. In this situation, the battery charger has to dissipate the maximum power. A trade-off must be made between the charge current, cost and thermal requirements of the charger.

### 6.1.1 COMPONENT SELECTION

Selection of the external components in Figure 6-1 is crucial to the integrity and reliability of the charging system. The following discussion is intended as a guide for the component selection process.

### 6.1.1.1 Charge Current

The preferred fast charge current for Li-Ion/Li-Poly cells is below the 1C rate, with an absolute maximum current at the 2C rate. The recommended fast charge current should be obtained from the battery manufacturer. For example, a 500 mAh battery pack with 0.7C preferred fast charge current has a charge current of 350 mA. Charging at this rate provides the shortest charge cycle times without degradation to the battery pack performance or life.

Note:	Please consult with your battery supplier
	or refer to the battery data sheet for the
	preferred charge rate.

### 6.1.1.2 Thermal Considerations

The worst-case power dissipation in the battery charger occurs when the input voltage is at the maximum and the device has transitioned from Preconditioning mode to Constant-Current mode. In this case, the power dissipation is:

### **EQUATION 6-1:**

 $\begin{aligned} &Power Dissipation = (V_{DDMAX} - V_{PTHMIN}) \times I_{REGMAX} \\ &\text{Where:} \\ &V_{DDMAX} = & \text{the maximum input voltage} \\ &I_{REGMAX} = & \text{the maximum fast charge current} \\ &V_{PTHMIN} = & \text{the minimum transition threshold} \end{aligned}$ 

voltage

Power dissipation with a 9V,  $\pm 10\%$  input voltage source, 350 mA  $\pm 10\%$  and preconditioning threshold voltage at 6V is:

### **EQUATION 6-2:**

Power dissipation = 
$$(9.9V - 6.0V) \times 385 \text{ mA} = 1.50W$$

This power dissipation with the battery charger in the DFN-10 package will result approximately 93°C above room temperature.

### 6.1.1.3 External Capacitors

The MCP73213 is stable with or without a battery load. In order to maintain good AC stability in Constant-Voltage mode, a minimum capacitance of  $1\,\mu F$  is recommended to bypass the  $V_{BAT}$  pin to  $V_{SS}.$  This capacitance provides compensation when there is no battery load. In addition, the battery and interconnections appear inductive at high frequencies. These elements are in the control feedback loop during Constant Voltage mode. Therefore, bypass capacitance may be necessary to compensate for the inductive nature of the battery pack.

For typical applications, it is recommended to apply a minimum of 16V rated 1  $\mu$ F to the output capacitor and a minimum of 25V rated 1  $\mu$ F to the input capacitor.

TABLE 6-1: MLCC CAPACITOR EXAMPLE

MLCC Capacitors	Temperature Range	Tolerance
X7R	-55°C to +125°C	±15%
X5R	-55°C to +85°C	±15%

Virtually any good quality output filter capacitor can be used independent of the capacitor's minimum Effective Series Resistance (ESR) value. The actual value of the capacitor (and its associated ESR) depends on the output load current. A 1  $\mu F$  ceramic, tantalum or aluminum electrolytic capacitor at the output is usually sufficient to ensure stability.

### 6.1.1.4 Reverse-Blocking Protection

The MCP73213 provides protection from a faulted or shorted input. Without the protection, a faulted or shorted input would discharge the battery pack through the body diode of the internal pass transistor.

### 6.2 PCB Layout Issues

For optimum voltage regulation, place the battery pack as close as possible to the device's  $V_{BAT}$  and  $V_{SS}$  pins to minimize voltage drops along the high-current-carrying PCB traces.

If the PCB layout is used as a heatsink, adding multiple vias in the heatsink pad can help conduct more heat to the backplane of the PCB, thus reducing the junction temperature. Figures 6-4 and 6-5 depict a typical layout with PCB heatsinking.




FIGURE 6-3: Typical Layout (Top).




FIGURE 6-4: Typical Layout (Top Metal).




FIGURE 6-5: Typical Layout (Bottom).

### 7.0 PACKAGING INFORMATION

### 7.1 Package Marking Information

10-Lead DFN (3x3)

XXXX YYWW NNN

Standard *				
Part Number	Code			
MCP73213-A6SI/MF	Z3HI			
MCP73213T-A6SI/MF	Z3HI			
MCP73213-B6SI/MF	Y3HI			
MCP73213T-B6SI/MF	Y3HI			

Example:

Z3HI 1443 256

**Legend:** XX...X Customer-specific information

Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

e3 Pb-free JEDEC® designator for Matte Tin (Sn)


This package is Pb-free. The Pb-free JEDEC designator (e3)

can be found on the outer packaging for this package.

**Note**: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

### 10-Lead Plastic Dual Flat, No Lead Package (MF) - 3x3x0.9mm Body [DFN]


**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



Microchip Technology Drawing No. C04-063C Sheet 1 of 2

### 10-Lead Plastic Dual Flat, No Lead Package (MF) - 3x3x0.9mm Body [DFN]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	MILLIMETERS			
Dimension	MIN	NOM	MAX	
Number of Pins	N	10		
Pitch	е	0.50 BSC		
Overall Height	Α	0.80	0.90	1.00
Standoff	A1	0.00	0.02	0.05
Contact Thickness	A3	0.20 REF		
Overall Length	D	3.00 BSC		
Exposed Pad Length	D2	2.15	2.35	2.45
Overall Width	E	3.00 BSC		
Exposed Pad Width	E2	1.40	1.50	1.75
Contact Width	b	0.18	0.25	0.30
Contact Length	L	0.30	0.40	0.50
Contact-to-Exposed Pad	K	0.20	-	-

### Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package may have one or more exposed tie bars at ends.
- 3. Package is saw singulated.
- 4. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing No. C04-063C Sheet 2 of 2

### 10-Lead Plastic Dual Flat, No Lead Package (MF) - 3x3x0.9mm Body [DFN]

**Note:** For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



### RECOMMENDED LAND PATTERN

Units		MILLIMETERS			
Dimension Limits		MIN	NOM	MAX	
Contact Pitch	Е	0.50 BSC			
Optional Center Pad Width	W2			2.48	
Optional Center Pad Length	T2			1.55	
Contact Pad Spacing	C1		3.10		
Contact Pad Width (X10)	X1			0.30	
Contact Pad Length (X10)	Y1			0.65	
Distance Between Pads	G	0.20		·	

### Notes:

1. Dimensioning and tolerancing per ASME Y14.5M

BSC: Basic Dimension. Theoretically exact value shown without tolerances.

Microchip Technology Drawing No. C04-2063B

### APPENDIX A: REVISION HISTORY

### **Revision D (January 2018)**

The following is the list of modifications:

- 1. Changed captions for Figure 2-16, Figure 2-17, Figure 2-18.
- 2. Minor typographical corrections.

### **Revision C (December 2014)**

The following is the list of modifications:

- 1. Added Note 7 in Table 1 regarding the Type 1 and Type 2 descriptions.
- 2. Updated the Functional Block Diagram.
- 3. Updated the thermal resistances in the Temperature Specifications.
- 4. Changed captions for the Figures 2-7, 2-8, 2-15, 2-16.
- 5. Updated Figure 4-1.
- 6. Updated Section 6.1.1.2, Thermal Considerations.
- Updated Section 7.1, Package Marking Information.
- 8. Minor typographical corrections.

### **Revision B (December 2009)**

The following is the list of modifications:

 Updated the Battery Short Protection values in the DC Characteristics table.

### Revision A (July 2009)

· Original Release of this Document.

### PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales office.

PART NO. Device	[X] <sup>(1)</sup>   Tape and Reel Option	X       Temperature   Range	/XX      Package	XXX       Pattern	a) b)		: 3213-A6S 3213-B6S
Device:		Dual Cell Li-lon/L Dual Cell Li-lon/L Tape and Reel			c) d)		3213T-A6
Tape and Ree Option:	·I T = Tape ar	nd Reel <sup>(1)</sup>			Note		Tape and Foatalog pa
Temperature Range:	I = -40°C to	o +85°C (Industrial	)			i: Ç Y	s used for printed on your Micro availability
Package:	MF = 10-Lead (DFN)	l Plastic Dual Flat,	No Lead - 3x3	mm Body			a valido liity

) MCP73213-A6SI/MF: Dual Cell Li-lon/

Li-Polymer Battery Device

) MCP73213-B6SI/MF: Dual Cell Li-Ion/

Li-Polymer Battery Device

e) MCP73213T-A6SI/MF: Tape and Reel, Dual Cell Li-lon/

Li-Polymer Battery Device

MCP73213T-B6SI/MF: Tape and Reel,

Dual Cell Li-Ion/

Li-Polymer Battery Device

Note 1: Tape and Reel identifier only appears in the catalog part number description. This identifier is used for ordering purposes and is not printed on the device package. Check with your Microchip Sales Office for package availability with the Tape and Reel option.

### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our
  knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data
  Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

### **Trademarks**

The Microchip name and logo, the Microchip logo, AnyRate, AVR, AVR logo, AVR Freaks, BeaconThings, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KEELOQ, KEELOQ logo, Kleer, LANCheck, LINK MD, maXStylus, maXTouch, MediaLB, megaAVR, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, Prochip Designer, QTouch, RightTouch, SAM-BA, SpyNIC, SST, SST Logo, SuperFlash, tinyAVR, UNI/O, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, EtherSynch, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and Quiet-Wire are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BodyCom, CodeGuard, CryptoAuthentication, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, Mindi, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, QMatrix, RightTouch logo, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

 $\ensuremath{\mathsf{SQTP}}$  is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc.. in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2009-2018, Microchip Technology Incorporated, All Rights Reserved.

ISBN: 978-1-5224-2559-5



### Worldwide Sales and Service

### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/support

Web Address:

www.microchip.com

Atlanta Duluth, GA Tel: 678-957-9614

Fax: 678-957-1455 Austin, TX

Tel: 512-257-3370

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453

Tel: 317-773-5453 Tel: 317-536-2380 **Los Angeles** Mission Viejo, CA

Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270 **Canada - Toronto** 

Tel: 905-695-1980 Fax: 905-695-2078

### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

**China - Chengdu** Tel: 86-28-8665-5511

**China - Chongqing** Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

**China - Guangzhou** Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

**China - Shanghai** Tel: 86-21-3326-8000

**China - Shenyang** Tel: 86-24-2334-2829

**China - Shenzhen** Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

**China - Wuhan** Tel: 86-27-5980-5300

**China - Xian** Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

**Japan - Tokyo** Tel: 81-3-6880- 3770

**Korea - Daegu** Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

### **EUROPE**

Austria - Wels Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-67-3636

**Germany - Karlsruhe** Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

**Israel - Ra'anana** Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7289-7561

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

**Sweden - Stockholm** Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820