Panasonic INDUSTRY

Aluminum Electrolytic Capacitors Radial Lead Type FS-A series



- Endurance : 105 ℃ 5000 h to 10000 h
- Low ESR, Miniaturized (1 size smaller than series FR)
- RoHS compliant



Country of origin


Malaysia

Specifications		10 % to 1105 %									
Category temp. range	_40 ℃ to +105 ℃										
Rated voltage range		6.3 V to 100 V									
Capacitance range		27 μF to 10000 μF									
Capacitance tolerance		±20 % (120 Hz / +20℃)									
Leakage current		$I \leq 0.01 \text{ CV} (\mu A) \text{ After 2 minutes}$									
	Rated voltage (V)	6.3 10 16 25 35 50 63 80 100	(100 H → /+00°C)								
Dissipation factor (tan δ)	Dissipation factor (tan δ)	0.22 0.19 0.16 0.14 0.12 0.10 0.09 0.08 0.08	(120 Hz /+20℃)								
	For capacitance value ≥ 1000	For capacitance value $\ge 1000 \mu$ F, add 0.02 per every 1000 μ F.									
	After following life test with DC	voltage and +105 ℃±2 ℃ ripple current value applied									
	(The sum of DC and ripple peak voltage shall not exceed the rated working voltage) when the										
	capacitors are restored to 20 $^{\circ}$ C, the capacitors shall meet the limits specified bellow.										
	Duration										
	ø5×11, ø6.3×11.2 : 5000 h										
Endurance	ø8×11.5, ø10×12.5 : 6000 h										
Enduranoo	,	ø8×15, ø10×16 : 8000 h, ø8×20 : 9000 h									
	ø10×10, ø10×10, o000 h, ø8×20 : 9000 h ø10×20 to ø10×25, ø12.5×20 to ø12.5×35, ø16×20 to ø16×25 : 10000 h										
		Within ±25 % of the initial value (6.3 V to 10 V : ±30 %)									
	Dissipation factor (tan δ) $\leq 200 \%$ of the initial limit										
	DC leakage current Within the initial limit										
	After storage for 1000 h at +105 $C\pm 2$ C with no voltage applied and then being										
Shelf life	stabilized at +20 °C, capacitors	shall meet the limits specified in endurance.									
	(With voltage treatment)										

Frequency correction factor for ripple current

Freq. (Hz) Cap. (μF)	60	120	1 k	10 k	100 k to
27 to 33	0.45	0.55	0.75	0.90	1.00
47 to 330	0.60	0.70	0.85	0.95	1.00
390 to 1000	0.65	0.75	0.90	0.98	1.00
1200 to 10000	0.75	0.80	0.95	1.00	1.00

Dimensions



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

Case size / Impedance / Ripple current

R. voltage		6.3 V to 3	5 V		50 V						
Case size (mm)	•	dance ^{*1} Ω)	Ripple current ^{*1} (mA rms)		lance ^{*1} Ω)	Ripple current ^{*1} (mA rms)					
(øD×Ĺ)	+20 ℃	-10 ℃	+105 ℃	+20 ℃	-10 ℃	+105 ℃					
5 × 11	0.300	1.000	280	0.340	1.130	250					
6.3 × 11.2	0.130	0.430	455	—	—	—					
8 × 11.5	0.056	0.168	950	—	—	—					
8 × 15	0.041	0.123	1240	0.045	0.135	1140					
8 × 20	0.030	0.090	1560	0.033	0.099	1430					
10 × 12.5	0.043	0.114	1290	—		_					
10 × 16	0.028	0.078	1790	—	—	_					
10 × 20	0.020	0.057	2180	0.023	0.069	1890					
10 × 25	0.018	0.054	2470	0.022	0.066	2150					
12.5 × 20	0.018	0.045	2600	—	—	_					
12.5 × 25	0.015	0.038	3190	0.018	0.045	2660					
12.5 × 30	0.013	0.033	3630	0.016	0.040	3160					
12.5 × 35	0.012	0.030	3750	0.014	0.035	3270					
16 × 20	0.017	0.043	3300	—	_						
16 × 25	0.014	0.035	3820	0.016	0.040	3320					

R. voltage		63 V		80 V to 100 V				
Case size (mm)		lance ^{*1} Ω)	Ripple current ^{*1} (mA rms)	Imped ۱	ance ^{*1} 2)	Ripple current ^{*1} (mA rms)		
(øD×L)	+20 ℃	-10 ℃	+105 °C	+20 ℃	-10 °C	+105 ℃		
5 × 11	0.510	2.040	175	—	—	—		
6.3 × 11.2	—	—	—		—	—		
8 × 11.5	_	—	—	0.160	0.720	490		
8 × 15	0.068	0.272	741	0.112	0.504	590		
8 × 20	0.050	0.200	930	0.096	0.432	810		
10 × 12.5	0.063	0.252	761	0.112	0.448	600		
10 × 16	0.045	0.180	1073	0.072	0.288	930		
10 × 20			—	0.054	0.224	1120		
10 × 25	0.033	0.132	1500	0.044	0.176	1200		
12.5 × 20	0.033	0.125	1582	0.043	0.135	1400		
12.5 × 25	0.027	0.092	1995	0.034	0.108	1800		
12.5 × 30		—	—	0.030	0.099	2200		
12.5 × 35	0.021	0.071	2780	0.023	0.070	2380		
16 × 20	0.029	0.093	2153	0.032	0.108	1450		
16 × 25	0.024	0.074	2988	0.025	0.076	2500		

*1: 100 kHz

Cha	racteristi	cs list	t										
Rated	Capacitance	Case size (mm)		Specification			Lead length (mm)					Min. Packaging Q'ty(PCS)	
voltage (V)	(±20 %) (μF)	øD	L	Ripple current ^{*1} (mA rms)	Impe- dance ^{*2} (Ω)	Endu- rance (h)	Lead dia. (ød)	Straight	ead spac Taping *B	Taping	Part No.	Straight leads	Taping
	220	5.0	11.0	280	0.300	5000	0.5	2.0	5.0	2.5	EEUFS0J221()	200	2000
	1500	8.0	15.0	1240	0.041	8000	0.6	3.5	5.0	_	EEUFS0J152L()	200	1000
	1500	10.0	12.5	1290	0.043	6000	0.6	5.0	5.0	_	EEUFS0J152()	200	500
	1800	8.0	20.0	1560	0.030	9000	0.6	3.5	5.0	_	EEUFS0J182L()	200	1000
	2000	8.0	20.0	1560	0.030	9000	0.6	3.5	5.0	_	EEUFS0J202L()	200	1000
	2000	10.0	16.0	1790	0.028	8000	0.6	5.0	5.0	—	EEUFS0J202()	200	500
	2200	10.0	16.0	1790	0.028	8000	0.6	5.0	5.0	_	EEUFS0J222()	200	500
	2700	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0	_	EEUFS0J272()	200	500
	3300	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0	—	EEUFS0J332()	200	500
	3900	10.0	25.0	2470	0.018	10000	0.6	5.0	5.0	—	EEUFS0J392L()	200	500
6.3	4700	12.5	20.0	2600	0.018	10000	0.6	5.0	5.0	—	EEUFS0J472()	200	500
	5100	12.5	25.0	3190	0.015	10000	0.6	5.0	5.0	—	EEUFS0J512()	200	500
	5600	12.5	25.0	3190	0.015	10000	0.6	5.0	5.0	—	EEUFS0J562()	200	500
	6200	12.5	30.0	3630	0.013	10000	0.8	5.0		—	EEUFS0J622L	100	—
	6800	12.5	30.0	3630	0.013	10000	0.8	5.0		—	EEUFS0J682L	100	—
	7500	12.5	35.0	3750	0.012	10000	0.8	5.0		_	EEUFS0J752L	100	—
	7300	16.0	20.0	3300	0.017	10000	0.8	7.5	7.5	—	EEUFS0J752S()	100	250
	8200	12.5	35.0	3750	0.012	10000	0.8	5.0		_	EEUFS0J822L	100	—
	0200	16.0	20.0	3300	0.017	10000	0.8	7.5	7.5	—	EEUFS0J822S()	100	250
	9100	16.0	25.0	3820	0.014	10000	0.8	7.5	7.5	_	EEUFS0J912()	100	250
	10000	16.0	25.0	3820	0.014	10000	0.8	7.5	7.5	_	EEUFS0J103()	100	250
	180	5.0	11.0	280	0.300	5000	0.5	2.0	5.0	2.5	EEUFS1A181()	200	2000
	330	6.3	11.2	455	0.130	5000	0.5	2.5	5.0	2.5	EEUFS1A331()	200	2000
	820	8.0	11.5	950	0.056	6000	0.6	3.5	5.0		EEUFS1A821()	200	1000
	1000	10.0	12.5	1290	0.043	6000	0.6	5.0	5.0	_	EEUFS1A102()	200	500
	1200	8.0	15.0	1240	0.041	8000	0.6	3.5	5.0	_	EEUFS1A122L()	200	1000
	1200	10.0	12.5	1290	0.043	6000	0.6	5.0	5.0	_	EEUFS1A122()	200	500
	1800	8.0	20.0	1560	0.030	9000	0.6	3.5	5.0		EEUFS1A182L()	200	1000
	1000	10.0	16.0	1790	0.028	8000	0.6	5.0	5.0		EEUFS1A182()	200	500
10	2000	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0	_	EEUFS1A202()	200	500
10	2200	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0	_	EEUFS1A222()	200	500
	2700	10.0	25.0	2470	0.018	10000	0.6	5.0	5.0	_	EEUFS1A272L()	200	500
	3600	12.5	20.0	2600	0.018	10000	0.6	5.0	5.0		EEUFS1A362()	200	500
	4700	12.5	25.0	3190	0.015	10000	0.6	5.0	5.0	_	EEUFS1A472()	200	500
	5100	12.5	30.0	3630	0.013	10000	0.8	5.0		—	EEUFS1A512L	100	_
	5600	12.5	30.0	3630	0.013	10000	0.8	5.0		—	EEUFS1A562L	100	—
	5000	16.0	20.0	3300	0.017	10000	0.8	7.5	7.5	—	EEUFS1A562S()	100	250
	7500	12.5	35.0	3750	0.012	10000	0.8	5.0		_	EEUFS1A752L	100	—
	8200	16.0	25.0	3820	0.014	10000	0.8	7.5	7.5	_	EEUFS1A822()	100	250

*1: Ripple current (100 kHz / +105 $^{\circ}\mathrm{C})$

*2: Impedance (100 kHz / +20 °C)

• When requesting taped product, please put the letter "B" or "H" be tween the "()". Lead wire pitch *B=5 mm, 7.5 mm, H=2.5 mm.

• Please refer to the page of "Taping dimensions".

Characteristics list														
Rated	Capacitance (±20 %)	-	e size m)	S	pecificatio	on			igth (mm) ead spac		Part No.		Min. Packaging Q'ty(PCS)	
voltage (V)	(±20 %) (μF)	øD	L	Ripple current ^{*1} (mA rms)	Impe- dance ^{*2} (Ω)	Endu- rance (h)	Lead dia. (ød)	Straight	Taping *B	æ Taping ★H	Fait NU.	Straight leads	Taping	
	120	5.0	11.0	280	0.300	5000	0.5	2.0	5.0	2.5	EEUFS1C121()	200	2000	
	510	8.0	11.5	950	0.056	6000	0.6	3.5	5.0		EEUFS1C511()	200	1000	
	820	8.0	15.0	1240	0.041	8000	0.6	3.5	5.0	—	EEUFS1C821L()	200	1000	
	020	10.0	12.5	1290	0.043	6000	0.6	5.0	5.0	_	EEUFS1C821()	200	500	
	1200	8.0	20.0	1560	0.030	9000	0.6	3.5	5.0		EEUFS1C122L()	200	1000	
		10.0	16.0	1790	0.028	8000	0.6	5.0	5.0	_	EEUFS1C122()	200	500	
10	1800	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0		EEUFS1C182()	200	500	
16	2200	10.0	25.0	2470	0.018	10000	0.6	5.0	5.0		EEUFS1C222L()	200	500	
	2400	12.5	20.0	2600	0.018	10000	0.6	5.0	5.0		EEUFS1C242()	200	500	
	3300	12.5	25.0	3190	0.015	10000	0.6	5.0	5.0		EEUFS1C332()	200	500	
	3600 3900	12.5 12.5	30.0	3630 3630	0.013	10000	0.8	5.0 5.0		_	EEUFS1C362L	100 100		
	4700	12.5	30.0	3300	0.013	10000 10000	0.8	5.0 7.5	— 7.5	_	EEUFS1C392L EEUFS1C472S()	100		
	5100	10.0	20.0 35.0	3750	0.017	10000	0.8	7.5 5.0			EEUFS1C4725() EEUFS1C512L	100	250	
	6200	12.5	25.0	3820	0.012	10000	0.8	7.5	— 7.5	_	EEUFS1C622()	100	250	
	1200	10.0	20.0	2180	0.014	10000	0.6	5.0	5.0		EEUFS1E122()	200	500	
	2200	12.5	25.0	3190	0.020	10000	0.0	5.0	5.0	_	EEUFS1E222()	200	500	
25	3300	12.5	35.0	3750	0.013	10000	0.0	5.0		_	EEUFS1E332L	100	- 500	
	3900	16.0	25.0	3820	0.012	10000	0.8	7.5	7.5		EEUFS1E392()	100	250	
	330	8.0	15.0	1240	0.041	8000	0.6	3.5	5.0		EEUFS1V331L()	200	1000	
	820	10.0	20.0	2180	0.020	10000	0.6	5.0	5.0	_	EEUFS1V821()	200	500	
	1000	10.0	25.0	2470	0.018	10000	0.6	5.0	5.0	_	EEUFS1V102L()	200	500	
35	1500	12.5	25.0	3190	0.015	10000	0.6	5.0	5.0		EEUFS1V152()	200	500	
	1800	16.0	20.0	3300	0.017	10000	0.8	7.5	7.5	_	EEUFS1V182S()	100	250	
	2700	16.0	25.0	3820	0.014	10000	0.8	7.5	7.5	_	EEUFS1V272()	100	250	
	27	5.0	11.0	250	0.340	5000	0.5	2.0	5.0	2.5	EEUFS1H270()	200	2000	
	150	8.0	15.0	1140	0.045	8000	0.6	3.5	5.0		EEUFS1H151L()	200	1000	
	220	8.0	20.0	1430	0.033	9000	0.6	3.5	5.0		EEUFS1H221L()	200	1000	
	330	10.0	20.0	1890	0.023	10000	0.6	5.0	5.0	_	EEUFS1H331()	200	500	
50	390	10.0	25.0	2150	0.022	10000	0.6	5.0	5.0		EEUFS1H391L()	200	500	
	680	12.5	25.0	2660	0.018	10000	0.6	5.0	5.0	_	EEUFS1H681()	200	500	
	820	12.5	30.0	3160	0.016	10000	0.8	5.0	—		EEUFS1H821L	100	_	
	1000	12.5	35.0	3270	0.014	10000	0.8	5.0	—		EEUFS1H102L	100		
	1200	16.0	25.0	3320	0.016	10000	0.8	7.5	7.5		EEUFS1H122()	100	250	
	27	5.0	11.0	175	0.510	5000	0.5	2.0	5.0	2.5	EEUFS1J270()	200	2000	
	120	8.0	15.0	741	0.068	8000	0.6	3.5	5.0		EEUFS1J121L()	200	1000	
	120	10.0	12.5	761	0.063	6000	0.6	5.0	5.0		EEUFS1J121()	200	500	
	180	8.0	20.0	930	0.050	9000	0.6	3.5	5.0		EEUFS1J181L()	200	1000	
		10.0	16.0	1073	0.045	8000	0.6	5.0	5.0		EEUFS1J181()	200	500	
63	330	10.0	25.0	1500	0.033	10000	0.6	5.0	5.0		EEUFS1J331L()	200	500	
	390	12.5	20.0	1582	0.033	10000	0.6	5.0	5.0		EEUFS1J391()	200	500	
	560	12.5	25.0	1995	0.027	10000	0.6	5.0	5.0		EEUFS1J561()	200	500	
	680	16.0	20.0	2153	0.029	10000	0.8	7.5	7.5		EEUFS1J681S()	100	250	
	820	12.5	35.0	2780	0.021	10000	0.8	5.0	-		EEUFS1J821L	100	-	
	1000	16.0	25.0	2988	0.024	10000	0.8	7.5	7.5	—	EEUFS1J102()	100	250	

*1: Ripple current (100 kHz / +105 °C)

1.41.41

...

*2: Impedance (100 kHz / +20 °C)

• When requesting taped product, please put the letter "B" or "H" be tween the "()". Lead wire pitch *B=5 mm, 7.5 mm, H=2.5 mm.

• Please refer to the page of "Taping dimensions".

Characteristics list												
Rated	Capacitance	Case size (mm)		Specification			Lea	d length	(mm)		Min. Pa Q'ty	ckaging (PCS)
voltage (V)	(±20 %) (µF)	øD	L	Ripple current ^{*1} (mA rms)	Impe- dance ^{*2} (Ω)	Endu- rance (h)	Lead dia. (ød)	Lead Straight	space Taping *B	Part No.	Straight leads	Taping
	47	8.0	11.5	490	0.160	6000	0.6	3.5	5.0	EEUFS1K470()	200	1000
	56	8.0	11.5	490	0.160	6000	0.6	3.5	5.0	EEUFS1K560()	200	1000
	68	8.0	15.0	590	0.112	8000	0.6	3.5	5.0	EEUFS1K680()	200	1000
	82	8.0	15.0	590	0.112	8000	0.6	3.5	5.0	EEUFS1K820()	200	1000
	100	8.0	20.0	810	0.096	9000	0.6	3.5	5.0	EEUFS1K101L()	200	1000
	100	10.0	12.5	600	0.112	6000	0.6	5.0	5.0	EEUFS1K101()	200	500
	120	8.0	20.0	810	0.096	9000	0.6	3.5	5.0	EEUFS1K121L()	200	1000
	150	10.0	16.0	930	0.072	8000	0.6	5.0	5.0	EEUFS1K151()	200	500
	180	10.0	20.0	1120	0.054	10000	0.6	5.0	5.0	EEUFS1K181()	200	500
80	000	10.0	20.0	1120	0.054	10000	0.6	5.0	5.0	EEUFS1K221()	200	500
	220	10.0	25.0	1200	0.044	10000	0.6	5.0	5.0	EEUFS1K221L()	200	500
	070	10.0	25.0	1200	0.044	10000	0.6	5.0	5.0	EEUFS1K271L()	200	500
	270	12.5	20.0	1400	0.043	10000	0.6	5.0	5.0	EEUFS1K271()	200	500
	390	12.5	25.0	1800	0.034	10000	0.6	5.0	5.0	EEUFS1K391()	200	500
	470	12.5	30.0	2200	0.030	10000	0.8	5.0		EEUFS1K471L()	100	_
	470	16.0	20.0	1450	0.032	10000	0.8	7.5	7.5	EEUFS1K471S()	100	250
	560	12.5	35.0	2380	0.023	10000	0.8	5.0		EEUFS1K561L()	100	_
	680	16.0	25.0	2500	0.025	10000	0.8	7.5	7.5	EEUFS1K681()	100	250
	27	8.0	11.5	490	0.160	6000	0.6	3.5	5.0	EEUFS2A270()	200	1000
	33	8.0	11.5	490	0.160	6000	0.6	3.5	5.0	EEUFS2A330()	200	1000
	39	8.0	15.0	590	0.112	8000	0.6	3.5	5.0	EEUFS2A390()	200	1000
	47	8.0	15.0	590	0.112	8000	0.6	3.5	5.0	EEUFS2A470L()	200	1000
	47	10.0	12.5	600	0.112	6000	0.6	5.0	5.0	EEUFS2A470()	200	500
	56	8.0	20.0	810	0.096	9000	0.6	3.5	5.0	EEUFS2A560L()	200	1000
	68	8.0	20.0	810	0.096	9000	0.6	3.5	5.0	EEUFS2A680L()	200	1000
	00	10.0	16.0	930	0.072	8000	0.6	5.0	5.0	EEUFS2A680()	200	500
100	120	10.0	20.0	1120	0.054	10000	0.6	5.0	5.0	EEUFS2A121()	200	500
100	120	10.0	25.0	1200	0.044	10000	0.6	5.0	5.0	EEUFS2A121L()	200	500
	450	10.0	25.0	1200	0.044	10000	0.6	5.0	5.0	EEUFS2A151L()	200	500
	150	12.5	20.0	1400	0.043	10000	0.6	5.0	5.0	EEUFS2A151()	200	500
	180	12.5	25.0	1800	0.034	10000	0.6	5.0	5.0	EEUFS2A181()	200	500
	220	12.5	25.0	1800	0.034	10000	0.6	5.0	5.0	EEUFS2A221()	200	500
	070	12.5	30.0	2200	0.030	10000	0.8	5.0	—	EEUFS2A271L()	100	_
	270	16.0	20.0	1450	0.032	10000	0.8	7.5	7.5	EEUFS2A271S()	100	250
	330	12.5	35.0	2380	0.023	10000	0.8	5.0	—	EEUFS2A331L()	100	_
	390	16.0	25.0	2500	0.025	10000	0.8	7.5	7.5	EEUFS2A391()	100	250

*1: Ripple current (100 kHz / +105 $^{\circ}$ C)

*2: Impedance (100 kHz / +20 °C)

• When requesting taped product, please put the letter "B" be tween the "()". Lead wire pitch *B=5 mm, 7.5 mm.

• Please refer to the page of "Taping dimensions".

Safety and Legal Matters to Be Observed

Product specifications and applications

- Please be advised that this product and product specifications are subject to change without notice for improvement purposes. Therefore, please request and confirm the latest delivery specifications that explain the specifications in detail before the final design, or purchase or use of the product, regardless of the application. In addition, do not use this product in any way that deviates from the contents of the company's delivery specifications.
- Unless otherwise specified in this catalog or the product specifications, this product is intended for use in general electronic equipment (AV products, home appliances, commercial equipment, office equipment, information and communication equipment, etc.).

When this product is used for the following special cases, the specification document suited to each application shall be signed/sealed (with Panasonic and the user) in advance..These include applications requiring special quality and reliability, wherein their failures or malfunctions may directly threaten human life or cause harm to the human body (e.g.: space/aircraft equipment, transportation/traffic equipment, combustion equipment, medical equipment, disaster prevention/crime prevention equipment, safety equipment, etc.).

Safety design and product evaluation

- Please ensure safety through protection circuits, redundant circuits, etc., in the customer's system design so that a defect in our company's product will not endanger human life or cause other serious damage.
- This catalog shows the quality and performance of individual parts. The durability of parts varies depending on the usage environment and conditions. Therefore, please ensure to evaluate and confirm the state of each part after it has been mounted in your product in the actual operating environment before use. If you have any doubts about the safety of this product, then please notify us immediately, and be sure to conduct a technical review including the above protection circuits and redundant circuits at your company.

Laws / Regulations / Intellectual property

- The transportation of dangerous goods as designated by UN numbers, UN classifications, etc., does not apply to this product. In addition, when exporting products, product specifications, and technical information described in this catalog, please comply with the laws and regulations of the countries to which the products are exported, especially those concerning security export control.
- Each model of this product complies with the RoHS Directive (Restriction of the use of hazardous substances in electrical and electronic equipment) (2011/65/EU and (EU) 2015/863). The date of compliance with the RoHS Directive and REACH Regulation varies depending on the product model. Further, if you are using product models in stock and are not sure whether or not they comply with the RoHS Directive or REACH Regulation, please contact us by selecting "Sales Inquiry" from the inquiry form.
- During the manufacturing process of this product and any of its components and materials to be used, Panasonic does not intentionally use ozone-depleting substances stipulated in the Montreal Protocol and specific bromine-based flame retardants such as PBBs (Poly-Brominated Biphenyls) / PBDEs (Poly-Brominated Diphenyl Ethers). In addition, the materials used in this product are all listed as existing chemical substances based on the Act on the Regulation of Manufacture and Evaluation of Chemical Substances.
- With regard to the disposal of this product, please confirm the disposal method in each country and region where it is incorporated into your company's product and used.
- The technical information contained in this catalog is intended to show only typical operation and application circuit examples of this product. This catalog does not guarantee that such information does not infringe upon the intellectual property rights of Panasonic or any third party, nor imply that the license of such rights has been granted.

Panasonic Industry will assume no liability whatsoever if the use of our company's products deviates from the contents of this catalog or does not comply with the precautions. Please be advised of these restrictions.

Matters to Be Observed When Using This Product

(Conductive polymer hybrid aluminum electrolytic capacitor / Aluminum electrolytic capacitor)

Use environments and cleaning conditions

This product (capacitor) is intended for standard general-purpose use in electronic equipment, and is not designed for use in the specific environments described below. Using the product in such specific environments or service conditions, therefore, may affect the performance of the product.

Check with us about the performance and reliability of the product first before using the product.

- (1) Used at a temperature higher than the upper limit category temperature or lower than the lower limit category temperature.
- (2) Used in an environment where the product is directly exposed to water, salt water, oil, etc., or in a liquid, such as water, oil, chemicals, and organic solvents.
- (3) Used in an outdoor environment where the product is exposed to direct sunlight, ozone, radiation, UV-rays, etc., or in a dusty place.
- (4) Used in a wet place (dew concentration on a resistor, water leakage, etc.), a place exposed to sea breeze, or a place filled with a corrosive gas, such as Cl₂, H₂S, NH₃, SO₂, or NO_X.
- (5) Used in an environment filled with a toxic gas (hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and chlorine compound, bromine and bromine compound, ammonia, etc.)
- (6) Used in an environment where static electricity and electromagnetic waves are strong.
- (7) Located close to heating component or a flammable material, such as a vinyl cable.
- (8) Sealed with a resin, etc.
- (9) Cleansed with a solvent, water, or a water-soluble cleaner, to remove solder flux after soldering.
- (10) Used in an environment where an acidic or alkali atmosphere is present.
- (11) Used in an environment where excessive vibration or mechanical shocks exceeding a specified range is applied to the product (even if the applied vibration or mechanical shocks is within the specified range, it may cause the product to resonate, in which a large vibration acceleration may be generated. Make sure to evaluate/check such vibrations or impacts applied to the product in an actual service condition).
- (12) Used under a low atmospheric pressure condition or depressurized condition.
- The capacitor withstands an immersion cleaning process where the board carrying the product is immersed in a cleaning solution of 60 °C or lower for less than 5 minutes and withstands an ultrasonic cleaning process as well. However, ensure to thoroughly rinse and dry it. Some cleaning methods erase or blur notes on the capacitor in some cases. Some types of capacitors are not washable and some cleaning solutions cannot be used to clean a capacitor. If you are not sure about which type of capacitor is not washable or which cleaning solution cannot be used, please contact us. Solvents you can use to clean the board are as follows.

Pine Alpha ST-100S, Aqua Cleaner 210SEP, Cleanthrough 750H/750L/710M, Sun Elec B-12, Techno Cleaner 219, Cold Cleaner P3-375, DK Be clear CW-5790, Terpene Cleaner EC-7R, Techno Care FRW-17/FRW-1/FRV-1

- Keep the cleaning solution under strict contamination control (conductivity, pH, specific gravity, water content, etc.). A contaminated cleaning solution will show a high chlorine concentration, thereby corroding the interior of the capacitor in some cases. Keep the flux concentration in the cleaning solution at a 2% mass or less.
- Unless otherwise specified in the specifications, avoid cleaning the capacitor with a halogen-based solvent, an alkaline solvent, a petroleum-based solvent, xylene, or acetone. Using a halogen-based solvent may result in a case where the solvent infiltrates (leaks) into the capacitor and break-down releasing chlorine, which reacts with aluminum which can corrode the capacitor interior. 1-1-1 trichloroethane is particularly harmful to a capacitor. Never use it to clean a capacitor. A alkaline solvent may corrode (dissolve) an aluminum case, a petroleum-based solvent and xylene may damage the sealing rubber and accelerate its deterioration, and acetone may erase notes on the capacitor.
- Right after the board cleaning, subject the capacitor to a forced drying process so that no cleaning solution remains between the sealing part of the capacitor and the printed board. Set a drying temperature equal to or lower than the upper limit category temperature.
- When an adhesive or coating agent is used to fix the capacitor and prevent dampening of the board, specific types of solvents included in some adhesives or coating agents may corrode the capacitor. Select a non-halogen solvent for the material making up the adhesive or coating agent. Do not use a chloroprene-based polymer. Solidify and dry the adhesive or coating agent sufficiently to prevent its solvent component from remaining on the capacitor. Leave at least 1/3 of the sealing part unsealed on the surface to which the adhesive or coating agent is applied.

- Do not use the product in a structure sealed by potting or molding. The pressure of a molding resin on a capacitor may deform the capacitor. In addition, the resin covering the capacitor may affect its heat dissipation performance or may leak into the product. These factors lead to the significant degradation of the capacitor's characteristics and reliability. There is also a concern that an electrolytic solution permeating the sealing rubber may agglomerate and cause a short circuit.
- When the capacitor is used in a circuit where an impact voltage is applied or a high voltage is applied in a short period (transient phenomenon) or a high pulse voltage is applied, make sure to use the capacitor at a voltage equal to or lower than its rated voltage.
- The product contains an electrolytic. Improper use of the capacitor leads not only to the rapid degradation of its characteristics but also to electrolytic leakage. These problems damage the circuit board and may lead to destruction of the entire circuit set.

Response to anomalies and handling conditions

- When you see gas coming out of an activated pressure relief valve of a capacitor during use of a circuit set, turn off the main power supply of the circuit set or pull the power cord plug out of the wall-outlet. If you leave the power supply on and the capacitor short-circuits, it will damage the circuit, or the gas can turn into a liquid, which will cause the circuit to short. In the worst case scenarios, these events may develop into a more serious incident, such as burnout of the circuit set. The gas coming out of the pressure relief valve of a capacitor is not smoke, but is the electrolytic solution in its gaseous state.
- When the pressure valve of the capacitor is activated, it emits a high-temperature gas of over 100 °C. Do not bring your face near the valve. In case the gas jetting out of the valve gets in your eyes or comes into your mouth, wash your eyes with water or rinse your mouth immediately. If the gas hits your skin, wash it away with soap.
- If you touch a terminal of the product during use of the circuit set, you will get an electric shock. The aluminum case of the product has an exposed part with no insulation. Do not touch the exposed part because it is as dangerous as the terminal.
- Do not create a short circuit between terminals of the product by inserting a conductor therebetween. Do not splash a conductive solution, such as an acidic or alkali solution, on the capacitor. It puts the capacitor in a shorted state, which causes the circuit to fail and destroys the capacitor as well.
- When a silicone material containing a relatively large amount of a low-molecular-weight siloxane is located close to the product, it may cause the capacitor problems with its electrical performance.
- When electronic equipment having the capacitor built therein is exported to overseas markets, wooden packaging materials are fumigated with a halogen compound, such as methyl bromide. In such cases, if the packaging material subjected to the fumigation treatment is not dried sufficiently, halogen remaining on the packaging material may leach into the capacitor during transportation and trigger a corrosive reaction in the capacitor. When carrying out the fumigation treatment, carefully examine the dried packaging material to confirm that no halogen remains on the packaging material. Never fumigate the entire electronic equipment in its packaged state.

Reliability and product life

- The product life is affected by temperatures. In general, a 10 °C drop in the temperature will double the life. Use the capacitor at a temperature as low as possible from the upper limit category temperature.
- Using a capacitor under a temperature condition outside a specified temperature range causes heavy degradation of the capacitor characteristics, which may result in breakage of the capacitor. You need to confirm not only the ambient temperature and internal temperature of the capacitor but also the temperature of the capacitor's top surface, which is given by radiant heat from built-in heating elements (a power transistor, IC, resistance, etc.) and heat generated by self-heating induced by ripple current. Do not place a heating element on the back of the capacitor.

The product life is given by the following equation.

T1-(T2+⊿T) $|2| = |1| \times |2|$

- L1 : Guaranteed life (h) at temperature T₁ (°C)
- L2 : Expected life (h) at temperature T_2 (°C)
- T1 : Upper category temperature (°C)
- T2 : Ambient temperature of capacitor (°C)
- ∠T : Temperature increase caused by ripple current (°C)

≥

- Do not use the product for a period longer than its specified service life. A capacitor with its service life ended may cause the following problems: rapid degradation of the product characteristics, short circuit, unnecessary activation of the pressure valve, electrolytic solution leakage, etc. Note that the estimated service life is not longer than 15 years due to the limited environment-resistant property of the sealing rubber.
- When the capacitor is used under a high-temperature condition for a long period, minute cracks develop on the surface of the sealing rubber or the case surface turns brown in some cases. These phenomena, however, have no effects on the reliability of the capacitor.
- A capacitor conforming to "AEC-Q200" refers to a capacitor having passed some or all of evaluation test items defined in AFC-Q200

To know the detailed specifications of each capacitor or specific evaluation test scores, please contact us. We issue a the product specifications sheet for each product ordered. Please confirm the product specifications sheet when you place an order to us.

Circuit design and circuit board design

The electrical characteristics change as a result of temperature/frequency fluctuations. Take electrical characteristic changes into consideration when working out a circuit design.

(1) Temperature fluctuations	
High-temperature condition	: increase in leak current
Low-temperature condition	: decrease in capacitance, increase in the tangent to the loss angle, increase in impedance (the hybrid type is excluded), etc.
(2) Frequency fluctuations	
High-frequency condition	: decrease in capacitance, increase in the tangent to the loss angle, decrease in impedance, etc.
Low-frequency condition	: more heat generation by ripple current as a result of an increase in equivalent series resistance

- The group of factors described below may lead to rapid degradation of the capacitor characteristics, short circuit, or electrolytic solution leakage. They may give rise to sharp heat/gas generation, too, in which case the increasing internal pressure actuates the pressure valve, causes the electrolytic solution to leak out of the sealing part, and, in a worst-case scenario, causes an explosion or ignition incident. When a capacitor bursts, it may scatter flammable materials (electrolytic solution, etc.) in its surroundings.
 - (1) Reverse voltage: The capacitor has preset polarity. Do not apply a reverse voltage to the capacitor. Confirm the polarity indicated on the capacitor and then use it.
 - (2) Charge/discharge: Avoid using the capacitor in a circuit that frequently repeats sharp charge/discharge cycles or a circuit that requires relatively slow but highly frequent charge/discharge cycles. In cases where you use the capacitor in such circuits, make sure to inform us of the charge/discharge conditions. Ensure that a rush current does not exceed 100 A.
 - (3) ON/OFF: Avoid using the capacitor in an on/off circuit that repeatedly switches on and off more than 10,000 times a day. In cases where you use the product in such circuits, make sure to inform us of the circuit conditions, etc.
 - (4) Overvoltage: Do not apply an overvoltage higher than the rated voltage (higher than the surge voltage when the voltage application period is short). A peak value given by superposing a ripple voltage (AC component) on a DC voltage must be equal to or lower than the rated voltage.
 - (5) Ripple current: Do not allow an excessively large ripple current (larger than the rated ripple current specified in the specifications) to flow through the capacitor. Even if a ripple current flow in the capacitor is equal to or smaller than the rated ripple current, a reverse voltage flow may be generated in the capacitor when the DC bias voltage is low flow in the capacitor. Keep the ripple current flow within a range in which no reverse voltage is generated. Even if the ripple current flow is kept equal to or smaller than the rated ripple current, using the capacitor for a period longer than its service life intensifies the degradation of the ESR characteristics, resulting in an increase in internal heating caused by the ripple current. As a result, the pressure valve is actuated, the exterior case or rubber swells, the electrolytic solution leaks, and, in a worst-case scenario, the capacitor short-circuits and ignites or explodes.

- * In the case of a hybrid type, category temperature (°C)
- + temperature increase caused by rated ripple current (°C)

- Because the impedance of the capacitor is close to the circuit impedance, capacitors connected in parallel in the circuit may damage the whole current balance, in which, a ripple current higher than the rated ripple current may flow in some of the capacitors. To prevent concentration of ripple current on the low-impedance side, use capacitors with the same part number and avoid the partiality of cable impedances. Do not use capacitors connected in series.
- When the capacitor is mounted on a double-side wiring board, do not place the wiring pattern directly underneath where the product is mounted. In case the electrolytic solution leaks out, it may short-circuit the pattern and cause tracking or migration. Consider a case where the product is a radial lead capacitor and is mounted on a board with through-holes. In this case, if the sealing part of the capacitor and the board surface stick close to each other, solder flows up to the capacitor during a dip soldering process, which may cause short circuit between the anode and cathode of the capacitor. In such a case, the outer laminate of the product may be damaged. The position of holes, therefore, must be determined properly.
- When designing a printed board carrying radial lead capacitors, make through-holes across the gap equal to the gap between the leads (terminals) of the capacitor. If the gap between the through-holes is narrower or wider than the gap between the leads, stress is applied to the leads when the capacitor is inserted in the holes. This may result in increasing leak current, short circuit, wire breaking, or electrolytic solution leakage.
- A capacitor which has the pressure valve on the case must be provided with a space formed above the pressure valve so that the pressure valve operates without hinderance. When the product is 6.3 mm to 16 mm in diameter, form a space of 2 mm or larger. When the product is 18 mm in diameter, form a space of 3 mm or larger. If the space is not large enough, it will impair the operability of the pressure valve and may lead to an explosion incident.
- Design the circuit in such that the pattern, especially a line pattern carrying high voltage or large current, is not formed above the pressure valve. Upon its activation, the pressure valve emits a flammable high-temperature gas of over 100 °C. This may cause a secondary accident, such as the gas condensing on the pattern and the wire sheathing being melted and catching on fire.
- Be careful with resonance of the capacitor mounted on the board. When a large load is applied to the capacitor at the frequency close to the resonance frequency, it may cause the capacitor to come off or widely change its characteristics.
- Completely isolate the case of the capacitor from the cathode terminal and the circuit pattern.
- The laminate or outer sleeve covering of the product is for displaying information on the product and does not have a guaranteed insulating function.

The laminate may turn brown under a high-temperature condition. However, that does not cause problems with markings recognition on the product surface or electrical performance.

The outer sleeve may crack when dipped in a xylene or toluene solution and exposed to high temperature.

Mounting conditions

Do not reuse a capacitor that was incorporated in a circuit set and energized in the past. Do not use a capacitor that was dropped on the floor.

Do not use a capacitor in its compressed form. Compressing the capacitor makes it less airtight, resulting in poor performance, shorter guaranteed life, and electrolyte leakage.

- A re-striking voltage is generated in a capacitor in some cases. In such a case, let the capacitor discharge through a resistor of about 1 kΩ.
- When a capacitor is kept in storage for a long period, you may find the leak current from the capacitor has increased. In such a case, make voltage adjustment through a resistor of about 1 kΩ.
- Before mounting the capacitor on the board, confirm the ratings (capacitance, rated voltage, etc.) and polarity of the capacitor. Before mounting a surface-mounted type capacitor, confirm its terminal dimensions and land size. Before mounting a radial lead type capacitor, confirm its terminal interval and hole interval. If the terminal interval is not the specified one, stress is applied to internal elements, which may cause problems, such as a short circuit and insufficient mounting strength.

When the terminal interval and the hole interval of the radial lead type capacitor do not match and therefore the capacitor's leads need to be readjusted, make sure that the readjustment does not apply any stress to the capacitor's body.

- Confirm the applied pressure when using an automatically mounting process for a surface-mounted type capacitor. Excessive pressure may result in increasing leak current, short circuit, the capacitor coming off from the board, and the like. When automatically mounting the radial lead type capacitor, check the wear of a cutter for cutting the leads and confirm that the angle of clinching the leads is not too acute with regards to the board. Clinching the leads at too acute of an angle applies tensile stress to the leads, which may lead to destruction of the capacitor.
- Follow soldering conditions (preheating, soldering temperature/time, the number of soldering, etc.) in the specification sheet. A high peak temperature or a long heating time causes the degradation of electrical characteristics or a reduction in the guaranteed life. Note that the specified soldering conditions indicate conditions under which the degradation of capacitor characteristics do not occur but do not indicate conditions under which stable soldering can be performed. Check and set conditions under which stable soldering can be performed, on a case-by-case basis. Measure the temperature of the capacitor, using a thermocouple bonded to the top of the capacitor with an epoxy-based adhesive. This temperature measurement must be conducted in a mass-production setup.
- The surface-mounted type capacitor is soldered by reflow soldering only. It cannot be soldered by flow soldering or dip soldering. Carry out reflow soldering with an atmospheric heat transfer method using infrared hot air, etc. When carrying out two rounds of reflow processes, carry out the second reflow process after the capacitor's temperature settles down to a normal temperature. In the case of VPS reflow, a sharp rise in the capacitor temperature causes a change in the characteristics and appearance of the capacitor, which may give rise to a problem with capacitor mounting. We therefore recommend execution of VPS flow at a temperature rise rate of 3 °C/second or lower. For more information about this matter, please contact us.
- Reflow soldering, under the reflow conditions we recommend, might result in discoloring or swelling of the case or crack formation on the ink mark indicating the cathode. These minor problems, however, do not affect the reliability of the capacitor at all.
- A 6.3-mm diameter vibration-resistant capacitor has a structure that covers the auxiliary terminals to the sides of a seat plate. In cases where you confirm formation of a fillet on the sides of the auxiliary terminals by an image recognition means, etc., examine soldering conditions for the formation of a sufficient fillet on the auxiliary terminals in advance before carrying out the soldering process.

Even if the formation of a sufficient fillet on the auxiliary terminals is not confirmed, a solder junction between the lower surface of the auxiliary terminals and the board ensures vibration-resistant performance, meaning the reliability of the capacitor is not affected.

- The radial lead type capacitor cannot be soldered by reflow soldering. Do not dip the capacitor body, except the leads, in solder. Heat from the solder raises the internal pressure of the capacitor and destroys it. Solder the capacitor according to the following soldering conditions: soldering temperature of 260 °C ±5 °C and soldering time of 10 seconds ±1 second.
- Ensure that other components do not come in contact with the capacitor during the soldering process. When a radial lead type capacitor is set in close contact with the board, check the soldered state of the capacitor well, because its sealing rubber has no venting structure.
- When manually soldering the capacitor, follow the soldering conditions (soldering temperature/time) specified in the specification sheet or adopt a soldering temperature of 350 °C and a soldering time of 3 seconds or less. When you need to remove a capacitor already soldered, remove it after the solder is melted sufficiently so that no stress is applied to the terminals of the capacitor. Be careful not to let the solder iron tip touch the capacitor. The solder iron touching the capacitor may damage the capacitor.
- When the temperature of the capacitor becomes extremely high due to preheating, solidification of the setting resin, etc., may cause the outer sleeve of the capacitor to shrink or crack. When treating the capacitor in a thermosetting furnace, etc., place the capacitor in an atmosphere of 150 °C for 2 minutes or less.
- Do not tilt or twist the capacitor soldered to a printed board or hold the capacitor to carry the board or hit the capacitor against something. Such actions apply a force to the internal elements through the terminals and may destroy the product.
- Using highly active halogenous (chlorine-based or bromic) solder flux poses a concern that residual solder flux will have negative impact on the performance and reliability of the capacitor. Check the influence of residual solder flux before using such solder flux.

Storage conditions

A capacitor left for a long period is prone to have a greater flow of leak current. This happens because the oxide film deteriorates under a no-load condition. Voltage application to the capacitor reduces the leak current. However, at the start of voltage application, a large flow of film recovery current increases the leak current, which may cause a circuit failure, etc.

The storage period of a capacitor is 42 months from the shipment inspection day. However, the storage period of capacitors not listed in the following table is specified as 12 months. Store the capacitor in a place where a normal temperature condition (5°C to 35°C) and a normal humidity condition

(45% to 85%) are maintained and direct sunlight is blocked.

Product category	Series	Storage period
Hybrid type	All hybrid series	
Surface-mounted type other than the hybrid type	S (hot lead-free reflow), HA (hot lead-free reflow) HB (hot lead-free reflow, 5.4 mm in height) HC, HD, FCA, FC, FKA, FK, FKS, FP, FT, FH TG, TK, TP, TC, TCU, TQ	42 months from the shipment inspection day
Radial lead type other than the hybrid type	FC-A, FK-A, HD-A, TA-A, TP-A, FP-A	

- Avoid storing the capacitor in environments not specified in the delivery specification sheet or in the following environments or conditions.
 - (1) Used at a temperature higher than the upper limit category temperature or lower than the lower limit category temperature
 - (2) Environments where the capacitor is exposed to water, salt water, or oil
 - (3) Environments where dew concentrates on the capacitor
 - (4) Environments filled with a toxic gas (hydrogen sulfide, sulfurous acid, nitrous acid, chlorine and chlorine compound, bromine and bromine compound, ammonia, etc.)
 - (5) Environments where the product is exposed to ozone, radiation, UV-rays, etc.
 - (6) Environments where vibrations or mechanical shocks exceeding a specified range is applied to the capacitor

Reference information

Guidelines

Some of the product use guidelines described herein are excerpted from JEITA RCR-2367D "Safety application guide for fixed aluminum electrolytic capacitors for use in electronic equipment," a technical report issued by the Japan Electronics and Information Technology Industries Association on October 2017. For more detailed information, please see the above technical report.

Intellectual property

Panasonic Group provides customers with safe products and services. We are also making great efforts to protect our intellectual property rights for Panasonic Group products. Typical patents related to this product are as follows. (Hybrid type)

[U.S. patent]

USP Nos. 7497879, 7621970, 9208954, 9595396, 9966200, 10453618, 10559432, 10679800, 10685788, and 10790095.

[Japanese patent] Japanese Patent No. 5360250

[European patent] EP-A Nos. 1808875 and 2698802

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

EEU-FS0J332B
EEU-FS1V182SB
EEU-FS1C222LB
EEU-FS1H331B
EEU-FS1H681B
EEU-FS1H821L
EEU-FS0J152B

FS0J222B
EEU-FS0J152LB
EEU-FS1C122B
EEU-FS1V331LB
EEU-FS1A562L
EEU-FS1V102LB
EEU-FS0J152B

EEU-FS1A222B
EEU-FS1H102L
EEU-FS1C332B
EEU-FS1C472SB
EEU-FS1C332L
EEU-FS1C182B
EEU-FS0J152B

FS1V152B
EEU-FS1A102B
EEU-FS1C332B
EEU-FS1C472SB
EEU-FS1C392L
EEU-FS1C182B
EEU-FS1C182B
EEU-FS1C182B
EEU-FS1C182B
EEU-FS1C182B
EEU-FS1C392L
EEU-FS1C392L
EEU-FS1C392L
EEU-FS1C392L
EEU-FS1C182B
EEU-FS1C392L
<td