





PRODUCT NUMBER
98481-XXXXL

ROHS COMPATIBLE, SEE NOTE 7
NUMBER OF POSITIONS : 02 TO 36

- 3=0.76µm GOLD/GXT ON CONTACT AREA
- 2µm MIN MATTE TIN ON TAIL
- 4=2µm MIN MATTE TIN FULL PLATED
- 1.27µm Ni: MIN UNDERPLATING

NOTES:

1. BODY MATERIAL: POLYESTER 30% GLASSFILLED COLOR BLUE, FLAME RETARDANT PER UL-94 V0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE.
3. 15N MIN PIN RETENTION IN EITHER DIRECTION
4. 0.6 MAX PROTRUSION PERMITTED AT 4 PLACES
5. PACKAGING :
- POLYBAGS FROM 02 TO 06 POSITIONS
- TUBE FROM 07 TO 36 POSITIONS
6. TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm
7. ROHS COMPATIBLE PRODUCT SPECIFICATIONS
- d - PLATING:
- "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
- b - MANUFACTURING PROCESS COMPATIBILITY
- THE HOUSING WILL WITHSTAND EXPOSURE TO 245°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- c - LABELING:
- MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-47-0004



mat'l. code	SEE NOTES	surface	tolerance
ltr	ecn no	dr	date
A	F00190	LMU	00.04.12
B	F05-0117	LMU	05.01.26
C	F05-0244	J00	05.09.06
D	F06-0228	LMU	08.07.11
E	F08-0147	XOV	08.04.14
F	B-19285	AMA	14.11.03
G	F-21810	AMA	15.06.19

tolerance	projection	product family
ISO 1302	ISO 406	ISO 1001
XXX ±0.05	mm	DUBOX HDR
linear	scale 4:1	DUBOX HEADER STRAIGHT, SINGLE ROW
XXX ±0.15		sheet 1 of 1
XXX ±0.05		size A3