



ENGLISH

Datasheet

Stock No: 240-185

RS Pro High Power Series Metal Oxide Varistor 1.71nF



Product Details

Metal Oxide Varistors High Power

High power metal oxide varistors suitable for reducing transient voltage spikes in industrial power applications.

Single and two-hole fixing types for distribution bus-bar mounting

Insulated plastic case types for flat surface mounting

High-mass large-diameter zinc oxide element

Repeatable protection against high-energy transient voltages

Operating Temperature Range: -40°C \rightarrow $+85^{\circ}\text{C}$

Transient Voltage Suppressors (MOV)



ENGLISH

Product Details

Dimensions (mm)					
Package Type	L	W	H	Fixing Hole Dia.	Fixing Centres
Radial disc, Ø40	66	40	22	6.35	–
Radial disc, Ø34	65	24	20	5.5	52
Encapsulated block	61	50	40	5.4	51

Specifications:

Varistor Voltage	610V
Maximum AC Voltage Rating	420V
Maximum DC Voltage Rating	560V
Clamping Voltage	1050V
Energy	260J
Series	High Power
Diameter	32mm
Maximum Surge Current	10000A
Capacitance	1.71nF
Thickness	5.5mm
Dimensions	32 Dia. x 5.5mm