2.0 MHz, 500 mA Synchronous Buck Regulator

Features

- · Over 90% Typical Efficiency
- · Output Current Up To 500 mA
- Low Quiescent Current = 45 μA, typical
- Low Shutdown Current = 0.1 μA, typical
- · Adjustable Output Voltage:
 - 0.8V to 4.5V
- · Fixed Output Voltage:
 - 1.2V, 1.5V, 1.8V, 2.5V, and 3.3V
- 2.0 MHz Fixed-Frequency PWM (Heavy Load)
- · Automatic PWM to PFM Mode Transition
- 100% Duty Cycle Operation
- · Internally Compensated
- Undervoltage Lockout (UVLO)
- · Overtemperature Protection
- · Space Saving Packages:
 - 5-Lead TSOT
 - 8-Lead 2X3 DFN

Applications

- · Cellular Telephones
- Portable Computers
- · Organizers / PDAs
- · USB Powered Devices
- · Digital Cameras
- · Portable Equipment
- +5V or +3.3V Distributed Systems

General Description


The MCP1603 is a high efficient, fully integrated 500 mA synchronous buck regulator whose 2.7V to 5.5V input voltage range makes it ideally suited for applications powered from 1-cell Li-lon or 2-cell/3-cell NiMH/NiCd batteries.

At heavy loads, the MCP1603 operates in the 2.0 MHz fixed frequency PWM mode which provides a low noise, low output ripple, small-size solution. When the load is reduced to light levels, the MCP1603 automatically changes operation to a PFM mode to minimize quiescent current draw from the battery. No intervention is necessary for a smooth transition from one mode to another. These two modes of operation allow the MCP1603 to achieve the highest efficiency over the entire operating current range.


The MCP1603 is available with either an adjustable or fixed output voltage. The available fixed output voltage options are 1.2V, 1.5V, 1.8V, 2.5V, and 3.3V. When a fixed option is used, only three additional small external components are needed to form a complete solution. Couple this with the low profile, small-foot print packages and the entire system solution is achieved with minimal size.

Additional protection features include: UVLO, overtemperature, and overcurrent protection.


Package Types







Functional Block Diagram



1.0 ELECTRICAL CHARACTERISTICS

Absolute Maximum Ratings †

V _{IN} - GND	+6.0V
All Other I/O	(GND - $0.3V$) to ($V_{IN} + 0.3V$)
L _X to GND	0.3V to (V _{IN} + 0.3V)
Output Short Circuit Current	Continuous
Power Dissipation (Note 5)	Internally Limited
Storage Temperature	65°C to +150°C
Ambient Temp. with Power Appl	ied40°C to +85°C
Operating Junction Temperature	40°C to +125°C
ESD Protection On All Pins:	
HBM	4 kV
MM	300V

† **Notice:** Stresses above those listed under "Maximum Ratings" may cause permanent damage to the device. This is a stress rating only and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

DC CHARACTERISTICS

Electrical Characteristics: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \mu F$, $L = 4.7 \mu H$, $V_{OUT}(ADJ) = 1.8V$, $I_{OUT} = 100 \text{ mA}$, $T_A = +25^{\circ}\text{C}$. Boldface specifications apply over the T_A range of -40°C to +85°C.								
Parameters	Sym	Min	Тур	Max	Units	Conditions		
Input Characteristics	Input Characteristics							
Input Voltage	V _{IN}	2.7		5.5	V	Note 1		
Maximum Output Current	I _{OUT}	500	_	_	mA	Note 1		
Shutdown Current	I _{IN_SHDN}	_	0.1	1	μA	SHDN = GND		
Quiescent Current	IQ	_	45	60	μA	SHDN = V _{IN} , I _{OUT} = 0 mA		
Shutdown/UVLO/Thermal Shutd	own Chara	cteristics						
SHDN, Logic Input Voltage Low	V_{IL}	_	_	15	%V _{IN}	V _{IN} = 2.7V to 5.5V		
SHDN, Logic Input Voltage High	V _{IH}	45		_	%V _{IN}	V _{IN} = 2.7V to 5.5V		
SHDN, Input Leakage Current	I _{L_SHDN}	-1.0	±0.1	1.0	μΑ	V _{IN} = 2.7V to 5.5V		
Undervoltage Lockout	UVLO	2.12	2.28	2.43	V	V _{IN} Falling		
Undervoltage Lockout Hysteresis	UVLO _{HYS}		140		mV			
Thermal Shutdown	T _{SHD}		150		°C	Note 4, Note 5		
Thermal Shutdown Hysteresis	T _{SHD-HYS}	_	10	_	°C	Note 4, Note 5		

- **Note 1:** The minimum V_{IN} has to meet two conditions: $V_{IN} \ge 2.7V$ and $V_{IN} \ge V_{OUT} + 0.5V$.
 - 2: Reference Feedback Voltage Tolerance applies to adjustable output voltage setting.
 - **3:** V_R is the output voltage setting.
 - **4:** The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable temperature and the thermal resistance from junction to air (i.e. T_A, T_J, θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown.
 - 5: The internal MOSFET switches have an integral diode from the L_X pin to the V_{IN} pin, and from the L_X pin to the GND pin. In cases where these diodes are forward-biased, the package power dissipation limits must be adhered to. Thermal protection is not able to limit the junction temperature for these cases.
 - 6: The current limit threshold is a cycle-by-cycle peak current limit.

DC CHARACTERISTICS (CONTINUED)

Electrical Characteristics: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \mu F$, $L = 4.7 \mu H$, $V_{OUT}(ADJ) = 1.8V$, $I_{OUT} = 100 \text{ mA}$, $T_A = +25^{\circ}\text{C}$. **Boldface** specifications apply over the T_A range of -40°C to +85°C.

Parameters	Sym	Min	Тур	Max	Units	Conditions			
Output Characteristics									
Adjustable Output Voltage Range	V _{OUT}	0.8	_	4.5	V	Note 2			
Reference Feedback Voltage	V_{FB}	_	0.8	_	V				
Reference Feedback Voltage		-3.0	_	+3.0	%	$T_A = -40$ °C to +25°C			
Tolerance		-2.5	_	+2.5	%	$T_A = +25^{\circ}C \text{ to } +85^{\circ}C$			
Feedback Input Bias Current	I_{VFB}	_	0.1	_	nA				
Output Voltage Tolerance Fixed	V _{OUT}	-3.0%	V_R	+3.0%	%	$T_A = -40^{\circ}C \text{ to } +25^{\circ}C, \text{ Note 3}$			
	V _{OUT}	-2.5	V_R	+2.5	%	$T_A = +25^{\circ}C$ to +85°C, Note 3			
Line Regulation	V _{LINE} -	_	0.3	_	%/V	$V_{IN} = V_{R} + 1V \text{ to } 5.5V,$			
	REG					I _{OUT} = 100 mA			
Load Regulation	V_{LOAD}	_	0.35	_	%	$V_{IN} = V_R + 1.5V$			
	REG					I_{LOAD} = 100 mA to 500 mA			
Internal Oscillator Frequency	Fosc	1.5	2.0	2.8	MHz				
Start Up Time	T _{SS}	_	0.6		ms	T _R = 10% to 90%			
R _{DSon} P-Channel	R _{DSon-P}	_	500		mΩ	I _P = 100 mA			
R _{DSon} N-Channel	R _{DSon-N}	_	500		mΩ	I _N = 100 mA			
L _X Pin Leakage Current	I_{LX}	-1.0	±0.1	1.0	μΑ	SHDN = 0V, V _{IN} = 5.5V,			
						$L_X = 0V, L_X = 5.5V$			
Positive Current Limit Threshold	+I _{LX(MAX)}	_	860	_	mA	Note 6			

- **Note 1:** The minimum V_{IN} has to meet two conditions: $V_{IN} \ge 2.7V$ and $V_{IN} \ge V_{OUT} + 0.5V$.
 - 2: Reference Feedback Voltage Tolerance applies to adjustable output voltage setting.
 - **3:** V_R is the output voltage setting.
 - **4:** The maximum allowable power dissipation is a function of ambient temperature, the maximum allowable temperature and the thermal resistance from junction to air (i.e. T_A , T_J , θ_{JA}). Exceeding the maximum allowable power dissipation causes the device to initiate thermal shutdown.
 - 5: The internal MOSFET switches have an integral diode from the L_X pin to the V_{IN} pin, and from the L_X pin to the GND pin. In cases where these diodes are forward-biased, the package power dissipation limits must be adhered to. Thermal protection is not able to limit the junction temperature for these cases.
 - 6: The current limit threshold is a cycle-by-cycle peak current limit.

TEMPERATURE SPECIFICATIONS

Electrical Specifications: Unless otherwise indicated, all limits are specified for: V _{IN} + 2.7V to 5.5V							
Parameters	Sym	Min	Тур	Max	Units	Conditions	
Temperature Ranges							
Operating Junction Temperature Range	T_J	-40	_	+125	°C	Steady State	
Storage Temperature Range	T _A	-65	_	+150	°C		
Maximum Junction Temperature	T_J	_	_	+150	°C	Transient	
Package Thermal Resistances							
Thermal Resistance, 5L-TSOT	$\theta_{\sf JA}$	_	256	_	°C/W	Typical 4-layer Board with Internal Ground Plane	
Thermal Resistance, 8L-2x3 DFN	$\theta_{\sf JA}$	_	84.5	_	°C/W	Typical 4-layer Board with Internal Ground Plane and 2-Vias in Thermal Pad	

2.0 TYPICAL PERFORMANCE CURVES

Note: The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g., outside specified power supply range) and therefore outside the warranted range.

Note: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \ \mu\text{F}$, $L = 4.7 \ \mu\text{H}$, $V_{OUT}(ADJ) = 1.8V$, $I_{LOAD} = 100 \ m\text{A}$, $T_A = +25^{\circ}\text{C}$. Adjustable or fixed output voltage options can be used to generate the Typical Performance Characteristics.




FIGURE 2-1: I_O vs. Ambient Temperature.




FIGURE 2-2: Efficiency vs. Input Voltage $(V_{OUT} = 1.2V)$.




FIGURE 2-3: Efficiency vs. Input Voltage $(V_{OUT} = 1.8V)$.




FIGURE 2-4: I_Q vs. Input Voltage.




FIGURE 2-5: Efficiency vs. Output Load $(V_{OUT} = 1.2V)$.




FIGURE 2-6: Efficiency vs. Output Load $(V_{OUT} = 1.8V)$.

Typical Performance Curves (Continued)

Note: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \,\mu\text{F}$, $L = 4.7 \,\mu\text{H}$, $V_{OUT}(ADJ) = 1.8V$, $I_{LOAD} = 100 \,\text{mA}$, $T_A = +25 \,^{\circ}\text{C}$. Adjustable or fixed output voltage options can be used to generate the Typical Performance Characteristics.




FIGURE 2-7: Efficiency vs. Input Voltage $(V_{OUT} = 2.4V)$.




FIGURE 2-8: Efficiency vs. Input Voltage $(V_{OUT} = 3.3V)$.




FIGURE 2-9: Line Regulation vs. Ambient Temperature ($V_{OUT} = 1.8V$).




FIGURE 2-10: Efficiency vs. Output Load $(V_{OUT} = 2.4V)$.




FIGURE 2-11: Efficiency vs. Output Load $(V_{OUT} = 3.3V)$.




FIGURE 2-12: Output Voltage vs. Load Current ($V_{OUT} = 1.8V$).

Typical Performance Curves (Continued)

Note: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \,\mu\text{F}$, $L = 4.7 \,\mu\text{H}$, $V_{OUT}(ADJ) = 1.8V$, $I_{LOAD} = 100 \,\text{mA}$, $T_A = +25^{\circ}\text{C}$. Adjustable or fixed output voltage options can be used to generate the Typical Performance Characteristics.




FIGURE 2-13: Switching Frequency vs. Ambient Temperature.




FIGURE 2-14: Switch Resistance vs. Input Voltage.




FIGURE 2-15: Output Voltage Startup Waveform.




FIGURE 2-16: Switching Frequency vs. Input Voltage.




FIGURE 2-17: Switch Resistance vs. Ambient Temperature.




FIGURE 2-18: Heavy Load Switching Waveform.

Typical Performance Curves (Continued)

Note: Unless otherwise indicated, $V_{IN} = \overline{SHDN} = 3.6V$, $C_{OUT} = C_{IN} = 4.7 \ \mu\text{F}$, $L = 4.7 \ \mu\text{H}$, $V_{OUT}(ADJ) = 1.8V$, $I_{LOAD} = 100 \ \text{mA}$, $T_A = +25^{\circ}\text{C}$. Adjustable or fixed output voltage options can be used to generate the Typical Performance Characteristics.





FIGURE 2-19: Light Load Switching Waveform.



Response vs. Time.




FIGURE 2-20: Output Voltage Load Step Response vs. Time.

3.0 PIN DESCRIPTIONS

The descriptions of the pins are listed in Table 3-1.

TABLE 3-1: PIN FUNCTION TABLE

	Pin No.			Description
MCP1603 TSOT23	MCP1603L TSOT23	2x3 DFN	Symbol	
1	4	7	V _{IN}	Power Supply Input Voltage Pin
2	2	8	GND	Ground Pin
3	1	3	SHDN	Shutdown Control Input Pin
4	5	4	V _{FB} /V _{OUT}	Feedback / Output Voltage Pin
5	3	1	L _X	Switch Node, Buck Inductor Connection Pin
_	_	2, 5, 6	NC	No Connect
_	_	Exposed Pad	EP	For the DFN package, the center exposed pad is a thermal path to remove heat from the device. Electrically this pad is at ground potential and should be connected to GND

3.1 Power Supply Input Voltage Pin (V_{IN})

Connect the input voltage source to $V_{IN}.$ The input source must be decoupled to GND with a 4.7 μF capacitor.

3.2 Ground Pin (GND)

Ground pin for the device. The loop area of the ground traces should be kept as minimal as possible.

3.3 Shutdown Control Input Pin (SHDN)

The \overline{SHDN} pin is a logic-level input used to enable or disable the device. A logic high (> 45% of V_{IN}) will enable the regulator output. A logic-low (< 15% of V_{IN}) will ensure that the regulator is disabled.

3.4 Feedback / Output Voltage Pin (V_{FB}/V_{OUT})

For adjustable output options, connect the center of the output voltage divider to the V_{FB}/V_{OUT} pin. For fixed-output voltage options, connect the output directly to the V_{FB}/V_{OUT} pin.

3.5 Switch Node, Buck Inductor Connection Pin (L_x)

Connect the L_X pin directly to the buck inductor. This pin carries large signal-level current; all connections should be made as short as possible.

3.6 Exposed Metal Pad (EP)

For the DFN package, connect the Exposed Pad to GND, with vias into the GND plane. This connection to the GND plane will aid in heat removal from the package.

4.0 DETAILED DESCRIPTION

4.1 Device Overview

The MCP1603 is a synchronous buck regulator that operates in a Pulse Frequency Modulation (PFM) mode or a Pulse Width Modulation (PWM) mode to maximize system efficiency over the entire operating current range. Capable of operating from a 2.7V to 5.5V input voltage source, the MCP1603 can deliver 500 mA of continuous output current.

When using the MCP1603, the PCB area required for a complete step-down converter is minimized since both the main P-Channel MOSFET and the synchronous N-Channel MOSFET are integrated. Also while in PWM mode, the device switches at a constant frequency of 2.0 MHz (typ) which allow for small filtering components. Both fixed and adjustable output voltage options are available. The fixed voltage options (1.2V, 1.5V 1.8V, 2.5V, 3.3V) do not require an external voltage divider which further reduces the required circuit board footprint. The adjustable output voltage options allow for more flexibility in the design, but require an external voltage divider.

Additionally the device features undervoltage lockout (UVLO), overtemperature shutdown, overcurrent protection, and enable/disable control.

4.2 Synchronous Buck Regulator

The MCP1603 has two distinct modes of operation that allow the device to maintain a high level of efficiency throughout the entire operating current and voltage range. The device automatically switched between PWM mode and PFM mode depending upon the output load requirements.

4.2.1 FIXED FREQUENCY, PWM MODE

During heavy load conditions, the MCP1603 operates at a high, fixed switching frequency of 2.0 MHz (typical) using current mode control. This minimizes output ripple (10 - 15 mV typically) and noise while maintaining high efficiency (88% typical with $V_{IN} = 3.6V$, $V_{OLIT} = 1.8V$, $I_{OLIT} = 300$ mA).

During normal PWM operation, the beginning of a switching cycle occurs when the internal P-Channel MOSFET is turned on. The ramping inductor current is sensed and tied to one input of the internal high-speed comparator. The other input to the high-speed comparator is the error amplifier output. This is the difference between the internal 0.8V reference and the divided-down output voltage. When the sensed current becomes equal to the amplified error signal, the high-speed comparator switches states and the P-Channel MOSFET is turned off. The N-Channel MOSFET is turned on until the internal oscillator sets an internal RS latch initiating the beginning of another switching cycle.

PFM-to-PWM mode transition is initiated for any of the following conditions:

- · Continuous device switching
- · Output voltage has dropped out of regulation

4.2.2 LIGHT LOAD, PFM MODE

During light load conditions, the MCP1603 operates in a PFM mode. When the MCP1603 enters this mode, it begins to skip pulses to minimize unnecessary quiescent current draw by reducing the number of switching cycles per second. The typical quiescent current draw for this device is 45 µA.

PWM-to-PFM mode transition is initiated for any of the following conditions:

- Discontinuous inductor current is sensed for a set duration
- Inductor peak current falls below the transition threshold limit

4.3 Soft Start

The output of the MCP1603 is controlled during start-up. This control allows for a very minimal amount of V_{OUT} overshoot during start-up from V_{IN} rising above the UVLO voltage or SHDN being enabled.

4.4 Overtemperature Protection

Overtemperature protection circuitry is integrated in the MCP1603. This circuitry monitors the device junction temperature and shuts the device off, if the junction temperature exceeds the typical 150°C threshold. If this threshold is exceeded, the device will automatically restart once the junction temperature drops by approximately 10°C. The soft start is reset during an overtemperture condition.

4.5 Overcurrent Protection

Cycle-by-cycle current limiting is used to protect the MCP1603 from being damaged when an external short circuit is applied. The typical peak current limit is 860 mA. If the sensed current reaches the 860 mA limit, the P-Channel MOSFET is turned off, even if the output voltage is not in regulation. The device will attempt to start a new switching cycle when the internal oscillator sets the internal RS latch.

4.6 Enable/Disable Control

The SHDN pin is used to enable or disable the MCP1603. When the SHDN pin is pulled low, the device is disabled. When pulled high the device is enabled and begins operation provided the input voltage is not below the UVLO threshold or a fault condition exists.

4.7 Undervoltage Lockout (UVLO)

The UVLO feature uses a comparator to sense the input voltage (V_{IN}) level. If the input voltage is lower than the voltage necessary to properly operate the MCP1603, the UVLO feature will hold the converter off. When V_{IN} rises above the necessary input voltage, the UVLO is released and soft start begins. Hysteresis is built into the UVLO circuit to compensate for input impedance. For example, if there is any resistance between the input voltage source and the device when it is operating, there will be a voltage drop at the input to the device equal to I_{IN} x R_{IN} . The typical hysteresis is 140 mV.

5.0 APPLICATION INFORMATION

5.1 Typical Applications

The MCP1603 500 mA synchronous buck regulator operates over a wide input voltage range (2.7V to 5.5V) and is ideal for single-cell Li-lon battery powered applications, USB powered applications, three cell NiMH or NiCd applications and 3V or 5V regulated input applications. The 5-lead TSOT and 8-lead 2x3 DFN packages provide a small footprint with minimal external components.

5.2 Fixed Output Voltage Applications

Typical Application Circuit shows a fixed MCP1603 in an application used to convert three NiMH batteries into a well regulated 1.8V @ 500 mA output. A 4.7 μ F input capacitor, 4.7 μ F output capacitor, and a 4.7 μ H inductor make up the entire external component solution for this application. No external voltage divider or compensation is necessary. In addition to the fixed 1.8V option, the MCP1603 is also available in 1.2V, 1.5V, 2.5V, or 3.3V fixed voltage options.

5.3 Adjustable Output Voltage Applications

When the desired output for a particular application is not covered by the fixed voltage options, an adjustable MCP1603 can be used. The circuit listed in Figure 6-2 shows an adjustable MCP1603 being used to convert a 5V rail to 1.0V @ 500 mA. The output voltage is adjustable by using two external resistors as a voltage divider. For adjustable-output voltages, it is recommended that the top resistor divider value be 200 k Ω . The bottom resistor value can be calculated using the following equation:

EQUATION 5-1:

$$R_{BOT} = R_{TOP} \times \left(\frac{V_{FB}}{V_{OUT} - V_{FB}}\right)$$

Example:

 $R_{TOP} = 200 \text{ k}\Omega$ $V_{OUT} = 1.0V$ $V_{FB} = 0.8V$

 R_{BOT} = 200 k Ω x (0.8V/(1.0V - 0.8V))

 $R_{BOT} = 800 k\Omega$

(Standard Value = 787 k Ω)

For adjustable output applications, an additional R-C compensation network is necessary for control loop stability. Recommended values for any output voltage are:

 $R_{COMP} = 4.99 \text{ k}\Omega$ $C_{COMP} = 33 \text{ pF}$

Refer to Figure 6-2 for proper placement of R_{COMP} and C_{COMP}

5.4 Input Capacitor Selection

The input current to a buck converter, when operating in continuous conduction mode, is a squarewave with a duty cycle defined by the output voltage (V_{OUT}) to input voltage (V_{IN}) relationship of V_{OUT}/V_{IN} . To prevent undesirable input voltage transients, the input capacitor should be a low ESR type with an RMS current rating given by Equation 5.5. Because of their small size and low ESR, ceramic capacitors are often used. Ceramic material X5R or X7R are well suited since they have a low temperature coefficient and acceptable ESR.

EQUATION 5-2:

$$I_{CIN,RMS} = I_{OUT,MAX} \times \left(\sqrt{\frac{V_{OUT} \times (V_{IN} - V_{OUT})}{V_{IN}}} \right)$$

Table 5-1 contains the recommend range for the input capacitor value.

5.5 Output Capacitor Selection

The output capacitor helps provide a stable output voltage during sudden load transients, smooths the current that flows from the inductor to the load, and reduces the output voltage ripple. Therefore, low ESR capacitors are a desirable choice for the output capacitor. As with the input capacitor, X5R and X7R ceramic capacitors are well suited for this application.

The output ripple voltage is often a design specification. A buck converters' output ripple voltage is a function of the charging and discharging of the output capacitor and the ESR of the capacitor. This ripple voltage can be calculated by Equation 5-3.

EQUATION 5-3:

$$\Delta V_{OUT} = \Delta I_L \times ESR + \frac{\Delta I_L}{8 \times f \times C}$$

Table 5-1 contains the recommend range for the output capacitor value.

TABLE 5-1: CAPACITOR VALUE RANGE

	C _{IN}	C _{OUT}
Minimum	4.7 µF	4.7 µF
Maximum	_	22 μF

5.6 Inductor Selection

When using the MCP1603, the inductance value can range from 3.3 μ H to 10 μ H. An inductance value of 4.7 μ H is recommended to achieve a good balance between converter load transient response and minimized noise.

The value of inductance is selected to achieve a desired amount of ripple current. It is reasonable to assume a ripple current that is 20% of the maximum load current. The larger the amount of ripple current allowed, the larger the output capacitor value becomes to meet ripple voltage specifications. The inductor ripple current can be calculated according to the following equation.

EQUATION 5-4:

$$\Delta I_L = \frac{V_{OUT}}{F_{SW} \times L} \times \left(1 - \frac{V_{OUT}}{V_{IN}}\right)$$

Where:

F_{SW} = Switching Frequency

When considering inductor ratings, the maximum DC current rating of the inductor should be at least equal to the maximum load current, plus one half the peak-to-peak inductor ripple current (1/2 * ΔI_L). The inductor DC resistance adds to the total converter power loss. An inductor with a low DC resistance allows for higher converter efficiency.

TABLE 5-2: MCP1603 RECOMMENDED INDUCTORS

Part Number	Value (µH)	$\begin{array}{c} \mathbf{DCR} \\ \Omega \\ (\mathbf{max}) \end{array}$	I _{SAT} (A)	Size WxLxH (mm)				
Coiltronics®								
SD3110	3.3	0.195	0.81	3.1x3.1x1.0				
SD3110	4.7	0.285	0.68	3.1x3.1x1.0				
SD3110	6.8	0.346	0.58	3.1x3.1x1.0				
SD3812	3.3	0.159	1.40	3.8x3.8x1.2				
SD3812	4.7	0.256	1.13	3.8x3.8x1.2				
SD3812	6.8	0.299	0.95	3.8x3.8x1.2				
Würth Elek	tronik [®]							
WE-TPC Type XS	3.3	0.225	0.72	3.3x3.5x0.95				
WE-TPC Type XS	4.7	0.290	0.50	3.3x3.5x0.95				
WE-TPC Type S	4.7	0.105	0.90	3.8x3.8x1.65				
WE-TPC Type S	6.8	0.156	0.75	3.8x3.8x1.65				
Sumida [®]								
CMD4D06	3.3	0.174	0.77	3.5x4.3x0.8				
CMD4D06	4.7	0.216	0.75	3.5x4.3x0.8				
CMD4D06	6.8	0.296	0.62	3.5x4.3x0.8				

5.7 Thermal Calculations

The MCP1603 is available in two different packages (TSOT-23 and 2x3 DFN). By calculating the power dissipation and applying the package thermal resistance, (θ_{JA}), the junction temperature is estimated. The maximum continuous junction temperature rating for the MCP1603 is +125°C.

To quickly estimate the internal power dissipation for the switching buck regulator, an empirical calculation using measured efficiency can be used. Given the measured efficiency, the internal power dissipation is estimated by:

EQUATION 5-5:

$$\left(\frac{V_{OUT} \times I_{OUT}}{Efficiency}\right) - (V_{OUT} \times I_{OUT}) = P_{Diss}$$

The difference between the first term, input power dissipation, and the second term, power delivered, is the internal power dissipation. This is an estimate assuming that most of the power lost is internal to the MCP1603. There is some percentage of power lost in the buck inductor, with very little loss in the input and output capacitors.

5.8 PCB Layout Information

Good printed circuit board layout techniques are important to any switching circuitry and switching power supplies are no different. When wiring the high current paths, short and wide traces should be used. This high current path is shown with red connections in Figure 5-1. The current in this path is switching.

Therefore, it is important that the components along the high current path should be placed as close as possible to the MCP1603 to minimize the loop area.

The feedback resistors and feedback signal should be routed away from the switching node and this switching current loop. When possible ground planes and traces should be used to help shield the feedback signal and minimize noise and magnetic interference.




FIGURE 5-1: PCB High Current Path.

6.0 TYPICAL APPLICATION CIRCUITS




FIGURE 6-1: Single Li-Ion to 1.5V @ 500 mA Application.




FIGURE 6-2: 5V to 1.0V @ 500 mA Application.




FIGURE 6-3: 3 NiMH Batteries to 1.2V @ 500 mA Application.9

7.0 PACKAGING INFORMATION


7.1 Package Marking Information (Not to Scale)

8-Lead 2x3 DFN




Part Number	Marking Code
MCP1603-120I/MC	AFM
MCP1603-150I/MC	AFK
MCP1603-180I/MC	AFJ
MCP1603-250I/MC	AFG
MCP1603-330I/MC	AFA
MCP1603-ADJI/MC	AFQ






5-Lead TSOT



Part Number	Marking Code
MCP1603T-120I/OS	ETNN
MCP1603T-150I/OS	EUNN
MCP1603T-180I/OS	EVNN
MCP1603T-250I/OS	EWNN
MCP1603T-330I/OS	EXNN
MCP1603T-ADJI/OS	EYNN

Part Number	Marking Code
MCP1603LT-120I/OS	FMNN
MCP1603LT-150I/OS	FKNN
MCP1603LT-180I/OS	EJNN
MCP1603LT-250I/OS	FGNN
MCP1603LT-330I/OS	FANN
MCP1603LT-ADJI/OS	FQNN

Example



Legend: XX...X Customer-specific information
Y Year code (last digit of calendar year)

YY Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')

NNN Alphanumeric traceability code

e3 Pb-free JEDEC designator for Matte Tin (Sn)


This package is Pb-free. The Pb-free JEDEC designator (e3) can be found on the outer packaging for this package.

can be found on the outer packaging for this package.

In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for customer-specific information.

8-Lead Plastic Dual Flat, No Lead Package (MC) - 2x3x0.9 mm Body [DFN]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units			3
Dimensio	n Limits	MIN	NOM	MAX
Number of Pins	N		8	
Pitch	е		0.50 BSC	
Overall Height	Α	0.80	0.90	1.00
Standoff	A1	0.00	0.02	0.05
Contact Thickness	A3	0.20 REF		
Overall Length	D	2.00 BSC		
Overall Width	Е	3.00 BSC		
Exposed Pad Length	D2	1.30	-	1.75
Exposed Pad Width	E2	1.50	-	1.90
Contact Width	b	0.18	0.25	0.30
Contact Length	L	0.30	0.40	0.50
Contact-to-Exposed Pad	K	0.20	-	_

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Package may have one or more exposed tie bars at ends.
- 3. Package is saw singulated.
- 4. Dimensioning and tolerancing per ASME Y14.5M.


BSC: Basic Dimension. Theoretically exact value shown without tolerances.

REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-123B

5-Lead Plastic Thin Small Outline Transistor (OS) [TSOT]

Note: For the most current package drawings, please see the Microchip Packaging Specification located at http://www.microchip.com/packaging



	Units		MILLIMETERS	3	
D	imension Limits	MIN	MIN NOM		
Number of Leads	N		5		
Lead Pitch	е		0.95 BSC		
Outside Lead Pitch	e1		1.90 BSC		
Overall Height	A	_	-	1.10	
Molded Package Thickness	A2	0.70	0.90	1.00	
Standoff	A1	0.00	_	0.10	
Overall Width	E	2.80 BSC			
Molded Package Width	E1	1.60 BSC			
Overall Length	D	2.90 BSC			
Foot Length	L	0.30	0.45	0.60	
Footprint	L1		0.60 REF		
Foot Angle	ф	0°	4°	8°	
Lead Thickness	С	0.08	-	0.20	
Lead Width	b	0.30	_	0.50	
Mold Draft Angle Top	α	4°	10°	12°	
Mold Draft Angle Bottom	β	4°	10°	12°	

Notes:

- 1. Pin 1 visual index feature may vary, but must be located within the hatched area.
- 2. Dimensions D and E1 do not include mold flash or protrusions. Mold flash or protrusions shall not exceed 0.15 mm per side.
- 3. Dimensioning and tolerancing per ASME Y14.5M.
 - BSC: Basic Dimension. Theoretically exact value shown without tolerances.
 - REF: Reference Dimension, usually without tolerance, for information purposes only.

Microchip Technology Drawing C04-128B

APPENDIX A: REVISION HISTORY

Revision A (May 2007)

• Original Release of this Document.

NOTES:

PRODUCT IDENTIFICATION SYSTEM

 $\underline{\text{To order or obtain information, e.g., on pricing or delivery, refer to the factory or the listed sales of fice.}\\$

PART NO. X	<u> </u>	Examples:
Device TSOT Config.	 Tape Voltage Temp. Package and Reel Option	8-Lead DFN:
		a) MCP1603-120I/MC: 1.20V Buck Reg., 8LD-DFN pkg.
Device:	MCP1603: 2.0 MHz, 500 mA Buck Regulator	b) MCP1603-150I/MC: 1.50V Buck Reg., 8LD-DFN pkg.
		c) MCP1603-180I/MC: 1.80V Buck Reg., 8LD-DFN pkg.
TSOT Pin Config. Designator *	Blank = Standard pinout L = Alternate pinout * Refer to Package Types for an explanation regarding the function of the device pins.	d) MCP1603-250I/MC: 2.50V Buck Reg., 8LD-DFN pkg.
		e) MCP1603-330I/MC: 3.30V Buck Reg., 8LD-DFN pkg.
Tape and Reel:	T = Tape and Reel Blank = Tube	5-Lead TSOT:
		a) MCP1603T-120I/OS: 1.20V Buck Reg., 5LD-TSOT pkg.
Voltage Option:	ADJ = Adjustable 120 = 1.20V "Standard" 150 = 1.50V "Standard" 180 = 1.80V "Standard" 250 = 2.50V "Standard"	b) MCP1603T-180I/OS: 1.80V Buck Reg., 5LD-TSOT pkg.
		c) MCP1603T-250I/OS: 2.50V Buck Reg., 5LD-TSOT pkg.
	330 = 3.30V "Standard"	d) MCP1603T-330I/OS: 3.30V Buck Reg., 5LD-TSOT pkg.
Temperature:	I = -40°C to +85°C	e) MCP1603T-ADJI/OS: Adj. Buck Reg., 5LD-TSOT pkg.
Package Type:	MC = Plastic Dual-Flat No-Lead Package (MC), 8-Lead OS = Plastic Thin Small Outline Transistor (OS), 5-Lead	f) MCP1603LT-250I/OS:2.50V Buck Reg.,
		5LD-TSOT pkg.
		g) MCP1603LT-ADJI/OS:Adj. Buck Reg., 5LD-TSOT pkg.

NOTES:

Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights.

Trademarks

The Microchip name and logo, the Microchip logo, Accuron, dsPIC, Keeloq, Keeloq logo, microID, MPLAB, PIC, PICmicro, PICSTART, PRO MATE, rfPIC and SmartShunt are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

AmpLab, FilterLab, Linear Active Thermistor, Migratable Memory, MXDEV, MXLAB, SEEVAL, SmartSensor and The Embedded Control Solutions Company are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Analog-for-the-Digital Age, Application Maestro, CodeGuard, dsPICDEM, dsPICDEM.net, dsPICworks, ECAN, ECONOMONITOR, FanSense, FlexROM, fuzzyLAB, In-Circuit Serial Programming, ICSP, ICEPIC, Mindi, MiWi, MPASM, MPLAB Certified logo, MPLIB, MPLINK, PICkit, PICDEM, PICDEM.net, PICLAB, PICtail, PowerCal, PowerInfo, PowerMate, PowerTool, REAL ICE, rfLAB, Select Mode, Smart Serial, SmartTel, Total Endurance, UNI/O, WiperLock and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

All other trademarks mentioned herein are property of their respective companies.

© 2007, Microchip Technology Incorporated, Printed in the U.S.A., All Rights Reserved.

Printed on recycled paper.

QUALITY MANAGEMENT SYSTEM

CERTIFIED BY DNV

ISO/TS 16949:2002

Microchip received ISO/TS-16949:2002 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.



WORLDWIDE SALES AND SERVICE

AMERICAS

Corporate Office 2355 West Chandler Blvd.

Chandler, AZ 85224-6199 Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://support.microchip.com

Web Address: www.microchip.com

Atlanta

Duluth, GA Tel: 678-957-9614 Fax: 678-957-1455

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

Detroit

Farmington Hills, MI Tel: 248-538-2250 Fax: 248-538-2260

Kokomo

Kokomo, IN Tel: 765-864-8360 Fax: 765-864-8387

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608

Santa Clara

Santa Clara, CA Tel: 408-961-6444 Fax: 408-961-6445

Toronto

Mississauga, Ontario, Canada

Tel: 905-673-0699

Fax: 905-673-6509

ASIA/PACIFIC

Asia Pacific Office

Suites 3707-14, 37th Floor Tower 6, The Gateway Habour City, Kowloon Hong Kong

Tel: 852-2401-1200 Fax: 852-2401-3431

Australia - Sydney Tel: 61-2-9868-6733 Fax: 61-2-9868-6755

China - Beijing Tel: 86-10-8528-2100

Fax: 86-10-8528-2104 China - Chengdu

Tel: 86-28-8665-5511 Fax: 86-28-8665-7889

China - Fuzhou Tel: 86-591-8750-3506 Fax: 86-591-8750-3521

China - Hong Kong SAR Tel: 852-2401-1200 Fax: 852-2401-3431

China - Qingdao

Tel: 86-532-8502-7355 Fax: 86-532-8502-7205

China - Shanghai Tel: 86-21-5407-5533

Fax: 86-21-5407-5066 China - Shenyang

Tel: 86-24-2334-2829 Fax: 86-24-2334-2393

China - Shenzhen Tel: 86-755-8203-2660 Fax: 86-755-8203-1760

China - Shunde Tel: 86-757-2839-5507 Fax: 86-757-2839-5571

China - Wuhan Tel: 86-27-5980-5300 Fax: 86-27-5980-5118

China - Xian Tel: 86-29-8833-7250

Fax: 86-29-8833-7256

ASIA/PACIFIC

India - Bangalore

Tel: 91-80-4182-8400 Fax: 91-80-4182-8422

India - New Delhi

Tel: 91-11-4160-8631 Fax: 91-11-4160-8632

India - Pune

Tel: 91-20-2566-1512 Fax: 91-20-2566-1513

Japan - Yokohama Tel: 81-45-471- 6166

Fax: 81-45-471-6122 **Korea - Gumi**

Tel: 82-54-473-4301 Fax: 82-54-473-4302

Korea - Seoul Tel: 82-2-554-7200 Fax: 82-2-558-5932 or 82-2-558-5934

Malaysia - Penang Tel: 60-4-646-8870 Fax: 60-4-646-5086

Philippines - Manila Tel: 63-2-634-9065

Fax: 63-2-634-9069 Singapore

Tel: 65-6334-8870 Fax: 65-6334-8850

Taiwan - Hsin Chu Tel: 886-3-572-9526 Fax: 886-3-572-6459

Taiwan - Kaohsiung Tel: 886-7-536-4818 Fax: 886-7-536-4803

Taiwan - Taipei Tel: 886-2-2500-6610 Fax: 886-2-2508-0102

Thailand - Bangkok Tel: 66-2-694-1351 Fax: 66-2-694-1350

EUROPE

Austria - Wels

Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

Denmark - Copenhagen

Tel: 45-4450-2828 Fax: 45-4485-2829

France - Paris

Tel: 33-1-69-53-63-20 Fax: 33-1-69-30-90-79

Germany - Munich Tel: 49-89-627-144-0

Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Netherlands - Drunen Tel: 31-416-690399

Fax: 31-416-690340

Spain - Madrid

Tel: 34-91-708-08-90 Fax: 34-91-708-08-91 **UK - Wokingham**

Tel: 44-118-921-5869 Fax: 44-118-921-5820

12/08/06