


# TN1215, TYN612, TYN812, TYN1012

#### Standard 12 A SCRs

Datasheet - production data



#### **Features**

- On-state RMS current, I<sub>T(RMS)</sub> 12 A
- Repetitive peak off-state voltage, V<sub>DRM</sub> and V<sub>RRM</sub> 600 V, 800 V and 1000 V
- Triggering gate current, I<sub>GT</sub> 5 mA or 15 mA

#### **Description**

The standard 12 A SCR series is suitable to fit all modes of control, found in applications such as overvoltage crowbar protection, motor control circuits in power tools and kitchen aids, inrush current limiting circuits, capacitive discharge ignition and voltage regulation circuits.

Available in through-hole or surface-mount packages, they provide an optimized performance in a limited space.

**Table 1. Device summary** 

Order code	Volt	age V <sub>DRM</sub> / V	r <sub>RRM</sub> (v)		Deskage
Order code	600	800	1000	I <sub>GT (mA)</sub>	Package
TYN1012RG			х	15	TO-220AB
TYN1012TRG			х	5	TO-220AB
TYN612RG	х			15	TO-220AB
TYN612TRG	х			5	TO-220AB
TYN812RG		х		15	TO-220AB
TYN812TRG		х		5	TO-220AB
TN1215-600B	х			15	DPAK
TN1215-600B-TR	х			15	DPAK
TN1215-600G	х			15	D <sup>2</sup> PAK
TN1215-600G-TR	х			15	D <sup>2</sup> PAK
TN1215-600H	х			15	IPAK
TN1215-800B-TR		х		15	DPAK
TN1215-800G-TR		х		15	D <sup>2</sup> PAK
TN1215-800H		х		15	IPAK

October 2016 DocID7475 Rev 11 1/17

# 1 Characteristics

Table 2. Absolute ratings (limiting values)

				Va	lue	
Symbol	Pa	rameter	TN1215-x00B TN1215-x00H (1) (2)	TN1215- x00G <sup>(1)(2)</sup> TYNx12 <sup>(2)(3)</sup> TYNx12T <sup>(2)(3)</sup>	Unit	
I <sub>T(RMS)</sub>	On-state RMS current (180° conduction angle)	TO-220AB ins. D <sup>2</sup> PAK	T = 110 °C	1	2	
I <sub>T(AV)</sub>	Average on-state current (180° conduction angle)	DPAK IPAK	T <sub>c</sub> = 110 °C	1	_ A	
1.	Non repetitive surge peak	t <sub>p</sub> = 8.3 ms	T - 25 °C	115 145		Α
I <sub>TSM</sub>	on-state current	t <sub>p</sub> = 10 ms	T <sub>jinitial</sub> = 25 °C	110 140		7 ^
I <sup>2</sup> t	I <sup>2</sup> t value for fusing		T <sub>jinitial</sub> = 25 °C	60	98	A <sup>2</sup> S
dI/dt	Critical rate of rise of on- state current $I_G = 2 \times I_{GT}$ , $t_r \le 100 \text{ ns}$	F = 60 Hz	T <sub>j</sub> = 125 °C	50		A/µs
I <sub>GM</sub>	Peak gate current	T <sub>j</sub> = 125 °C	4		Α	
P <sub>G(AV)</sub>	Average gate power dissipa	ation	1		W	
T <sub>stg</sub> T <sub>j</sub>	Storage junction temperatu Operating junction tempera	•	- 40 to + 150 - 40 to + 125		°C	
$V_{RGM}$	Maximum peak reverse gar	te voltage			V	

<sup>1.</sup> x00= 600, 800



<sup>2.</sup> Check Table 1 for devices availability

<sup>3.</sup> x= 6,8,10

Table 3. Standard electrical characteristics ( $T_j = 25$  °C, unless otherwise specified)

Cumbal	Test condi	itiana	_	TN1215-	x00 <sup>(1)(2)</sup>	TYN <sup>(2)</sup>		l loit	
Symbol	Test condi	itions		-B/-H	-G	x12T <sup>(3)</sup>	x12 <sup>(3)</sup>	Unit	
1			Min.	2	2	0.5	2	mA	
I <sub>GT</sub>	$V_D = 12 \text{ V}, R_L = 33 \Omega$		Max.	1	5	5	15	IIIA	
V <sub>GT</sub>			Max.		1.3				
$V_{GD}$	$V_D = V_{DRM,} R_L = 3.3 \text{ k}\Omega$	T <sub>j</sub> = 125 °C	Min.	0.2				V	
I <sub>H</sub>	I <sub>T</sub> = 500 mA, gate open	Max.	40	30	15	30	mA		
ΙL	I <sub>G</sub> = 1.2 I <sub>GT</sub>		Max.	80	60	30	60	mA	
dV/dt	V <sub>D</sub> = 67% V <sub>DRM,</sub> gate open	T <sub>j</sub> =125 °C	Min.	200		40	200	V/µs	
V <sub>TM</sub>	$I_{TM}$ = 24 A $t_p$ = 380 $\mu$ s	T <sub>j</sub> = 25 °C	Max.	1.6				V	
V <sub>to</sub>	Threshold voltage $T_j = 125 ^{\circ}\text{C}$		Max.	0.85				V	
R <sub>d</sub>	Dynamic resistance $T_j = 125 ^{\circ}\text{C}$		Max.	30				mΩ	
I <sub>DRM</sub>	\\ -\\ -\\ -\\	T <sub>j</sub> = 25 °C	May	5				μΑ	
I <sub>RRM</sub>	$V_D = V_R = V_{DRM} = V_{RRM}$	T <sub>j</sub> = 125 °C	Max.			2		mA	

<sup>1.</sup> x00= 600, 800

**Table 4. Thermal resistance** 

Symbol		Value	Unit		
R <sub>th(j-c)</sub>	Junction to case (DC)	D <sup>2</sup> PAK, DPAK,	D <sup>2</sup> PAK, DPAK, IPAK, TO-220AB		
	R <sub>th(j-a)</sub> Junction to ambient (DC)	$S^{(1)} = 0.5 \text{ cm}^2$	DPAK	70	
В		$S^{(1)} = 1.0 \text{ cm}^2$	D²PAK	45	°C/W
Rth(j-a)			IPAK	100	C/VV
			TO-220AB	60	


<sup>1.</sup> S = Copper surface under tab




<sup>2.</sup> Check Table 1 for devices availability

<sup>3.</sup> x= 6,8,10

Figure 3. Average and DC on-state current versus ambient temperature (DPAK, D<sup>2</sup>PAK)  $I_{T(AV)}(A)$ 3.0 Device mounted on FR4 with recommended pad layout 2.5 D.C. ..... D<sup>2</sup>PAK 20 DPAK D<sup>2</sup>PAk 1.5 **DPAK** 1.0  $\alpha = 180^{\circ}$ 0.5 Ta(°C) 0.0 25 50 75 100 125








Figure 8. Non repetitive surge peak on-state current for a sinusoidal pulse with width tp<10 ms  $I_{\mathsf{TSM}}(\mathsf{A})$ 10000 T<sub>i</sub> initial = 25 °C TN1215G / TYN12 1000 ITSM TN1215-B/-H 100 tp(ms) 10 0.01 0.10 1.00

Figure 9. On-state characteristics (maximum values) I<sub>TM</sub>(A) 200 100 10 V<sub>TM</sub>(V) 5.0 0.0 0.5 1.5 2.5 3.0 3.5 4.0 4.5 1.0 2.0




Figure 10. Thermal resistance junction to



#### 2 **Package information**

- Halogen free molding resin
- Epoxy meets UL94, V0
- Lead-free packages
- Recommended torque: 0.4 to 0.6 N·m (TO-220AB)

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

#### 2.1 **DPAK** package information

Figure 11. DPAK package outline

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.




Table 5. DPAK package mechanical data

	Dimensions							
Ref.		Millimeters		Inches <sup>(1)</sup>				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
Α	2.18		2.40	0.0858		0.0945		
A1	0.9		1.10	0.0354		0.0433		
A2	0.03		0.23	0.0012		0.0091		
b	0.64		0.90	0.0252		0.0354		
b4	4.95		5.46	0.1949		0.2150		
С	0.46		0.61	0.0181		0.0236		
c2	0.46		0.60	0.0181		0.0236		
D	5.97		6.22	0.2350		0.2449		
D1	4.95		5.60	0.1949		0.2205		
E	6.35		6.73	0.2500		0.2650		
E1	4.32		5.50	0.1701		0.2165		
е		2.286			0.0900			
e1	4.40		4.70	0.1732		0.1850		
Н	9.35		10.40	0.3681		0.4094		
L	1.0		1.78	0.0394		0.0701		
L2			1.27			0.0500		
L4	0.6		1.02	0.0236		0.0402		
V2	-8°		+8°	-8°		+8°		

<sup>1.</sup> Inches only for reference.

Figure 12. Footprint (dimensions in mm)



## 2.2 IPAK package information

E b4 V1 A1 H

Figure 13. IPAK package outline

Note:

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

57/

Table 6. IPAK package mechanical data

			Dime	nsions				
Ref.		Millimeters		Inches <sup>(1)</sup>				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
Α	2.20		2.40	0.0866		0.0945		
A1	0.90		1.10	0.0354		0.0433		
b	0.64		0.90	0.0252		0.0354		
b2			0.95			0.0374		
b4	5.20		5.43	0.2047		0.2138		
B5		0.30			0.0118			
С	0.45		0.60	0.0177		0.0236		
c2	0.46		0.60	0.0181		0.0236		
D	6.00		6.20	0.2362		0.2441		
Е	6.40		6.65	0.2520		0.2618		
е		2.28			0.0898			
e1	4.40		4.60	0.1732		0.1811		
Н		16.10			0.6339			
L	9.00		9.60	0.3543		0.3780		
L1	0.80		1.20	0.0315		0.0472		
L2		0.80	1.25		0.0315	0.0492		
V1		10°			10°			

<sup>1.</sup> Inches dimensions given only for reference.

## 2.3 TO-220AB package information




Figure 14. TO-220AB package outline

577

Table 7. TO-220AB package mechanical data

			Dimer	nsions		
Ref.	Millimeters				Inches <sup>(1)</sup>	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	15.2		15.9	0.5984		0.6260
a1		3.75			0.1476	
a2	13		14	0.5118		0.5512
В	10		10.4	0.3937		0.4094
b1	0.61		0.88	0.0240		0.0346
b2	1.23		1.32	0.0484		0.0520
С	4.4		4.6	0.1732		0.1811
c1	0.49		0.7	0.0193		0.0276
c2	2.4		2.72	0.0945		0.1071
е	2.40		2.70	0.0945		0.1063
F	6.2		6.6	0.2441		0.2598
I	3.73		3.88	0.1469		0.1528
L	2.65		2.95	0.1043		0.1161
12	1.14		1.7	0.0449		0.0669
13	1.14		1.7	0.0449		0.0669
14	15.8	16.4	16.8	0.6220	0.6457	0.6614
М		2.6			0.1024	

<sup>1.</sup> Inches dimensions given only for reference.

# 2.4 D<sup>2</sup>PAK package information




Figure 15. D<sup>2</sup>PAK package outline

**577** 

Table 8. D<sup>2</sup>PAK package mechanical data

			Dime	nsions				
Ref.	Millimeters			Inches <sup>(1)</sup>				
	Min.	Тур.	Max.	Min.	Тур.	Max.		
Α	4.30		4.60	0.1693		0.1811		
A1	2.49		2.69	0.0980		0.1059		
A2	0.03		0.23	0.0012		0.0091		
В	0.70		0.93	0.0276		0.0366		
B2	1.25	1.40		0.0492	0.0551			
С	0.45		0.60	0.0177		0.0236		
C2	1.21		1.36	0.0476		0.0535		
D	8.95		9.35	0.3524		0.3681		
D1	7.50		8.0	0.2953		0.3150		
D2	1.3		1.7	0.0512		0.0669		
E	10.00		10.28	0.3937		0.4047		
E1	8.3		8.7	0.3268		0.3425		
E2	6.85		7.25	0.2697		0.2854		
G	4.88		5.28	0.1921		0.2079		
L	15.00		15.85	0.5906		0.6240		
L2	1.27		1.40	0.0500		0.0551		
L3	1.40		1.75	0.0551		0.0689		
R		0.40			0.0157			
V2	0°		8°	0°		8°		

<sup>1.</sup> Inches dimensions given only for reference.

16.90 10.30 5.08 ··--- ‡1.30 -3.70 8.90

Figure 16. Footprint (dimensions in mm)

5/

# 3 Ordering information

Figure 17. TN1215 series





Figure 18. TYNx12 series



577

Table 9. Ordering information

Order code	Voltage V <sub>DRM</sub> / V <sub>RRM</sub> (v)			Package	Weight	Base qty.	Delivery mode	
Order code	600	800	1000	I <sub>GT (mA)</sub>	rackage	(g)	(pc)	Delivery mode
TYN1012RG			х	15	TO-220AB	2.3	50	Tube
TYN1012TRG			х	5	TO-220AB	2.3	50	Tube
TYN612RG	х			15	TO-220AB	2.3	50	Tube
TYN612TRG	х			5	TO-220AB	2.3	50	Tube
TYN812RG		Х		15	TO-220AB	2.3	50	Tube
TYN812TRG		Х		5	TO-220AB	2.3	50	Tube
TN1215-600B	Х			15	DPAK	0.3	75	Tube
TN1215-600B-TR	х			15	DPAK	0.3	2500	Tape and reel
TN1215-600G	х			15	D <sup>2</sup> PAK	1.5	50	Tube
TN1215-600G-TR	Х			15	D <sup>2</sup> PAK	1.5	1000	Tape and reel
TN1215-600H	Х			15	IPAK	0.3	75	Tube
TN1215-800B-TR		Х		15	DPAK	0.3	2500	Tape and reel
TN1215-800G-TR		Х		15	D <sup>2</sup> PAK	1.5	1000	Tape and reel
TN1215-800H		Х		15	IPAK	0.3	75	Tube



# 4 Revision history

**Table 10. Document revision history** 

Date	Revision	Changes
Sep-2000	3	Last update.
25-Mar-2005	4	TO-220AB delivery mode changed from bulk to tube.
14-Oct-2005	5	Changed sensitivity values in <i>Table 1</i> for TYNx12 (30 to 15 mA) and TYNx12T (15 to 5 mA). Added ECOPACK statement.
08-Mar-2007	6	Reformatted to current standard. Figure 17: TN1215 series product name corrected. Figure 23: TS1220 series product name corrected.
23-Oct-2009	7	Added TS1220-xxxT device.
03-Jun-2014	8	Updated DPAK and IPAK package information and reformatted to current standard.
25-Feb-2015	9	The part number TS1220 series has been moved to a separate document.Removed TO-220AB insulated package information.
29-Jul-2015	10	Updated Figure 11.
05-Oct-2016	11	Updated Section 2: Package information. Minor text changes.



#### **IMPORTANT NOTICE - PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved



DocID7475 Rev 11

17/17