

STAC2932B

HF/VHF/UHF RF power N-channel MOSFETs

Features

- Gold metallization
- Excellent thermal stability
- Common source push-pull configuration
- P_{OUT} = 300 W min. with 20 dB gain @ 175 MHz
- In compliance with the 2002/95/EC European directive
- ST air cavity packaging technology STACTM package

Description

The STAC2932B is a gold metallized N-channel MOS field-effect RF power transistor. It is intended for use in 50 V DC large signal applications up to 250 MHz. The STAC2932B benefits from the latest generation of efficient, patent-pending STAC[™] package technology.




Figure 1. Pin connection




Table 1. Device summary

Order code	Marking	Base qty.	Package	Packaging
STAC2932B	STAC2932 ⁽¹⁾	20	STAC244B	Tray

1. For more details please refer to Chapter 7: Marking, packing and shipping specifications.

```
September 2011
```

Doc ID 15497 Rev 4

www.st.com

Contents

1	Electr	ical data	\$
	1.1	Maximum ratings	3
	1.2	Thermal data 3	3
2	Electr	ical characteristics	ŀ
	2.1	Static 4	ł
	2.2	Dynamic 4	1
3	Imped	lance	5
4	Туріса	al performance	5
5	Test o	eircuit	3
6	Packa	ige mechanical data 10)
7	Marki	ng, packing and shipping specifications	2
8	Revis	ion history	}



1 Electrical data

1.1 Maximum ratings

 $(T_{CASE} = 25 \ ^{\circ}C)$

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V _{(BR)DSS} ⁽¹⁾	Drain source voltage	125	V
V _{DGR}	Drain-gate voltage (R_{GS} = 1 M Ω)	125	V
V _{GS}	Gate-source voltage	±20	V
I _D	Drain current	40	А
P _{DISS}	Power dissipation	625	W
Т _Ј	Max. operating junction temperature	200	°C
T _{STG}	Storage temperature	-65 to +150	°C

1. $T_J = 150 \ ^{\circ}C$

1.2 Thermal data

Table 3. Thermal data

Symbol	Parameter	Value	Unit
R _{thJC}	Junction - case thermal resistance	0.28	°C/W



2 Electrical characteristics

 $T_{CASE} = +25 \ ^{\circ}C$

2.1 Static

Table 4.	Static (per si	ide)					
Symbol		Test conditions		Min.	Тур.	Max.	Unit
V _{(BR)DSS}	V _{GS} = 0 V	I _{DS} = 100 mA		125			V
I _{DSS}	V _{GS} = 0 V	$V_{DS} = 50 V$				50	μA
I _{GSS}	V _{GS} = 20 V	$V_{DS} = 0 V$				250	nA
V _{GS(Q)}	V _{DS} = 10 V	I _D = 250 mA		1.5	2.5	4.0	V
V _{DS(ON)}	V _{GS} = 10 V	I _D = 10 A				3.0	V
G _{FS}	V _{DS} = 10 V	I _D = 5 A		5			S
C _{ISS}					468		pF
C _{OSS}	$V_{GS} = 0 V$	$V_{DS} = 50 V$	f = 1 MHz		206		pF
C _{RSS}					16		pF

2.2 Dynamic

Table 5. Dynamic

Symbol	Test conditions	Min.	Тур.	Max.	Unit
P _{OUT}	V _{DD} = 50 V, I _{DQ} = 2 x 250 mA, P _{IN} = 4 W, f = 175 MHz	300	390		W
h _D	V_{DD} = 50 V, I_{DQ} = 2 x 250 mA, P_{IN} = 4 W, f = 175 MHz	55	68		%



3 Impedance

Figure 2. Current conventions




Table 6.Impedance data

Freq. (MHz)	Ζ_{ΙΝ} (Ω)	Ζ_{DL}(Ω)
175 MHz	2.0 - j2.0	3.5 + j5.2

Note: Measured gate to gate and drain to drain, respectively.



Typical performance 4




Figure 4.






Figure 5. Output power vs gate voltage



Output power vs drain supply









Figure 7. Output power vs input power and case temperature





5 Test circuit




Figure 9.	175 MHz test circuit schematic (production test circuit)
1 19410 01	in o mine toot on our oon and (production toot on our)

Table 7.	175 MHz test circuit component list
----------	-------------------------------------


Component	Description
C1, C2, C14, C15, C24, C25	1200 pF ATC 700B chip capacitor
C5	75 pF ATC 100B chip capacitor
C6	ST406 variable capacitor
C9, C10	47 pF ATC 100B chip capacitor
C11, C12, C13	43 pF ATC 100B chip capacitor
C16, C18	470 pF ATC 100B chip capacitor
C17, C19, C20, C21	10,000 pF ATC 200B chip capacitor
C22, C23	0.1 µF 200 V chip capacitor
C28	10 µF 100 V electrolytic capacitor
C29	0.8 - 8 pF variable capacitor
R1, R2, R5, R6	430 Ω, 1/2 W chip resistor



Component Description	
R3, R4	270 Ω 1/2 W axial lead resistor
B1	RG-316 50 Ω 11.8" through ferrite toroidal
B2	RG-142 50 Ω 11.8"
T1	4:1, RG-316 25 Ω , 5.9", 2 turns thru ferrite core
T2	1:4, 25 Ω semi-rigid cable, OD.141", 5.9"
L1	$\lambda/4$ inductor, RG-142 50 Ω , 11.8", 3 turns thru ferrite toroid
FB1,FB5	ferrite toroidal
FB2, FB6	multi-aperture core
FB3, FB4	surface mount ferrite bead
PCB	Rogers ultralam 2000, Er 2.55, 0.060"

Table 7.	175 MHz test circuit component list	(continued))
----------	-------------------------------------	-------------	---

Figure 10. Circuit layout





6 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.

Dim.	mm.			
	Min.	Тур.	Max.	
A	5.08		5.59	
A1	4.32		4.83	
В	4.32		5.33	
С	9.65		9.91	
D	17.78		18.08	
E	33.88		34.19	
F	0.10		0.15	
G		1.02		
н	1.45		1.70	
I	4.83		5.33	
J	9.27		9.52	
К	27.69		28.19	
L	3.12	3.23	3.33	
М	3.35	3.45	3.56	

 Table 8.
 STAC244B mechanical data






Figure 11. Package dimensions



7 Marking, packing and shipping specifications

 Table 9.
 Packing and shipping specifications

Order code	Packaging	Pcs per tray	Dry pack humidity	Lot code
STAC2932B	Tray	20	< 10 %	Not mixed

Figure 12. Marking layout



Table 10. Marking specifications

Symbol	Description
CZ	Assembly plant
ххх	Last 3 digits of diffusion lot
VY	Diffusion plant
MAR	Country of origin
CZ	Test and finishing plant
у	Assembly year
уу	Assembly week



8 Revision history

Table 11.	Document	revision	history
	Document	164131011	matory

Date	Revision	Changes
20-Mar-2009	1	First release.
29-Jun-2010	2	Updated features and description on cover page.
12-Aug-2011	3	Update figures on coverpage and <i>Section 6: Package mechanical data.</i> Inserted <i>Section 7: Marking, packing and shipping specifications.</i> Minor text changes.
05-Sep-2011	4	Update L and M dimensions Table 9 on page 12.



Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY TWO AUTHORIZED ST REPRESENTATIVES, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2011 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

14/14

Doc ID 15497 Rev 4

