
Powerpole® Connectors - PP15 to PP45: up to 55 Amps



PP15-45 series are the smallest Powerpole® housings. They can be used for wire-to-wire or wire-to-board applications. Wire sizes from #20 AWG (0.75 mm²) to #10 (6 mm²) offer power capabilities up to 55 amps per pole. Finger proof housings and the ability to incorporate first-mate last-break ground connectors enhance the capabilities of this Powerpole® series.

High Power Density

· Up to 55 amps in a compact footprint

Wire-to Wire & Wire-to-Board Configurations

Wire & PCB contacts can be used in the same housings


Finger Proof Housings Available

Protects against accidental contact with live circuits


PP15-45 ORDERING INFORMATION |

PP15-45 Finger Proof HousingsImproved on the original APP design by adding ribs to mating interface to protect against accidental contact with live circuits. Meets the requirements of UL1977 section 10.2 and is rated IP20. Will not mate with standard housings.

Description	Part Numbers				
Minimum Quantity .	2,500	200			
Red	1327FP-BK	1327FP			
Green	1327G5FP-BK	1327G5FP			
Black	1327G6FP-BK	1327G6FP			
White	1327G7FP-BK	1327G7FP			
Blue	1327G8FP-BK	1327G8FP			
Yellow	1327G16FP-BK	1327G16FP			




PP15-45 Finger Proof & Standard & Ground **Housing Dimensions**



PP15-45 Standard Housings

This original housing design has an open interface and is available in a wide array of colors. Will not mate with finger proof housings.


Description	Part Numbers		
Minimum Quantity	2,500	200	
Red Green	1327-BK 1327G5-BK	1327 1327G5	
Black	1327G6-BK	1327G6	
White	1327G7-BK	1327G7	
Blue	1327G8-BK	1327G8	
Yellow	1327G16-BK	1327G16	
Orange	1327G17-BK	1327G17	
Gray	1327G18-BK	1327G18	
Brown	1327G21-BK	1327G21	
Pink	1327G22-BK	1327G22	
Purple	1327G23-BK	1327G23	



45A Premate Ground Housings

Green housings are keyed to prevent accidental mating with standard or finger proof Powerpole® housings.

J. I		
Description	Part Nui	mbers
Minimum Quantity	2,500	200
Green	1827G1-BK	1827G1



© 2017 Anderson Power Products, Inc. All rights reserved. APP®, Anderson Power Products®, A®, Powerpole®, SPEC Pak® and the APP Logo are registered trademarks of Anderson Power Products. Inc



PP15-45 Tin Plated Power Contacts

Offer cost effective performance up to 1,500 mating cycles. See specifications and temperature charts for amperage ratings by wire size.

						Dimen	sions
			Mating	Loose Piece	Reeled	- A	-
Barrel	AWG	mm²	Force	Part Numb	oers	inches	mm
Minimu	ım Quantity			200	5,000		
Open Open Open Open Open Open Open Open	14 to 10 K* 14 to 10 K* 14 to 10 SF* 14 to 10 SF* 16 to 12 20 to 16 20 to 16	2.1 to 5.3 2.1 to 5.3 2.1 to 6.0 2.1 to 6.0 1.3 to 3.3 1.3 to 3.3 0.52 to 1.3	High Low High Low High Low High Low	269G3-LPBK 261G2-LPBK 201G1H-LPBK 200G1L-LPBK 269G1-LPBK 261G1-LPBK 269G2-LPBK 262G1-LPBK	269G3 261G2 201G1H 200G1L 269G1 261G1 269G2 262G1	0.21 0.20 0.24 0.24 0.18 0.18 0.16 0.16	5.33 5.08 6.10 6.10 4.57 4.57 4.06 4.06

K* - For #10 AWG class K stranded wire or smaller. For larger wires use superflex contacts.

SF*- Indicates wires with high stranding such as Super Flex.

PP15-45 Silver Plated Power Contacts


Maximize performance by offering up to 10,000 mating cycles and are recommended for circuit interrupt or hot plug applications. See specifications and temperature charts for amperage ratings by wire size. Only closed barrel contacts are suitable for soldering.

								Dime	nsions	
			Mating	Loc	se Piece	Reeled	- A	١-	- B	-
Barrel	AWG	mm²	Force	Part	Numbers	Part Numbers	inches	mm	inches	mm
Minimum	Quantity			5,000	200	5,000				
Open	14 to 10 K*	2.1 to 5.3	Low	-	261G3-LPBK	261G3	0.20	5.08	-	-
Open .	14 to 10 SF*	2.1 to 6.0	Low	-	200G3L-LPBK	200G3L	0.24	6.10	-	-
Open	20 to 16	0.52 to 1.3	Low	-	262G2-LPBK	262G2	0.16	4.06	-	-
Closed	16 to 12	1.3 to 3.3	Low	1331-BK	1331	-	0.15	3.81	0.10	2.54
Closed	20 to 16	0.52 to 1.3	Low	1332-BK	1332	-	0.12	3.05	0.07	1.78


K* - For #10 AWG class K stranded wire or smaller. For larger wires use superflex contacts.

SF*- Indicates wires with high stranding such as Super Flex.


Open Barrel Contact



Open Barrel Contact



Closed Barrel Contact



45A Premate Ground Wire Contacts

Tin or silver plated contacts are rated for ground or power. Hand tools are available for loose piece contacts. Reeled contacts can be used with high volume press and applicator tooling. Tin contacts are rated for up to 1,500 mating cycles. Silver contacts are rated up to 10,000 mating cycles.

					Reeled
			Mating	Loose Piece	Part
Туре	AWG	mm²	Force	- Part Numbers -	- Numbers -
Minimum Qua	ntity	200	5,000		
Open, Tin	14 to 10	2.1 to 6.0	Low	1830G1-LPBK	1830G1
Open, Silver	14 to 10	2.1 to 6.0	Low	1830G2-LPBK	1830G2

25A Right Angle PCB Contacts Tin Plated Suitable for right angle applications up to 25A per pole. Tin plating enhances solderability. Cannot be mixed with 45A PCB contacts. For mating with wire contacts only.


					Dime	nsions	
	Mating	Loose I	Piece	- A	١-	- B -	
Row	Force	Part Nur	mbers	inches	mm	inches	mm
Minimum	Quantity .	1,000	100				
Тор	Low High	1377G1-BK 1317G1-BK	1377G1 1317G1	0.59	14.80	1.52	38.60
Bottom	Low High	1377G2-BK 1317G2-BK	1377G2 1317G2	0.29	7.20	1.36	34.50
Тор	Low High	1377G11-BK 1317G11-BK	1377G11 1317G11	0.59	14.80	1.21	30.70
Bottom	Low High	1377G12-BK 1317G12-BK	1377G12 1317G12	0.29	7.20	1.01	25.70


25A Vertical PCB Contacts Tin Plated

For mating with wire contacts only. Suitable for vertical applications up to 25A per pole, tin plating enhances solderability.

an placing officioes soldstability.							
	Dimensions						
Loose Piece	:	- A -					
Part Numbers	inches	s mm					
n Quantity 1,000	100						
1377G3-BK	1377G3	2.22	56.40				
1317G3-BK	1317G3	2.22	56.40				
1377G4-BK	1377G4	1.76	44.70				
1317G4-BK	1317G4	1.76	44.70				
1377G13-BK	1377G13	1.17	29.70				
1317G13-BK	1317G13	1.17	29.70				
	Loose Piece ———————————————————————————————————	Loose Piece ———————————————————————————————————	Loose Piece - inches n Quantity 1,000 100 1377G3-BK 1377G3 2.22 1317G3-BK 1317G3 2.22 1377G4-BK 1377G4 1.76 1317G4-BK 1317G4 1.76 1377G13-BK 1317G1 1.17				








Use mounting staples with right angle contacts (see accessories).


See website for PCB layout drawing.





45A Right Angle and Vertical PCB Contacts Tin Plated

Suitable for right angle or vertical applications up to 45A per pole. Tin plating enhances solderability. Right angle contacts cannot be mixed with 25A PCB contacts. For mating with wire contacts only.

	Loose Piece		
Description	Part	Numbers	
Minimum Quantity	1,000	100	
Vertical	3-5911P1	1335G1	
Right Angle Bottom Row	3-5912P1	1336G1	
Right Angle Top Row	3-5913P1	1337G1	








45A Premate Ground PCB Contacts

Right angle contacts are suitable for power or ground. Use to mate with 45A ground wire contacts. Tin plated contacts are rated up to 1,500 mating cycles. Can be used with other 45A PCB connectors in the bottom row.

	Mating	Loose Piece			
	Force	Part Numbers			
Minimum Quantity		1000	100		
PCB, Bottom Row	Low	3-5952P1	1836G1		



| PP15-45 ULTRASONICALLY BONDED ASSEMBLIES |

Assemblies feature housings that are ultrasonically welded to create a one piece connector unit using an APP special process. After welding, retaining pins are no longer required to secure the stacked housings to each other. This allows Powerpole® 15-45 connectors to be used as a durable one piece connector header. Contact customer service for configurations not shown below.

Single Row 1x2 Assemblies

		Housings with	Housings with		
		45A Vertical	45A Right Angle	Color & Type	
Circuit Description	Housings Only	PCB Contacts	PCB Contacts	Position Matrix	
Minimum Quantity	500	500	500	1 2	
DC 2 Wire Standard Housings	ASMPP30-1X2-RK	ASMPV45-1X2-RK	ASMPR45-1X2-RK	RED/STD BLK/ST	D
DC 2 Wire Reverse Standard Housings	ASMPP30-1X2-KR	ASMPV45-1X2-KR	ASMPR45-1X2-KR	BLK/STD RED/ST	ſD
DC 2 Wire Finger Proof	ASMFP30-1X2-RK	ASMFV45-1X2-RK	ASMFR45-1X2-RK	RED / FP BLK / FP	
DC 2 Wire Finger Proof Reverse	ASMFP30-1X2-KR	ASMFV45-1X2-KR	ASMFR45-1X2-KR	BLK / FP RED / FP)

Single Row 1x3 Assemblies

		Housings with	Housings with			
		45A Vertical	45A Right Angle		Color & Type	
Circuit Description	Housings Only	PCB Contacts	PCB Contacts		Position Matrix	
Minimum Quantity	500	500	500	1	2	3
DC 2 Wire Finger Proof with Ground	ASMFP30-1X3-KER	N/A	ASMFR45-1X3-KER	BLK / FP	GRN / GND I	RED / FP
AC Single Phase Finger Proof	ASMFP30-1X3-KEW	ASMFV45-1X3-KEW	ASMFR45-1X3-KEW	BLK / FP	GRN / GND	WHT / FP

Two Row 2x1 Assemblies

		Housings with	Housings with		
		45A Vertical	45A Right Angle	Color &	Туре
Circuit Description	Housings Only	PCB Contacts	PCB Contacts	Position	Matrix
Minimum Quantity		500	500	1	2
DC 2 Wire Finger Proof	ASMFP30-2X1-KR	ASMFV45-2X1-KR	ASMFR45-2X1-KR	BLK / FP	RED / FP
DC 2 Wire Finger Proof Mate	ASMFP30-2X1-RK	ASMFV45-2X1-RK	ASMFR45-2X1-RK	RED / FP	BLK / FP

Two Row 2x2 Assemblies

		Housings with	Housings with				
		45A Vertical	45A Right Angle		Color	& Type	
Circuit Description	Housings Only	PCB Contacts	PCB Contacts		Positio	n Matrix	
Minimum Quantity	500	500	500	1	2	3	4
AC 3 Phase, 3 Wire Finger Proof	ASMFP30-2X2-KRWE	N/A	N/A	BLK / FP	RED / FP	WHT / FP	GRN / GND
AC 3 Phase, 3 Wire Finger Proof Mate	ASMFP30-2X2-WEKR	N/A	ASMFR45-2X2-WEKR	WHT / FP	GRN / GND	BLK / FP	RED / FP




Single Row 1x2 Assembly Single Ro



Single Row 1x3 Assembly



Two Row 2x1 Assembly




Type

STD = Standard Housing

FP = Finger Proof Housing

GND = Ground Housing

Powerpole® Pak Connectors - PP15 to PP45



Powerpole® Pak connector shells enclose stacked groupings of PP15-45 sized housings in a durable black shell for a finished connector appearance and additional features. Inline, panel mount, and blindmate configurations are available. Plug shells offer the option of integral latches and strain relief to help secure your connection.

- Package Groupings of PP15-45 Connectors
 Provides a finished appearance while protecting the individual connectors with an outer shell
- Inline, Panel Mount, "T" or Blindmate Configurations
 Allows one connection system to meet multiple needs
- Optional Latching and Strain Relief Secures your connection and wires

For environmentally sealed connector shells to hold Powerpole® 15-180 connectors, see SPEC Pak® product series on our website, <u>www.andersonpower.com</u>




| Powerpole® Pak ORDERING INFORMATION |

Powerpole® housings and contacts are sold separately. See page 20 for ordering information.

Plug Shell without Latch

Can mate inline with other plug shells with or without latches, or mate to a panel mount receptacle. For use with Powerpole® wire connectors only. Cable Clamp and Hardware Pak or Retaining Pins must be ordered separately.

				Dimen	sions
				- A	
Description	Pa	art Numbers		inches	mm
Minimum Quantity	1,000	500	25		
Black, 2-4 Poles	1461G1-BK	-	1461G1	1.24	31.50
Black, 5-6 Poles	-	1461G2-BK	1461G2	1.56	39.62
Black, 7-8 Poles	-	1461G3-BK	1461G3	1.87	47.50




NOTE: Retaining pins are used to secure and position Powerpole® housings in one of three positions in plug shells.

Max wire O.D. for 2-4 pole plug shells is 0.60 inches [15.2mm²]. For all other plug shells is 0.63 inches [16.0 mm²].

Plug Shell with Latch

Can mate inline with other plug shells without latches, or mate to a panel mount receptacle. For use with Powerpole® wire connectors only. Cable Clamp and Hardware Pak or Retaining Pins must be ordered seperately.


			Dimensions					
			- B	-	- C	; -	- D) -
Pa	rt Numbers		inches	mm	inches	mm	inches	mm
1,000	500	25						
1460G1-BK	-	1460G1	1.94	49.28	2.25	57.15	1.24	31.50
-	1460G2-BK	1460G2	1.94	49.28	2.25	57.15	1.56	39.62
-	1460G3-BK	1460G3	1.94	49.28	2.25	57.15	1.87	47.50
-	1460G4-BK	1460G4	2.51	63.75	2.82	71.63	1.84	46.74
	1,000 1460G1-BK -	1,000 500 1460G1-BK - - 1460G2-BK - 1460G3-BK	1460G1-BK - 1460G1 - 1460G2-BK 1460G2 - 1460G3-BK 1460G3	Part Numbers	1,000 500 25	-B - C inches mm inches inches mm inches inches mm inches		-B - C - Description - C - Description - Description - C - Description -



Plug Shell with Latch & Non-Conductive Strain Relief

New 2X3 Powerpole® Pak offers an improved ergonomic shell for easier latch operation as well as a plastic, non-conductive strain relief. The new strain relief can accommodate up to a 6 conductor #10 AWG cable. Can mate to a panel mount receptacle. For use with Powerpole® wire connectors only. Cable Clamp and Hardware Pak or Retaining Pins must be ordered separately. To be used with 115G23 cable clamp only.

Description	Part Numbers			
Minimum Quantity	1,000	25		
Black, 5-6 Poles	1460G23-BK	1460G23		



Snap-in Receptacle Shell

Mate to plug shells with or without latches, or mate to another panel mount receptacle to create a bulkhead to bulkhead connection. For use with Powerpole® wire or PCB connectors. Order the number of retaining pins for each receptacle as shown below separately.

Description	Pa	art Numbers		Number of Retaining Pins to Order	Dimen: - E inches	-	Knock (- Wid inches	
Minimum Quantity	1,000	500	25					
Black, 2-4 Poles	1470G1-BK	-	1470G1	1	1.50	38.10	1.25	31.75
Black, 5-6 Poles	-	1470G2-BK	1470G2	2	1.88	47.75	1.62	41.15
Black, 7-8 Poles	-	1470G3-BK	1470G3	3	2.13	54.10	1.88	47.75
Black, 9-10 Poles	-	1470G4-BK	1470G4	4	2.44	61.98	2.19	55.63
* Hoight = [25.4 mg	n1 1 0 in							

^[19.56] [27.94] 0.77 1.10 Retaining Pin

[1.78]


NOTE: Retaining pins are used to secure and position Powerpole® housings in one of two positions in receptacle shells.

Height = [25.4 mm] 1.0 in.

Cable Clamp & Hardware Pak

Includes cable clamp, 2 screws, and required amount of retaining pins for each configuration.


	Screw Head	Cable			
Description	Type	Type	Pa	rt Numbers -	
Minimum Qua	ntity		1,000	500	25
2-4 Poles	Straight Slot	Bundled	115G1-BK	-	115G1
5-6 Poles	Straight Slot	Bundled	115G2-BK	-	115G2
7-8 Poles	Straight Slot	Bundled	115G3-BK	-	115G3
9-10 Poles	Straight Slot	Bundled	-	115G4-BK	115G4
2-4 Poles	Philips	Bundled	115G7-BK	-	115G7
5-6 Poles	Philips	Bundled	115G8-BK	-	115G8



Cable Clamp & Hardware Pak

Includes 2 cable clamp halves, 2 screws and 2 retaining pins. To be used with 1460G23 Plug Shell only.

Description	Screw Head Type	Cable Type	Part Num	nbers
Minimum Qua	antity	Rundled	1,000 115G23-BK	25 115G23



Flexible Conduit Clamp & Hardware Pak

Includes cable clamp, 2 screws, and need amount of retaining pins for each configuration.

Description	- Part Number -
Minimum Quantity	100
2-4 Poles	110G10

Retaining Pin Conduit Clamp With Screws Plug Shell With Latch Shown Shell, housing and contacts are sold separately.

Retaining Pin for Snap-in Receptacle

Order the number of retaining pins for each receptacle shown in the Snap-in Receptacle Shell ordering information. Pins are also required for the plug side when the Cable Clamp & Hardware Pak is not ordered.

Description	Part Number		
Minimum Quantity	1,000	100	
Retaining Pin	110G9-BK	110G9	







Shell and housing are sold separately.

Blindmate Pak Connector

Ideal for panel to panel, bulkhead to bulkhead, or rack mount applications that require the power connector to compensate for up to 0.45 in. [11.43 mm] of misalignment in either axis. Eight positions can be filled with Powerpole® 10-45 connectors. The receptacle side can be used with wire or PCB contacts. Hardware bag includes retaining pins.


Description	Part I	Numbers
Minimum Quantity	50	25
2x4 Blindmate Plug Shell, Hardware & Pins	-	BMPP10-45P
2x4 Blindmate Receptacle Shell, Hardware & Pins	-	BMPP10-45R
2x4 Blindmate Plug Shell	BMHSG-P	-
2x4 Blindmate Receptacle Shell	BMHSG-R	-
Hardware Bag Plug Side	-	110G50
Hardware Bag Receptacle Side	-	110G51






Plug Outline

Receptacle Outline





See our innovative MARC Connector that offers straight-on or rotational blindmate capability. MARC holds 6 PP15/45 power contacts and 2 PP15/45 premate ground contacts in a high temperature housing. Visit our website, www.andersonpower.com to learn more.



"T" Pak 2 Way Splitter


The Powerpole® "T" Pak connector is a 2 way electrical splitter that splits electrical current from one incoming circuit into two outgoing circuits. The standard configuration is pre-wired for AC 3 phase, 3 wire plus ground configurations. The "T" Pak can also be used for AC single phase plus ground or DC 2 wire plus ground applications by not using either the red or white power positions. "T" Pak is pre-wired from the factory allowing plug and play field installation of modular office and industrial equipment. UL recognition up to 20 amps and 600 volts is achieved when mating Powerpole® Pak plugs with #12 AWG wire.


For OEM manufacturing scale applications, the "T" Pak can be loaded with custom configurations of any of our finger proof, standard, or ground housings and contacts in the PP15-45 series. Contact sales or customer service for additional information.

Description	- Part Numbers -
Minimum Quantity	80
Assembled "T" Pak	20-01
Mating Plug Shell with Latch 2x2	26-01
Mating Plug Shell without Latch 2x2	27-01

Standard configuration for each side of the T includes (1) each Red, Black, and White Standard PP 15-45 Housings & 261G2-LPBK contacts with (1) 45A Green Premate Ground Housing and 1830G1-LPBK contact.

Mating plug shells include (1) each Red, Black, and White Standard PP 15-45 Housings & (3) 261G2-LPBK contacts with (1) 45A Green Premate Ground Housing and 1830G1-LPBK contact. Cable clamp & hardware pak also included.







| PP15-45 & POWERPOLE® PAK SPECIFICATIONS |

Electrical		
Current Rating Amperes ¹	UL 1977	CSA/TUV
Singlepole Wire to Wire (10 AWG)	55	40
Singlepole Ground Wire to Wire or PCB (10 AWG)45	35
3x3 Block Wire to Wire (10 AWG)	40	27
Singlepole 25A PCB to Wire (12 AWG)	25	-
2x3 Block 25A PCB to Wire (12 AWG)	25	22 *
Singlepole 45A PCB to Wire (10 AWG)	45	40 *
2x3 Block 45A PCB to Wire (10 AWG)	45	25 *
Voltage Rating AC/DC		
UL 1977	600	
Dielectric Withstanding Voltage		
Volts AC	2,200	
Avg. Mated Contact Resistance Milliohms 1		
15A Wire Contact with 5/8" of #16 AWG	0.875	
30A Wire Contact with 5/8" of #12 AWG	0.600	
45A Wire Contact with 5/8" of #10 AWG	0.525	
45A PCB Contact to Contact	0.500	
25A PCB Contact to Contact	0.600	
UL Hot Plug Current Rating Amperes ⁵		
250 cycles at 72V DC	45A	
250 cycles at 120V DC	30A	
200 0,0.00 at 120 v 20	3071	
UL Ground Short Time Current Test - 45A Pro	emate Gro	und
750 Amps, #10 AWG Wire	4 Second	-
470 Amps, #12 AWG Wire	4 Second	s

470 Amps, #12 AWG Wire	4 Seconds
Materials	
Housing	
Plastic Resin	Polycarbonate
Contact Retention Spring	Stainless Steel
Housing Flammability Rating	
UL94	V-0
Glow Wire	825°C (GWFI) / 800°C (GWIT)
Contact	
Base	Copper Alloy
Plating	Tin or Silver
Contact Termination Methods	
Crimp ³	Wire Contacts
Hand Solder	1331, 1332 & PCB Contacts
Solder Dip	PCB Contacts
Wave Solder	PCB Contacts

Mechanical		
Wire Size Range	AWG	mm²
	20 to 10	0.75 to 6.0
Max. Wire Insulation Diameter	in.	mm
	0.175	4.450
Operating Temperature ²	°F	°C
Powerpole® Housings & Powerpole® Pak Shells	-4° to 221°	-20° to 105°
Mating Cycles No Load by Plating	Silver (Ag)	Tin (Sn)
PCB to Wire	- -	1,500
Wire to Wire	10,000	1,500
	,	1,000
Avg. Mating / Unmating Force	Lbf.	N
Low Force Wire, High Force PCB, & Ground	3	13
High Force Wire	5	22
Low Force PCB	2	9
Min. Contact / Spring Retention Force	Lbf.	N
	20	90
Powerpole® Pak Latch Avg. Defeat Force	Lbf.	N
Fowerpole 1 ak Laten Avg. Deleat 1 orce	150	667
	100	001
PCB Specifications		
Mounting Style	Plated Through Hole	
PCB Thickness- in. [mm]	0.090 - 0.150	(2.3-3.8)
25A PCB Recommended Traces	#12 AWG Cross Section	
45A PCB Recommended Traces	#10 AWG Cross Section	
Market State Object 4		
Mechanical Shock ⁴	040 0	50'-
MIL-STD-202	213 Condition A	50g's
Vibration High Frequency ⁴		
MIL-STD-202	204 Condition A	10g's
		9 -

Protection

Touch Safety with Finger Proof Housings & Wire Contacts or PCB Mating Interface

UL1977 Sec. 10.2 Pass IEC 60950 Pass IEC 60529 IP20

Touch Safety Standard Housings

IEC 60529 IP10

Connector Series	Configurations		Creepage / Clearance per IEC 60950-1	Material Group
	Single Pole	Unmated	1.64 mm	
	origie i die	Mated	1.64 mm	
	ndard	Unmated	1.64 mm	
PP15/45 Standard		Mated	1.64 mm	IIIa
		Unmated	1.64 mm	
	PCB - 25A	Mated	1.64 mm	
	PCB - 45A	Unmated	1.39 mm	
	1 00 - 404	Mated	1.39 mm	

Connector Series	Configurations		Creepage / Clearance per IEC 60950-1	Material Group
	Single Pole	Unmated	1.64 mm	
		Mated	4.20 mm	
PP15/45 Stack	Stacked Powerpole®	Unmated	1.64 mm	IIIa
	Stacked Fowerpole	Mated	4.20 mm	
i iligoi i iooi		Unmated	1.64 mm	
PCB - 25A	PCB - 25A	Mated	2.90 mm	
	PCB - 45A	Unmated	1.39 mm	
	1 OB - 40A	Mated	1.39 mm	

NOTE 1: See IEC 60664-1 for working voltage.

NOTE 2: Amp ratings are stated per position and based on all positions being fully loaded.

⁵ Based on 2 housings blocked together.











^{*} No TUV Recognition

¹Based on: 105°C rated or better cable of the largest size, Properly calibrated APP recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.


² Limited by the thermal properties of the connector plastic housing.


³ Use APP recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.


⁴ Tested with contact part number 261G2.

PP15-45 TEMPERATURE CHARTS | Temperature rise charts are based on a 25°C ambient temperature.


For Temperature Rise Above 60°C, Consult the Extended Temperature Rise Charts in the Appropriate Product Section on the Website.









Current - Temperature Derating per IEC 60512-5-2 Test 5B









 $For Temperature \ Rise \ Above \ 60^{\circ}C, \ Consult \ the \ Extended \ Temperature \ Rise \ Charts \ in \ the \ Appropriate \ Product \ Section \ on \ the \ Website.$

Current - Temperature Derating per IEC 60512-5-2 Test 5B






NOTE: PP25 PCB charts based on 0.002 in² foil on board side, mated to #12 AWG conductor on wire side. PP45 PCB charts based on #10 AWG equivalent copper foil on board side, mated to #10 AWG conductor on wire side.

| Powerpole® 15-45 Accessories |

Mounting Wing

Secure dovetailed Powerpole® 15-45 series housings by passing fasteners through the wings in either a horizontal or vertical orientation. Useful for sheet metal panels, printed circuit boards, and many other mounting surfaces. Fasteners not included.


Description	Part Nu	mbers
Minimum Quantity	2,500	100
Red	1399G9-BK	1399G9
Blue	1399G8-BK	1399G8




Spacer

Used to separate housings under high power to minimize derating. They are recommended for squaring off a block of Powerpole® 15-45 housings for use in connector shells and mounting clamps. Use a combination of long and short spacers opposite each other in a mated block to add keying features or use two short spacers to avoid interference. Spacers with holes can also be used to fasten the blocked housings to a surface with a fastener.

Description	Part Num	bers
Minimum Quantity	2,500	100
Red, Short w/ Hole	1399G1-BK	1399G1
Red, Long	1399G2-BK	1399G2
Red, Short	1399G6-BK	1399G6
Black, Long	1399G10-BK	1399G10
Blue, Short	1399G13-BK	1399G13
White, Short w/ Hole	1399G14-BK	1399G14
White, Long	1399G17-BK	1399G17






Retaining Pins

Keep stacked Powerpole® 15-45 series housings from separating. Retaining pins are inserted in the circular opening between two housings stacked side by side.

				Dimensions		
			- A -		- E	3 -
Description	Part Num	bers	inches	mm	inches	mm
Minimum Quantity .	1,000	100				
1 Block High	H1507P38	110G16	0.093 / 0.103	2.360 / 2.62	0.250	6.350
2 Block High	111812P5	110G17	0.093 / 0.103	2.360 / 2.62	0.440	11.180



Mounting Clamp

Mounting clamps can be used for fastening a block of Powerpole® 15-45 series housings to a panel. Connector blocks must be a complete square for the clamps to work properly. Fastening hardware not included.

Description	Part Numbers
Minimum Quantity	. 100 sets of 2
2 or 4 Pole	1462G1
3 or 6 Pole	1462G2
4 or 8 Pole	1462G3










3 or 6 Pole 4 or 8 Pole

PCB Mounting Staples

PCB staples are soldered into place to secure Powerpole® 15-45 series housings in a horizontal configuration to the board. Reduce strain on soldering joints during mating and unmating.


				Dime	ensions	
Part			- A		- E	3 -
Numbers	$H \times W$	Length	inches	mm	inches	mm
Minimum Qu	uantity 10	00				
114555P1	1 x 1	Short	0.47	12.0	0.28	7.0
114555P2	1 x 2	Short	0.47	12.0	0.57	14.5
114555P3	1 x 3	Short	0.47	12.0	0.89	22.5
114555P7	1 x 4	Short	0.47	12.0	1.20	30.5
114555P10	2 x 1	Short	0.79	20.0	0.28	7.0
114555P6	2 x 2	Short	0.79	20.0	0.57	14.5
114555P9	2 x 2	Long	0.91	23.0	0.57	14.5



Retention Clip

Retention clips prevent Powerpole® 15-45 blocks from unintended disconnects. They feature a tab for easy insertion and removal.


Description	Part Number
Minimum Quantity	100
1 Block High	110G68



Block Lok

Block locks secure mated Powerpole® 15-45 series housings together. For use in high vibration or shock applications where connectors are unmated infrequently.

Description	- Part Numbers -
Minimum Quantity .	100
2 Pole, Black	110G21
4 Pole, Black	110G12




Shown without Powerpoles®

Shown with Powerpoles®

Splash Boot

Splash boots protect a 2x2 block of any combination of Powerpole® 15-45 series housings and feature snip off sealed ends for flexibility in wire O.D. Designed for through panel or inline applications. Not a hermetic seal.

Description	- Part Numbers -
Minimum Quantity	25
Female, Black	1441G1
Male, Black	1442G1



For environmentally sealed connector shells to hold Powerpole® 15-180 connectors, see SPEC Pak® product series on our website, www.andersonpower.com



Powerpole® - Tooling Information

Wire	Wire Size Reeled Part Numbers		Reeled Contact Crimp Tool						
AWG	mm²	Tin Plating	Silver Plating	APP Applicator	+ APP Press				
PP15 / 45 Flat Wiping Power & Ground									
#16 / 20	1.3 / 0.52	262G1	262G2						
#16 / 20	1.3 / 0.52	269G2	N/A						
#12 / 16	3.3 / 1.3	261G1	N/A	TD0101					
#10 / 14	5.3 / 2.1	261G2	261G3	100101	115V= TE0101				
#12 / 16	3.3 / 1.3	269G1	N/A		230V = TE0102				
#10 / 14	5.3 / 2.1	269G3	N/A						
#10 / 14	5.3 / 2.1	200G1L	200G3L						
#10 / 14	5.3 / 2.1	201G1H	N/A	TD0102					
#10 / 14	5.3 / 2.1	1830G1	1830G2						

 $^{^{\}star}$ APP applicators are mechanical feed style and do not require an air feed kit.

Plating Plating Plating Plating Tool Tool Die Locator Of Crin	Wire Size Loose Piece Part Numbers			Loose Piece Contact Crimp Tool							
#16 / 20	AWG	mm²				Bench		+ Locator	Number of Crimps		
#12 / 16	PP15 / 45 Flat Wiping Power & Ground										
#12 / 16	#16 / 20	1.3 / 0.52	N/A	1332		1367@1					
#16 / 20	#12 / 16	3.3 / 1.3	N/A	1331		130701					
#12 / 16 3.3 / 1.3 261G1-LPBK N/A 1309G3 or 1309G8 N/A N/A Singl #10 / 14 5.3 / 2.1 261G2-LPBK N/A 1309G8 N/A N/A N/A Singl #10 / 14 5.3 / 2.1 269G3-LPBK N/A 1309G8 N/A 1309G8 N/A N/A #10 / 14 5.3 / 2.1 200G1L-LPBK 200G3L-LPBK 1309G6 or 1309G8 N/A 1309G8 N/A 1309G8 N/A N/A 1309G8 N/A	#16 / 20	1.3 / 0.52	262G1-LPBK	262G2-LPBK							
#10 / 14	#16 / 20	1.3 / 0.52	269G2-LPBK	N/A							
#10 / 14 5.3 / 2.1 261G2-LPBK N/A 1309G8 N/A N/A N/A Singl #10 / 14 5.3 / 2.1 269G3-LPBK N/A 1309G8 #10 / 14 5.3 / 2.1 200G1L-LPBK 200G3L-LPBK 1309G6 or 1309G8 1309G8	#12 / 16	3.3 / 1.3	261G1-LPBK	N/A							
#12 / 16 3.3 / 1.3 269G1-LPBK N/A 1309G8 1309G8 1389G2 1389G2	#10 / 14	5.3 / 2.1	261G2-LPBK	261G3-LPBK		N1/A	N/A	N/A	Single		
#10 / 14 5.3 / 2.1 200G1L-LPBK 200G3L-LPBK 1309G6 or 1309G8 1309G8 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G21 1389G6 1389G21 13	#12 / 16	3.3 / 1.3	269G1-LPBK	N/A		N/A					
#10 / 14 5.3 / 2.1 201G1H-LPBK N/A 1309G8 or	#10 / 14	5.3 / 2.1	269G3-LPBK	N/A							
#10 / 14	#10 / 14	5.3 / 2.1	200G1L-LPBK	200G3L-LPBK	130006						
#6 13.3 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1	#10 / 14	5.3 / 2.1	201G1H-LPBK	N/A	or						
#8 8.4 13.7 5900 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 1389G21 1389G6 1389G21 1389G21 1389G6 1389G21 1389G21 1389G6 1389G21 1389G2	310 / 14	5.3 / 2.1	1830G1-LPBK	1830G2-LPBK	1309G8						
#8 8.4 5900 1389G6 1389G21 1389G6 1389G21 1389G6 1389G21 138				PF	75		1				
#8 8.4 5900 1875G1 1388G6 1389G21 1389G6 1389G21 138	#6	13.3		1307				1389G6	Single		
#10 / 12 5.3 / 3.3		10.0									
#10 / 12 5.3 / 3.3 N/A 1875G2 5953 1389G4 1387G1 1389G21 Single Fig. 1389G2 1 1389G21	#8	8.4	N/A				1388G6				
#10 / 12 5.3 / 3.3 5953 1389G6 1389G21 1389G21 1389G21 1389G21 170 53.5 1323G2 1388G3					1309G4	1387G1					
1389G6 5915 1875G3 1389G21 1389G21 170 53.5 1323G2 1388G3	#10 / 12	52/22			100004	1007 01		1389G21			
1875G3 1389G21 PP120 1/0 53.5 1323G2 1388G3	#10712	5.575.5						1389G6			
PP120 1/0 53.5 1323G2 1388G3								1380G21			
1/0 53.5 1323G2 1388G3	101000										
1388G3	1/0	53.5									
	#1	42.4		1323G1			1388G3	1389G4	Single		
			N/A		1368	1387G1	1 1388G4				
Series											
#6 13.3 1319G6											
PP180											
3/0 85 1328G2	3/0	85									
2/0 53.5 1328G1							1303G12				
1/0 53.5 1382			N/A			1387G2	1303G13	1304G32	Double		
					1368						
#2 33.6 Series					Series						
#4 21.1 1384	#4	21.1		1384							
						1387G1	1388G4	1389G3	Single		

^{1.} NOTE: See website for the most current information.

^{2.} NOTE: Insertion / Extraction fool for PP15/45 contacts = 111038G2