## Crimp Terminal Spade





#### **Specifications:**

Type : Spade
Series : SNYD
Termination Method : Crimp
Contact Plating : Tin
Insulator Material : Nylon
Max. Electrical Rating : 105°C 600V


Insulation Colour : Red (22AWG to 16 AWG)

: Blue (16AWG to 14 AWG) : Yellow (12AWG to 10 AWG)

Double Crimp : With copper sleeve on barrel

Packing : 100 pieces

### Diagram



Dimensions								
d2	W	F	L	E	D	d1	Т	Part Number
0.126 (3.2)	0.224 (5.7)	0.256 (6.5)	0.866 (22)	0.433 (11)	0.177 (4.5)	0.067 (1.7)	0.03 (0.75)	SNYD1-3.2
					0.205 (5.2)	0.091 (2.3)	0.031 (0.8)	SNYD2-3.2
0.146 (3.7)	0.252 (6.4)				0.177 (4.5)	0.067 (1.7)	0.03 (0.75)	SNYDL1-3.7
0.169 (4.3)	0.319 (8.1)							SNYDL1-4
0.252 (6.4)	0.472 (12)	0.433 (11)	1.102 (28)					SNYDL1-6
0.209 (5.3)	0.354 (9)	0.276 (7)	1.004 (25.5)	0.512 (13)	0.276 (7)	0.134 (3.4)	0.039 (1)	SNYD5-5
0.252 (6.4)	0.472 (12)	0.433 (11)	1.102 (28)					SNYDL2-6
0.169 (4.3)	0.311 (7.9)	0.256 (6.5)	0.866 (22)	0.433 (11)	0.205 (5.2)	0.091 (2.3)	0.031 (0.8)	SNYDM2-4

Dimensions: Inches (Millimetres)

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



# Crimp Terminal Spade



#### **Part Number Table**

Description	Wire Range AWG (mm²)	Stud Size	Crimping Tool	Part Number
	22 to 16 (0.5 to 1.5)	#4		SNYD1-3.2
		#4	IZUMI Model 34 With Die Index Colour : Red Or K.S. Model KST2000B With Die Index Colour : Red	SNYD2-3.2
		#6		SNYDL1-3.7
		#8		SNYDL1-4
		1/4		SNYDL1-6
Crimp Terminal, Spade, PK100	12 to 10 (4 to 6)	#10	IZUMI Model 5 With Die Index Colour : Yellow Or K.S. Model KST2000B With Die Index Colour : Yellow	SNYD5-5
		1/4	ZUMI Model 34 With Die Index	SNYDL2-6
	16 to 14 (1.5 to 2.5)	#8	Colour : Blue Or K.S. Model KST2000B With Die Index Colour : Blue	SNYDM2-4

Dimensions: Inches (Millimetres)

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

