





PART NUMBER	ENGINEERING NO.	LENGTH
1300070113	207002A01F030	3' 0" +1.75 - 0 [ .9M +44.5 - 0 ]
1300070115	207002A01F060	6' 0" +2.19 - 0 [ 1.8M +55.6 - 0 ]
1300070117	207002A01F120	12' 0" +3.50 - 0 [ 3.7M +88.9 - 0 ]



1"-16 UN THREADS



Section Z-Z

S1	
1	WHITE/BLACK
2	BLACK
3	WHITE
4	RED
5	ORANGE
6	BLUE
7	GREEN/YELLOW

WIRING DIAGRAM

NOTES:

1. MATERIAL: SEE TABLE
2. FINISHES: SEE TABLE
3. CABLE ASSEMBLIES ARE BAGGED SEPERATELY IN POLY BAGS WITH BARCODE LABEL ATTACHED TO OUTSIDE OF BAG
4. WRAP LABEL IS MARKED WITH P/N, DATE CODE VOLTAGE & AMPERAGE
5. MATES WITH: MINI CHANGE, B-SIZE 7 POLE RECEPTACLE  
VOLTAGE RATING: 600V  
CURRENT RATING: 8 AMPS
6. ELECTRICAL SPECIFICATIONS:
7. ASSEMBLY IS RoHS COMPLIANT

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
7	1	LABEL	PLASTIC FILM	BLACK/YELLOW
6	1	OVERMOLD	PVC	YELLOW
5	1	COUPLING NUT	ZINC DIE CAST	BLACK
4	1	FRICTION RING	NYLON	NATURAL
3	7	PIN CONTACT 16 AWG	BRASS	GOLD PLATED
2	1	INSERT, FEMALE, 7 POLE	PVC	YELLOW
1	1	CABLE, 16-7 ST00W/ST	PVC JACKET	YELLOW

RELEASED EC NO: WNA2009-0795 DRAWN: BRUPERT 2009/06/02 CHKD: B. RUPERT APPR: J. MURPHY 2009/06/10	QUALITY SYMBOLS
	$\nabla=0$ $\nabla=0$
	DESCRIPTION
	REV

GENERAL TOLERANCES (UNLESS SPECIFIED)	
	IN/MM
4 PLACES	$\pm$ --- $\pm$ ---
3 PLACES	$\pm$ --- $\pm$ ---
2 PLACES	$\pm$ --- $\pm$ .01
1 PLACE	$\pm$ 0.3 $\pm$ ---
ANGULAR $\pm$ 1/2°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
IN/MM	
DRAWN BY	DATE
BRUPERT	2009/04/02
CHECKED BY	DATE
B. WOODMAN	2009/04/03
APPROVED BY	DATE
J. MURPHY	2008/04/06
MATERIAL NO.	
SEE CHART	
SIZE	C

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
1:1	INCH	
TITLE		
MINI-CHANGE CORD ASSY MALE, B-SIZE 7 POLE		
MOLEX INCORPORATED		
DOCUMENT NO.	SHEET NO.	
SD-130007-003	1 OF 1	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		