

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

**UFI:**

Sn60Pb40: VTJ9-V0WX-H009-K4RV
 Sn63Pb37: A3R2-T3KG-A002-4SQ7
 Sn50Pb50: F5R2-A38V-M00K-T499
 Pb60Sn40: E8R2-T3Y8-X002-FFVC
 Pb65Sn35: JHR2-C31F-U00J-FGMJ
 Pb67Sn33: DPR2-C3E8-F00J-S5SP
 Pb70Sn30: MCR2-A3NP-700J-4TFE
 Pb71Sn27Sb2: 1MR2-U3QV-5001-3U6M
 Pb74Sn25Sb1: NER2-U3C2-J002-S51G

1.2 Relevant identified uses of the substance or mixture and uses advised against

No further relevant information available.

Application of the substance / the mixture *Brazing alloy*

1.3 Details of the supplier of the safety data sheet**Manufacturer/Supplier:**

Felder GmbH
 Im Lipperfeld 11
 D-46047 Oberhausen

Tel.: +49 (0)208/ 85035-0

Fax.: +49 (0)208/ 26080

<http://www.felder.de>

e-mail: info@felder.de

Further information obtainable from:

lab

(mo-thu. 8:00 a.m. - 4:00 p.m./ fr. 8:00 a.m. - 1:00 p.m.)

email: mprobst@felder.de

1.4 Emergency telephone number:

24 hr. emergency information:

Poison emergency call Berlin

"Giftnotruf Berlin"

Tel.: 0049-30-30686 790

Information which should have been included on the identification label.**(Annex I No. 1.3.4 REGULATION (EC) No 1272/2008)**

Metals in massive form, alloys, mixtures containing polymers and mixtures containing elastomers do not require a label

according to this Annex, if they do not present a hazard to human health by inhalation, ingestion or contact with skin or

to the aquatic environment in the form in which they are placed on the market, although classified as hazardous in accordance with the criteria of this Annex.

see chapter 2.2

EuPCS: PC-TEC-24

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture**Classification according to Regulation (EC) No 1272/2008**

GHS08 health hazard

Repr. 1A H360FD-H362 May damage fertility. May damage the unborn child. May cause harm to breast-fed children.

STOT RE 1 H372 Causes damage to organs through prolonged or repeated exposure.

(Contd. on page 2)

— EU —

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 1)

2.2 Label elements**Labelling according to Regulation (EC) No 1272/2008**

The product is classified according to the CLP regulation. A label is not required (CLP Annex I, 1.3.4.1.)

The information according to CLP Annex I, 1.3.4.2. will be announced in section 2.2.

The product is classified and labelled according to the CLP regulation.

Hazard pictograms

GHS08

Signal word *Danger***Hazard-determining components of labelling:***lead***Hazard statements**

H360FD-H362 May damage fertility. May damage the unborn child. May cause harm to breast-fed children.

H372 Causes damage to organs through prolonged or repeated exposure.

Precautionary statements

P260 Do not breathe dusts or mists.

P263 Avoid contact during pregnancy and while nursing.

P264 Wash thoroughly after handling.

P280 Wear protective gloves/protective clothing/eye protection/face protection/hearing protection.

P405 Store locked up.

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

Additional information:

Restricted to professional users.

2.3 Other hazards**Results of PBT and vPvB assessment**

PBT: *Not applicable.*


vPvB: *Not applicable.*

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Description: *Mixture: consisting of the following components.*

Dangerous components:

CAS: 7439-92-1 EINECS: 231-100-4 Index number: 082-014-00-7 Reg.nr.: 01-2119513221-59	lead	 Repr. 1A, H360FD-H362; STOT RE 1, H372	20-75%
CAS: 7440-31-5 EINECS: 231-141-8 Reg.nr.: 01-2119486474-28	tin	substance with a Community workplace exposure limit	25-80%
CAS: 7440-36-0 EINECS: 231-146-5 Reg.nr.: 01-2119475609-24	antimony	substance with a Community workplace exposure limit	0-5%

SVHC

7439-92-1 | lead

Additional information: *For the wording of the listed hazard phrases refer to section 16.*

SECTION 4: First aid measures

4.1 Description of first aid measures

General information: *Take affected persons out into the fresh air.*

After inhalation: *Supply fresh air; consult doctor in case of complaints.*

After skin contact:

After contact with the molten product, cool rapidly with cold water.

Do not pull solidified product off the skin.

Call a doctor immediately.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 2)

After eye contact: *Rinse opened eye for several minutes under running water.*

After swallowing: *Rinse out mouth and then drink plenty of water.*

4.2 Most important symptoms and effects, both acute and delayed *No further relevant information available.*

4.3 Indication of any immediate medical attention and special treatment needed
No further relevant information available.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing agents:

Use fire extinguishing methods suitable to surrounding conditions.

CO₂, sand, extinguishing powder. Do not use water.

For safety reasons unsuitable extinguishing agents: *Water*

5.2 Special hazards arising from the substance or mixture *No further relevant information available.*

5.3 Advice for firefighters

Protective equipment: *Do not inhale explosion gases or combustion gases.*

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Use respiratory protective device against the effects of fumes/dust/aerosol.

Wear protective clothing.

6.2 Environmental precautions: *No special measures required.*

6.3 Methods and material for containment and cleaning up:

Allow to solidify. Pick up mechanically.

Dispose contaminated material as waste according to item 13.

6.4 Reference to other sections

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Extractors are required on all machines used for thermal processing or splinter removal processes.

Provide suction extractors if dust is formed.

Any unavoidable deposit of dust must be regularly removed.

Use appropriate industrial vacuum cleaners or central vacuum systems for dust removal.

Information about fire - and explosion protection: *No special measures required.*

7.2 Conditions for safe storage, including any incompatibilities

Storage:

Requirements to be met by storerooms and receptacles: *No special requirements.*

Information about storage in one common storage facility: *Store away from foodstuffs.*

Further information about storage conditions: *Store in dry conditions.*

Storage class: 6.1 C

7.3 Specific end use(s) *No further relevant information available.*

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredients with limit values that require monitoring at the workplace:

7439-92-1 lead

AGW (EU) *Long-term value: 0.15 mg/m³*

BOELV (EU) *Long-term value: 0.15 mg/m³
as Pb*

MAK (Germany) *vgl. Abschn. XII*

7440-31-5 tin

MAK (Germany) *vgl. Abschn. IIb*

(Contd. on page 4)

— EU —

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 3)

7440-36-0 antimony

MAK (Germany) | vgl. Abschn. XII

Regulatory information

BOELV (EU): 2004/37/EG (EU/2019/983)

MAK (Germany): MAK- und BAT-Liste

recommended monitoring procedures in accordance with 2020/878/EU no. 8.1.2:

7439-92-1 lead: NIOSH 7702(E), OSHA 1006(E), OSHA ID-206(E)

Ingredients with biological limit values:**7439-92-1 lead**

BAT (EU)	70 µg/dl blood lead
BGW (Germany)	300 µg/l Untersuchungsmaterial: Vollblut Probennahmezeitpunkt: keine Beschränkung Parameter: Blei Frauen < 45 J.
	400 µg/l Untersuchungsmaterial: Vollblut Probennahmezeitpunkt: keine Beschränkung Parameter: Blei

Regulatory information BGW (Germany): TRGS 903**Additional information:** The lists valid during the making were used as basis.**8.2 Exposure controls****Appropriate engineering controls** No further data; see item 7.**Appropriate engineering controls:**

Ensure adequate ventilation.

Remove the fumes by means of suitable suction devices.

Individual protection measures, such as personal protective equipment**General protective and hygienic measures:**

Pregnant women should strictly avoid inhalation or skin contact.

Do not eat, drink, smoke or sniff while working.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Respiratory protection:

Use suitable respiratory protective device in case of insufficient ventilation.

Filter P3

Hand protection

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

Material of gloves

heat-resistant glove with nitrile inner glove.

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material cannot be calculated in advance and has therefore to be checked prior to the application.

Recommended thickness of the material: ≥ 0.2 mm**Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

The determined penetration times according to EN 16523-1:2015 are not performed under practical conditions.

Therefore a maximum wearing time, which corresponds to 50% of the penetration time, is recommended.

Value for the permeation: Level ≤ 6 **Eye/face protection**

Tightly sealed goggles

Body protection: Protective work clothing

(Contd. on page 5)

— EU —

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
 Soft solder SnPb(Sb), PbSn(Sb)
 Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 4)

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

General Information

Colour:	Silver grey
Odour:	Odourless
Odour threshold:	Not determined.
Melting point/freezing point:	Not applicable
Boiling point or initial boiling point and boiling range	Undetermined.
Flammability	Not determined.
Lower and upper explosion limit	
Lower:	Not determined.
Upper:	Not determined.
Flash point:	Not applicable.
Auto-ignition temperature:	Product is not selfigniting.
Decomposition temperature:	Not determined.
pH	Not applicable.
Viscosity:	
Kinematic viscosity	Not applicable.
Dynamic:	Not applicable.
Solubility	
water:	Insoluble.
Partition coefficient n-octanol/water (log value)	Not determined.
Vapour pressure:	Not applicable.
Density and/or relative density	
Density:	Not determined.
Relative density	Not determined.
Vapour density	Not applicable.
Particle characteristics	See item 3.

9.2 Other information

Appearance:	
Form:	Solid
Important information on protection of health and environment, and on safety.	
Explosive properties:	Product does not present an explosion hazard.
Solvent content:	
VOC (EC)	0.00 %
Change in condition	
Evaporation rate	Not applicable.

Information with regard to physical hazard classes

Explosives	Void
Flammable gases	Void
Aerosols	Void
Oxidising gases	Void
Gases under pressure	Void
Flammable liquids	Void
Flammable solids	Void
Self-reactive substances and mixtures	Void
Pyrophoric liquids	Void
Pyrophoric solids	Void
Self-heating substances and mixtures	Void
Substances and mixtures, which emit flammable gases in contact with water	Void
Oxidising liquids	Void
Oxidising solids	Void
Organic peroxides	Void
Corrosive to metals	Void
Desensitised explosives	Void

(Contd. on page 6)

— EU —

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 5)

SECTION 10: Stability and reactivity

10.1 Reactivity *No further relevant information available.*

10.2 Chemical stability

Thermal decomposition / conditions to be avoided: *No decomposition if used according to specifications.*

10.3 Possibility of hazardous reactions

Toxic fumes may be released if heated above the decomposition point.

Reacts with strong acids and alkali.

Reacts with strong oxidising agents.

10.4 Conditions to avoid *No further relevant information available.*

10.5 Incompatible materials: *No further relevant information available.*

10.6 Hazardous decomposition products:

Toxic metal oxide smoke

Leadoxide vapour

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity *Based on available data, the classification criteria are not met.*

Skin corrosion/irritation *Based on available data, the classification criteria are not met.*

Serious eye damage/irritation *Based on available data, the classification criteria are not met.*

Respiratory or skin sensitisation *Based on available data, the classification criteria are not met.*

Germ cell mutagenicity *Based on available data, the classification criteria are not met.*

Carcinogenicity *Based on available data, the classification criteria are not met.*

Reproductive toxicity

May damage fertility. May damage the unborn child. May cause harm to breast-fed children.

STOT-single exposure *Based on available data, the classification criteria are not met.*

STOT-repeated exposure

Causes damage to organs through prolonged or repeated exposure.

Aspiration hazard *Based on available data, the classification criteria are not met.*

11.2 Information on other hazards

Endocrine disrupting properties

None of the ingredients is listed.

SECTION 12: Ecological information

12.1 Toxicity

Aquatic toxicity: *No further relevant information available.*

12.2 Persistence and degradability *No further relevant information available.*

12.3 Bioaccumulative potential *No further relevant information available.*

12.4 Mobility in soil *No further relevant information available.*

12.5 Results of PBT and vPvB assessment

PBT: *Not applicable.*

vPvB: *Not applicable.*

12.6 Endocrine disrupting properties

The product does not contain substances with endocrine disrupting properties.

12.7 Other adverse effects

Additional ecological information:

General notes:

The product contains heavy metals. Avoid transfer into the environment. Specific preliminary treatments are necessary

Not hazardous for water.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Recommendation

Contact manufacturer for recycling information.

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

(Contd. on page 7)

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 6)

European waste catalogue

17 04 09*: metal waste contaminated with hazardous substances

HP 5: Specific Target Organ Toxicity (STOT)/Aspiration Toxicity

HP 10: Toxic for reproduction

spool:

15 01 02: plastic packaging

packaging:

15 01 01: paper and cardboard packaging

Uncleaned packaging: void.**Recommendation: Disposal must be made according to official regulations.**

SECTION 14: Transport information

14.1 UN number or ID number

ADR, ADN, IMDG, IATA

Void

14.2 UN proper shipping name

ADR, ADN, IMDG, IATA

Void

14.3 Transport hazard class(es)

ADR, ADN, IMDG, IATA

Class

Void

14.4 Packing group

ADR, IMDG, IATA

Void

14.5 Environmental hazards:

Marine pollutant:

No

14.6 Special precautions for user

Not applicable.

14.7 Maritime transport in bulk according to IMO

instruments

Not applicable.

UN "Model Regulation":

Void

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Directive 2012/18/EU

Named dangerous substances - ANNEX I None of the ingredients is listed.

REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 63, 30

DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II

7439-92-1 lead

National regulations:**Additional classification according to Decree on Hazardous Materials, Annex II:**

Can cause cancer if present as respirable dust.

Information about limitation of use:

Employment restrictions concerning pregnant and lactating women must be observed.

Employment restrictions concerning women of child-bearing age must be observed.

Employment restrictions concerning juveniles must be observed.

Waterhazard class: Generally not hazardous for water.**Other regulations, limitations and prohibitive regulations**

Substances of very high concern (SVHC) according to REACH, Article 57
--

7439-92-1 lead

15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31 and 2020/878/EU

Printing date 21.06.2021

Version number 6

Revision: 26.01.2021

Trade name: Weichlotlegierung SnPb(Sb), PbSn(Sb)
Soft solder SnPb(Sb), PbSn(Sb)
Sn 25,0-80,0%, Pb 20,0-75,0%, Sb 0,0-5,5%

(Contd. of page 7)

Reasons for changes:

28.06.2018: chapter 3, SVHC

20.01.2020: chapter 1

15.04.2020: chapter 1

08.01.2021: chapter 1, 7

26.01.2021: chapter 1

Information referred to in Annex I, point 1.3.4.2 of Regulation 1272/2008/EC:**Relevant phrases**

H360FD May damage fertility. May damage the unborn child.

H362 May cause harm to breast-fed children.

H372 Causes damage to organs through prolonged or repeated exposure.

Recommended restriction of use For commercial use only.**Contact:** Dr. M. Probst**Version number of previous version: 5****Abbreviations and acronyms:**

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Repr. 1A: Reproductive toxicity – Category 1A

STOT RE 1: Specific target organ toxicity (repeated exposure) – Category 1

Safety data sheet SD3457

— EU —