

Aluminum electrolytic capacitors

Single-ended capacitors

 Series/Type:
 B41828, B43828

 Date:
 December 2010

© EPCOS AG 2010. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

Single-ended capacitors

Standard series - 105 °C

General-purpose grade capacitors

Applications

- General-purpose applications
- Semi-professional to professional application range
- For filtering, coupling and pulse circuits

Features

- Miniaturized dimensions
- RoHS-compatible
- Useful life of 2000 h at 105 °C

Construction

- Radial leads
- Charge-discharge proof, polar
- Aluminum case with insulating sleeve
- Minus pole marking on the insulating sleeve
- Case with safety vent from diameter 8 mm

Delivery mode

- Bulk
- Taped, Ammo pack
- Cut (see chapter "Single-ended Taping, packing and lead configurations, Cut leads (Chapter A)")
- Kinked (see chapter "Single-ended Taping, packing and lead configurations, Kinked leads (Chapter A)")

Refer to chapter "Single-ended capacitors – Taping, packing and lead configurations" for further details.



B41828, B43828



B41828, B43828


Specifications and characteristics in brief

Series	B41828					B43828					
Rated voltage V _R	6.3 100	D V DC)			160 450 V DC					
Surge voltage Vs	$V_{\rm R} \le 250$	V DC:	1.15 •	V _R (a	t room	tempe	erature	e)			
	$V_{R} > 250$	$V_{R} > 250 \text{ V DC: } 1.1 \cdot V_{R} \text{ (at room temperature)}$									
Rated capacitance C _R	0.47 15	0.47 15000 μF 0.47 220 μF									
Capacitance tolerance	$\pm 20\% \triangleq 1$	М				±20%	⊳ ≙ M				
Dissipation factor (max.)	For capao 1000 µF.	citance	e highe	er than	1000	µF ado	d 0.02	for ev	ery inc	rease	of
(20 °C, 120 Hz)	V _R	6.3	10	16	25	35	50	63	100	160	315
	(V DC)									 250	 450
	tan δ	0.24	0.20	0.16	0.14	0.12	0.10	0.09	0.08	0.12	0.15
Leakage current I _{leak} (20 °C, after 5 minutes)	$ I_{\text{leak}} \le 0.01 \mu \text{A} \cdot \left(\frac{C_R}{\mu F} \cdot \frac{V_R}{V}\right) $ or 3 μ A, whichever is greater				10 µA						
Useful life				3	-						<u> </u>
105 °C; V _R ; I _{AC,R}	> 2000 h										
Requirements	$\Delta C/C$	$\leq \pm 20$	0% of i	nitial v	alue						
	tan δ	≤ 2 ti	mes in	itial sp	ecified	d value	•				
	I _{leak}	≤ initi	ial spe	cified I	imit						
Shelf life	After storage for 1000 h at 105 °C, the capacitors shall meet the requirement of load life test after reforming process. After test: V_{R} to be applied for 30 minutes, 24 to 48 hours before measurement.										
Vibration resistance	To IEC 60	0068-2	2-6, tes	st Fc:							
test	Frequenc							nplitud	le 0.75	i mm,	
	accelerat			-							
	If can size			•							
	If can size			capad	citor rig	gidly cl	ampeo	d by th	e alun	ninum	case
IEC climatic category	To IEC 60				40.00		00/50	- مامى -	al a	h + +	+)
	$V_{\rm R} \le 200$							-			
	$V_{\rm R} \! \geq \! 250$ V DC: 25/105/56 (–25 °C/+105 °C/56 days damp heat test)										





Dimensional drawing



Safety vent for diameter ≥ 8 mm.

Case Dimensions

d×l	$d_{max} imes I_{max}$	а	b
mm	mm	mm	mm
5 ×11	5.5 × 12.5	2.0 ±0.5	0.50 ±0.1
6.3×11	6.8 × 12.5	2.5 ±0.5	0.50 ±0.1
8 ×11.5	8.5 × 13.0	3.5 ±0.5	0.60 ±0.1
10 × 12.5	11.0 × 14.0	5.0 ±0.5	0.60 ±0.1
10 ×16	11.0 × 17.5	5.0 ±0.5	0.60 ±0.1
10 × 20	11.0 × 22.0	5.0 ±0.5	0.60 ±0.1
12.5×20	13.5 imes 22.0	5.0 ±0.5	0.60 ±0.1
12.5×25	13.5 imes 27.0	5.0 ±0.5	0.60 ±0.1
16 ×25	17.0×27.0	7.5 ±0.5	0.80 ±0.1
16 × 31.5	17.0 × 33.5	7.5 ±0.5	0.80 ±0.1
18 × 35.5	19.0 × 37.5	7.5 ±0.5	0.80 ±0.1



B41828

Overview of available types - B41828

V _R (V DC)	6.3	10	16	25
	Case dimension	s d × l (mm)		·
C _R (μF)				
10			5 ×11	5 × 11
20			5 ×11	
33			5 ×11	
47	5 × 11	5 × 11	5 ×11	5 ×11
100	5 ×11	5 × 11	6.3×11	6.3×11
220	6.3×11	6.3 × 11	8 × 11.5	8 × 11.5
330	6.3×11	8 × 11.5	8 ×11.5	10 × 12.5
470	8 × 11.5	8 × 11.5	8 ×11.5	10 × 16
1000	10 × 12.5	10 × 16	10 ×20	10 ×20
2200	12.5×20	12.5×20	12.5 imes 20	16 ×25
3300	12.5×20	12.5×25	16 × 25	16 × 31.5
4700	16 × 25	16 × 25	16 × 31.5	18 × 35.5
10000	16 × 31.5	18 × 35.5		
15000	18 × 35.5			





B41828

Standard series - 105 °C

V _R (V DC)	35	50	63	100
	Case dimensions	d × l (mm)		
C _R (μF)				
0.47				5 ×11
1.0		5 × 11		5 ×11
2.2				5 ×11
3.3				5 ×11
4.7	5 × 11			5 ×11
10	5 × 11	5 × 11	5 × 11	6.3×11
22	5 × 11	5 × 11	6.3×11	8 × 11.5
33	5 × 11	6.3×11	6.3×11	10 × 12.5
47	6.3×11	6.3×11	8 × 11.5	10 × 16
100	6.3×11	8 × 11.5	10 × 12.5	12.5 imes 20
220	10 × 12.5	10 × 16	12.5 imes 20	16 × 25
330	10 × 16	10 × 20	12.5 imes 20	16 × 25
470	10 × 20	12.5 imes 20	12.5 imes 25	16 × 31.5
1000	12.5×25	16 × 25	16 × 31.5	
2200	16 × 31.5	18 × 35.5		
3300	18 × 35.5			



B43828

Overview of available types - B43828

V _R (V DC)	160	200	250	350	400	450
	Case dimens	sions $d \times I$ (mn	n)			
C _R (μF)						
0.47	5 × 11		6.3 × 11			
1.0	5 × 11	6.3×11	6.3 × 11	6.3×11	8 × 11.5	8 × 11.5
1.5						10 × 12.5
2.2	6.3 × 11	6.3×11	8 × 11.5	8 ×11.5	10 × 12.5	10 × 12.5
3.3	8 × 11.5	8 × 11.5	10 × 12.5	10 × 12.5	10 × 16	10 × 16
4.7	8 × 11.5	10 × 12.5	10 × 12.5	10 ×16	10 ×20	10 × 20
6.8						12.5 imes 20
10	10 × 12.5	10 ×16	10 ×20	12.5×20	12.5 imes 20	12.5×20
15						12.5 imes 25
22	10 × 16	10 ×20	12.5 × 25	16 × 25	16 × 25	16 × 25
33	12.5 imes 20	12.5×25	12.5×25	16 × 25	16 × 31.5	16 × 31.5
47	12.5 × 25	12.5 × 25	16 × 25	16 × 35.5	18 × 35.5	16 × 35.5
						18 × 35.5
68						18 × 35.5
100	16 × 25	16 × 31.5	18 × 35.5			
220	18 × 35.5	18 × 40				



B41828

Standard series - 105 °C

C _B	Case dimensions	I _{AC.B}	Ordering code			
120 Hz, 20 °C	d×l	120 Hz, 105 °C	(composition see below)			
μF	mm	mA				
V _R = 6.3 V DC	V _R = 6.3 V DC					
47	5 ×11	66	B41828A2476M***			
100	5 ×11	97	B41828A2107M***			
220	6.3×11	162	B41828A2227M***			
330	6.3×11	198	B41828A2337M***			
470	8 ×11.5	259	B41828A2477M***			
1000	10 × 12.5	454	B41828A2108M***			
2200	12.5×20	793	B41828A2228M***			
3300	12.5×20	939	B41828A2338M***			
4700	16 × 25	1378	B41828A2478M***			
10000	16 × 31.5	1852	B41828A2109M***			
15000	18 × 35.5	2131	B41828A2159M***			
V _R = 10 V DC						
47	5 ×11	68	B41828A3476M***			
100	5 ×11	106	B41828A3107M***			
220	6.3×11	177	B41828A3227M***			
330	8 ×11.5	236	B41828A3337M***			
470	8 × 11.5	281	B41828A3477M***			
1000	10 × 16	520	B41828A3108M***			
2200	12.5 × 20	849	B41828A3228M***			
3300	12.5×25	1118	B41828A3338M***			
4700	16 × 25	1425	B41828A3478M***			
10000	18 × 35.5	2004	B41828A3109M***			

Technical data and ordering codes - B41828

Composition of ordering code

*** = Version

000 = for standard leads, bulk

001 = for kinked leads, bulk

002 = for cut leads, bulk

016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)

007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \oslash 5 ... 6.3 mm)

006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \varnothing 8 mm)

008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \oslash 5 ... 12.5 mm)

009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



B41828

Technical data and ordering codes - B41828

<u> </u>	Casa dimensiona	1	Ordering code			
	Case dimensions	I _{AC,R}	Ordering code			
120 Hz, 20 °C	d×l	120 Hz, 105 °C	(composition see below)			
μF	mm	mA				
V _R = 16 V DC	V _R = 16 V DC					
10	5 ×11	35	B41828A4106M***			
20	5 ×11	55	B41828A4226M***			
33	5 ×11	66	B41828A4336M***			
47	5 ×11	80	B41828A4476M***			
100	6.3×11	129	B41828A4107M***			
220	8 × 11.5	214	B41828A4227M***			
330	8 × 11.5	266	B41828A4337M***			
470	8 × 11.5	314	B41828A4477M***			
1000	10 ×20	626	B41828A4108M***			
2200	12.5 × 20	1028	B41828A4228M***			
3300	16 × 25	1323	B41828A4338M***			
4700	16 × 31.5	1661	B41828A4478M***			
V _R = 25 V DC						
10	5 × 11	37	B41828A5106M***			
47	5 ×11	85	B41828A5476M***			
100	6.3×11	143	B41828A5107M***			
220	8 × 11.5	245	B41828A5227M***			
330	10 × 12.5	319	B41828A5337M***			
470	10 × 16	429	B41828A5477M***			
1000	10 × 20	680	B41828A5108M***			
2200	16 × 25	1233	B41828A5228M***			
3300	16 × 31.5	1571	B41828A5338M***			
4700	18 × 35.5	1925	B41828A5478M***			

Composition of ordering code

- 000 = for standard leads, bulk
- 001 = for kinked leads, bulk
- 002 = for cut leads, bulk
- 016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)
- 007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \emptyset 5 ... 6.3 mm)
- 006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \emptyset 8 mm)
- 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \varnothing 5 ... 12.5 mm)
- 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



B41828

Standard series - 105 °C

C _B	Case dimensions	I _{AC.B}	Ordering code
120 Hz, 20 °C	d×I	120 Hz, 105 °C	(composition see below)
μF	mm	mA	
V _R = 35 V DC			
4.7	5 × 11	28	B41828A7475M***
10	5 ×11	42	B41828A7106M***
22	5 ×11	62	B41828A7226M***
33	5 ×11	76	B41828A7336M***
47	6.3×11	104	B41828A7476M***
100	6.3×11	169	B41828A7107M***
220	10 × 12.5	278	B41828A7227M***
330	10 × 16	395	B41828A7337M***
470	10 × 20	514	B41828A7477M***
1000	12.5×25	905	B41828A7108M***
2200	16 × 31.5	1403	B41828A7228M***
3300	18 × 35.5	1707	B41828A7338M***
V _R = 50 V DC			
1.0	5 ×11	14	B41828A6105M***
10	5 ×11	48	B41828A6106M***
22	5 ×11	70	B41828A6226M***
33	6.3×11	101	B41828A6336M***
47	6.3×11	118	B41828A6476M***
100	8 × 11.5	193	B41828A6107M***
220	10 × 16	369	B41828A6227M***
330	10 × 20	458	B41828A6337M***
470	12.5×20	535	B41828A6477M***
1000	16 × 25	1085	B41828A6108M***
2200	18 × 35.5	1559	B41828A6228M***

Technical data and ordering codes - B41828

Composition of ordering code

- 000 = for standard leads, bulk
- 001 = for kinked leads, bulk
- 002 = for cut leads, bulk
- 016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)
- 007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \emptyset 5 ... 6.3 mm)
- 006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \emptyset 8 mm)
- 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \oslash 5 ... 12.5 mm)
- 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



B41828

Technical data and ordering codes - B41828

C _R	Case dimensions	I _{AC,R}	Ordering code			
120 Hz, 20 °C	d×I	120 Hz, 105 °C	(composition see below)			
μF	mm	mA				
V _R = 63 V DC						
10	5 ×11	50	B41828A8106M***			
22	6.3×11	79	B41828A8226M***			
33	6.3×11	103	B41828A8336M***			
47	8 × 11.5	135	B41828A8476M***			
100	10 × 12.5	217	B41828A8107M***			
220	12.5 imes 20	374	B41828A8227M***			
330	12.5 imes 20	570	B41828A8337M***			
470	12.5×25	715	B41828A8477M***			
1000	16 × 31.5	1043	B41828A8108M***			
V _R = 100 V DC						
0.47	5 ×11	11	B41828A9474M***			
1.0	5 ×11	17	B41828A9105M***			
2.2	5 ×11	25	B41828A9225M***			
3.3	5 ×11	31	B41828A9335M***			
4.7	5 ×11	37	B41828A9475M***			
10	6.3×11	55	B41828A9106M***			
22	8 ×11.5	104	B41828A9226M***			
33	10 × 12.5	145	B41828A9336M***			
47	10 × 16	186	B41828A9476M***			
100	12.5 × 20	296	B41828A9107M***			
220	16 × 25	497	B41828A9227M***			
330	16 × 25	609	B41828A9337M***			
470	16 × 31.5	802	B41828A9477M***			

Composition of ordering code

- 000 = for standard leads, bulk
- 001 = for kinked leads, bulk
- 002 = for cut leads, bulk
- 016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)
- 007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \emptyset 5 ... 6.3 mm)
- 006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \emptyset 8 mm)
- 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \varnothing 5 ... 12.5 mm)
- 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \emptyset 16 mm)



B43828

Standard series - 105 °C

C _B	Case dimensions	I _{AC,B}	Ordering code			
120 Hz, 20 °C	d×l	120 Hz, 105 °C	(composition see below)			
μF	mm	mA				
V _R = 160 V DC						
0.47	5 × 11	12	B43828A1474M***			
1.0	5 ×11	18	B43828A1105M***			
2.2	6.3×11	26	B43828A1225M***			
3.3	8 × 11.5	33	B43828A1335M***			
4.7	8 × 11.5	38	B43828A1475M***			
10	10 × 12.5	56	B43828A1106M***			
22	10 × 16	111	B43828A1226M***			
33	12.5×20	162	B43828A1336M***			
47	12.5×25	218	B43828A1476M***			
100	16 × 25	322	B43828A1107M***			
220	18 × 35.5	604	B43828A1227M***			
V _R = 200 V DC						
1.0	6.3×11	18	B43828A2105M***			
2.2	6.3×11	26	B43828A2225M***			
3.3	8 × 11.5	33	B43828A2335M***			
4.7	10 × 12.5	43	B43828A2475M***			
10	10 × 16	73	B43828A2106M***			
22	10 × 20	122	B43828A2226M***			
33	12.5 × 25	178	B43828A2336M***			
47	12.5×25	218	B43828A2476M***			
100	16 × 31.5	376	B43828A2107M***			
220	18 × 40	610	B43828A2227M***			

Technical data and ordering codes - B43828

Composition of ordering code

- 000 = for standard leads, bulk
- 001 = for kinked leads, bulk
- 002 = for cut leads, bulk
- 016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)
- 007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \emptyset 5 ... 6.3 mm)
- 006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \emptyset 8 mm)
- 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \emptyset 5 ... 12.5 mm)
- 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



B43828

Technical data and ordering codes - B43828

C _R	Case dimensions	I _{AC,R}	Ordering code
120 Hz, 20 °C	d×l	120 Hz, 105 °C	(composition see below)
μF	mm	mA	
V _R = 250 V DC			
0.47	6.3×11	12	B43828F2474M***
1.0	6.3×11	18	B43828F2105M***
2.2	8 × 11.5	29	B43828F2225M***
3.3	10 × 12.5	36	B43828F2335M***
4.7	10 × 12.5	43	B43828F2475M***
10	10 × 20	82	B43828F2106M***
22	12.5×25	132	B43828F2226M***
33	12.5×25	178	B43828F2336M***
47	16 × 25	237	B43828F2476M***
100	18 × 35.5	410	B43828F2107M***
V _R = 350 V DC			
1.0	6.3×11	18	B43828A4105M***
2.2	8 ×11.5	29	B43828A4225M***
3.3	10 × 12.5	36	B43828A4335M***
4.7	10 ×16	50	B43828A4475M***
10	12.5 × 20	89	B43828A4106M***
22	16 × 25	149	B43828A4226M***
33	16 × 25	196	B43828A4336M***
47	16 × 35.5	272	B43828A4476M***

Composition of ordering code

*** = Version

000 = for standard leads, bulk

001 = for kinked leads, bulk

002 = for cut leads, bulk

016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)

007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \emptyset 5 ... 6.3 mm)

006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \emptyset 8 mm)

008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \emptyset 5 ... 12.5 mm)

009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



B43828

Standard series - 105 °C

Technical data and ordering codes - B43828

C _B	Case dimensions	I _{AC,R}	Ordering code			
120 Hz, 20 °C	d×l	120 Hz, 105 °C	(composition see below)			
μF	mm	mA				
V _R = 400 V DC	V _R = 400 V DC					
1.0	8 ×11.5	18	B43828A9105M***			
2.2	10 × 12.5	32	B43828A9225M***			
3.3	10 ×16	42	B43828A9335M***			
4.7	10 ×20	55	B43828A9475M***			
10	12.5×20	89	B43828A9106M***			
22	16 ×25	149	B43828A9226M***			
33	16 × 31.5	217	B43828A9336M***			
47	18 × 35.5	289	B43828A9476M***			
V _R = 450 V DC						
1.0	8 ×11.5	18	B43828A5105M***			
1.5	10 × 12.5	26	B43828A5155M***			
2.2	10 × 12.5	32	B43828A5225M***			
3.3	10 ×16	42	B43828A5335M***			
4.7	10 ×20	55	B43828A5475M***			
6.8	12.5 × 20	73	B43828A5685M***			
10	12.5×20	89	B43828A5106M***			
15	12.5 × 25	120	B43828A5156M***			
22	16 ×25	149	B43828A5226M***			
33	16 × 31.5	217	B43828A5336M***			
47	16 × 35.5	273	B43828B5476M***			
47	18 × 35.5	289	B43828A5476M***			
68	18 × 35.5	351	B43828A5686M***			

Composition of ordering code


- 000 = for standard leads, bulk
- 001 = for kinked leads, bulk
- 002 = for cut leads, bulk
- 016 = for taped leads, Ammo pack, lead spacing F = 2.0 mm (for \emptyset 5 mm)
- 007 = for taped leads, Ammo pack, lead spacing F = 2.5 mm (for \oslash 5 ... 6.3 mm)
- 006 = for taped leads, Ammo pack, lead spacing F = 3.5 mm (for \oslash 8 mm)
- 008 = for taped leads, Ammo pack, lead spacing F = 5.0 mm (for \oslash 5 ... 12.5 mm)
- 009 = for taped leads, Ammo pack, lead spacing F = 7.5 mm (for \oslash 16 mm)



Standard series - 105 °C

Useful life


depending on ambient temperature T_A under ripple current operating conditions¹⁾ B41828



Useful life

depending on ambient temperature $T_{\scriptscriptstyle A}$ under ripple current operating conditions $^{\scriptscriptstyle 1)}$


B43828



 Refer to chapter "General technical information, 5.3 Calculation of useful life" for an explanation on how to interpret the useful life graphs.



Frequency factor of permissible ripple current I_{AC} versus frequency f





Standard series - 105 °C

Taping, packing and lead configurations


Taping

Single-ended capacitors are available taped in Ammo pack from diameter 4 to 18 mm as follows:

Lead spacing F = 2.0 mm (\emptyset d = 4 ... 5 mm) Lead spacing F = 2.5 mm (\emptyset d = 4 ... 6.3 mm) Lead spacing F = 3.5 mm (\emptyset d = 8 mm) Lead spacing F = 5.0 mm (\emptyset d = 4 ... 12.5 mm) Lead spacing F = 7.5 mm (\emptyset d = 16 ... 18 mm).

Lead spacing 2.0 mm (\emptyset d = 4 ... 5 mm)

Last 3 digits of ordering code: 016



Dimensions in mm


$\emptyset d$	F	Н	W	W _o	W_1	W_2	Р	P ₀	P ₁	I ₁	t	Δh	D ₀
4 5	2.0	18.5	18.0	7.0	9.0	3.0	12.7	12.7	5.10	1.0	0.7	1	4.0
	+0.8 -0.2	±0.75	±0.5	min.	±0.5	max.	±1.0	±0.3	±0.7	max.	±0.2	±1.0	±0.2



Standard series - 105 $^\circ\text{C}$

Lead spacing 2.5 mm (Ø d = 4 ... 6.3 mm)

Last 3 digits of ordering code: 007




Dimensions in mm

Ød	F	Н	W	W ₀	W_1	W_2	H₀	Р	P ₀	P ₁	I_1	t	Δh	D ₀
4 6.3												0.7	1.0	4.0
Toler- rance	+0.8 -0.2	±0.75	±0.5	min.	±0.5	max.	±0.5	±1.0	±0.2	±0.5	max.	±0.2	max.	±0.2

Lead spacing 3.5 mm (\emptyset d = 8 mm)

Last 3 digits of ordering code: 006



Dimensions in mm

Ød	F	Н	W	W _o	W ₁	W ₂	Р	P ₀	P ₁	I_1	t	Δh	D ₀
8	3.5	18.5	18.0	10	9.0	3.0	12.7	12.7	4.6	1.0	0.7	1.0	4.0
Toler- ance	+0.8 -0.2	±1.0	±0.5	min.	±0.5	max.	±1.0	±0.3	±0.6	max.	±0.2	max.	±0.2


Leads can also run straight through the taping area. Taping is available up to dimensions $d\times I=8\times 15$ mm.



B41828, B43828


Lead spacing 5.0 mm (\oslash d = 4 ... 8 mm)

Last 3 digits of ordering code: 008



Lead spacing 5.0 mm (\varnothing d = 10 ... 12.5 mm)

Last 3 digits of ordering code: 008



Dimensions in mm

\varnothing d	F	Н	W	W _o	W_1	W ₂	H₀	Р	P ₀	P ₁	I ₁	t	Δh	D ₀
4 6.3	5.0	18.5	18.0	5.5	9.0	1.5	16.0	12.7	12.7	3.85	1.0	0.6	1.0	4.0
8		20.0		10.0			16.0	12.7	12.7	3.85				
10	5.0	19.0	18.0	12.5	9.0	1.5	-	12.7	12.7	3.85	1.0	0.6	1.0	4.0
12.5		19.0		12.5			_	15.0	15.0	5.0				
Toler- ance	+0.8 -0.2	±0.75	±0.5	min.	±0.5	max.	±0.5	±1.0	±0.2	±0.5	max.	+0.3 -0.2	max.	±0.2


Taping is available up to dimensions d \times I = 10 \times 31.5 mm and 12.5 \times 25 mm. Taping is not available for d \times I = 8 \times 20 mm.



Standard series - 105 °C

Lead spacing 7.5 mm (\emptyset d = 16 ...18 mm)

Last 3 digits of ordering code: 009



Dimensions in mm

\varnothing d	F	Н	W	W _o	W_1	W_2	Р	P ₀	P ₁	I ₁	t	ΔP	Δh	D_0
16	7.5	10 5	10.0	12.5	0.0	1.5	20.0	15.0	0.75	10	0.7	0	0	4.0
18	7.5	10.5	10.0	12.5	9.0	1.5	30.0	15.0	3.75	1.0	0.7	0	0	4.0
Toler-	±0.8	-0.5 +0.75	+0.5	min.	+0.5	max.	+1.0	+0.2	+0.5	max.	+0.2	+1.0	+1.0	+0.2
ance	_0.0	+0.75	_0.0		_0.0	masti		_0.2	_0.0	marti		=•	•	

Taping is available up to dimensions d \times l = 16 \times 31.5 mm and 18 \times 31.5 mm.



Standard series - 105 °C


Cut or kinked leads

Single-ended capacitors are available with cut or kinked leads. Other lead configurations also available upon request.

Cut leads (Chapter A)

Available for series B41002, B41022, B41044, B41827, B41828, B43044, B43082, B43086, B43088, B43827, B43828.

Last 3 digits of ordering code: 002



KAL1086-R

Case size d x l (mm)	Dimensions
	(mm)
	a ±0.5
4 x 7	1.5
5 x 7	2.0
5 x 11	2.0
6.3 x 7	2.5
6.3 x 11	2.5
8 x 7	3.5
8 x 11.5	3.5
8 x 15	3.5
8 x 20	3.5
10 x 12.5	5.0
10 x 16	5.0
10 x 20	5.0
10 x 25	5.0
10 x 31.5	5.0

	Dimensions
Case size d x l (mm)	Dimensions
	(mm)
	a ±0.5
12.5 x 16	5.0
12.5 x 20	5.0
12.5 x 25	5.0
12.5 x 31.5	5.0
12.5 x 35.5	5.0
12.5 x 40	5.0
16 x 20	7.5
16 x 25	7.5
16 x 31.5	7.5
16 x 35.5	7.5
16 x 40	7.5
18 x 20	7.5
18 x 25	7.5
18 x 31.5	7.5
18 x 35.5	7.5
18 x 40	7.5






Cut leads (Chapter B)

Available for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.


Last 3 digits of ordering code: 002

With stand-off rubber seal





With flat rubber seal



KAL1086-R

Case size	Dimensions (mm)
$d \times I$ (mm)	a ±0.5
10 × 12.5	5.0
10×16	5.0
10×20	5.0
12.5 × 20	5.0
12.5 × 25	5.0
16×20	7.5
16 × 25	7.5
16 × 31.5	7.5
16 imes 35.5	7.5
18×20	7.5
18×25	7.5
18×31.5	7.5
18 × 35	7.5
18×40	7.5





B41828, B43828

Kinked leads (Chapter A)

Available for series B41002, B41022, B41044, B41827, B41828, B43044, B43082, B43086, B43088, B43827, B43828.

Last 3 digits of ordering code: 001





KAL1084-A

Case size d x I (mm)	Dimensions
	(mm)
	a ±0.5
4 x 7	1.5
5 x 7	2.0
5 x 11	2.0
6.3 x 7	2.5
6.3 x 11	2.5
8 x 7	3.5
8 x 11.5	3.5
8 x 15	3.5
8 x 20	3.5
10 x 12.5	5.0
10 x 16	5.0
10 x 20	5.0
10 x 25	5.0
10 x 31.5	5.0

Case size d x I (mm)	Dimensions
	(mm)
	a ±0.5
12.5 x 16	5.0
12.5 x 20	5.0
12.5 x 25	5.0
12.5 x 31.5	5.0
12.5 x 35.5	5.0
12.5 x 40	5.0
16 x 20	7.5
16 x 25	7.5
16 x 31.5	7.5
16 x 35.5	7.5
16 x 40	7.5
18 x 20	7.5
18 x 25	7.5
18 x 31.5	7.5
18 x 35.5	7.5
18 x 40	7.5







Kinked leads (Chapter B)

Available for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.

Last 3 digits of ordering code: 001


With stand-off rubber seal






KAL1083-2

With flat rubber seal







Case size	Dimensions (mm)
$d \times I$ (mm)	a ±0.5
10×20	5.0
12.5 imes 20	5.0
12.5 × 25	5.0
16 × 20	7.5
16 imes 25	7.5
16 imes 31.5	7.5
16 imes 35.5	7.5
18×20	7.5
18 × 25	7.5
18×31.5	7.5
18 × 35	7.5
18×40	7.5



PAPR leads (Protection Against Polarity Reversal)


These lead configurations ensure correct placement of the capacitor on the PCB with regard to polarity. PAPR leads are available for diameters from 10 mm up to 18 mm.

There are three configurations available: Crimped leads, J leads, bent 90° leads

Available for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.

Crimped leads


Last 3 digits of ordering code: 003




Suggestion for PCB hole diameter



Suggestion for PCB hole diameter, wire ø0.8 mm



Suggestion for PCB hole diameter, wire ø1.0 mm




Case size	Dimensio	ons (mm)				
d × l (mm)	B ±0.2	C ±0.5	D ±0.1	E ±0.1	a ±0.5	Øb
16×20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16×25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16×31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
16 × 35.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.05
18×20	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18×25	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18×31.5	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18×35	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1
18×40	1.5	3.0	1.3	0.3	7.5	0.8 ±0.1






J leads

Last 3 digits of ordering code: 004




Suggestion for PCB hole diameter

Suggestion for PCB hole diameter, wire $\emptyset 0.6 \text{ mm}$



Suggestion for PCB hole diameter, wire $\emptyset 0.8 \text{ mm}$




Case size	Dimensions (mm)						
$d \times I$ (mm)	C ±0.5	E ±0.5	J ±0.2	a ±0.5	Øb		
10 × 12.5	3.2	0.7	1.2	5.0	0.6 ±0.05		
10×16	3.2	0.7	1.2	5.0	0.6 ±0.05		
10×20	3.2	0.7	1.2	5.0	0.6 ±0.05		
12.5 × 20	3.2	0.7	1.2	5.0	0.6 ±0.05		
12.5×25	3.2	0.7	1.2	5.0	0.6 ±0.05		
16×20	3.5	0.7	1.6	7.5	0.8 ±0.05		
16×25	3.5	0.7	1.6	7.5	0.8 ±0.05		
16 × 31.5	3.5	0.7	1.6	7.5	0.8 ±0.05		
16 × 35.5	3.5	0.7	1.6	7.5	0.8 ±0.05		
18×20	3.5	0.7	1.6	7.5	0.8 ±0.1		
18×25	3.5	0.7	1.6	7.5	0.8 ±0.1		
18×31.5	3.5	0.7	1.6	7.5	0.8 ±0.1		
18 × 35	3.5	0.7	1.6	7.5	0.8 ±0.1		




Standard series - 105 °C

Bent 90° leads for horizontal mounting pinning

Last 3 digits of ordering code: 012






Case size	Dimensions (Dimensions (mm)						
d imes I (mm)	C ±0.5	E ±0.5	F ±0.5	a ±0.5	Øb			
16×20	4.0	4.0	12.0	7.5	0.8 ±0.05			
16×25	4.0	4.0	12.0	7.5	0.8 ±0.05			
16 imes 31.5	4.0	4.0	12.0	7.5	0.8 ±0.05			
16 imes 35.5	4.0	4.0	12.0	7.5	0.8 ±0.05			
18×20	4.0	4.0	13.0	7.5	0.8 ±0.1			
18×25	4.0	4.0	13.0	7.5	0.8 ±0.1			
18 imes 31.5	4.0	4.0	13.0	7.5	0.8 ±0.1			
18 imes 35	4.0	4.0	13.0	7.5	0.8 ±0.1			
18×40	4.0	4.0	13.0	7.5	0.8 ±0.1			

Bent leads for diameter 12.5 mm available upon request.






Packing units and box dimensions

Ammo pack

Valid for series B41002, B41022, B41044, B41827, B41828, B43044, B43082, B43086, B43088, B43827, B43828.




Case size	Dimer	Dimensions (mm)				
$d \times I$						
mm	A _{max}	B _{max}	C _{max}	pcs.		
4×7	330	50	196	2000		
5×7	330	50	226	2000		
5×11	330	50	226	2000		
6.3×7	330	50	286	2000		
6.3 × 11	330	50	286	2000		
8×7	330	50	246	1000		
8×11.5	330	50	246	1000		
8×15	330	50	246	500		
10 × 12.5	330	50	196	500		
10 × 16	330	54	196	500		
10×20	330	58	196	500		
12.5 imes 20	341	60	272	500		
12.5 imes 25	341	65	272	500		
16 imes 25	320	65	270	300		
16 imes 31.5	315	65	275	300		
18×20	315	65	275	250		
18×25	315	65	275	250		
18×31.5	315	65	275	250		



B41828, B43828

Ammo pack

Valid for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.



Case size d × l	Dimens	Packing units		
mm	A _{max}	B _{max}	C _{max}	pcs.
8×11.5	345	55	240	1000
10 × 12.5	345	55	280	750
10 × 16	345	60	200	500
10×20	345	60	200	500
12.5 × 20	345	65	280	500
12.5 imes 25	345	65	280	500
16×20	315	65	275	300
16 × 25	315	65	275	300
16 imes 31.5	315	65	275	300
18×20	315	65	275	250
18 × 25	315	65	275	250
18×31.5	315	65	275	250





Standard series - 105 $^{\circ}$ C

Overview of packing units and code numbers for case sizes 4 x 7 ... 16 x 40

Valid for series B41002, B41022, B41044, B41827, B41828, B43044, B43082, B43086, B43088, B43827, B43828.

Case size	Standard,	Taped,			Kinked leads,	Cut leads,
dxl	bulk	Ammo p	ack		bulk	bulk
mm	pcs.	pcs.			pcs.	pcs.
4 x 7	10000	2000			15000	15000
5 x 7	7500	2000			10000	10000
5 x 11	5000	2000			10000	10000
6.3 x 7	5000	2000			10000	10000
6.3 x 11	5000	2000			5000	5000
8 x 7	5000	1000			5000	5000
8 x 11.5	2500	1000			4000	4000
8 x 15	2000	1000			2500	2500
8 x 20	1500	-			2000	2000
10 x 12.5	2000	500			2500	2500
10 x 16	1500	500			2000	2000
10 x 20	1000	500			1500	1500
10 x 25	1000	500			1250	1250
12.5 x 16	750	500			1000	1000
12.5 x 20	750	500			500	500
12.5 x 25	750	500			500	500
12.5 x 31.5	500	-			750	750
12.5 x 35.5	500	-			750	750
12.5 x 40	500	-			750	750
16 x 20	375	300			500	500
16 x 25	375	300			500	500
16 x 31.5	250	300	300		375	375
16 x 35.5	250	-		375	375	
16 x 40	250	-			375	375
The last three	000	Code	F (mm)	d (mm)	001	002
digits of the		006	3.5	8		
complete		007	2.5	4 6.3		
ordering code		008	5.0	4 12.5		
state the lead		009	7.5	16 18		
configuration		016	2.0	4 5		



B41828, B43828

Standard series - 105 $^{\circ}$ C

Overview of packing units and code numbers for case sizes 18 x 20 ... 18 x 40

Valid for series B41002, B41022, B41044, B41827, B41828, B43044, B43082, B43086, B43088, B43827, B43828.

Case size	Standard,	Taped,			Kinked leads,	Cut leads,
dxl	bulk	Ammo pa	ack		bulk	bulk
mm	pcs.	pcs.			pcs.	pcs.
18 x 20	250	250			100	100
18 x 25	250	250			100	100
18 x 31.5	250	250			100	100
18 x 35.5	250	-			100	100
18 x 40	250	-			100	100
The last three	000	Code	F (mm)	d (mm)	001	002
digits of the		009	7.5	16 18		
complete						
ordering code						
state the lead						
configuration						





Standard series - 105 $^\circ\text{C}$

Overview of packing units and code numbers for case sizes 8×11.5 ... 16×35.5

Valid for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.

								PAPR	
Case size	Stan-	Taped	l,		Kinked	Cut	Crimped	J leads,	Bent 90°
$d \times I$	dard,	Ammo	pack		leads,	leads,	leads,	blister	leads,
	bulk				bulk	bulk	blister		blister
mm	pcs.	pcs.			pcs.	pcs.	pcs.	pcs.	pcs.
8×11.5	1000	1000			-	—	_	_	
10 × 12.5	1000	750			-	1000	-	675	
10×16	1000	500			-	1000	-	675	
10×20	500	500			500	500	-	500	
12.5 × 20	350	500	500			350	-	300	1)
12.5 × 25	250	500			500	500	-	225	1)
12.5 × 30	200	-	-			_	-	_	
12.5 × 35	175	-			-	-	-	—	
12.5 × 40	175	-			-	-	-	-	
16×20	250	300			200	200	200	200	120
16×25	250	300			200	200	200	200	120
16×31.5	200	300			250	250	344	344	120
16×35.5	100	-			100	100	150	150	150
The last three	000	Code	F (mm)	d (mm)	001	002	003	004	012
digits of the		006	3.5	8					
complete		008	5	512.5					
ordering code		009	7.5	1618					
state the lead									
configuration									



B41828, B43828

Overview of packing units and code numbers for case sizes $18 \times 20 \dots 18 \times 40$

Valid for series B41858, B41859, B41863, B41866, B41868, B41888, B41890, B41896, B42824, B42851, B43866, B43867, B43890, B43896.

								PAPR	<u> </u>
Case size	Stan-	Taped	l,		Kinked	Cut	Crimped	J leads,	Bent 90°
$d \times I$	dard,	Ammo	pack		leads,	leads,	leads,	blister	leads,
	bulk				bulk	bulk	blister		blister
mm	pcs.	pcs.	pcs.			pcs.	pcs.	pcs.	pcs.
18×20	175	250	250			175	200	200	120
18×25	150	250			150	150	200	200	120
18×31.5	100	250	250			100	150	150	120
18 × 35	100	-	_			100	150	150	150
18×40	125	-			100	100	120	-	72
The last three	000	Code	F (mm)	d (mm)	001	002	003	004	012
digits of the		009	7.5	1618					
complete									
ordering code									
state the lead									
configuration									



B41828, B43828 Standard series – 105 °C

Cautions and warnings

Personal safety

The electrolytes used by EPCOS have not only been optimized with a view to the intended application, but also with regard to health and environmental compatibility. They do not contain any solvents that are detrimental to health, e.g. dimethyl formamide (DMF) or dimethyl acetamide (DMAC).

Furthermore, part of the high-voltage electrolytes used by EPCOS are self-extinguishing. They contain flame-retarding substances which will quickly extinguish any flame that may have been ignited.

As far as possible, EPCOS does not use any dangerous chemicals or compounds to produce operating electrolytes. However, in exceptional cases, such materials must be used in order to achieve specific physical and electrical properties because no safe substitute materials are currently known. However, the amount of dangerous materials used in our products has been limited to an absolute minimum. Nevertheless, the following rules should be observed when handling aluminum electrolytic capacitors:

- Any escaping electrolyte should not come into contact with eyes or skin.
- If electrolyte does come into contact with the skin, wash the affected parts immediately with running water. If the eyes are affected, rinse them for 10 minutes with plenty of water. If symptoms persist, seek medical treatment.
- Avoid breathing in electrolyte vapor or mists. Workplaces and other affected areas should be well ventilated. Clothing that has been contaminated by electrolyte must be changed and rinsed in water.



B41828, B43828

Product safety

The table below summarizes the safety instructions that must be observed without fail. A detailed description can be found in the relevant sections of chapter "General technical information".

Торіс	Safety information	Reference chapter "General technical information"
Polarity	Make sure that polar capacitors are connected with the right polarity.	1 "Basic construction of aluminum electrolytic capacitors"
Reverse voltage	Voltages polarity classes should be prevented by connecting a diode.	3.1.6 "Reverse voltage"
Upper category temperature	Do not exceed the upper category temperature.	7.2 "Maximum permissible operating temperature"
Maintenance	Make periodic inspections of the capacitors. Before the inspection, make sure that the power supply is turned off and carefully discharge the electricity of the capacitors. Do not apply any mechanical stress to the capacitor terminals.	10 "Maintenance"
Mounting position of screw- terminal capacitors	Do not mount the capacitor with the terminals (safety vent) upside down.	11.1. "Mounting positions of capacitors with screw terminals"
Mounting of single-ended capacitors	The internal structure of single-ended capacitors might be damaged if excessive force is applied to the lead wires. Avoid any compressive, tensile or flexural stress. Do not move the capacitor after soldering to PC board. Do not pick up the PC board by the soldered capacitor. Do not insert the capacitor on the PC board with a hole space different to the lead space specified.	11.4 "Mounting considerations for single-ended capacitors"
Robustness of terminals	The following maximum tightening torques must not be exceeded when connecting screw terminals: M5: 2 Nm M6: 2.5 Nm	11.3 "Mounting torques"
Soldering	Do not exceed the specified time or temperature limits during soldering.	11.5 "Soldering"





Standard series - 105 °C

Торіс	Safety information	Reference chapter "General technical information"
Soldering, cleaning agents	Do not allow halogenated hydrocarbons to come into contact with aluminum electrolytic capacitors.	11.6 "Cleaning agents"
Passive flammability	Avoid external energy, such as fire or electricity.	8.1 "Passive flammability"
Active flammability	Avoid overload of the capacitors.	8.2 "Active flammability"
		Reference chapter "Capacitors with screw terminals"
Breakdown strength of insulating sleeves	Do not damage the insulating sleeve, especially when ring clips are used for mounting.	"Screw terminals - accessories"



B41828, B43828

Standard series - 105 $^{\circ}$ C

Symbols and terms

Symbol	English	German
С	Capacitance	Kapazität
C _R	Rated capacitance	Nennkapazität
Cs	Series capacitance	Serienkapazität
C _{S,T}	Series capacitance at temperature T	Serienkapazität bei Temperatur T
C _f	Capacitance at frequency f	Kapazität bei Frequenz f
d	Case diameter, nominal dimension	Gehäusedurchmesser, Nennmaß
\mathbf{d}_{\max}	Maximum case diameter	Maximaler Gehäusedurchmesser
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatzserienwiderstand
ESR _f	Equivalent series resistance at frequency f	Ersatzserienwiderstand bei Frequenz f
ESR_{T}	Equivalent series resistance at temperature T	Ersatzserienwiderstand bei Temperatur T
f	Frequency	Frequenz
I	Current	Strom
I _{AC}	Alternating current (ripple current)	Wechselstrom
I _{AC,rms}	Root-mean-square value of alternating current	Wechselstrom, Effektivwert
I _{AC,f}	Ripple current at frequency f	Wechselstrom bei Frequenz f
I _{AC,max}	Maximum permissible ripple current	Maximal zulässiger Wechselstrom
I _{AC,R}	Rated ripple current	Nennwechselstrom
I _{AC,R} (B)	Rated ripple current for base cooling	Nennwechselstromstrom für Bodenkühlung
I _{leak}	Leakage current	Reststrom
I _{leak,op}	Operating leakage current	Betriebsreststrom
I	Case length, nominal dimension	Gehäuselänge, Nennmaß
I _{max}	Maximum case length (without terminals and mounting stud)	Maximale Gehäuselänge (ohne Anschlüsse und Gewindebolzen)
R	Resistance	Widerstand
R _{ins}	Insulation resistance	Isolationswiderstand
R _{symm}	Balancing resistance	Symmetrierwiderstand
Т	Temperature	Temperatur
ΔT	Temperature difference	Temperaturdifferenz
T _A	Ambient temperature	Umgebungstemperatur
T _c	Case temperature	Gehäusetemperatur
T _B	Capacitor base temperature	Temperatur des Becherbodens
t	Time	Zeit
Δt	Period	Zeitraum
t _b	Service life (operating hours)	Brauchbarkeitsdauer (Betriebszeit)





Standard series - 105 °C

Symbol	English	German
V	Voltage	Spannung
V _F	Forming voltage	Formierspannung
V _{op}	Operating voltage	Betriebsspannung
V _R	Rated voltage, DC voltage	Nennspannung, Gleichspannung
Vs	Surge voltage	Spitzenspannung
X _c	Capacitive reactance	Kapazitiver Blindwiderstand
XL	Inductive reactance	Induktiver Blindwiderstand
Z	Impedance	Scheinwiderstand
Ζ _τ	Impedance at temperature T	Scheinwiderstand bei Temperatur T
tan δ	Dissipation factor	Verlustfaktor
λ	Failure rate	Ausfallrate
ε ₀	Absolute permittivity	Elektrische Feldkonstante
ε _r	Relative permittivity	Dielektrizitätszahl
ω	Angular velocity; $2 \cdot \pi \cdot f$	Kreisfrequenz; $2 \cdot \pi \cdot f$

Note

All dimensions are given in mm.

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or lifesaving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, FormFit, MiniBlue, MiniCell, MKK, MKD, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.