


1727312

Dome 05-09 Enclosure 24 splice

1727313

Dome 05-09 Enclosure 60 splice

Dome 05-09 Fiber Splice Enclosure



This ruggedised splice enclosure is designed to allow up to 60 individual fibers, incorporating a hinged door to provide easy access for installation and re-work. The enclosure is suitable for a range of harsh environments with an impressive IP68 rating. It can be placed in aerial, wall mounted, or duct mounted locations.

FEATURES/BENEFITS

- Opens via left hand hinge
- Multi cable entry points
- Integrated Pressure valve
- Integrated Earth Point
- Holds up to 60 single Fibers
- Integrated fiber management
- Mechanically Sealed (compression)
- Multi Functional Splicing Options
- Includes All Splice Protection
- Includes Wall Mounting Bracket and Fixings
- Can Be Pole Mounted (Optional Extra)
- Can Be Aerial Mounted (Optional Extra)
- IP68

SPECIFICATIONS

Maximum Single Fiber Count	
Maximum Fibers Per Tray	60
Maximum Number Of Trays	12
Number Of Cable Entry Points	5
Suitable For Cable Diameters	3
Number of Pigtail Outlets	8mm to 15mm Ø
Suitable For Pigtail Diameter	4
Number of Uncut Cable Entry	2mm Ø
Suitable For Cable Diameter	1
Number of Test outlets	8mm to 15mm Ø
Suitable For Test Cable Diameter	1
Sealing Rating	6mm Ø
Sealing Method For All Entry And Exit	IP68
Height	Mechanical (compression)
Width	300mm
Depth	220mm
Weight	100mm
Colour	2.4kg to 2.7kg
Material	Black
RoHS Compliant	ABS
Optimal Operating Temperature	Yes
	-40 °C to +65 °C

