


# X5R Dielectric, KGM Series

## General Specifications



### GENERAL DESCRIPTION

- General Purpose Dielectric for Ceramic Capacitors
- EIA Class II Dielectric
- Temperature variation of capacitance is within  $\pm 15\%$  from  $-55^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$
- Well suited for decoupling and filtering applications
- Available in High Capacitance values (up to  $100\mu\text{F}$ )

### HOW TO ORDER

KGM	03	A	R5	1E	101	M	N
<b>Series</b>	<b>Size</b>	<b>Thickness</b>	<b>Dielectric</b>	<b>Voltage</b>	<b>Capacitance Code Code (in pF)</b>	<b>Capacitance Tolerance</b>	<b>Packaging</b>
General Purpose Tin/Nickel Finish	02 = 01005 03 = 0201 05 = 0402 15 = 0603 21 = 0805 31 = 1206 32 = 1210 43 = 1812	See Cap Chart	R5 = X5R	0G = 4.0V 0J = 6.3V 1A = 10V 1C = 16V 1E = 25V 1H = 50V	Two Significant Digits + Number of zeroes eg. 106 = 10 $\mu\text{F}$ 103 = 10nF 470 = 47pF	J* = +/- 5% K = +/- 10% M = +/- 20%	See Table Below



NOTE: Contact factory for availability of Tolerance Options for Specific Part Numbers.  
Contact factory for non-specified capacitance values.



### PACKAGING CODES

Code	EIA (inch)	IEC(mm)	7" Paper	7" Embossed	13" Paper	13" Embossed
02	01005	0402	H	P	N	
03	0201	0603	H		N	
05	0402	1005	H		N	
15	0603	1608	T		M	
21	0805	2012		U		L
31	1206	3216		U		L
32	1210	3225		U		L
43	1812	4532		V		S

### TYPICAL ELECTRICAL CHARACTERISTICS



# X5R Dielectric, KGM Series

## Specifications and Test Methods



X5R Specification Limits		X5R Specification Limits	Measuring Conditions (Complies with JIS C5101 / IEC60384)									
Operating Temperature Range		-55°C to +85°C	Temperature Cycle Chamber									
Capacitance		Within specified tolerance	Measure after heat treatment Capacitance Frequency Volt C≤10μF Frequency : 1KHz±10% Volt : 1.0±0.2Vrms *0.5±0.2Vrms * :KGM02AR50J104, KGM02AR50J474, KGM03CR50J225, KGM03BR50J225 KGM03DR50J475, KGM03CR50G475, KGM05CR50J106  C>10μF Frequency : 120Hz±10% Volt : 0.5±0.2Vrms  The charge and discharge current of the capacitor must not exceed 50mA.									
Dissipation Factor / Tanδ		Refer to <a href="https://spicat.kyocera-avx.com">https://spicat.kyocera-avx.com</a> for individual part number specification										
Insulation Resistance		Refer to <a href="https://spicat.kyocera-avx.com">https://spicat.kyocera-avx.com</a> for individual part number specification	Apply the rated voltage for 1 minute, and measure it in normal temperature and humidity. The charge and discharge current of the capacitor must not exceed 50mA.									
Dielectric Strength		No breakdown or visual defects	Charge device with 250% of rated voltage for 1-5 seconds, w/ charge and discharge current limited to 50 mA (max) * KGM31AR52A225: 200% of rated voltage									
Bending Strength		No significant damage with 1mm bending	Glass epoxy PCB: Fulcrum spacing: 90mm, duration time 10 seconds.									
Solderability		Solder coverage : 95% min.	Soaking condition Sn-3Ag-0.5Cu 245±5°C 3±0.5 sec.									
Resistance to Solder Heat	Appearance	No problem observed	Take the initial value after heat treatment.									
	Capacitance Variation	± 7.5%	Soak the sample in 260°C±5°C solder for 10±0.5 seconds and place in normal temperature and humidity, and measure after heat treatment. (Pre-heating conditions) <table border="1"> <thead> <tr> <th>Order</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>80 to 100°C</td> <td>2 minutes</td> </tr> <tr> <td>2</td> <td>150 to 200°C</td> <td>2 minutes</td> </tr> </tbody> </table> The charge and discharge current of the capacitor must not exceed 50mA for IR and withstanding voltage measurement.	Order	Temperature	Time	1	80 to 100°C	2 minutes	2	150 to 200°C	2 minutes
	Order	Temperature		Time								
	1	80 to 100°C		2 minutes								
	2	150 to 200°C		2 minutes								
Dissipation Factor / Tanδ	Within specification											
Insulation Resistance	Within specification											
Withstanding Voltage / Dielectric Strength	Resist without problem											
Thermal Shock	Appearance	No visual defects	Take the initial value after heat treatment. (Cycle) Room temperature (3 min.) → Lowest operation temperature (30 min.) → Room temperature (3 min.) → Highest operation temperature (30 min.) After 5 cycles, measure after heat treatment.									
	Capacitance Variation	± 7.5%	The charge and discharge current of the capacitor must not exceed 50mA for IR and withstanding voltage measurement.									
	Dissipation Factor	Within specification	Take the initial value after heat treatment.									
	Insulation Resistance	Within specification	After applying *1.5 the rated voltage at the highest operation temperature for 1000+12/-0 hours, and measure the sample after heat treatment in normal temperature and humidity. The charge and discharge current of the capacitor must not exceed 50mA for IR measurement. *Apply 1.0 times when the rated voltage is 4V or less. Applied voltages for respective products are indicated in the chart below.									
	Withstanding Voltage / Dielectric Strength	Resist without problem	Take the initial value after heat treatment. After applying rated voltage for 500+12/-0 hours in the condition of 40°C±2°C and 90 to 95%RH, and place in normal temperature and humidity, then measure the sample after heat treatment. The charge and discharge current of the capacitor must not exceed 50mA for IR measurement.									
Load Life	Appearance	No visual defects	Take the initial value after heat treatment.									
	Capacitance Variation	± 12.5%	After applying *1.5 the rated voltage at the highest operation temperature for 1000+12/-0 hours, and measure the sample after heat treatment in normal temperature and humidity. The charge and discharge current of the capacitor must not exceed 50mA for IR measurement. *Apply 1.0 times when the rated voltage is 4V or less. Applied voltages for respective products are indicated in the chart below.									
	Dissipation Factor / Tanδ	≤ Initial Value x 2.0 (See Above)	Take the initial value after heat treatment.									
	Insulation Resistance	Over 1000MΩ or 50MΩ·μF, whichever is less. *Exceptions Listed Below	After applying rated voltage for 500+12/-0 hours in the condition of 40°C±2°C and 90 to 95%RH, and place in normal temperature and humidity, then measure the sample after heat treatment. The charge and discharge current of the capacitor must not exceed 50mA for IR measurement.									
Load Humidity	Appearance	No visual defects	Take the initial value after heat treatment.									
	Capacitance Variation	± 12.5%	After applying rated voltage for 500+12/-0 hours in the condition of 40°C±2°C and 90 to 95%RH, and place in normal temperature and humidity, then measure the sample after heat treatment. The charge and discharge current of the capacitor must not exceed 50mA for IR measurement.									
	Dissipation Factor / Tanδ	Within specification										
	Insulation Resistance	Over 1000MΩ or 50MΩ·μF, whichever is less. *Exceptions Listed Below										
Appearance		No problem observed	Microscope									
Termination Strength		No problem observed	Apply a sideward force of 500g (5N) to a PCB-mounted sample. note : 2N for 0201 size, and 1N for 01005 size.									
Vibration	Appearance	No problem observed	Take the initial value after heat treatment.									
	Capacitance	Within tolerance	Vibration frequency: 10 to 55 (Hz) Amplitude: 1.5mm Sweeping condition: 10 → 55 → 10Hz/ 1 minute in X, Y and Z directions: 2 hours each, 6 hours in total, and place in normal temperature and humidity, then measure the sample after heat treatment.									
	Tanδ	Within tolerance										
Heat treatment		Expose sample in the temperature of 150+0/-10°C for 1 hour and leave the sample in normal temperature and humidity for 24±2 hours.										

Voltage to be applied in the High Temperature Load (Applied voltage is the multiple of the rated voltage)

Rated Voltage	Products
×1.0	6.3V KGM02AR50J224, KGM02AR50J474, KGM03BR50J225, KGM03CR50J225, KGM03DR50J475, KGM05CR50J106, KGM05BR50J156, KGM05DR50J226, KGM21AR50J476
	10V KGM02AR51A104, KGM03CR51A225, KGM15CR51A226
	16V KGM03CR51C105, KGM05AR51C225, KGM05CR51C475, KGM15CR51C226
	25V KGM05AR51E105, KGM05AR51E225, KGM05CR51E225, KGM05CR51E475, KGM15CR51E475, KGM15CR51E106, KGM21AR51E226
	35V KGM05AR51V105, KGM15CR51V475, KGM15CR51V106
	100V KGM31AR52A225
×1.2	6.3V KGM03BR50J105
×1.3	6.3V KGM02AR50J153-104, KGM03AR50J474
	10V KGM03AR51A223-224, KGM05AR51A105-225
	16V KGM05AR51C105

<Load Life / Load Humidity>Insulation Resistance : Over 10MΩ·μF

X5R / R5	Products
03	KGM03BR51A105, KGM03CR51C224, KGM03CR51E224
05	KGM05BR51A475, KGM05CR51A106, KGM05CR51V225



# X5R Dielectric, KGM Series

## Capacitance Range



### PREFERRED SIZES ARE SHADED

Case Size	1206								1210								1812							
Soldering	Reflow/Wave								Reflow Only								Reflow Only							
Packaging	All Embossed								All Embossed								All Embossed							
(L) Length	3.20 ± 0.40 (0.126 ± 0.016)								3.20 ± 0.40 (0.126 ± 0.016)								4.50 ± 0.30 (0.177 ± 0.012)							
W) Width	1.60 ± 0.30 (0.063 ± 0.012)								2.50 ± 0.30 (0.098 ± 0.012)								3.20 ± 0.20 (0.126 ± 0.008)							
(t) Terminal	0.50 ± 0.25 (0.020 ± 0.010)								0.50 ± 0.25 (0.020 ± 0.010)								0.61 ± 0.36 (0.024 ± 0.014)							
Voltage:	4	6.3	10	16	25	35	50	100	4	6.3	10	16	25	35	50	4	6.3	10	16	25	35	50		
Cap (pF)	100	101																						
	150	151.0																						
	220	221																						
	330	331																						
	470	471																						
	680	681																						
	1000	102																						
	1500	152																						
	2200	222																						
	3300	332																						
	3900	392																						
	4700	472																						
Cap (µF)	5600	562																						
	6800	682																						
	0.01	103																						
	0.012	123																						
	0.015	153																						
	0.018	183																						
	0.022	223																						
	0.027	273																						
	0.033	333																						
	0.039	393																						
	0.047	473																						
	0.068	683																						
	0.082	823																						
	0.10	104																						
	0.12	124																						
	0.15	154																						
	0.22	224																						
	0.33	334																						
	0.47	474	M	M	M	M	M	M							C	C								
	0.68	684																						
	1	105	H	H	H	H	H	H		E	E	E	E	E	E	E								
	2.2	225	H	H	H	H	H	H	A	L	L	L	L	L	L	L								
	4.7	475	H	H	H	H	A	H	A	J	J	J	J	J	A	A								
	10	106	H	H	H	H	A	H	H	J	J	J	J	J	A	A					J			
	22	226	H	H	H	A	H			A	A	A	L	A			J	J	J					
	47	476	H	H	H	H				L	L	L	L	L										
	100	107	H	H						L	L													
Voltage:	4	6.3	10	16	25	35	50	100	4	6.3	10	16	25	35	50	4	6.3	10	16	25	35	50		
Case Size	1206								1210								1812							

Case Size	1206 (KGM 31)				1210 (KGM 32)					1812 (KGM 43)
Thickness Letter	M	A	H	C	E	J	A	L	J	
Max Thickness (mm)	1.25	1.8	1.9	1.27	1.45	2.21	2.7	2.80	2.80	
Carrier Tape	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	EMB	
Packaging Code 7"reel	U	U	U	U	U	U	U	U	V	
Packaging Code 13"reel	L	L	L	L	L	L	L	L	S	
EMBOSSED (EMB)										

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## [KYOCERA AVX:](#)

[08056D106KAT2A](#) [08056D106KAT4A](#) [08056D106MAT2A](#) [08056D475KAT2A](#) [08056D475KAT4A](#)  
[08056D475MAT2A](#) [0805YD105KAT2A](#) [0805YD105KAT4A](#) [0805YD105MAT2A](#) [0805YD105MAT4A](#)  
[0805YD225KAT2A](#) [12063D105KAT2A](#) [12063D105MAT2A](#) [12063D225KAT2A](#) [12063D475KAT2A](#) [0805ZD225KAT2A](#)  
[0805ZD225KAT4A](#) [0805ZD225MAT2A](#) [0805ZD475KAT2A](#) [0805ZD475KAT4A](#) [0805ZD475MAT2A](#)  
[12066D106KAT2A](#) [12066D106MAT2A](#) [12066D106MAT4A](#) [12066D226KAT2A](#) [12066D226MAT2A](#)  
[12066D226MAT4A](#) [1206YD106KAT2A](#) [1206YD225KAT2A](#) [1206YD225KAT4A](#) [1206YD225MAT2A](#)  
[1206YD475KAT2A](#) [1206YD475MAT2A](#) [1206ZD106KAT2A](#) [1206ZD106KAT4A](#) [1206ZD106MAT2A](#)  
[1206ZD106MAT4A](#) [1206ZD475KAT2A](#) [1206ZD475KAT4A](#) [1206ZD475MAT2A](#) [12103D106KAT2A](#) [12103D225KAT2A](#)  
[12103D225MAT2A](#) [12103D475KAT2A](#) [12103D475MAT2A](#) [12106D106KAT2A](#) [12106D106MAT2A](#)  
[12106D107MAT2A](#) [12106D226KAT2A](#) [12106D226MAT2A](#) [12106D476MAT2A](#) [1210DD225KAT2A](#)  
[1210DD225MAT2A](#) [18123D106KAT2A](#) [18123D106MAT2A](#) [1210YD106KAT2A](#) [1210YD106MAT2A](#)  
[1210YD226KAT2A](#) [1210YD475KAT2A](#) [1210ZD106KAT2A](#) [1210ZD106KAT4A](#) [1210ZD106MAT2A](#)  
[1210ZD106MAT4A](#) [1210ZD226KAT2A](#) [1210ZD226KAT4A](#) [1210ZD226MAT2A](#) [1210ZD475KAT2A](#)  
[1210ZD475MAT2A](#) [1812ZD226KAT2A](#) [1812ZD226MAT2A](#) [0201ZD222KAT2A](#) [0201ZD222MAT2A](#)  
[0201ZD332KAT2A](#) [0201ZD472KAT2A](#) [0201ZD682KAT2A](#) [0201ZD103KAT2A](#) [0201ZD103MAT2A](#) [04024D105MAT2A](#)  
[04026D105KAT2A](#) [04026D224KAT2A](#) [04026D224KAT4A](#) [04026D224MAT2A](#) [0402YD104KAT2A](#)  
[0402YD333KAT2A](#) [0402YD333KAT4A](#) [0402YD333MAT2A](#) [0402YD473KAT2A](#) [0402YD473MAT2A](#)  
[0402YD473MAT4A](#) [0402ZD104KAT2A](#) [0402ZD104KAT4A](#) [0402ZD104MAT2A](#) [0402ZD104MAT4A](#)  
[0402ZD224KAT2A](#) [06033D104KAT2A](#) [06033D104KAT4A](#) [06033D104MAT2A](#) [06033D154KAT2A](#) [06033D224KAT2A](#)  
[06036D105KAT2A](#)