

ASDX SERIES 15, 30, 100 PSI SILICON PRESSURE SENSORS (CONT.)

Mfg. Part No	Pressure Range (psi)	Pressure Type	Sensor Output	Stock No.	Price Each	
					1-9	10-49
ASDXACX030PA2A5	0-30	Absolute	Digital I ² C address 0x28	34R2749	32.46	
ASDXACX030PA7A5	0-30	Absolute	Digital I ² C address 0x78	34R2750	32.46	
ASDXACX100PAA5	0-100	Absolute	Analog	34R2751	33.11	
ASDXACX100PA2A5	0-100	Absolute	Digital I ² C address 0x28	34R2752	32.46	
ASDXACX100PA7A5	0-100	Absolute	Digital I ² C address 0x78	34R2753	33.11	

AXIAL PORT, VENTED COVER

Mfg. Part No	Pressure Range (psi)	Pressure Type	Sensor Output	Stock No.	Price Each	
					1-9	10-49
ASDXAVX015PGA5	0-15	Gage	Analog	34R2754	32.46	
ASDXAVX015PGA5	0-15	Gage	Digital I ² C address 0x28	34R2755	33.11	
ASDXAVX015PGA5	0-15	Gage	Digital I ² C address 0x78	34R2756	33.11	
ASDXAVX030PGA5	0-30	Gage	Analog	34R2757	32.46	
ASDXAVX030PGA5	0-30	Gage	Digital I ² C address 0x28	34R2758	32.46	
ASDXAVX030PGA5	0-30	Gage	Digital I ² C address 0x78	34R2759	33.15	
ASDXAVX100PGA5	0-100	Gage	Analog	34R2760	33.15	
ASDXAVX100PGA5	0-100	Gage	Digital I ² C address 0x28	34R2761	33.11	
ASDXAVX100PGA5	0-100	Gage	Digital I ² C address 0x78	34R2762	33.15	

RADIAL PORT

Mfg. Part No	Pressure Range (psi)	Pressure Type	Sensor Output	Stock No.	Price Each	
					1-9	10-49
ASDXRRX015PDA5	0-15	Differential	Analog	34R2763	32.46	
ASDXRRX015PDA5	0-15	Differential	Digital I ² C address 0x28	34R2764	33.11	
ASDXRRX015PDA5	0-15	Differential	Digital I ² C address 0x78	34R2765	32.46	
ASDXRRX015PGA5	0-15	Gage	Analog	34R2766	32.46	
ASDXRRX015PGA5	0-15	Gage	Digital I ² C address 0x28	34R2767	32.46	
ASDXRRX015PGA5	0-15	Gage	Digital I ² C address 0x78	34R2768	32.46	
ASDXRRX030PDA5	0-30	Differential	Analog	34R2769	33.15	
ASDXRRX030PDA5	0-30	Differential	Digital I ² C address 0x28	34R2770	33.11	
ASDXRRX030PGA5	0-30	Gage	Digital I ² C address 0x28	34R2771	32.46	
ASDXRRX030PGA5	0-30	Gage	Digital I ² C address 0x78	34R2772	33.11	
ASDXRRX100PDA5	0-100	Differential	Digital I ² C address 0x28	34R2773	32.46	
ASDXRRX100PDA5	0-100	Differential	Digital I ² C address 0x78	34R2774	33.11	
ASDXRRX100PGA5	0-100	Gage	Analog	34R2775	33.11	
ASDXRRX100PGA5	0-100	Gage	Digital I ² C address 0x28	34R2776	33.11	
ASDXRRX100PGA5	0-100	Gage	Digital I ² C address 0x78	34R2777	33.11	

(15/90)

ML SERIES ALL METAL PRESSURE SENSORS

- All metal wetted parts
- No internal elastomeric seals - no o-ring compatibility issues
- Amplified outputs - eliminates cost of external amplifiers
- Reverse polarity and overvoltage protection
- Less than 2ms response time - accurate high speed measurement

Combines the latest in ASIC technology with a proven media isolating, steel diaphragm design. Exceeds CE heavy industrial EMC allowing for use in areas of high EMI/RFI. Accuracy: +/- 0.25% FSO. Compensated operating and storage temperature range: -40°C to +125°C. Gauge parts -300 psi, -40 to 85°C +/- 3%, 85 to 125°C +/- 10%. Connector: Packard Electric Metri-Pack™ Connector (mfg. part no. 3685302) 3M leads.

1/4" -18 NPT PRESSURE CONNECTION

Mfg. Part No.	Pressure Range (PSI)	Output	Stock No.	Price Each	
				1-9	10-49
MLH150PSB01A	150	0.5-4.5VDC, Ratiometric	71M5256	99.47	84.31
MLH500PSB01A	500	0.5-4.5VDC, Ratiometric	42J5752	104.86	88.79
MLH05KPSB01A	5000	0.5-4.5VDC, Ratiometric	95M4336	104.86	88.79
MLH150PSB01B	150	4-20mA, Current Loop	71M5257	104.86	88.79
MLH250PSB01B	250	4-20mA, Current Loop	71M5259	104.70	88.74
MLH500PSB01B	500	4-20mA, Current Loop	42J5753	104.70	88.74
MLH01KPSB01B	1000	4-20mA, Current Loop	42J5733	104.86	88.79
MLH03KPSB01B	3000	4-20mA, Current Loop	71M5254	114.28	104.07
MLH03KPSL01B	3000	4-20mA, Revers Polarity	62M4898	104.86	88.79
MLH05KPSB01B	5000	4-20mA, Current Loop	42J5741	104.86	88.79

1/4" -27 NPT PRESSURE CONNECTION

Mfg. Part No.	Pressure Range (PSI)	Output	Stock No.	Price Each	
				1-9	10-49
MLH500PSB06A	500	0.5-4.5VDC, Ratiometric	71M5281	104.70	88.74
MLH02KPSB06A	2000	0.5-4.5VDC, Ratiometric	71J5885	104.86	88.79
MLH03KPSB06A	3000	0.5-4.5VDC, Ratiometric	51M8880	104.86	88.79
MLH05KPSB06A	5000	0.5-4.5VDC, Ratiometric	71M5255	98.00	83.06
MLH150PSB06B	150	4-20mA, Current Loop	71M5258	99.47	84.31
MLH250PSB06B	250	4-20mA, Current Loop	71M5260	104.70	88.74
MLH500PSB06B	5000	4-20mA, Current Loop	71M5262	104.70	88.74

CONNECTION

Mfg. Part No.	Description	Stock No.	Price Each	
			1-9	10-49
3685302	Packard Electric Female Metri-Pack™ Connector with 3M leads	72M5174	86.50	

(05/05)


SCX AND SCXL SERIES PRECISION COMPENSATED PRESSURE SENSORS



- SCX series response time: 100msec
- Operating temperature: -40°C to +85°C
- SIP Package



Just Added



- SCXL series response time: 500msec
- Operating temperature: 0 to +70°C

Provide a very cost-effective solution for pressure applications that require high accuracy over a wide temperature range. Feature an integrated sensor element and laser-trimmed thick film ceramic housed in a compact nylon case. All devices are calibrated for span to within +/-1% and provide a very low pressure output of +/-300 microvolts maximum. Ideal for medical equipment, computer peripherals and pneumatic control applications.

SCX SERIES

Mfg. Part No.	Pressure	Pressure Type	Output/ Span (mV)	Supply Voltage (VDC)	Stock No.	Price Each	
						1-9	10-49
SCX01DNC	0-1 Psi	Differential/Gage	19	20	23K1087	68.47	51.10
SCX05DN	0-5 Psi	Differential/Gage	60	20	78H1478	88.25	83.06
SCX05DN	0-5 Psi	Differential/Gage	62.5	20	95H7744	65.49	60.25
SCX15AN	0-15 Psi	Absolute	90	20	10M5247	88.25	83.06
SCX15DN	0-15 Psi	Differential/Gage	90	20	10M5248	88.25	83.06
SCX15ANC	0-15 Psi	Absolute	95	20	23K1097	51.17	48.16
SCX15DNC	0-15 Psi	Differential/Gage	95	20	23K1100	51.17	48.16
SCX100DN	0-100 Psi	Differential/Gage	100	20	78H1480	92.68	90.77

SCXL SERIES

SCXL004DN	0-4" H ₂ O	Differential/Gage	Ratio	18	10M5245	119.42	112.40
-----------	-----------------------	-------------------	-------	----	---------	--------	--------

(2/2/0)

SDX SERIES PRECISION COMPENSATED PRESSURE SENSORS

Just Added



Honeywell Sensing and Control

- Supply Voltage: +20VDC
- Response Time: 100msec
- Operating Temperature: -40°C to +85°C
- DIP Package



Provide a very cost-effective solution for pressure applications that require small size plus performance. Feature an integrated circuit sensor element and laser-trimmed thick film ceramic housed in a compact, solvent-resistant case. Double wide (0.600" lead spacing) dual-inline package. The PC board area used by each DIP is approximately 0.26 square inches, enabling the use of multiple sensors in limited board space. Thru-hole mounting. Ideal for medical equipment, computer peripherals, HVAC and pneumatic control applications.

Mfg. Part No.	Pressure	Pressure Type	Output/ Span	Stock No.	Price Each	
					1-9	10-49
SDX0504	0-5 Psi	Differential/Gage	Voltage	10M5254	39.57	
SDX1004	0-100 Psi	Differential/Gage	Voltage	10M5257	39.41	
SDX01G2	0-1 Psi	Gage	Voltage	78H1489	39.57	
SDX15A2	0-15 Psi	Absolute	Voltage	78H1487	39.77	
SDX15A4-A	0-15 Psi	Absolute	Voltage	23K1121	49.13	
SDX1504-A	0-15 Psi	Differential/Gage	Voltage	23K1122	49.13	

(02/07)

eQuotes

Retrieve and process Newark quotes online from our website under MY ACCOUNT eSuite. Or email them to your Purchasing department. Log in or register today.

Make it easy. Make it fast. Make it Newark.



(14/02/05)