

**KEMET Part Number: C0603C150J5GACTU**  
(C0603C150J5GAC7867)

SMD Comm C0G, Ceramic, 15 pF, 5%, 50 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 0603



| Dimensions |                  |
|------------|------------------|
| <b>L</b>   | 1.6mm +/-0.15mm  |
| <b>W</b>   | 0.8mm +/-0.15mm  |
| <b>T</b>   | 0.8mm +/-0.07mm  |
| <b>S</b>   | 0.7mm MIN        |
| <b>B</b>   | 0.35mm +/-0.15mm |

| Packaging Specifications   |                        |
|----------------------------|------------------------|
| <b>Packaging:</b>          | T&R, 180mm, Paper Tape |
| <b>Packaging Quantity:</b> | 4000                   |

| General Information   |                                                         |
|-----------------------|---------------------------------------------------------|
| <b>Supplier:</b>      | KEMET                                                   |
| <b>Series:</b>        | SMD Comm C0G                                            |
| <b>Style:</b>         | SMD Chip                                                |
| <b>Description:</b>   | SMD, MLCC, Ultra-Stable, Low Loss, Class I              |
| <b>Features:</b>      | Ultra-Stable, Low Loss, Class I                         |
| <b>RoHS:</b>          | Yes                                                     |
| <b>Termination:</b>   | Tin                                                     |
| <b>Marking:</b>       | No                                                      |
| <b>Miscellaneous:</b> | Note: KEMET 50V rated parts may be operated at 63 Volts |
| <b>Chip Size:</b>     | 0603                                                    |

| Specifications                          |                     |
|-----------------------------------------|---------------------|
| <b>Capacitance:</b>                     | 15 pF               |
| <b>Capacitance Tolerance:</b>           | 5%                  |
| <b>Voltage DC:</b>                      | 50 VDC              |
| <b>Dielectric Withstanding Voltage:</b> | 125 VDC             |
| <b>Temperature Range:</b>               | -55/+125C           |
| <b>Temperature Coefficient:</b>         | C0G                 |
| <b>Dissipation Factor:</b>              | 0.10% 1MHz 25C      |
| <b>Aging Rate:</b>                      | 0% Loss/Decade Hour |
| <b>Insulation Resistance:</b>           | 100 GOhms           |