


Sep.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	DIS-C-000409	D.M	M.S	06.12.19					



NOTE ① HAND CRIMPING TOOL, REF. NO. ⑧ :
 HR10A-TC-02 (CL150-0041-2)
 THE HOLE DIAMETER FOR CRIMPING: φ 5.3
 ② THE RECOMMENDED CLAMP TORQUE,
 REF. NO. ⑥ : 1.5-2 N · m.

- ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑦ : 1.27 THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑦ : 0.3-0.4N · m.
- ④ LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ① AND ⑦ FROM LOOSENING.
- ⑤ ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑥ TO REF. NO. ① IS SHOWN.
- ⑥ THE CABLE STRENGTH, ROTATORY STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

4	BRASS	MATTE FINISH NICKEL PLATED	9	CHLOROPRENE RUBBER (BLACK)	
3	PHOSPHOR BRONZE	GOLD PLATING : 0.2 μ m min. NICKEL UNDER PLATING : 2 μ m min.	8	BRASS	
2	POLYAMIDE	(BLACK) UL94V-0	7	STEEL	NICKEL PLATING HEXAGON SOCKET SET SCREW M2.6×0.45×2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	NICKEL PLATING
			5	STEEL	NICKEL PLATING

NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS		
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
CL			M.SATO	D.MATSUNE	E.KUNII	M.SATO	
			060801	060801	060801	060801	

SACLE 2 : 1 UNITS mm	DRAWING NO.	PART NO.
	EDC4-020537-74	HR10A-7P-6S(74)
HRS HIROSE ELECTRIC CO., LTD.	CODE NO.	
	CL110-0304-0-74	1/1