




	SM6	SM66+	SM12
Material:	Polyamide 6	Polyamide 6.6 modified	Polyamide 12
Colours:	black	black	black
Temperatures of use:	-20 to +70°C +120°C short time	-40 to +70°C +120°C short time	-40 to +60°C +120°C short time
Specifications:	good resistance against U.V. HB UL94	protected against U.V. HB UL94	protected against U.V. conform to norm NFC20540 HB UL94
Application:	For indoor use	For indoor and outdoor use	For indoor and outdoor use

type	art. no.	dimensions length x width mm	maximum bundle Ø mm	tensile strength mini. daN	
Cable ties for installations SM6 (in bags)					
SM6-183/60 BK-C	0189 0050 010	183 x 6	43	30	100
SM6-183/90 BK-C	0189 0060 010	183 x 9	41	40	100
SM6-265/90 BK-C	0189 0070 010	265 x 9	63	51	100
SM6-355/90 BK-C	0189 0080 010	355 x 9	90	51	100
Cable ties for installations SM66+ (in boxes)					
SM66+ 183/90 BK-C	0189 0201 010	183 x 9	41	40	100
SM66+ 265/90 BK-C	0189 0202 010	265 x 9	63	51	100
SM66+ 355/90 BK-C	0189 0203 010	355 x 9	90	51	100
Cable ties for installations SM12 (in boxes)					
SM12-183/60 BK-C	0189 0105 010	183 x 6	43	30	100
SM12-130/90 BK-C	0189 0165 010	130 x 9	25	40	100
SM12-183/90 BK-C	0189 0115 010	183 x 9	41	40	100
SM12-265/90 BK-C	0189 0125 010	265 x 9	63	51	100
SM12-355/90 BK-C	0189 0135 010	355 x 9	90	51	100
SM12-550/90 BK-C	0189 0145 010	550 x 9	150	55	100
SM12-780/90 BK-C	0189 0155 010	780 x 9	225	55	100

