

## Screw insert - SF-BIT-PH 2-50 - 1212580

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Screw bit, PH cross, E6.3-1/4" drive, size: PH 2 x 50 mm, hardened, suitable for holders as per DIN 3126-F 6.3 / ISO 1173

### Your advantages

- Tools for SF-ASD 21 cordless screwdriver in various versions

### Key Commercial Data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	
GTIN	4046356590150
Weight per Piece (excluding packing)	11.350 g
Custom tariff number	82079030
Country of origin	Czech Republic

### Technical data

#### Dimensions

Length (b)	50 mm
Blade height	50 mm

#### General

Color	silver
Type	Phillips
Material	Steel
Test standard	DIN 3126

#### Standards and Regulations

Test standard	DIN 3126
---------------	----------

#### Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

### Drawings

# Screw insert - SF-BIT-PH 2-50 - 1212580

Pictogram



## Classifications

### eCl@ss

eCl@ss 10.0.1	21044203
eCl@ss 4.0	21040402
eCl@ss 4.1	21040402
eCl@ss 5.0	21040402
eCl@ss 5.1	21040400
eCl@ss 6.0	21049200
eCl@ss 7.0	21044203
eCl@ss 8.0	21044203
eCl@ss 9.0	21044203

### ETIM

ETIM 4.0	EC002169
ETIM 5.0	EC002115
ETIM 6.0	EC002115

### UNSPSC

UNSPSC 6.01	27111701
UNSPSC 7.0901	27111701
UNSPSC 11	27111701
UNSPSC 12.01	27111701
UNSPSC 13.2	27112836

## Approvals

### Approvals

Approvals

EAC

Ex Approvals

### Approval details

EAC		RU C- DE.AI30.B.01750
-----	--	--------------------------

