



Chemical system:	Zinc Chloride, ZnCl ₂
Designations:	IEC 4R25, ANSI 908D
Nominal Voltage:	6V
Minimum Duration:	>700min at 15.6Ohm, continuously to 3.6V
Average Weight:	475 g
Average Volume:	516.2 cm ³
Recommended storage temperature:	10 – 25 °C, RH no more than 75%.
Reaction:	$2 \text{ MnO}_2 + \text{ Zn} + \text{ H}_2\text{O} \rightarrow 2 \text{ MnOOH} + \text{ ZnO}$
Terminals:	Spring Terminals
Jacket:	Plastic Shell

Note:

- 1) No added Mercury / 99.9999% Mercury Free
- 2) No added Lead /99.999% Lead Free
- 3) No added Cadmium / 99.9999% Cadmium Free
- 4) No added PFOS (Perfluorooctane sulfonates)
- 5) This battery complies with ANSI C18, IEC 60086, and EU Directive 2006/66/EC, 2006/122/EC