

brennenstuhl®

Mobile Rechargeable LED Floodlight RUFUS 3020 MA with colour rendering 15CRI 96, 2700lm, IP65



Technical data

Product number:	1173110300	Impact strength:	IK08
EAN:	4007123668465	Protection class:	III
Total luminous flux primary source:	2,700 lm	Degree of protection (IP):	IP65
Power:	30 W	Colour:	black
Colour temperature:	6,500 K	Packaging:	
Number of batteries:	1	Weight of product (without packaging):	1.11 kg
Battery type:	Built-in battery pack	Length of product (without packaging):	5 cm
Battery technology:	Lithium-ion	Width of product (without packaging):	14 cm

Voltage:	7.4 V	Height of product (without packaging):	21 cm
Battery capacity:	5 Ah	Weight of product (including packaging):	1.41 kg
Light duration max.:	25 h	Length of product (including packaging):	7 cm
Charging time:	5 h	Width of product (including packaging):	16.3 cm
		Height of product (including packaging):	23 cm

Product texts

Highest light quality for painters and varnishers.

- * Bright light, all the time, even in areas without an electrical connection.
- * Switch with functions
- Light: 100 % - 75 % - 50 % - 25 % - 10 %.
- * Light colour: 5 levels 2700 K to 6500 K with best colour rendering 15CRI 96.
- * On/off switch with memory function for the last used status.
- * USB charging cable A / C.
- * Powerbank function: USB charging port 1 A for devices with USB charging cable such as smartphones, tablets, etc.
- * Integrated lithium-ion battery 7,4 V/5 Ah with power bank function and charging indicator.
- * Casing made of die-cast aluminum, edge protection made of high-quality plastic.
- * Impact-resistant and drop-proof up to 3 m.
- * Stable, multi-stage, folding frame.
- * With a robust matching bag for safe transport.
- * In colourful display-packaging.