

KFXX

Very low drop voltage regulators with inhibit

Datasheet - production data



The KF series are very low drop regulators available in SO-8 and DPAK packages and in a wide range of output voltages.

The very low dropout voltage (0.4 V) and the very low quiescent current make them particularly suitable for low noise, low power applications and especially in battery powered systems.

A shutdown logic control function is available (pin 5, TTL compatible). This means that when the device is used as a local regulator, it is possible to put a part of the board in standby, decreasing the total power consumption. It requires only a 2.2 μ F capacitor for stability allowing space and cost saving.

Features

Very low dropout voltage (0.4 V)

SO-8

 Very low quiescent current (typ. 50 μA in OFF mode, 500 μA in ON mode)

DPAK

- Output current up to 500 mA
- Logic-controlled electronic shutdown
- Output voltages of 2.5; 3.3; 5; 8 V
- Internal current and thermal limit
- Only 2.2 µF for stability
- Available in ± 2 % accuracy at 25 °C
- Supply voltage rejection: 70 db (typ.)
- Temperature range: 40 to 125 °C

Table 1. Device summary

Order	Order codes		
SO-8 (tape and reel)	DPAK (tape and reel)	Output voltages	
KF25BD-TR	KF25BDT-TR	2.5 V	
KF33BD-TR	KF33BDT-TR	3.3 V	
KF50BD-TR	KF50BDT-TR	5 V	
	KF80BDT-TR	8 V	

DocID4337 Rev 13

This is information on a product in full production.


Contents

1	Diagram
2	Pin configuration
3	Maximum ratings
4	Electrical characteristics
5	Typical performance characteristics
6	Package mechanical data 11
7	Packaging mechanical data 17
8	Revision history






1 Diagram







2 Pin configuration





3 Maximum ratings

Symbol	Parameter	Value	Unit
VI	DC input voltage	- 0.5 to 20	V
Ι _Ο	Output current	Internally Limited	
P _{TOT}	Power dissipation	Internally Limited	
T _{STG}	Storage temperature range	- 40 to 150	°C
T _{OP}	Operating junction temperature range	- 40 to 125	°C


Table 2. Absolute maximum ratings

Note: Absolute maximum ratings are those values beyond which damage to the device may occur. Functional operation under these condition is not implied.

Symbol	Parameter	DPAK	SO-8	Unit
R _{thJC}	Thermal resistance junction-case	8	20	°C/W
R _{thJA}	Thermal resistance junction-ambient	100	55	°C/W

Table 3. Thermal data

Figure 3. Test circuit



4 Electrical characteristics

Refer to the test circuits, T_J = 25 °C, C_I = 0.1 $\mu F,$ C_O = 2.2 μF unless otherwise specified.

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
M	Output	I _O = 50 mA, V _I = 4.5 V		2.45	2.5	2.55	V
Vo	Output voltage	$I_0 = 50 \text{ mA}, V_1 = 4.5 \text{ V}, T_a =$	-25 to 85°C	2.4		2.6	v
VI	Operating input voltage	I _O = 500 mA				20	V
Ι _Ο	Output current limit				1		А
ΔV_{O}	Line regulation	$V_{\rm I} = 3.5$ to 20 V, $I_{\rm O} = 5$ mA			2	12	mV
ΔV_{O}	Load regulation	$V_{\rm I} = 3.8$ V, $I_{\rm O} = 5$ to 500 mA			2	50	mV
		$V_{I} = 3.5$ to 20V, $I_{O} = 0$ mA			0.5	1	
I _d	Quiescent current $V_1 = 3.8 \text{ to } 20V, I_0 = 500 \text{mA}$	ON MODE			12	mA	
		V _I = 6 V	OFF MODE		50	100	μA
			f = 120 Hz		82		
SVR	Supply voltage rejection	$I_{O} = 5 \text{ mA}, V_{I} = 4.5 \pm 1 \text{ V}$	f = 1 kHz		77		dB
			f = 10 kHz		60		
eN	Output noise voltage	B = 10 Hz to 100 KHz			50		μV
V	Dranautualtara	I _O = 200 mA			0.2	0.35	V
V _d	Dropout voltage	$I_{O} = 500 \text{ mA}$	I _O = 500 mA		0.4	0.7	V
V_{IL}	Control input logic low	T _a = -40 to 125°C				0.8	V
V _{IH}	Control input logic high	$T_a = -40$ to 125°C		2			V
l _l	Control input current	V _I = 6 V, V _C = 6 V			10		μA
C _O	Output bypass capacitance	ESR = 0.1 to 10 Ω, $I_0 = 0$ to	o 500 mA	2	10		μF

Table 4.	Electrical	characteristics	$(V_0 = 2.5 V)$
10010 11	Liootiioai		(-0) = -0 + 0



Refer to the test circuits, T_J = 25 °C, C_I = 0.1 $\mu F,$ C_O = 2.2 μF unless otherwise specified.

Symbol	Parameter	Test condition	S	Min.	Тур.	Max.	Unit
Vo	Output voltage	$I_{O} = 50 \text{ mA}, V_{I} = 5.3 \text{ V}$		3.234	3.3	3.366	V
۷O	Oulput voltage	$I_0 = 50 \text{ mA}, V_1 = 5.3 \text{ V}, T_a =$	-25 to 85°C	3.168		3.432	v
VI	Operating input voltage	I _O = 500 mA				20	V
Ι _Ο	Output current limit				1		Α
ΔV_{O}	Line regulation	$V_{I} = 4.3$ to 20 V, $I_{O} = 5$ mA			2	12	mV
ΔV_{O}	Load regulation	$V_{I} = 4.6 V, I_{O} = 5 to 500 mA$			2	50	mV
		$V_{I} = 4.3$ to 20V, $I_{O} = 0$ mA	ON MODE		0.5	1	mA
I _d	Quiescent current	$V_{I} = 4.6$ to 20V, $I_{O} = 500$ mA	ONNODE			12	111/4
		V _I = 6 V	OFF MODE		50	100	μA
	SVR Supply voltage rejection $I_0 = 5 \text{ mA}, V_1 = 1$		f = 120 Hz		80		
SVR		$I_{O} = 5 \text{ mA}, V_{I} = 5.3 \pm 1 \text{ V}$	f = 1 kHz		75		dB
			f = 10 kHz		60		
eN	Output noise voltage	B = 10 Hz to 100 KHz	B = 10 Hz to 100 KHz		50		μV
V	Dropout voltogo	I _O = 200 mA			0.2	0.35	v
V _d	Dropout voltage	I _O = 500 mA			0.4	0.7	v
V_{IL}	Control input logic low	$T_a = -40 \text{ to } 125^{\circ}\text{C}$				0.8	V
V _{IH}	Control input logic high	$T_a = -40 \text{ to } 125^{\circ}\text{C}$	$T_{a} = -40$ to 125°C				V
I _I	Control input current	$V_1 = 6 V, V_C = 6 V$			10		μA
Co	Output bypass capacitance	ESR = 0.1 to 10 Ω , I _O = 0 to 500 mA		2	10		μF

Table 5. Electrical characteristics (V_0 = 3.3 V)



Refer to the test circuits, T_J = 25 °C, C_I = 0.1 $\mu F,$ C_O = 2.2 μF unless otherwise specified.

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
V		I _O = 50 mA, V _I = 7 V		4.9	5	5.1	V
Vo	Output voltage	$I_{O} = 50 \text{ mA}, V_{I} = 7 \text{ V}, T_{a} = -25 \text{ to } 85^{\circ}\text{C}$		4.8		5.2	v
VI	Operating input voltage	I _O = 500 mA				20	V
Ι _Ο	Output current limit				1		Α
ΔV_{O}	Line regulation	$V_{I} = 6 \text{ to } 20 \text{ V}, I_{O} = 5 \text{ mA}$			3	18	mV
ΔV_{O}	Load regulation	$V_{\rm I} = 6.3 \text{ V}, I_{\rm O} = 5 \text{ to } 500 \text{ mA}$	L.		2	50	mV
		$V_{I} = 6 \text{ to } 20V, I_{O} = 0mA$	ON MODE		0.5	1	
I _d	Quiescent current	$V_{I} = 6.3$ to 20V, $I_{O} = 500$ mA				12	mA
		V _I = 6 V	OFF MODE		50	100	μA
			f = 120 Hz		76		
SVR	Supply voltage rejection	$I_0 = 5 \text{ mA}, V_1 = 7 \pm 1 \text{ V}$	f = 1 kHz		71		dB
		f = 10 kHz			60		
eN	Output noise voltage	B = 10 Hz to 100 KHz	B = 10 Hz to 100 KHz		50		μV
		I _O = 200 mA			0.2	0.35	
V _d	Dropout voltage	I _O = 500 mA			0.4	0.7	V
V _{IL}	Control input logic low	$T_a = -40 \text{ to } 125^{\circ}\text{C}$				0.8	V
V _{IH}	Control input logic high	T _a = -40 to 125°C		2			V
I	Control input current	$V_{I} = 6 V, V_{C} = 6 V$			10		μA
Co	Output bypass capacitance	ESR = 0.1 to 10 Ω , I _O = 0 to 500 mA		2	10		μF

Table 6. Electrical characteristics (V_0 = 5 V)




Refer to the test circuits, T_J = 25 °C, C_I = 0.1 $\mu\text{F},$ C_O = 2.2 μF unless otherwise specified.

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
M	Output voltogo	I _O = 50 mA, V _I = 10 V		7.84	8	8.16	V
V _O	Output voltage	$I_{O} = 50 \text{ mA}, V_{I} = 10 \text{ V}, T_{a} = -25 \text{ to } 85^{\circ}\text{C}$		7.68		8.32	v
VI	Operating input voltage	I _O = 500 mA				20	V
Ι _Ο	Output current limit				1		A
ΔV_{O}	Line regulation	$V_{I} = 9$ to 20 V, $I_{O} = 5$ mA			4	24	mV
ΔV_{O}	Load regulation	$V_{\rm I} = 9.3 \text{ V}, I_{\rm O} = 5 \text{ to } 500 \text{ mA}$			2	50	mV
		$V_{I} = 9 \text{ to } 20V, I_{O} = 0mA$	ON MODE		0.7	1.5	mA
I _d	Quiescent current	$V_{I} = 9.3$ to 20V, $I_{O} = 500$ mA				12	ШA
		V _I = 9 V	OFF MODE		70	140	μA
		f = 120 Hz		72			
SVR	Supply voltage rejection	$I_0 = 5 \text{ mA}, V_1 = 10 \pm 1 \text{ V}$	f = 1 kHz		67		dB
			f = 10 kHz		60		
eN	Output noise voltage	B = 10 Hz to 100 KHz			50		μV
N/	Dranautwaltana	I _O = 200 mA			0.2	0.35	v
V _d	Dropout voltage	I _O = 500 mA			0.4	0.7	V
V _{IL}	Control input logic low	T _a = -40 to 125°C				0.8	V
V _{IH}	Control input logic high	T _a = -40 to 125°C		2			V
I _I	Control input current	$V_1 = 6 V, V_C = 6 V$			10		μA
Co	Output bypass capacitance	ESR = 0.1 to 10 Ω, $I_0 = 0$ to 500 mA		2	10		μF

Table 7. Electrical characteristics (V_0 = 8 V)




5 Typical performance characteristics



6 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK[®] packages, depending on their level of environmental compliance. ECOPACK[®] specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK[®] is an ST trademark.








Dim.	Min.	Тур.	Max.
A	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
с	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1		5.10	
E	6.40		6.60
E1		4.70	
е		2.28	
e1	4.40		4.60
Н	9.35		10.10
L	1.00		1.50
L1)		2.80	
L2		0.80	
L4	0.60		1.00
R		0.20	
V2	0°		8°


Table 8. DPAK (TO-252) type A mechanical data





a. All dimensions are in millimeters








Table 9. SO-8 mechanical data


Dim.			
Dim.	Min.	Тур.	Max.
А			1.75
A1	0.10		0.25
A2	1.25		
b	0.31		0.51
b1	0.28		0.48
с	0.10		0.25
c1	0.10		0.23
D	4.80	4.90	5.00
E	5.80	6.00	6.20
E1	3.80	3.90	4.00
е		1.27	
h	0.25		0.50
L	0.40		1.27
L1		1.04	
L2		0.25	



Dim.		mm				
Dini.	Min.	Тур.	Max.			
k	0°		8°			
CCC			0.10			

Table 9. SO-8 mechanical data (continued)





b. All dimensions are in millimeters.



7 Packaging mechanical data





Figure 14. Tape for DPAK (TO-252)







Таре				Reel		
Dim.	mm		Dim	mm		
	Min.	Max.	— Dim.	Min.	Max.	
A0	6.8	7	А		330	
B0	10.4	10.6	В	1.5		
B1		12.1	С	12.8	13.2	
D	1.5	1.6	D	20.2		
D1	1.5		G	16.4	18.4	
Е	1.65	1.85	N	50		
F	7.4	7.6	Т		22.4	
K0	2.55	2.75			·	
P0	3.9	4.1		Base qty.	2500	
P1	7.9	8.1		Bulk qty. 2500		
P2	1.9	2.1				
R	40					
Т	0.25	0.35				
W	15.7	16.3				

Table 10. DPAK (TO-252) tape and reel mechanical data








Table 11.	. SO-8 tape	and reel	mechanical data
-----------	-------------	----------	-----------------

Dim.	mm				
	Min.	Тур.	Max.		
А			330		
С	12.8		13.2		
D	20.2				
Ν	60				
Т			22.4		
Ao	8.1		8.5		
Bo	5.5		5.9		
Ko	2.1		2.3		
Po	3.9		4.1		
Р	7.9		8.1		



8 Revision history

Date	Revision	Changes
06-Jun-2007	9	Order codes updated.
14-Dec-2007	10	Modified: Table 1.
21-Feb-2008 11 Modified: <i>Table 1</i> .		Modified: Table 1.
23-Oct-2012	12	Change title description in cover page. Updated: <i>Table 1 on page 1</i> . Added: R _{thJA} value for DPAK and SO-8 <i>Table 3 on page 5</i> . Modified: titles <i>Figure 6</i> and <i>Figure 7 on page 10</i> .
19-Mar-2014	13	The part numbers KF25B, KF33B, KF50B, KF80B changed to KF. Updated Section 6: Package mechanical data and Section 7: Packaging mechanical data. Minor text changes.

Table 12. Document revision history



Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries. Information in this document supersedes and replaces all information previously supplied. The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2014 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan -Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

