

Rotary cam switch GX series, ON-OFF switch 1 pole 16A, for front mounting with black handle, front plate 48X48mm

			Rotary cam
Product designation			switches
Product type designation			GX16
General characteristics			90 - ON/OFF
Switching diagram			switch 1 pole
N° of elements			1
			U - Front
Mounting form			mounting with black handle
Contact characteristics			black Harlaid
Rated insulation voltage Ui			
	IEC/EN	V	690
	UL/CSA	V	600
Rated impulse withstand voltage Uimp		kV	6
Conventional free air thermal current Ith			
	IEC/EN	А	16
	UL/CSA	A	12
Rated operational voltage		V	440
Rated operational impulse voltage		kV	4
Maximum fuse size for short-circuit protection In (gG)			
	10kA	A	16
	15kA	А	16
	25kA	A	16
Rated short time current Icw			
<u> </u>	1s	A	250
Conductivity			10/5 mA/V
Operational current le IEC/EN			
AC1/AC21A			10
		A	16
AC15	4401/	٨	10
	110V	A	10
	220/230V	A	8
	380/400V 660/690V	A	4
Deted energianal neuror in AC	000/090V	A	1.5
Rated operational power in AC			
Three-phase AC3	220/230V	kW	3.5
	220/230V 380/440V	kw	3.5 4.5
	500/690V	kW	4.5 5.5
Single-phase AC3	500/030V	i V V	0.0
Ungle-phase AUS	110V	kW	0.55
	220/230V	kW	1.5
	380/440V	kW	2.2
Three-phase AC23A	000/1101	11.0.0	<u> </u>
	220/230V	kW	3.7
	380/440V	kW	6.5
	500/690V	kW	7.5
Single-phase AC23A			
	110V	kW	0.75
	220/230V	kW	1.8
	380/440V	kW	3

## Rated operational current in DC

GX1690U

GX1690U

GX1690U



Rotary cam switch GX series, ON-OFF switch 1 pole 16A, for front mounting with black handle, front plate 48X48mm


	DC21A	40)/		40
		48V	A	16
		60V	A	16
		110V 220V	A	4
		220V 440V	A A	0.6 0.25
	DC23A (poles in series)	440 V	A	0.25
	DOZSA (poles in selies)	24V	А	16 (1)
		48V	A	16 (2)
		60V	A	16 (3)
		110V	A	10 (3)
		220V	А	7 (4)
	DC13			
		24V	А	16
		48V	А	14
		60V	А	10
		110V	А	1
		220V	А	0.4
		440V	А	0.15
Power dissipation			W	0.6
Mechanical features				
Terminals screw				3M
Tightening torque for te	erminals max		Nm	0.5
Conductor size				
	AWG - Rigid cable			
		min	AWG	20
	AWG - Flexible cable	Max	AWG	12
	AWG - Flexible Cable	min	AWG	20
		Max	AWG	12
	Conductor size (IEC) - Flexible cable	IVICA	ANG	12
		min	mm²	0.5
		Max	mm²	2.5
	Conductor size (IEC) - Rigid cable			
		min	mm²	0.5
		Max	mm²	2.5
Weight			g	96
Mechanical life			cycles	1X10 <sup>6</sup>
UL technical data				
Motor power for direct-	on-line control			
	for three-phase motor			
		120V	HP	1.5
		240V	HP	3
		480V	HP	5
	The shade of the state of the	600V	HP	5
	for single-phase motor	40014		0.75
		120V	HP	0.75
Ambient conditions		240V	HP	1
Temperature				
remperature	Operating temperature			
		min	°C	-25
		max	°C	+55
	Storage temperature	max	<u> </u>	




Rotary cam switch GX series, ON-OFF switch 1 pole 16A, for front mounting with black handle, front plate 48X48mm

	min max	°C ℃	-40 +70
Resistance & Protection			
Frontal IP degree			IP65
Terminals IP degree			IP20
Dimensions			

Dimensions






Drillings for 4 screws fixing (4V version).

GX1690U

Series Dimensions				L Number of elements															
Selles	□A	С	ØD1	ØD2	E	□K	□N	1	2	3	4	5	6	7	8	9	10	11	12
GX16	48	39.5	12	5	26.5	36	6	43	51.5	60	68.5	77	85.5	94	102.5	111	119.5	128	136.5
GX20	48	39.5	12	5	26.5	36	6	43	51.5	60	68.5	77	85.5	94	102.5	111	119.5	128	136.5
GX32	65	53	14	5	34.5	48	7	51	63	75	85	99	111	123	135	147	159	171	183
GX40	65	53	14	5	34.5	48	7	51	63	75	85	99	111	123	135	147	159	171	183

Wiring diagrams



## Certifications and compliance

Compliance

•••••		
	CSA C22.2 n° 14	
	IEC/EN/BS 60947-1	
	IEC/EN/BS 60947-3	
	IEC/EN/BS 60947-5-1	
	IEC/EN/BS 61058-1	
	UL60947-4-1	
Certificates		
	cULus	
	EAC	
ETIM classification		
ETIM 8.0		EC001105 - Off- load switch

GX1690U