
LED integrated monoblock pilot light, steady light Ø22mm Platinum series chromed plastic, yellow,




Product designation				LED integrated monoblock pilot lights steady light
Product type designati	on			LPML
General characteristics	S			
Colour				Yellow
Material				Polyamide
IEC degree of protecti				IP66, IP67 and IP69K on front; IP20 on rear
Electrical characteristic	CS CONTRACTOR CONTRACT			
Rated frequency			Hz	50-60
Supply voltage (AC)			V	230 (-15% +10% Ue)
Operations				
Electrical life			hours	>30000
Mechanical features				
Tightening torque for te	erminals max		Nm	0.8
Terminals screw				Screw termination
Conductor section				
	AWG/kcmil conductor section			
		min		18
		max		16
	IEC			
		max	mm²	2.5
Fixing				Ring fixing Ø22mm
Weight			g	24
UL technical data				
UL degree of protectio	on			Type1, 2, 3R, 4, 4X, 12, 12K on front
Ambient conditions				
Temperature				
	Operating temperature			
		min	°C	-25
		max	°C	+70
Dimensions				

ENERGY AND AUTOMATION

LED integrated monoblock pilot light, steady light Ø22mm Platinum series chromed plastic, yellow,



Wiring diagrams



Certifications and compliance

Compliance

CSA C22.2 n° 14

IEC/EN/BS 60947-1

IEC/EN/BS 60947-5-1

UL508

Certificates

cULus

EAC

ETIM classification

ETIM 8.0

EC000272 -Indicator light complete