


**Features :**







- High performance thermal insulation materials
- Good thermal fatigue performance
- International standard package

**Typical Applications**

- Various rectifiers
- DC supply for PWM inverter

$V_{RSM}$	$V_{RRM}$	Type & Outline
900V	800V	MDx100-08
1100V	1000V	MDx100-10
1300V	1200V	MDx100-12
1500V	1400V	MDx100-14
1700V	1600V	MDx100-16
1900V	1800V	MDx100-18

SYMBOL	CHARACTERISTIC	TEST CONDITIONS	$T_j(^{\circ}C)$	VALUE			UNIT
				Min	Type	Max	
$I_{F(AV)}$	Mean forward current	180° half sine wave 50Hz Single side cooled, $T_C=100^{\circ}C$	150			100	A
$I_{F(RMS)}$	RMS forward current		150			157	A
$I_{RRM}$	Repetitive peak current	at $V_{RRM}$	150			10	mA
$I_{FSM}$	Surge forward current	10ms half sine wave	150			2.60	KA
$I^2t$	$I^2t$ for fusing coordination	$V_R=0.6V_{RRM}$				34	$A^2s*10^3$
$V_{FO}$	Threshold voltage		150			0.80	V
$r_F$	Forward slop resistance					1.74	mΩ
$V_{FM}$	Peak forward voltage	$I_{FM}=300A$	25			1.45	V
$R_{th(j-c)}$	Thermal resistance Junction to case	At 180° sine: Single side cooled per chip				0.350	$^{\circ}C/W$
$R_{th(c-h)}$	Thermal resistance case to heatsink	At 180° sine: Single side cooled per chip				0.2	$^{\circ}C/W$
$V_{iso}$	Isolation voltage	50Hz, R.M.S, t=1min, $I_{iso}:1mA(max)$		2500			V
$F_m$	Terminal connection torque(M5)				4		N·m
	Mounting torque(M6)				6		N·m
$T_{stg}$	Stored temperature			-40		125	$^{\circ}C$
$W_t$	Weight				105		g
<b>Outline</b>	<b>M01H</b>						


**Fig.1**

**Fig.2**

**Fig.3**

**Fig.4**

**Fig.5**

**Fig.6**

Surge Current Vs.Cycles




Fig.7



 $I^2t$  Vs.Time


Fig.8

**Outline:**

**M01H**
