



PRODUCT DESCRIPTION

Tflex™ HD700 combines 5 W/mK thermal conductivity with superior pressure versus deflection characteristics. The combination will allow minimal stress on components while also yielding low thermal resistance. As a result, less mechanical and thermal stresses will be experienced within your device.



Tflex™ HD700 is available in thickness from 0.5mm (0.020”) to 5mm (0.200”). Laird can provide material to meet your production needs in any region through our local production facilities. Please contact your local Laird sales or field engineering contact for samples or questions.

FEATURES AND BENEFITS

- 5.0 W/mK thermal conductivity
- Low pressure versus deflection
- Excellent surface wetting for low contact resistance
- Minimizes board and component stress
- Large tolerance applications
- Environmentally friendly solution that meets regulatory requirements including RoHS and REACH

SPECIFICATIONS

TYPICAL PROPERTIES	VALUE	TEST METHOD
Construction & Composition	Ceramic filled silicone sheet	N/A
Color	Pink (*Option for Grey)	Visual
Thickness Range	0.50mm (0.020”) 5.0mm (0.200”)	N/A
Thickness Tolerance	+/- 10%	N/A
Thermal Conductivity (W/mK)	5.0	ASTM D5470
Density (g/cc)	3.3	Helium Pycnometer
Hardness (Shore 00)	54	ASTM D2240
Outgassing TML (weight %)	0.23	ASTM E595
Outgassing CVCM (weight %)	0.07	ASTM E595
Temperature Range	-50°C to 200°C	Laird Test Method
Rth@ 40 mils, 10 psi	0.287°C-in ² /W	ASTM D5470 (Modified)
Dielectric Constant @ 1 MHz	5.01	ASTM D150
UL Flammability Rating	V-0	UL 94
Volume Resistivity	1.4x 10 ¹⁴ ohm-cm	ASTM D257



AVAILABILITY

STANDARD THICKNESSES

- 0.5mm (0.020") to 5.0mm (0.200") thick material available in 0.25mm (0.010") increments
- Available in standard sheet sizes of 18" x 18" and 9" x 9" or custom die cut parts

OPTIONS

- DC1 – eliminate tack from one side
- Grey Color – Tflex HD700,GR

PART NUMBER SYSTEM

Tflex™ indicates Laird elastomeric thermal gap filler product line. HD7xxx indicates Tflex HD700 product line with thickness in mils (0.001")

EXAMPLES:

- Tflex™ HD740 = 0.040" thick Tflex™ HD700 material
- Tflex™ HD7100,DC1 = 0.10" thick Tflex™ HD700 material with DC1 option
- Tflex™ HD7120,GR = 0.120" thick Tflex™ HD700 material in grey color

A17758-00 Tflex HD700 DS 12-01-2021

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Performance Materials:

[A17536-02](#) [A17536-04](#) [A17653-03](#) [A17653-04](#) [A17653-06](#) [A17653-12](#) [A17690-02](#) [A17690-12](#) [A17689-03](#)
[A17689-06](#) [A17653-02](#) [A17689-04](#) [A17690-06](#) [A17690-08](#) [A17690-05](#) [A17690-04](#) [A17536-06](#)