

## **Type CRGP Series**

**Key Features** 

Small size and light weight


Suitable for both wave and reflow soldering techniques

Supplied on tape

**Pulse Rated** 

7 different package sizes

Terminal finish matte Sn over Ni



TE Connectivity is pleased to introduce this SMD Pulse withstand thick film Chip resistor, suitable for auto placement in volume and for most applications. Available in five different packages and supplied on tape and reel for automatic insertion processes. Standard values – E24 Series

Characteristics – Electrical

| Туре                  | CRGP0402 | CRGP0603 | CRGP0805 | CRGP1206 |
|-----------------------|----------|----------|----------|----------|
| Power Rating @ 70°C   | 0.125W   | 0.25W    | 0.33W    | 0.5W     |
| Max. Working Voltage  | 50V      | 50V      | 150V     | 200V     |
| Max. Overload Voltage | 100V     | 100V     | 300V     | 400V     |
| Dielectric Withstand  | 100V     | 300V     | 500V     | 500V     |
| Temperature Range     |          | -55°C    | ~ +155°C |          |
| Ambient Temperature   |          |          | 70°C     |          |

| Туре                  | CRGP1210       | CRGP2010 | CRGP2512 |  |
|-----------------------|----------------|----------|----------|--|
| Power Rating @ 70°C   | 0.75W          | 1.25W    | 2W       |  |
| Max. Working Voltage  | 200V           | 400V     | 500V     |  |
| Max. Overload Voltage | 500V           | 800V     | 1000V    |  |
| Dielectric Withstand  | 500V           | 500V     | 500V     |  |
| Temperature Range     | -55°C ~ +155°C |          |          |  |
| Ambient Temperature   |                | 70°C     |          |  |


#### 9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change




#### Power derating curve

Power rating based on continuous load operation in ambient temperature of 70°C. For resistors operated in ambient temperatures above 70°C, power rating must be derated in accordance with this curve.



**Dimensions:** 




| Turne    |           | C         | imension (mn | n)        |           |
|----------|-----------|-----------|--------------|-----------|-----------|
| Туре     | L         | W         | Н            | £1        | £2        |
| CRGP0402 | 1.10±0.10 | 0.50±0.05 | 0.35±0.05    | 0.20±0.10 | 0.25±0.10 |
| CRGP0603 | 1.60±0.10 | 0.80±0.10 | 0.45±0.10    | 0.30±0.20 | 0.30±0.20 |
| CRGP0805 | 2.00±0.15 | 1.25+0.15 | 0.55±0.10    | 0.40±0.20 | 0.40±0.20 |
|          |           | -0.10     |              |           |           |
| CRGP1206 | 3.10±0.15 | 1.55+0.15 | 0.55±0.10    | 0.45±0.20 | 0.45±0.20 |
|          |           | -0.10     |              |           |           |
| CRGP1210 | 3.10±0.10 | 2.60±0.20 | 0.55±0.10    | 0.55±0.25 | 0.50±0.20 |
| CRGP2010 | 5.00±0.10 | 2.50±0.20 | 0.55±0.10    | 0.60±0.25 | 0.50±0.20 |
| CRGP2512 | 6.35±0.10 | 3.20±0.20 | 0.55±0.10    | 0.60±0.25 | 0.50±0.20 |

9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



## **Construction:**




## **Power Rating and Resistance Range:**

| Туре     | Power Rating | Tolerance | Resistance | Standard    |
|----------|--------------|-----------|------------|-------------|
|          | @ 70°C       |           | Range      | Series      |
|          |              | ±1%       |            | E24         |
| CRGP0402 | 0.125W       | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP0603 | 0.25W        | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP0805 | 0.33W        | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP1206 | 0.5W         | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP1210 | 0.75W        | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP2010 | 1.25W        | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |
|          |              | ±1%       |            | E24         |
| CRGP2512 | 2W           | ±5%       | 1R0 – 10M  | E96 by      |
|          |              |           |            | negotiation |

## Marking:

E24 series 0603 – 2512 3 Digits – first two digits denote significant figures of resistance and third digit denotes number of zeros thereafter. EG




9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



Marking for E96 Series 0805 – 2512 4 digits – First three digits denote significant figures of resistance and fourth digit denotes number of zeros thereafter. EG.



For ohmic values below 100R letter "R" denotes decimal point. EG

0402 size chips are not marked

0603 E96 3 digit marking.

| Mutiplier Code : |  |
|------------------|--|
|------------------|--|

| 0 1 2 3 4 5 6 7 -1 -2                                      | 0 1 2 3 4 5 6 7 -1 -2 -3   10 | Code       | A  | В  | С  | D  | E  | F      | G   | H        | Х           | Y    | Z  |
|--|--|------------|----|----|----|----|----|--------|-----|----------|-------------|------|----|
|  | 10 10 10 10 10 10 10 10 10 10 10 10  |            | 0  | 1  | 2  | 3  | 4  | 5      | б   | 7        | -1          | -2   | -3 |
| Multiplier 10 10 10 10 10 10 10 10 10 10 10                |  | Multiplier | 10 | 10 | 10 | 10 | 10 | 10     | 10  | 10       | 10          | 10   | 10 |
|  |  | 18<br>18   | 20 | 8  | 8  |    |    |        | 1   | 3        | 6 - Z       |      | 5  |
|  |  |            |    |    |    | 3  |    | 2722 C | 222 | 03136372 | S - 1988-22 | 1222 |    |
| oding Formula Example: $10.2K\Omega = 102 \times 10^{-10}$ | Formula Example : $10.2K\Omega = 102$ X 10 $\Omega$  | (2723)     |    |    |    |    |    |        |     |          |             |      |    |

| Coung    |                 | rormula | Example :       | 10.24 1       | - | 102            | Λ | 10                                  | 77 | 125.45 | 020 |  |
|----------|-----------------|---------|-----------------|---------------|---|----------------|---|-------------------------------------|----|--------|-----|--|
| XX       |                 | x       |                 |               |   | 02             |   | č                                   |    |        |     |  |
|          |                 |         |                 |               |   |                |   | -1                                  |    |        |     |  |
| <u> </u> | Resistance Code | 14      | Multiplier Code | <b>33</b> .2Ω | = | 332<br>↓<br>51 | x | $\stackrel{10}{\downarrow}_{\rm X}$ | Ω  | =      | 51X |  |

| Value | Code |
|-------|------|-------|------|-------|------|-------|------|-------|------|
| 100   | 01   | 162   | 21   | 261   | 41   | 422   | 61   | 681   | 81   |
| 102   | 02   | 165   | 22   | 267   | 42   | 432   | 62   | 698   | 82   |
| 105   | 03   | 169   | 23   | 274   | 43   | 442   | 63   | 715   | 83   |
| 107   | 04   | 174   | 24   | 280   | 44   | 453   | 64   | 732   | 84   |
| 110   | 05   | 178   | 25   | 287   | 45   | 464   | 65   | 750   | 85   |
| 113   | 06   | 182   | 26   | 294   | 46   | 475   | 66   | 768   | 86   |
| 115   | 07   | 187   | 27   | 301   | 47   | 487   | 67   | 787   | 87   |
| 118   | 08   | 191   | 28   | 309   | 48   | 499   | 68   | 806   | 88   |
| 121   | 09   | 196   | 29   | 316   | 49   | 511   | 69   | 825   | 89   |
| 124   | 10   | 200   | 30   | 324   | 50   | 523   | 70   | 845   | 90   |
| 127   | 11   | 205   | 31   | 332   | 51   | 536   | 71   | 866   | 91   |
| 130   | 12   | 210   | 32   | 340   | 52   | 549   | 72   | 887   | 92   |
| 133   | 13   | 215   | 33   | 348   | 53   | 562   | 73   | 909   | 93   |
| 137   | 14   | 221   | 34   | 357   | 54   | 576   | 74   | 931   | 94   |
| 140   | 15   | 226   | 35   | 365   | 55   | 590   | 75   | 953   | 95   |
| 143   | 16   | 232   | 36   | 374   | 56   | 604   | 76   | 976   | 96   |
| 147   | 17   | 237   | 37   | 383   | 57   | 619   | 77   |       |      |
| 150   | 18   | 243   | 38   | 392   | 58   | 634   | 78   |       |      |
| 154   | 19   | 249   | 39   | 402   | 59   | 649   | 79   | I     |      |
| 158   | 20   | 255   | 40   | 412   | 60   | 665   | 80   |       |      |

9-1773463-9 CIS WR 03/2018


Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change




• Marking for E96 series 0603 size with no marking code marked as per E24 values.

#### **Pulse withstand capacity**

The single impulse graph is the result of 50 impulses of rectangular shape applied at one-minute intervals. The limit of acceptance was a shift in resistance of less than 1% from the initial value. The power applied was subject to the restrictions of the maximum permissible impulse voltage graph shown.





9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



## **Performance Specification:**

| Characteristic  | Limits  | Test Methods                                 |
|-----------------|---|--|
| Characteristic  | Linito  | (JIS C 5201-1)                               |
| Temperature     | ±100PPM/°C                                      | Natural resistance change per temp.          |
| Coefficient     | *0402:  | degree centigrade                            |
| coefficient     | 1Ω-10Ω : ± 400 PPM/°C                           | R1-R2  |
|                 | $11\Omega - 100\Omega : \pm 200 \text{ PPM/°C}$ | x10 <sup>6</sup> (PPM/°C)                    |
|                 | $>100\Omega : \pm 100 \text{ PPM/°C}$           | R1(t2-t1)                                    |
|                 | 210022 ± 10011 My C                             | R1 resistance value at room temperature      |
|                 |   | (t1)   |
|                 |   | R2 Resistance value at room temperature      |
|                 |   | +100°C (t2)                                  |
|                 |   | (Sub-clause 4.8)                             |
| Short term      | Resistance change rate is                       | Permanent resistance change after the        |
| overload        | $\pm 5\%$ : $\pm (2.0\% \pm 0.1\Omega)$ Max.    | application of a potential of 2.5 times      |
| oventoad        | $\pm 1\%$ : $\pm (1.0\% \pm 0.1\Omega)$ Max.    | RCWV for 5 seconds                           |
|                 | 11/0 · 1(1.0/0 10.112/ Wax.                     | Sub-clause 4.13                              |
| Terminal        | ± (1.0% ±0.05Ω) Max.                            | Twist of Test Board :                        |
| Bending         | = (1.070 ±0.0032) Widx.                         | Y/X = 5/90 mm for 10 seconds                 |
| Dentanig        |   | (Sub-clause 4.33)                            |
| Insulation      | 1,000MΩ or more                                 | Apply 500V DC between protective coating     |
| Resistance      | 1,0001112 01 11010                              | and termination for 1 min, then measure      |
| neoistance      |   | (Sub-clause 5.6)                             |
| Dielectric      | No evidence of flashover,                       | Apply 500V AC between protective coating     |
| Withstand       | mechanical damage, arcing                       | and termination for 1 minute                 |
| Voltage         | or insulation breakdown.                        | (Sub-clause 4.7)                             |
| Soldering Heat  | Resistance change rate is                       | Dip the resistor into a solder bath having a |
| Soldering field | $\pm(1.0\%+0.05\Omega)$ Max.                    | temperature of 260°C±3°C and hold it for     |
|                 | ±(1.0/0+0.0322) Wax.                            | 10±1 seconds                                 |
|                 |   | (Sub-clause 4.18)                            |
| Solderability   | 95% coverage Min.                               | Test temperature of solder : 245 ± 3 °C      |
| Soluciusiity    | soverage min                                    | Dwell time in solder : 2 ~ 3 seconds         |
|                 |   | (Sub-clause 4.17)                            |
| Solder Temp.    | Electrical characteristics                      | Wave soldering condition: (2 cycles Max.)    |
| Reference       | shall be satisfied without                      | Pre-heat : 100 ~ 120 °C, 30 ± 5 sec.         |
|                 | distinct deformation in                         | Peak temp.: 260 °C                           |
|                 | appearance.                                     | Reflow soldering condition: (2 cycles Max.)  |
|                 | (95% coverage Min.)                             | Pre-heat : 150 ~ 180 °C, 90 ~ 120 sec.       |
|                 | (,  | Suggestion solder temp.: 235 ~ 255 °C, 20 ~  |
|                 |   | 40 sec.                                      |
|                 |   | Peak temp.: 260 °C                           |
|                 |   | (°C) Peak: 260°C (Max)                       |
|                 |   | 250 235°C ~ 255°C                            |
|                 |   | 200  |
|                 |   | 160 °C Pre Heating Zone                      |
|                 |   | 150 150 °C                                   |
|                 |   | 90 ~ 120 sec                                 |
|                 |   | 100 20~40 sec                                |
|                 |   | Soldering Zone                               |
|                 |   | 50 Heating time                              |
|                 |   | Temperature profile for avaluation           |
|                 |   | Hand Soldering 300°C 5 seconds               |
|                 | l   |  |

#### 9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change




## **Performance Specification (continued)**

| Characteristic | Limits                                     | T                                     |                     | , ala                    |  |  |
|----------------|--|---------------------------------------|---------------------|--------------------------|--|--|
| Characteristic | Limits                                     |                                       | Test Metho          |                          |  |  |
|                |  |                                       | (JIS C 5201         | 1                        |  |  |
|                |  |                                       | ance change after   |                          |  |  |
|                |  | cycles                                | for duty specified  | below:                   |  |  |
|                | Resistance change rate is:                 | Step                                  | Temperature         | Time                     |  |  |
| Temperature    | $\pm 5\%$ : $\pm (3\% \pm 0.1\Omega)$ Max. | 1                                     | -55°C±3°C           | 30 mins.                 |  |  |
| Cycling        | $\pm 1\%$ : ±(0.5%±0.1Ω) Max.              | 2                                     | Room Temp.          | 10~15 mins.              |  |  |
|                | ±1%. ±(0.3%±0.122) Wax.                    | 3                                     | +155°C±2°C          | 30 mins.                 |  |  |
|                |  | 4                                     | Room Temp.          | 10~15 mins.              |  |  |
|                |  | (Sub-clause 4.19)                     |                     |                          |  |  |
|                |  | Temp                                  | orary resistance c  | hange after              |  |  |
|                | Desistance change rate is:                 | 240 hours exposure in a humidity test |                     |                          |  |  |
| Humidity       | Resistance change rate is:                 | cham                                  | ber controlled at 4 | 10±2°C and 90-           |  |  |
|                | ± (3.0% + 0.1Ω) Max.                       | 95% r                                 | elative humidity    |                          |  |  |
|                |  | (Sub-clause 4.24)                     |                     |                          |  |  |
| Load Life In   | Resistance change rate is:                 | Resist                                | ance change after   | <sup>-</sup> 1,000 hours |  |  |
| Humidity       | ±5% : ±(3.0% ±0.1Ω) Max.                   | (1.5 h                                | ours "on", 0.5 hoι  | ır "off") at             |  |  |
|                | ±1% : ±(1.0% ±0.1Ω) Max.                   | RCWV                                  | in a humidity cha   | amber                    |  |  |
|                |  | contro                                | olled at 40°C ± 2°C | 2 and 90 to 95           |  |  |
|                |  | % rela                                | itive humidity.     |                          |  |  |
|                |  | (Sub-c                                | clause 4.24.2.1)    |                          |  |  |
| Load Life      | Resistance change rate is:                 | Perma                                 | anent resistance c  | hange after              |  |  |
|                | ±5% : ±(3.0% ±0.1Ω) Max.                   | 1,000                                 | hours operating a   | at RCWV, with            |  |  |
|                | ±1% : ±(1.0% ±0.1Ω) Max.                   | duty o                                | cycle of (1.5 hours | "on", 0.5 hour           |  |  |
|                |  | "off")                                | at 70°C ± 2°C am    | pient                    |  |  |
|                |  | (Sub-c                                | clause 4.25.1       |                          |  |  |

## **Packaging Specification**

Paper taping




| Туре | Α±   | В±   | C ±  | ØD +0.1 | Е±   | F±   | G ± | W ± | Τ±   |
|------|------|------|------|---------|------|------|-----|-----|------|
|      | 0.2  | 0.2  | 0.05 | -0      | 0.1  | 0.05 | 0.1 | 0.2 | 0.1  |
| 0402 | 0.65 | 1.15 | 2.0  | 1.5     | 1.75 | 3.5  | 4.0 | 8.0 | 0.45 |
| 0603 | 1.10 | 1.90 | 2.0  | 1.5     | 1.75 | 3.5  | 4.0 | 8.0 | 0.67 |
| 0805 | 1.65 | 2.40 | 2.0  | 1.5     | 1.75 | 3.5  | 4.0 | 8.0 | 0.81 |
| 1206 | 2.00 | 3.60 | 2.0  | 1.5     | 1.75 | 3.5  | 4.0 | 8.0 | 0.81 |
| 1210 | 2.80 | 3.50 | 2.0  | 1.5     | 1.75 | 3.5  | 4.0 | 8.0 | 0.75 |

#### 9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change




#### **Embossed Taping**




| Туре | А    | В    | С     | ØD   | ØD1  | E    | F     | G    | W    | Τ±  |
|------|------|------|-------|------|------|------|-------|------|------|-----|
|      | ±0.2 | ±0.2 | ±0.05 | +0.1 | +0.1 | ±0.1 | ±0.05 | ±0.1 | ±0.2 | 0.1 |
|      |      |      |       | -0   | -0   |      |       |      |      |     |
| 2010 | 2.90 | 5.60 | 2.0   | 1.5  | 1.5  | 1.75 | 5.5   | 4.0  | 12.0 | 1.0 |
| 2512 | 3.50 | 6.70 | 2.0   | 1.5  | 1.5  | 1.75 | 5.5   | 4.0  | 12.0 | 1.0 |

Peeling strength of cover tape:

Test condition: 0.1 to 0.7 N at a peel off speed of 300mm / min.



Reel Dimensions (mm):



| Туре | Таре     | Reel   | A ± 0.5 | B ± 0.5 | C ± 0.5 | D ± 1 | M ± 2 | W ± 1 |
|------|----------|--------|---------|---------|---------|-------|-------|-------|
|      |          | Qty    |         |         |         |       |       |       |
| 0402 | Paper    | 10,000 | 2       | 13      | 21      | 60    | 178   | 10    |
| 0603 | Paper    | 5,000  | 2       | 13      | 21      | 60    | 178   | 10    |
| 0805 | Paper    | 5,000  | 2       | 13      | 21      | 60    | 178   | 10    |
| 1206 | Paper    | 5,000  | 2       | 13      | 21      | 60    | 178   | 10    |
| 1210 | Paper    | 5,000  | 2       | 13      | 21      | 60    | 178   | 10    |
| 2010 | Embossed | 4,000  | 2       | 13      | 21      | 60    | 178   | 13.8  |
| 2512 | Embossed | 4,000  | 2       | 13      | 21      | 60    | 178   | 13.8  |

9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



#### Label:

- A. TE Product Number
- B. Product Description
- C. Quantity E. RoHS Statement
- D. Lot Number

#### Example:

| TYCO Pn | CRGP0603F68R    |      |      |  |  |  |
|---------|-----------------|------|------|--|--|--|
| DESC    | CRGP 0603       | 68R  | ± 1% |  |  |  |
| QTY     | 5000            | Pcs. | PPM: |  |  |  |
| LOT     | SAMPLE          |      |      |  |  |  |
| RFF     | RoHS 2011/65/EU |      |      |  |  |  |

#### **Environment Related Substance**

This product complies to EU RoHS directive, EU PAHs directive, EU PFOS directive and Halogen free.

#### Ozone layer depleting substances.

Ozone depleting substances are not used in our manufacturing process of this product.

This product is not manufactured using Chloro fluorocarbons (CFCs), Hydrochlorofluorocarbons (HCFCs), Hydrobromofluorocarbons (HBFCs) or other ozone depleting substances in any phase of the manufacturing process.

#### **Storage Condition**

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of  $25^{\circ}C \pm 10^{\circ}C$  and a relative humidity of 60%RH ± 10%RH, chemical and dust free atmosphere

Even within the above guarantee periods, do not store these products in the following conditions otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

1. In salty air or in air with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NO2

2. In direct sunlight

#### 9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change



### **Solder Profile**

Wave soldering condition: (2 cycles Max.)

Pre-heat : 100 ~ 120 °C, 30 ± 5 sec.


Peak temp.: 260 °C

Reflow soldering condition: (2 cycles Max.)

Pre-heat : 150 ~ 180 °C, 90 ~ 120 sec.

Suggestion solder temp.: 235 ~ 255 °C, 20 ~ 40 sec.

Peak temp.: 260 °C



Hand Soldering condition: The Soldering iron tip should be less than 300°C and maximum contact time should be 5 seconds

#### **How To Order**

| CRGP  | 0603   | J                  | 10K   |
|---|--|--------------------|---|
| Common Part   | Size   | Tolerance          | Resistance Value  |
| CRGP – Pulse<br>Withstand Thick<br>Film Chip Resistor | 0402<br>0603<br>0805<br>1206<br>1210<br>2010<br>2512 | F - ±1%<br>J - ±5% | 1 ohm (1Ω) 1R0<br>1K ohm (1000Ω) 1K0<br>100K ohm (100000Ω)<br>100K<br>1M ohm (1000000Ω) 1M0 |

#### 9-1773463-9 CIS WR 03/2018

Dimensions in millimetres unless otherwise specified Dimensions Shown for reference purposes only. Specifications subject to change

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# TE Connectivity:

CRGP1206F68K CRGP0402F5K6 CRGP1206F390R CRGP0805F18K CRGP0402F68K CRGP2512F390R CRGP1210F820R CRGP1206F100R CRGP1206F220K CRGP0603F150K CRGP2010F180R CRGP2512F39R CRGP1206F680R CRGP0603F470R CRGP2010F560R CRGP1210F470R CRGP1206F33R CRGP0402F39K CRGP0402F33R CRGP0402F1K8 CRGP0402F100K CRGP2512F680R CRGP1210F270K CRGP0402F1M0 CRGP0402F1K2 CRGP1206F1K8 CRGP2010F560K CRGP0603F470K CRGP1210F470K CRGP1206F10K CRGP0402F390R CRGP2010F4K7 CRGP2512F470K CRGP2010F10K CRGP0402F560K CRGP2010F82R CRGP1210F15K CRGP1210F220R CRGP2010F1K5 CRGP0603F8K2 CRGP2010F270K CRGP0402F180K CRGP0805F1K8 CRGP2010F27K CRGP1206F56R CRGP2010F5K6 CRGP1210F4K7 CRGP1210F390R CRGP0402F18K CRGP0402F1K0 CRGP1210F560R CRGP0402F3K3 CRGP1210F120K CRGP1206F470R CRGP2512F270K CRGP2010F150R CRGP2512F33R CRGP1206F330K CRGP0603F2K7 CRGP2512F820R CRGP2512F56K CRGP0805F68K CRGP1210F33R CRGP2512F180K CRGP2010F820K CRGP0402F470K CRGP2512F12R CRGP1206F18R CRGP0402F330R CRGP2512F27K CRGP2512F560R CRGP0603F330K CRGP1206F150R CRGP0603F39K CRGP1210F1M0 CRGP0402F15R CRGP0805F15K CRGP0805F33K CRGP1210F68R CRGP0805F390K CRGP0603F33K CRGP2010F220K CRGP1210F1K0 CRGP1206F3K9 CRGP2512F22K CRGP2512F560K CRGP1210F56K CRGP0402F47K CRGP0805F82K CRGP0603F68K CRGP0402F820R CRGP0805F12K CRGP2512F15R CRGP2010F6K8 CRGP0805F10R CRGP0402F82R CRGP1206F47K CRGP0603F3K9 CRGP1206F390K CRGP2010F1K0