# **Full Bridge Rectifier**

Dual 20 V N-Channel with dual 3.2 A Schottky Barrier Diode, 4.0 x 4.0 x 0.5 mm µCool<sup>™</sup> Package

## Features

- Full-Bridge Rectifier Block
- Up to 3.2 A operation
- Low R<sub>DS(on</sub>) MOSFET to minimize conduction loss
- Low gate charge MOSFET
- Low VF Schottky diode
- Ultra Low Inductance Package
- This Device uses Halogen-Free Molding Compound
- These are Pb-Free Devices

## Applications

- Wireless Charging
- AC–DC Rectification
- Optimized for Power Management Applications for Portable Products, such as Cell Phones, PMP, DSC, GPS, and others

		1		,
Parameter		Symbol	Value	Unit
Input voltage between two MOSFET drain		V <sub>LL</sub>	20	V
Bridge Operating Junction and Storage Temperature		T <sub>J</sub> , T <sub>STG</sub>	–55 to 125	°C
Lead Temperature for Solder (1/8" from case for 10 s)	ing Purposes	ΤL	260	°C
Continuous Drain Current	T <sub>A</sub> = 25°C	۱ <sub>0</sub>	2.2	А
R_JA (Note 1)	T <sub>A</sub> = 85°C		1.16	
Power Dissipation	$T_A = 25^{\circ}C$	PD	1.2	W
R_JA (Note 1)	T <sub>A</sub> = 85°C		0.47	
Continuous Drain Current	$T_A = 25^{\circ}C$	Ι <sub>Ο</sub>	3.2	А
R_JA t < 5 s (Note 1)	T <sub>A</sub> = 85°C		1.88	
Power Dissipation	$T_A = 25^{\circ}C$	PD	2.34	W
R_JA t < 5 s (Note 1)	T <sub>A</sub> = 85°C		0.94	
Continuous Drain Current	T <sub>A</sub> = 25°C	Ι <sub>Ο</sub>	1.16	А
R_JA (Note 2)	$T_A = 85^{\circ}C$		0.6	
Power Dissipation	T <sub>A</sub> = 25°C	PD	0.47	W
R_JA (Note 2)	T <sub>A</sub> = 85°C		0.185	

RECTIFIER MAXIMUM RATINGS (T<sub>J</sub> = 25°C unless otherwise stated)

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces).
2. Surface-mounted on FR4 board using the minimum recommended pad size

of 30 mm<sup>2</sup>, 2 oz. Cu.



# **ON Semiconductor®**


## http://onsemi.com

V<sub>(BR)DSS</sub>

#### MOSFET R<sub>DS(on)</sub> TYP


(811)866	56(61)	5			
20 V	23 mΩ @ 4.5 V	3.2 A			
20 V	17 mΩ @ 10 V	5.2 A			
SCHOTTKY DIODE					
V <sub>R</sub> MAX	V <sub>F</sub> TYP	I <sub>F</sub> MAX			

	VFITP	
20 V	0.45 V	3.2 A




## RECTIFIER

4.0 4.0 mm µCool Pin Connections (Top View)



## (\*Note: Microdot may be in either location)

## **PIN CONNECTIONS**



ORDERING INFORMATION							
Device	Package	Shipping <sup>†</sup>					
NMLU1210TWG	UDFN (Pb-Free)	3000 / Tape & Reel					

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## THERMAL RESISTANCE RATINGS

Parameter	Symbol	Мах	Unit
Junction-to-Ambient - Steady State (Note 3)	R <sub>θJA</sub>	82.5	°C/W
Junction-to-Ambient – t $\leq$ 5 s (Note 3)	R <sub>θJA</sub>	42.5	
Junction-to-Ambient - Steady State min Pad (Note 4)	R <sub>θJA</sub>	209	

Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces).
 Surface-mounted on FR4 board using the minimum recommended pad size of 30 mm<sup>2</sup>, 2 oz. Cu.

## BRIDGE ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = $25^{\circ}$ C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
ON CHARACTERISTICS						
Rectifying Forward Voltage (Note 5)	V <sub>fd2</sub>	Input voltage V <sub>LL</sub> = $\pm$ 5 V; The output current of Rectifier I <sub>out</sub> = 2 A		0.45	.56	V
Rectifier leakage current	l <sub>leak</sub>	Input voltage V <sub>LL</sub> = 16 V; No Load on the Rectifier output		31	1000	uA
Rectifier Reverse leakage current	I <sub>rleak</sub>	Input voltage V <sub>LL</sub> = 0 V; The output voltage of the Rectifier V <sub>out</sub> = 5 V		21	1000	uA

5. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%

### MOSFET ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Тур	Max	Unit
ON CHARACTERISTICS	_				_		
Gate Threshold Voltage	V <sub>GS(TH)</sub>	$V_{GS}$ = VDS, I <sub>D</sub> =	250 μΑ	1.2		2.2	V
Negative Threshold Temperature Coefficient	V <sub>GS(TH)</sub> / T <sub>J</sub>				4		mV/°C
Drain-to-Source On Resistance (Note 6)	D	V <sub>GS</sub> = 10 V, I <sub>D</sub> =	= 3.2 A		17	26	mΩ
	R <sub>DS(on)</sub>	$V_{GS}$ = 4.5 V, I <sub>D</sub> =	= 3.2 A		23	32	11152
Forward Transconductance	9 <sub>FS</sub>	VDS = 10 V, I <sub>D</sub> =	= 2.0 A		3.5		S
DRAIN-SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage (Note 6)	V <sub>SD</sub>	$V_{GS}$ = 0 V, I <sub>S</sub> = 2.0 A	$T_J = 25^{\circ}C$		0.79		V

T<sub>J</sub> = 125°C

0.65

6. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%

## SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Maximum Instantaneous Forward	V <sub>F</sub>	I <sub>F</sub> = 1.0 A		0.36		V
Voltage (Note 7)		I <sub>F</sub> = 2.0 A		0.41		
Maximum Instantaneous Reverse Current	Ι <sub>R</sub>	V <sub>R</sub> = 20 V		0.04		mA


7. Pulse Test: pulse width  $\leq$  300  $\mu$ s, duty cycle  $\leq$  2%

### SCHOTTKY DIODE ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 100°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Тур	Max	Unit
Maximum Instantaneous Forward	VF	I <sub>F</sub> = 1.0 A		0.29		V
Voltage (Note 8)	۷F	I <sub>F</sub> = 2.0 A		0.36		
Maximum Instantaneous Reverse Current	I <sub>R</sub>	V <sub>R</sub> = 20 V		4		mA

8. Pulse Test: pulse width  $\leq$  300  $\mu s,$  duty cycle  $\leq$  2%


9. For detailed MOSFET and Diode parameters, please refer to the ON Semiconductor datasheets of NTTFS4930N and MBR230LSFT1G. The test on each individual die is limited to the system package.



GND1 and GND2 are not internally connected. The user should make the connection in the PCB design.


## **TYPICAL PERFORMANCE CURVES**

 $(T_J = 25^{\circ}C \text{ unless otherwise specified})$ 




## **TYPICAL PERFORMANCE CURVES**

(T<sub>J</sub> = 25°C unless otherwise specified)



#### PACKAGE DIMENSIONS



\*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

μCool is a trademark of Semiconductor Components Industries, LLC (SCILLC).

**ON Semiconductor** and **W** are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of SCILLC's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights of others. SCILLC products are not designed, intended, or authorized for use as components insystems intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use publicable copyright have and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

ON Semiconductor Website: www.onsemi.com Order Literature: http://www.onsemi.com/orderlit

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81–3–5817–1050 For additional information, please contact your local Sales Representative