

HG741 Operational Amplifier


General Description

The HG741 series are general purpose operational amplifiers which feature improved performance over industry standards like the HG709. They are direct, plug-in replacements for the 709C, LM201, MC1439 and 748 in most applications. The amplifiers offer many features which make their application nearly foolproof: overload protection on the input and output, no latch-up when the common mode range is exceeded, as well as freedom from oscillations.


Ordering Information

DEVICE	Package Type	MARKING	Packing	Packing Qty
HG741CN	DIP8	HG741	TUBE	2000pcs/Box
HG741ACN	DIP8	HG741A	TUBE	2000pcs/Box
HG741CM/TR	SOP8	HG741	REEL	2500pcs/Reel
HG741ACM/TR	SOP8	HG741A	REEL	2500pcs/Reel
HG741CMM/TR	MSOP8	HG741	REEL	3000pcs/Reel
HG741ACMM/TR	MSOP8	HG741A	REEL	3000pcs/Reel


Connection Diagram



Schematic Diagram



Offset Nulling Circuit



Absolute Maximum Ratings

CONDITION		LIMITS	
Supply Voltage		$\pm 22V$	
Power Dissipation(Note2)		500mW	
Differential Input Voltage		$\pm 30V$	
Input Voltage(Note3)		$\pm 15V$	
Output Short Circuit Duration		Continuous	
Operating Temperature Range		0°C to +70°C	
Junction Temperature	HG741A	150°C	
	HG741	100°C	
Soldering Information	N-Package(10 seconds)	260°C	
	J-or H-Package(10 seconds)	300°C	
M-Package	Vapor Phase(60 seconds)	215°C	
	Infrared(15 seconds)	215°C	
Storage Temperature Range		-65°C to +150°C	
ESD Tolerance(Note7)		400V	

Electrical Characteristics

Parameter	Conditions	HG741A			HG741			Units
		Min	Typ	Max	Min	Typ	Max	
Input Offset Voltage	TA=25°C Rs≤10KΩ					2.0	6.0	mW
	Rs≤50Ω	0.8		3.0				mW
	T _{A MIN} ≤TA≤T _{A MAX} Rs≤50Ω			4.0				mW
	Rs≤10KΩ					7.5		mW
Average Input Offset Voltage Drift				15				μV/°C
Input Offset Voltage Adjustment Range	TA=25°C, Vs=±20V	±10				±15		mV
Input Offset Current	TA=25°C		3.0	30		20	200	nA
	T _{A MIN} ≤TA≤T _{A MAX}			70			300	nA
Average Input Offset Current Drift				0.5				nA/°C
Input Bias Current	TA=25°C T _{A MIN} ≤TA≤T _{A MAX}		30	80 0.210		80	500 0.8	nA μA
Input Resistance	TA=25°C, Vs=±20V	1.0	6.0		0.3	2.0		MΩ
	T _{A MIN} ≤TA≤T _{A MAX} , Vs=±20V	0.5						MΩ
Input Voltage Range	TA=25°C				±12	±13		V
	T _{A MIN} ≤TA≤T _{A MAX}							V

Large Signal Voltage Gain	TA=25°C, RL≥2KΩ Vs=±20V, Vo=±15V Vs=±15V, Vo=±10V	50			20	200		V/mW V/mW
	TA _{MIN} ≤TA≤TA _{MAX} RL≥2KΩ Vs=±20V, Vo=±15V Vs=±15V, Vo=±10V Vs=±5V, Vo=±2V	32			15			V/mW V/mW V/mW
		10						
Output Voltage Swing	Vs=±20V RL≥10KΩ RL≥2KΩ	±16						V V
	Vs=±15V RL≥10KΩ RL≥2KΩ	±15			±12 ±10	±14 ±13		V V
	Output Short Circuit Current	TA=25°C TA _{MIN} ≤TA≤TA _{MAX}	10 10	25 40	35		25	mA mA
	Common-Mode Rejection Ratio	TA _{MIN} ≤TA≤TA _{MAX} Rs≤10KΩ, V _{CM} =±12V Rs≤50Ω, V _{CM} =±12V	80	95	0.5	70	90	dB dB
Supply Voltage Rejection Ratio	TA _{MIN} ≤TA≤TA _{MAX} Vs=±20V to VS=±5V Rs≤50Ω Rs≤10KΩ	86	96			77	96	dB dB
Transient Response Rise Time Overshoot	TA=25°C, Unity Gain		0.25 6.0	0.8 20		0.3 5		μs
Bandwidth(Note5)	TA=25°C	0.43 7	1.5					MHz
Slew Rate	TA=25°C, Unity Gain	0.3	0.7			0.5		V/μs
Supply Current	TA=25°C					1.7	2.8	mA
Power Consumption	TA=25°C Vs=±20V Vs=±15V		80	150		50	85	mw mw

Note1: "Absolute Maximum Ratings" indicate limits beyond which damage to the device may occur. Operating Ratings indicate conditions for which the device is functional, but do not guarantee specific performance limits.

Note 2: For operation at elevated temperatures, these devices must be derated based on thermal resistance, and T_j max. (listed under "Absolute Maximum Ratings"). T_j = T_A + (θ_{JA} P_D).

Thermal Resistance	DIP(B)	SOP-8(M)
θ _{JA} (Junction to Ambient)	100°C/W	195°C/W
θ _{JC} (Junction to Case)	N/A	N/A


Note 3: For supply voltages less than ±15V, the absolute maximum input voltage is equal to the supply voltage.

Note 4: Calculated value from: BW (MHz) = 0.35/Rise Time(μs).

Note 5: Human body model, 1.5 kΩ in series with 100 pF.

Physical Dimensions


DIP-8L



Dimensions In Millimeters(DIP8L)

Symbol:	A	B	D	D1	E	L	L1	a	b	c	d
Min:	6.10	9.00	8.40	7.42	3.10	0.50	3.00	1.50	0.85	0.40	2.54 BSC
Max:	6.68	9.50	9.00	7.82	3.55	0.70	3.60	1.55	0.90	0.50	


SOP-8L 150mil



Dimensions In Millimeters(SOP8L)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	1.35	0.05	4.90	5.80	3.80	0.40	0°	0.35	1.27 BSC
Max:	1.55	0.20	5.10	6.20	4.00	0.80	8°	0.45	

MSOP8



Dimensions In Millimeters(MSOP8L)

Symbol:	A	A1	B	C	C1	D	Q	a	b
Min:	0.80	0.05	2.90	4.75	2.90	0.35	0°	0.25	0.65 BSC
Max:	0.90	0.20	3.10	5.05	3.10	0.75	8°	0.35	

IMPORTANT STATEMENT:

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the consequences of the application of these products in these fields.

Huaguan Semiconductor Co,Ltd. the performance of the semiconductor products produced by the company can reach the performance indicators that can be applied at the time of sales. The use of testing and other quality control technologies is limited to the quality assurance scope of Huaguan semiconductor. Not all parameters of each device need to be tested. The above documents are for reference only, and all are subject to the physical parameters.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.