# 

## **Metal Oxide Varistors**

## **RL4032A Series**

#### Features

- I Electrical equivalents to leaded types
- I SMD plastic package.
- I RoHS-compatible. AECQ101
- I Suitable for lead-free soldering
- I PSpice models available
- I Cylindrical varistor element, encapsulated.
- I Encapsulation: thermoplastic, flame-retardant to UL 94 V-0.
- I Termination: tinned copper alloy, suitable for lead-free wave and reflow soldering, and compatible with tin/lead solder.
- I Operating Temperature: -40°C to +125°C
- I Storage Temperature: -40 °C to +150°C

## Applications


- I Power supplies for telecommunication systems
- I Protection for LED circuits
- I Protection for consumer, industrial equipment
- I Protection for automotive electronics

## Part Number Code



#### APPLICABLE STANDARDS

- I CUL
- I CQC (GB/T10193, GB/T10194, GB4943.1, GB8898)
- I TUV



## **Electrical Characteristics**

Type Number	Varistor Voltage		llowable tage	Max. Energy (10/1000µs)	Volt	amping age 0µs)	Withstanding Surge Current (8/20µs)	•	s&1.2/50μs Ri=2 Ω	Maximum DC Leakage Current	C <sub>typ</sub> (1 kHz, 1 V)
	V <sub>1mA</sub> (V)	V <sub>AC</sub> (V)	V <sub>DC</sub> (V)	(J)	I <sub>P</sub> (A)	V <sub>c</sub> (V)	I(A) @1 Time	ĸv	Times	μA	pF
RL4032A271K	243~297	175	225	30.4	25	455	2500	4	40	20	330
RL4032A471K	423~517	300	385	52.9	25	775	2500	4	40	20	190
RL4032A511K	459~561	320	418	52.9	25	842	2500	4	40	20	180
RL4032A561K	504~616	350	460	52.9	25	920	2500	4	40	20	170

## **General Technical Data**

	Storage Temperature	-10~40°C
Taping Package Storage Condition	Relative Humidity	≦ 75%
	Storage Time	12 Months max

(Do not use this product in corrosive gases or direct sunlight environment preservation)

# **361°**Circuit Protection System

Specifications are subject to change without notice. Please refer to http://www.ruilon.com.cn for current information.







## **Metal Oxide Varistors**

**RL4032A Series** 

# Reliability Test (Note: For CU varistors mounted on PCB by reflow soldering.)

Items	Test Condition/Description	Specification
Varistor voltage	The voltage between two terminals with the specified measuring current applied is called $V_{\rm V}$ (1 mA_{DC} @ 0.2 2 s).	To meet the specified value
Clamping voltage	The maximum voltage between two terminals with the specified standard impulse current (8/20 $\mu s$ ) applied.	To meet the specified value
Endurance at upper Category temperature	1000 h at UCT After having continuously applied the maximum allowable AC voltage at UCT $\pm 2$ °C for 1000 h, the specimen shall be stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V <sub>V</sub> shall be measured.	∆V/ V(1mA)   ≤10 <i>%</i>
Surge current derating,8/20 µs	10 surge currents (8/20 $\mu s$ ), unipolar ,interval 30 s, amplitude corresponding to derating curve for 10 impulses at 20 $\mu s$	│ △V/ V(1mA) │ ≤10 % (measured in direction of surge current) No visible damage
Surge current derating,2 ms	10 surge currents (2 ms), unipolar, interval 120 s, amplitude corresponding to derating curve for 10 impulses at 2 ms	│ △V/ V(1mA) │ ≤10 % (measured in direction of surge current) No visible damage
Climatic sequence	The specimen shall be subjected to:a) dry heat at UCT, 16 h, IEC 60068-2-2, test Ba b) damp heat, 1st cycle: 55 °C, 93% r. H., 24 h, IEC 60068-2-30, test Db. c) cold, LCT, 2 h, IEC 60068-2-1, test Aa. d) damp heat, additional 5 cycles:55 °C/ 25°C, 93% r. H., 24 h/cycle,IEC 60068-2-30, test Db. Then the specimen shall be stored at room temperature and normal humidity for 1 to 2h. Thereafter, the change of $V_V$ shall be measured. Thereafter, insulation resistance $R_{ins}$ shall be measured at V = 500V.	│
Rapid change of temperature	IEC 60068-2-14, test Na, LCT/UCT, dwell time 30 min, 5 cycles	∆V/ V(1mA)   ≤5 <i>%</i> No visible damage
Damp heat, steady state	IEC 60068-2-78, test Ca The specimen shall be subjected to 40 $\pm 2$ °C, 90 to 95% r. H. for 56 days without load / with 10% of the maximum continuous DC operating voltage V <sub>DC</sub> . Then stored at room temperature and normal humidity for 1 to 2 h. Thereafter, the change of V <sub>V</sub> shall be measured. Thereafter, insulation resistance R <sub>ins</sub> shall be measured at V = 500 V (insulated varistors only).	│
Solderability	IEC 60068-2-58, test Td1, method 1 - solder bath, Sn96, 5Ag3Cu0.5 T = 245 $\pm$ 3 °C , t = 2 s	The terminations shall be uniformly tinned for soldering test.
Resistance to soldering heat	IEC 60068-2-58, test Td2, method 1 - solder bath, Sn96, 5Ag3Cu0.5 T = 260 $\pm$ 5 °C , d = 10 $\pm$ 1 s	$   riangle V/ V(1mA)   \le 5\%$ No visible damage
Robustness of	Substrate bending test : IEC 60068-2-21, test Ue1 Deflection = 2 mm , t = 60 s	∆V/ V(1mA)   ≤10 % No visible damage
termination	Shear test: IEC 60068-2-21, test Ue3 Force = 5 N , t = 10 $\pm$ 1 s	∆V/ V(1mA)   ≤10 % No visible damage
Vibration	IEC 60068-2-6, test Fc, method B4: Frequency range: 10 55 Hz , Amplitude: 0.75 mm or 98 m/s <sup>2</sup> , Duration: 6 h (3 · 2 h) Pulse: sine wave After repeatedly applying a single harmonic vibration according to the table above. The change of $V_V$ shall be measured and the specimen shall be visually examined.	│
Bump	IEC 60068-2-27, test Ea: Pulse duration: 6 ms , Max. acceleration: 400 $\mbox{m/s}^2$ Number: 6 x 5000 shocks , Pulse shape: half sine	∆V/ V(1mA)   ≤5 <i>%</i> No visible damage
Fire hazard	IEC 60695-11-5 (needle flame test) Severity: vertical 10 s	5 s max.

# **361°**Circuit Protection

Specifications are subject to change without notice. Please refer to http://www.ruilon.com.cn for current information.






#### Metal Oxide Varistors

**RL4032A Series** 

#### Soldering Parameters - Reflow Soldering (Surface Mount Devices)



#### **Precaution for soldering**

Note that this product will be easily damaged by rapid heating, rapid cooling or local heating.

Do not give heat shock over 100°C in the process of soldering. We recommend to take preheating and gradual cooling

#### Soldering gun procedure


Note the follows, in case of using solder gun for replacement. 1)The tip temperature must be less than 280 for the period within 3 seconds by using soldering gun under 30W


2) The soldering gun tip shall not touch this product directly.

#### Soldering volume

Note that excess of soldering volume will easily get crack the body of this product.

### **Dimensions And Recommended Pad Layout**





Reflow Condition		Pb - Free assembly	
Pre	-Temperature Min (T <sub>s(min)</sub> )	150°C	
Не	-Temperature Max (T <sub>s(max)</sub> )	200°C	
at	- Time (min to max) ( $t_s$ )	60 -180 Seconds	
Average ramp up rate ( Liquids Temp $T_L$ ) to peak		3°C/second max	
T <sub>S(max</sub>	) to TL - Ramp-up Rate	3°C/second max	
Ref	- Temperature (T <sub>⊾</sub> ) (Liquids)	217°C	
low	- Time (min to max) (t <sub>s</sub> )	60 -150 Seconds	
Peak	Temperature (T <sub>P</sub> )	260 +0/-5°C	
	within 5°C of actual peak perature (t <sub>p</sub> )	20 - 40 Seconds	
Ramp-down Rate		6°C/second max	
Time	25°C to peak Temperature	8 minutes Max	
Do not exceed		260°C	

DIM	Millimeters	Inches
Α	3.0±0.3	0.118±0.012
С	8.0±0.3	0.315±0.012
D	5.0±2.0	0.197±0.079
Е	1.5±0.3	$0.059 {\pm} 0.012$
G	10.7±0.5	0.421±0.02
I	3.5	0.138
J	2.8	0.110
к	6.5	0.256
L	2.8	0.110



Specifications are subject to change without notice. Please refer to http://www.ruilon.com.cn for current information.




Revised: 2021-06-07



## Metal Oxide Varistors

## **RL4032A Series**

## **Taping and Reel Specifications**





D'2

W1

Symbol	Millimeters	Inches
w	16.00±0.30	0.630±0.012
E	1.75±0.10	0.069±0.004
F	7.50±0.10	0.295±0.004
D	1.55±0.05	0.061±0.002
D1	Φ1.50±0.10	Ф0.059±0.004
Р	12.00±0.10	0.471±0.004
P0	4.00±0.10	0.157±0.004
P2	2.00±0.10	0.079±0.004

# **Packing Specifications**





**Direction of Unreeling** 

Symbol Millimeters		Inches
D1	380+0/-2.0	14.961+0/-0.079
D2	Ф100.0±3.0	Ф3.937±0.118
W1	16.4±0.2	0.646±0.008

#### **Taping Specifications**

There Shall be the portion having no product in both the head and the end of taping, and there shall be the cover tape in the heat of taping.

Quantity of products in the taping package

SIZE EIA (EIAJ)	4032	
Standard Packing Quantity (PCS/reel)	1500	



Specifications are subject to change without notice. Please refer to http://www.ruilon.com.cn for current information.



