



# 413.1660

## FLUSH-MOUNTING SOCKET

16A 2P+E 4h 100-130V 50Hz 60Hz 70X87MM  
Screw terminals

Product Approvals

TECHDATA		STANDARDS AND LAWS	
Commercial series	OPTIMA Series	EN 60309-1 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Type of product	FLUSH-MOUNTING SOCKET	EN 60309-2 (1999)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Synthetical description	FLUSH-MOUNTING SOCKET		
Rated current	16A	EN 60309-1/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Poles	2P+E	EN 60309-2/A1 (2007)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Hour position	4h		
Rated voltage (range)	50-200V		
Rated voltage	100-130V	EN 60309-1/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 1: General requirements
Working frequency	60Hz	EN 60309-2/A2 (2012)	[European Standard] Plugs, socket-outlets and couplers for industrial purposes. Part 2: Dimensional interchangeability requirements for pin and contact-tube accessories of harmonized configurations
Working frequency	50Hz		
Colour	YELLOW		
Material	THERMOPLASTIC	DIRECTIVE LOW VOLTAGE 2014/35 /UE	[European Directives] Low Voltage Directive
Protection degree	Splash proof		
Protection degree IP	IP44/IP54		
Types of available outlets	ANGLED		
Terminals	Screw terminals		
Flange	70X87MM		