



<b>Form Type</b>	Distribute	<b>Version</b>	2.0	<b>Ref</b>	IPC 1752A	<b>Sectionals</b>	Material Info	<b>Subsectionals</b>	D, A
<b>Supplier Information</b>									
<b>Company Name</b>	TE Connectivity	<b>Request Document ID</b>		<b>Contact Name</b>	David Benfer	<b>Contact Title</b>	Product Compliance Engineer		
<b>Company Unique ID</b>	485203835	<b>Response Date</b>	2014-06-17	<b>Contact Email</b>	dave.benfer@te.com				
<b>Contact Phone Number</b>	717-986-3725								
<b>Legal Statement</b>									
<b>Supplier Acceptance</b>	true								
<b>Legal Statement</b>									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
<b>Product</b>									
<b>Manufacturer Item number</b>	1-111446-6	<b>Amount</b>	4327.257848	<b>Version</b>	-	<b>Identity</b>			
<b>Manufacturer Item Name</b>		<b>Weight Uom</b>	mg	<b>Mfr Site</b>		<b>Authority</b>			
<b>Date</b>		<b>UOM</b>	Each						
<b>EUroHS-0508</b>	Product(s) meets EU RoHS requirement without any exemptions - true								
<b>ChinaRoHS-0508</b>	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products - true								
<b>Product Disclosure</b>									
<b>Sub-Item/Material/Substance</b>	<b>Level</b>	<b>Name</b>	<b>Substance Category</b>	<b>Substance CAS</b>	<b>Substance Concentration</b>	<b>Quantity</b>	<b>Mass per Unit</b>	<b>UOM</b>	<b>Exemption</b>
Sub-Item	1	111906-3				1.0	1745.367	mg	
Material	2	(PBT+PC)-GF30				1.0	1745.367	mg	
Substance	3	Phosphoric acid, zinc salt (2:1)	Supplier	13598-37-3	0.3	1.0	5.2361	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.5	1.0	8.72683	mg	
Substance	3	Acetic acid ethenyl ester, polymer with ethene	Supplier	24937-78-8	2.5	1.0	43.63417	mg	
Substance	3	Paraffin waxes and Hydrocarbon waxes	Supplier	8002-74-2	0.5	1.0	8.72683	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	87.26835	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	0.2	1.0	3.49073	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	0.5	1.0	8.72683	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[phenol], 4-(1-methyl-1-phenylethyl)phenyl ester	Supplier	111211-39-3	25.0	1.0	436.34175	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.1	1.0	1.74537	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.5	1.0	8.72683	mg	

Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	19.1	1.0	333.3651	mg	
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	523.6101	mg	
Substance	3	Silica gel, pptd., cryst.-free	Supplier	112926-00-8	0.4	1.0	6.98147	mg	
Substance	3	2-Propenenitrile, polymer with ethenylbenzene	Supplier	9003-54-7	0.4	1.0	6.98147	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol], bis(2,4,6-tribromophenyl) ester	Brominated Flame Retardants (other than PBBs or PBDEs)	71342-77-3	15.0	1.0	261.80505	mg	
Sub-Item	1	111916-5				16.0	46.161928	mg	
Material	2	Gold Plate				16.0	0.077601	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	16.0	0.0773682	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	16.0	2.328E-4	mg	
Material	2	Phos Bronze				16.0	43.994	mg	
Substance	3	Copper	Supplier	7440-50-8	94.6835	16.0	41.65506	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	16.0	0.0087988	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.01	16.0	0.0043994	mg	
Substance	3	Tin	Supplier	7440-31-5	4.5	16.0	1.97973	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.015	16.0	0.0065991	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	16.0	0.0043994	mg	
Substance	3	Iron	Supplier	7439-89-6	0.1	16.0	0.043994	mg	
Substance	3	Beryllium	Supplier	7440-41-7	0.0010	16.0	4.3994E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	0.3	16.0	0.13198	mg	
Substance	3	Phosphorus	Supplier	7723-14-0	0.1	16.0	0.043994	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	16.0	0.043994	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.01	16.0	0.0043994	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	16.0	0.021997	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.1	16.0	0.043994	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	16.0	2.1997E-4	mg	
Material	2	Nickel Plate				16.0	1.352835	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	16.0	0.00270567	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	16.0	0.00135283	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	16.0	1.34878	mg	
Material	2	Tin Plate				16.0	0.737492	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.0999	16.0	7.3675E-4	mg	
Substance	3	Tin	Supplier	7440-31-5	99.9001	16.0	0.73676	mg	
Sub-Item	1	111909-3				1.0	1843.3	mg	
Material	2	PBT-GF30FR(17)				1.0	1843.3	mg	
Substance	3	Carbonic dichloride, polymer with 4,4-(1-methylethylidene)bis[2,6-dibromophenol] and phenol	Brominated Flame Retardants (other than PBBs or PBDEs)	94334-64-2	30.0	1.0	552.99	mg	
Substance	3	1,4-Benzenedicarboxylic acid, 1,4-dimethyl ester, polymer with 1,4-butanediol	Supplier	30965-26-5	33.0	1.0	608.289	mg	
Substance	3	Furan, tetrahydro-	Supplier	109-99-9	1.0	1.0	18.433	mg	
Substance	3	Carbon black	Supplier	1333-86-4	1.0	1.0	18.433	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	5.0	1.0	92.165	mg	

Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	30.0	1.0	552.99	mg	
-----------	---	----------------------------	----------	------------	------	-----	--------	----	--