

## 344 Series Blown Fuse Indicating Holders for 3AG and 3AB Fuses




344 000 Series


344 400 Series

### Dimensions


#### 344 000 Series



#### Mounting Hole



#### 344 400 Series



### Additional Information



Datasheet



Resources



Samples

### Product Characteristics

Compatible Fuses	3AG, 3AB
<b>Electrical</b>	Rated at 20 amperes at lamp voltage shown below. Dielectric: withstanding voltage exceeds 1500 volts. All fuseholders are supplied with a resistor. When designing indicating type fuseholders into a circuit, consideration should be given to the resistance of fractional amperage fuses and the parallel resistance of the indicator lamp and its resistor
<b>Mounting</b>	Withstands 15 lb.-in. mounting torque. Maximum panel thickness is .250"
<b>Molded Parts</b>	Black Body and knob are thermoset (UL94 V-0), except lens is thermoplastic (UL 94HB). See Table below for lens color
<b>Knob</b>	Bayonet style
<b>Terminals</b>	Copper & copper alloy. Tin plated
<b>Ambient Temperature</b>	-40 °C to +85 °C
<b>Hardware</b>	Neoprene washer, lockwasher & hex nut unassembled. O-ring option available must be ordered separately using part number 901-108

\* Refer to [Fuseology](#) for information on proper fuseholder re-rating

### Agency Approvals

Agency	Agency File Number
	E14721

### Ordering Information

Catalog Number		Voltage Range	Lamp Type Rating	Lamp Current Rear Panel	Lens Color
344 000 Series (Bar Knob)	344 400 Series (Round Knob)				
344 006	344 401	2.5 to 7	6V Incandescent	.20 amp	Amber
344 012	344 402	7 to 16	14V Incandescent	.08 amp	Amber
344 024	344 403	16 to 32	28V Incandescent	.04 amp	Amber
344 125	344 404	100 to 125	Neon	.002 amp	Clear
344 250	344 405	200 to 250	Neon	.002 amp	Clear

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[03440401X](#) [03440405X](#) [03440125H](#) [03440402X](#) [03440024H](#) [03440403X](#) [03440012X](#) [03440250H](#) [03440404X](#)