



VNN7NV04P-E, VNS7NV04P-E


OMNIFET II

fully autoprotected Power MOSFET

Features

| Type | $R_{DS(on)}$ | I_{lim} | V_{clamp} |
|----------------------------|---------------|-----------|-------------|
| VNN7NV04P-E VNS7NV04P-E | 60 m Ω | 6 A | 40 V |

- Linear current limitation
- Thermal shutdown
- Short circuit protection
- Integrated clamp
- Low current drawn from input pin
- Diagnostic feedback through input pin
- ESD protection
- Direct access to the gate of the Power MOSFET (analog driving)
- Compatible with standard Power MOSFET in compliance with the 2002/95/EC European Directive



Description

The VNN7NV04P-E, VNS7NV04P-E, are monolithic devices designed in STMicroelectronics VIPower™ M0-3 Technology, intended for replacement of standard Power MOSFETs from DC up to 50 kHz applications. Built in thermal shutdown, linear current limitation and overvoltage clamp protect the chip in harsh environments.

Fault feedback can be detected by monitoring the voltage at the input pin.

Table 1. Device summary

| Package | Order codes | |
|---------|-------------|---------------|
| | Tube | Tape and reel |
| SOT-223 | - | VNN7NV04PTR-E |
| SO-8 | VNS7NV04P-E | VNS7NV04PTR-E |

Contents

- 1 Block diagram and pin description 5**
- 2 Electrical specifications 6**
 - 2.1 Absolute maximum ratings 6
 - 2.2 Thermal data 7
 - 2.3 Electrical characteristics 7
- 3 Protection features 9**
 - 3.1 Electrical characteristics curves 12
 - 3.2 SO-8 maximum demagnetization energy 16
 - 3.3 SOT-223 maximum demagnetization energy 17
- 4 Package and PCB thermal data 18**
 - 4.1 SO-8 thermal data 18
 - 4.2 SOT-223 thermal data 20
- 5 Package and packing information 23**
 - 5.1 SOT-223 mechanical data 23
 - 5.2 SO-8 mechanical data 24
 - 5.3 SOT-223 packing information 26
 - 5.4 SO-8 packing information 27
- 6 Revision history 28**

List of tables

| | | |
|----------|--------------------------------------|----|
| Table 1. | Device summary | 1 |
| Table 2. | Absolute maximum ratings | 6 |
| Table 3. | Thermal data | 7 |
| Table 4. | Electrical characteristics | 7 |
| Table 5. | SO-8 thermal parameter | 19 |
| Table 6. | SOT-223 thermal parameter | 22 |
| Table 7. | SOT-223 mechanical data | 23 |
| Table 8. | SO-8 mechanical data | 24 |
| Table 9. | Document revision history | 28 |

List of figures

| | | |
|------------|--------------------------------------------------------------------------|----|
| Figure 1. | Block diagram | 5 |
| Figure 2. | Configuration diagram (top view) | 5 |
| Figure 3. | Current and voltage conventions | 6 |
| Figure 4. | Switching time test circuit for resistive load | 10 |
| Figure 5. | Test circuit for diode recovery times | 10 |
| Figure 6. | Unclamped inductive load test circuits | 11 |
| Figure 7. | Input charge test circuit. | 11 |
| Figure 8. | Unclamped inductive waveforms | 11 |
| Figure 9. | Derating curve | 12 |
| Figure 10. | Transconductance | 12 |
| Figure 11. | Static drain-source on resistance vs input voltage (part 1/2) | 12 |
| Figure 12. | Static drain-source on resistance vs input voltage (part 2/2) | 12 |
| Figure 13. | Source-drain diode forward characteristics | 12 |
| Figure 14. | Static drain source on resistance | 12 |
| Figure 15. | Turn-on current slope (part 1/2) | 13 |
| Figure 16. | Turn-on current slope (part 2/2) | 13 |
| Figure 17. | Transfer characteristics | 13 |
| Figure 18. | Static drain-source on resistance vs I_d | 13 |
| Figure 19. | Input voltage vs input charge | 13 |
| Figure 20. | Turn-off drain source voltage slope (part 1/2). | 13 |
| Figure 21. | Turn-off drain source voltage slope (part 2/2). | 14 |
| Figure 22. | Capacitance variations | 14 |
| Figure 23. | Output characteristics | 14 |
| Figure 24. | Normalized on resistance vs temperature | 14 |
| Figure 25. | Switching time resistive load (part 1/2) | 14 |
| Figure 26. | Switching time resistive load (part 2/2) | 14 |
| Figure 27. | Normalized input threshold voltage vs temperature | 15 |
| Figure 28. | Normalized current limit vs junction temperature | 15 |
| Figure 29. | Step response current limit. | 15 |
| Figure 30. | SO-8 maximum turn-off current versus load inductance. | 16 |
| Figure 31. | SO-8 demagnetization | 16 |
| Figure 32. | SOT-223 maximum turn-off current versus load inductance | 17 |
| Figure 33. | SOT-223 demagnetization | 17 |
| Figure 34. | SO-8 PC board | 18 |
| Figure 35. | $R_{thj-amb}$ vs PCB copper area in open box free air condition. | 18 |
| Figure 36. | SO-8 thermal impedance junction ambient single pulse. | 19 |
| Figure 37. | Thermal fitting model of an OMNIFET II in SO-8 | 19 |
| Figure 38. | SOT-223 PC board | 20 |
| Figure 39. | $R_{thj-amb}$ vs PCB copper area in open box free air condition. | 20 |
| Figure 40. | SOT-223 thermal impedance junction ambient single pulse. | 21 |
| Figure 41. | Thermal fitting model of an OMNIFET II in SOT-223 | 21 |
| Figure 42. | SOT-223 package dimensions | 23 |
| Figure 43. | SO-8 package dimensions | 25 |
| Figure 44. | SOT-223 tape and reel shipment (suffix "TR") | 26 |
| Figure 45. | SO-8 tube shipment (no suffix) | 27 |
| Figure 46. | SO-8 tape and reel shipment (suffix "TR") | 27 |

1 Block diagram and pin description

Figure 1. Block diagram






Figure 2. Configuration diagram (top view)



1. For the pins configuration related to SOT-223 see outlines at page 1.

2 Electrical specifications

Figure 3. Current and voltage conventions



2.1 Absolute maximum ratings

Table 2. Absolute maximum ratings

| Symbol | Parameter | Value | | Unit |
|---------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|------|------------------|
| | | SOT-223 | SO-8 | |
| V_{DS} | Drain-source voltage ($V_{IN} = 0\text{ V}$) | Internally clamped | | V |
| V_{IN} | Input voltage | Internally clamped | | V |
| I_{IN} | Input current | +/-20 | | mA |
| $R_{IN\text{ MIN}}$ | Minimum input series impedance | 150 | | Ω |
| I_D | Drain current | Internally limited | | A |
| I_R | Reverse DC output current | -10.5 | | A |
| V_{ESD1} | Electrostatic discharge ($R = 1.5\text{ K}\Omega$, $C = 100\text{ pF}$) | 4000 | | V |
| V_{ESD2} | Electrostatic discharge on output pin only ($R = 330\ \Omega$, $C = 150\text{ pF}$) | 16500 | | V |
| P_{tot} | Total dissipation at $T_c = 25\text{ }^\circ\text{C}$ | 7 | 4.6 | W |
| E_{MAX} | Maximum switching energy ($L = 0.7\text{ mH}$; $R_L = 0\ \Omega$; $V_{bat} = 13.5\text{ V}$; $T_{jstart} = 150\text{ }^\circ\text{C}$; $I_L = 9\text{ A}$) | 40 | | mJ |
| E_{MAX} | Maximum switching energy ($L = 0.6\text{ mH}$; $R_L = 0\ \Omega$; $V_{bat} = 13.5\text{ V}$; $T_{jstart} = 150\text{ }^\circ\text{C}$; $I_L = 9\text{ A}$) | | 37 | mJ |
| T_j | Operating junction temperature | Internally limited | | $^\circ\text{C}$ |
| T_c | Case operating temperature | Internally limited | | $^\circ\text{C}$ |
| T_{stg} | Storage temperature | -55 to 150 | | $^\circ\text{C}$ |

2.2 Thermal data

Table 3. Thermal data

| Symbol | Parameter | Value | | Unit |
|----------------|-----------------------------------------|-------------------|-------------------|------|
| | | SOT-223 | SO-8 | |
| $R_{thj-case}$ | Thermal resistance junction-case max | 18 | | °C/W |
| $R_{thj-lead}$ | Thermal resistance junction-lead max | | 27 | °C/W |
| $R_{thj-amb}$ | Thermal resistance junction-ambient max | 96 ⁽¹⁾ | 90 ⁽¹⁾ | °C/W |

1. When mounted on a standard single-sided FR4 board with 0.5 mm² of Cu (at least 35 µm thick) connected to all DRAIN pins.

2.3 Electrical characteristics

-40 °C < T_j < 150 °C, unless otherwise specified.

Table 4. Electrical characteristics

| Symbol | Parameter | Test conditions | Min | Typ | Max | Unit |
|------------------------------------------------------------------------------|------------------------------------------------------------|-----------------------------------------------------------------|------|-----|------|------|
| Off | | | | | | |
| V_{CLAMP} | Drain-source clamp voltage | $V_{IN} = 0\text{ V}; I_D = 3.5\text{ A}$ | 40 | 45 | 55 | V |
| V_{CLTH} | Drain-source clamp threshold voltage | $V_{IN} = 0\text{ V}; I_D = 2\text{ mA}$ | 36 | | | V |
| V_{INTH} | Input threshold voltage | $V_{DS} = V_{IN}; I_D = 1\text{ mA}$ | 0.5 | | 2.5 | V |
| I_{ISS} | Supply current from input pin | $V_{DS} = 0\text{ V}; V_{IN} = 5\text{ V}$ | | 100 | 150 | µA |
| V_{INCL} | Input-source clamp voltage | $I_{IN} = 1\text{ mA}$ | 6 | 6.8 | 8 | V |
| | | $I_{IN} = -1\text{ mA}$ | -1.0 | | -0.3 | V |
| I_{DSS} | Zero input voltage drain current ($V_{IN} = 0\text{ V}$) | $V_{DS} = 13\text{ V}; V_{IN} = 0\text{ V}; T_j = 25\text{ °C}$ | | | 30 | µA |
| | | $V_{DS} = 25\text{ V}; V_{IN} = 0\text{ V}$ | | | 75 | µA |
| On | | | | | | |
| $R_{DS(on)}$ | Static drain-source on resistance | $V_{IN} = 5\text{ V}; I_D = 3.5\text{ A}; T_j = 25\text{ °C}$ | | | 65 | mΩ |
| | | $V_{IN} = 5\text{ V}; I_D = 3.5\text{ A}$ | | | 130 | mΩ |
| Dynamic ($T_j = 25\text{ °C}$, unless otherwise specified) | | | | | | |
| $g_{fs}^{(1)}$ | Forward transconductance | $V_{DD} = 13\text{ V}; I_D = 3.5\text{ A}$ | | 9 | | S |
| C_{OSS} | Output capacitance | $V_{DS} = 13\text{ V}; f = 1\text{ MHz}; V_{IN} = 0\text{ V}$ | | 220 | | pF |

Table 4. Electrical characteristics (continued)

| Symbol | Parameter | Test conditions | Min | Typ | Max | Unit | |
|---------------------------------------------------------------------------------------------------------|-------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----|------|------|------------------------|---------------|
| Switching ($T_j = 25\text{ °C}$, unless otherwise specified) | | | | | | | |
| $t_{d(on)}$ | Turn-on delay time | $V_{DD} = 15\text{ V}; I_D = 3.5\text{ A};$ $V_{gen} = 5\text{ V}; R_{gen} = R_{IN\text{ MIN}} = 150\text{ }\Omega;$ (see figure Figure 4) | | 100 | 300 | ns | |
| t_r | Rise time | | | 470 | 1500 | ns | |
| $t_{d(off)}$ | Turn-off delay time | | | 500 | 1500 | ns | |
| t_f | Fall time | | | 350 | 1000 | ns | |
| $t_{d(on)}$ | Turn-on delay time | $V_{DD} = 15\text{ V}; I_D = 3.5\text{ A};$ $V_{gen} = 5\text{ V}; R_{gen} = 2.2\text{ K}\Omega;$ (see figure Figure 4) | | 0.75 | 2.3 | μs | |
| t_r | Rise time | | | 4.6 | 14.0 | μs | |
| $t_{d(off)}$ | Turn-off delay time | | | 5.4 | 16.0 | μs | |
| t_f | Fall time | | | 3.6 | 11.0 | μs | |
| $(di/dt)_{on}$ | Turn-on current slope | $V_{DD} = 15\text{ V}; I_D = 3.5\text{ A}; V_{gen} = 5\text{ V};$ $R_{gen} = R_{IN\text{ MIN}} = 150\text{ }\Omega$ | | 6.5 | | $\text{A}/\mu\text{s}$ | |
| Q_i | Total input charge | $V_{DD} = 12\text{ V}; I_D = 3.5\text{ A}; V_{IN} = 5\text{ V};$ $I_{gen} = 2.13\text{ mA}$ (see figure Figure 7) | | 18 | | nC | |
| Source drain diode ($T_j = 25\text{ °C}$, unless otherwise specified) | | | | | | | |
| $V_{SD}^{(1)}$ | Forward on voltage | $I_{SD} = 3.5\text{ A}; V_{IN} = 0\text{ V}$ | | 0.8 | | V | |
| t_{rr} | Reverse recovery time | $I_{SD} = 3.5\text{ A}; di/dt = 20\text{ A}/\mu\text{s};$ $V_{DD} = 30\text{ V}; L = 200\text{ }\mu\text{H};$ (see test circuit, figure Figure 5) | | 220 | | ns | |
| Q_{rr} | Reverse recovery charge | | | | 0.28 | | μC |
| I_{RRM} | Reverse recovery current | | | | 2.5 | | A |
| Protections ($-40\text{ °C} < T_j < 150\text{ °C}$, unless otherwise specified) | | | | | | | |
| I_{lim} | Drain current limit | $V_{IN} = 5\text{ V}; V_{DS} = 13\text{ V}$ | 6 | 9 | 12 | A | |
| t_{dlim} | Step response current limit | $V_{IN} = 5\text{ V}; V_{DS} = 13\text{ V}$ | | 4.0 | | μs | |
| T_{jsh} | Overtemperature shutdown | | 150 | 175 | 200 | $^{\circ}\text{C}$ | |
| T_{jrs} | Overtemperature reset | | 135 | | | $^{\circ}\text{C}$ | |
| I_{gf} | Fault sink current | $V_{IN} = 5\text{ V}; V_{DS} = 13\text{ V}; T_j = T_{jsh}$ | | 15 | | mA | |
| E_{as} | Single pulse avalanche energy | starting $T_j = 25\text{ °C}; V_{DD} = 24\text{ V}; V_{IN} = 5\text{ V};$ $R_{gen} = R_{IN\text{ MIN}} = 150\text{ }\Omega; L = 24\text{ mH};$ (see Figure 6 and Figure 8) | 200 | | | mJ | |

1. Pulsed: Pulse duration = 300 μs , duty cycle 1.5 %

3 Protection features

During normal operation, the input pin is electrically connected to the gate of the internal Power MOSFET through a low impedance path.

The device then behaves like a standard Power MOSFET and can be used as a switch from DC up to 50 kHz. The only difference from the user's standpoint is that a small DC current I_{ISS} (typ. 100 μ A) flows into the input pin in order to supply the internal circuitry.

The device integrates:

- Overvoltage clamp protection: internally set at 45 V, along with the rugged avalanche characteristics of the Power MOSFET stage give this device unrivalled ruggedness and energy handling capability. This feature is mainly important when driving inductive loads.
- Linear current limiter circuit: limits the drain current I_D to I_{lim} whatever the input pin voltages. When the current limiter is active, the device operates in the linear region, so power dissipation may exceed the capability of the heatsink. Both case and junction temperatures increase, and if this phase lasts long enough, junction temperature may reach the overtemperature threshold T_{jsh} .
- Overtemperature and short circuit protection: these are based on sensing the chip temperature and are not dependent on the input voltage. The location of the sensing element on the chip in the power stage area ensures fast, accurate detection of the junction temperature. Overtemperature cutout occurs in the range 150 to 190 °C, a typical value being 170 °C. The device is automatically restarted when the chip temperature falls of about 15 °C below shutdown temperature.
- Status feedback: in the case of an overtemperature fault condition ($T_j > T_{jsh}$), the device tries to sink a diagnostic current I_{gf} through the input pin in order to indicate fault condition. If driven from a low impedance source, this current may be used in order to warn the control circuit of a device shutdown. If the drive impedance is high enough so that the input pin driver is not able to supply the current I_{gf} , the input pin falls to 0 V. This however not affects the device operation: no requirement is put on the current capability of the input pin driver except to be able to supply the normal operation drive current I_{ISS} .

Additional features of this device are ESD protection according to the Human Body model and the ability to be driven from a TTL logic circuit.

Figure 4. Switching time test circuit for resistive load




Figure 5. Test circuit for diode recovery times




Figure 6. Unclamped inductive load test circuits




Figure 7. Input charge test circuit





Figure 8. Unclamped inductive waveforms



3.1 Electrical characteristics curves

Figure 9. Derating curve




Figure 10. Transconductance




Figure 11. Static drain-source on resistance vs input voltage (part 1/2)




Figure 12. Static drain-source on resistance vs input voltage (part 2/2)




Figure 13. Source-drain diode forward characteristics




Figure 14. Static drain source on resistance




Figure 15. Turn-on current slope (part 1/2)




Figure 16. Turn-on current slope (part 2/2)




Figure 17. Transfer characteristics




Figure 18. Static drain-source on resistance vs Id




Figure 19. Input voltage vs input charge




Figure 20. Turn-off drain source voltage slope (part 1/2)




Figure 21. Turn-off drain source voltage slope (part 2/2) **Figure 22. Capacitance variations**





Figure 23. Output characteristics

Figure 24. Normalized on resistance vs temperature





Figure 25. Switching time resistive load (part 1/2)

Figure 26. Switching time resistive load (part 2/2)





Figure 27. Normalized input threshold voltage vs temperature




Figure 28. Normalized current limit vs junction temperature






Figure 29. Step response current limit



3.2 SO-8 maximum demagnetization energy

Figure 30. SO-8 maximum turn-off current versus load inductance



Legend


- A = Single Pulse at $T_{jstart} = 150\text{ }^{\circ}\text{C}$
- B = Repetitive pulse at $T_{jstart} = 100\text{ }^{\circ}\text{C}$
- C = Repetitive Pulse at $T_{jstart} = 125\text{ }^{\circ}\text{C}$

Conditions:

$V_{CC} = 13.5\text{ V}$


Values are generated with $R_L = 0\text{ }\Omega$. In case of repetitive pulses, T_{jstart} (at beginning of each demagnetization) of every pulse must not exceed the temperature specified above for curves B and C.

Figure 31. SO-8 demagnetization



3.3 SOT-223 maximum demagnetization energy

Figure 32. SOT-223 maximum turn-off current versus load inductance



Legend

A = Single Pulse at $T_{Jstart} = 150\text{ }^{\circ}\text{C}$

B = Repetitive pulse at $T_{Jstart} = 100\text{ }^{\circ}\text{C}$


C = Repetitive Pulse at $T_{Jstart} = 125\text{ }^{\circ}\text{C}$

Conditions:

$V_{CC} = 13.5\text{ V}$

Values are generated with $R_L = 0\text{ }\Omega$. In case of repetitive pulses, T_{Jstart} (at beginning of each demagnetization) of every pulse must not exceed the temperature specified above for curves B and C.


Figure 33. SOT-223 demagnetization



4 Package and PCB thermal data

4.1 SO-8 thermal data

Figure 34. SO-8 PC board



Note: Layout condition of R_{th} and Z_{th} measurements (PCB FR4 area = 58 mm x 58 mm, PCB thickness = 2 mm, Cu thickness = 35 μm , Copper areas: 0.14 cm^2 , 0.8 cm^2 , 2 cm^2).

Figure 35. $R_{thj-amb}$ vs PCB copper area in open box free air condition




Figure 36. SO-8 thermal impedance junction ambient single pulse





Figure 37. Thermal fitting model of an OMNIFET II in SO-8



Equation 1 Pulse calculation formula

$$Z_{TH\delta} = R_{TH} \cdot \delta + Z_{THtp}(1 - \delta)$$

where $\delta = t_p/T$

Table 5. SO-8 thermal parameter


| Area/island (cm ²) | Footprint | 2 |
|--------------------------------|-----------|----|
| R1 (°C/W) | 0.2 | |
| R2 (°C/W) | 0.9 | |
| R3 (°C/W) | 3.5 | |
| R4 (°C/W) | 21 | |
| R5 (°C/W) | 16 | |
| R6 (°C/W) | 58 | 28 |
| C1 (W.s/°C) | 3.00E-04 | |

Table 5. SO-8 thermal parameter (continued)

| Area/island (cm ²) | Footprint | 2 |
|--------------------------------|-----------|---|
| C2 (W.s/°C) | 9.00E-04 | |
| C3 (W.s/°C) | 7.50E-03 | |
| C4 (W.s/°C) | 0.045 | |
| C5 (W.s/°C) | 0.35 | |
| C6 (W.s/°C) | 1.05 | 2 |

4.2 SOT-223 thermal data

Figure 38. SOT-223 PC board



Note: Layout condition of R_{th} and Z_{th} measurements (PCB FR4 area = 58 mm x 58 mm, PCB thickness = 2 mm, Cu thickness = 35 μm, Copper areas: 0.11 cm², 1 cm², 2 cm²).

Figure 39. $R_{thj-amb}$ vs PCB copper area in open box free air condition




Figure 40. SOT-223 thermal impedance junction ambient single pulse





Figure 41. Thermal fitting model of an OMNIFET II in SOT-223



Equation 2 Pulse calculation formula

$$Z_{TH\delta} = R_{TH} \cdot \delta + Z_{THtp}(1 - \delta)$$

where $\delta = t_p/T$

Table 6. SOT-223 thermal parameter

| Area/island (cm ²) | Footprint | 2 |
|--------------------------------|-----------|----|
| R1 (°C/W) | 0.2 | |
| R2 (°C/W) | 1.1 | |
| R3 (°C/W) | 4.5 | |
| R4 (°C/W) | 24 | |
| R5 (°C/W) | 0.1 | |
| R6 (°C/W) | 100 | 45 |
| C1 (W.s/°C) | 3.00E-04 | |
| C2 (W.s/°C) | 9.00E-04 | |
| C3 (W.s/°C) | 3.00E-02 | |
| C4 (W.s/°C) | 0.16 | |
| C5 (W.s/°C) | 1000 | |
| C6 (W.s/°C) | 0.5 | 2 |

5 Package and packing information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com.


ECOPACK® is an ST trademark.

5.1 SOT-223 mechanical data

Table 7. SOT-223 mechanical data

| Symbol | millimeters | | |
|--------|-------------|------|------|
| | Min. | Typ. | Max. |
| A | | | 1.8 |
| B | 0.6 | 0.7 | 0.85 |
| B1 | 2.9 | 3 | 3.15 |
| c | 0.24 | 0.26 | 0.35 |
| D | 6.3 | 6.5 | 6.7 |
| e | | 2.3 | |
| e1 | | 4.6 | |
| E | 3.3 | 3.5 | 3.7 |
| H | 6.7 | 7 | 7.3 |
| V | 10 (max) | | |
| A1 | 0.02 | | 0.1 |

Figure 42. SOT-223 package dimensions




5.2 SO-8 mechanical data

Table 8. SO-8 mechanical data


| Dim. | mm | | |
|------|-----------|------|------|
| | Min. | Typ. | Max. |
| A | | | 1.75 |
| a1 | 0.1 | | 0.25 |
| a2 | | | 1.65 |
| a3 | 0.65 | | 0.85 |
| b | 0.35 | | 0.48 |
| b1 | 0.19 | | 0.25 |
| C | 0.25 | | 0.5 |
| c1 | 45 (typ.) | | |
| D | 4.8 | | 5 |
| E | 5.8 | | 6.2 |
| e | | 1.27 | |
| e3 | | 3.81 | |
| F | 3.8 | | 4 |
| L | 0.4 | | 1.27 |
| M | | | 0.6 |
| S | 8 (max.) | | |
| L1 | 0.8 | | 1.2 |

Figure 43. SO-8 package dimensions



5.3 SOT-223 packing information

Figure 44. SOT-223 tape and reel shipment (suffix “TR”)



5.4 SO-8 packing information

Figure 45. SO-8 tube shipment (no suffix)





Figure 46. SO-8 tape and reel shipment (suffix "TR")



6 Revision history

Table 9. Document revision history

| Date | Revision | Changes |
|-------------|----------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 15-Oct-2009 | 1 | Initial release. |
| 26-Oct-2009 | 2 | Updated Figure 43: SO-8 package dimensions . Updated Table 8: SO-8 mechanical data . |
| 05-Jul-2011 | 3 | Table 4: Electrical characteristics : – $R_{DS(on)}$: updated maximum values – $t_{d(on)}$, t_r , $t_{d(off)}$, t_f : updated min, typ and max values |
| 18-Sep-2013 | 4 | Updated Disclaimer. |

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

ST PRODUCTS ARE NOT DESIGNED OR AUTHORIZED FOR USE IN: (A) SAFETY CRITICAL APPLICATIONS SUCH AS LIFE SUPPORTING, ACTIVE IMPLANTED DEVICES OR SYSTEMS WITH PRODUCT FUNCTIONAL SAFETY REQUIREMENTS; (B) AERONAUTIC APPLICATIONS; (C) AUTOMOTIVE APPLICATIONS OR ENVIRONMENTS, AND/OR (D) AEROSPACE APPLICATIONS OR ENVIRONMENTS. WHERE ST PRODUCTS ARE NOT DESIGNED FOR SUCH USE, THE PURCHASER SHALL USE PRODUCTS AT PURCHASER'S SOLE RISK, EVEN IF ST HAS BEEN INFORMED IN WRITING OF SUCH USAGE, UNLESS A PRODUCT IS EXPRESSLY DESIGNATED BY ST AS BEING INTENDED FOR "AUTOMOTIVE, AUTOMOTIVE SAFETY OR MEDICAL" INDUSTRY DOMAINS ACCORDING TO ST PRODUCT DESIGN SPECIFICATIONS. PRODUCTS FORMALLY ESCC, QML OR JAN QUALIFIED ARE DEEMED SUITABLE FOR USE IN AEROSPACE BY THE CORRESPONDING GOVERNMENTAL AGENCY.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2013 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[VNN7NV04PTR-E](#) [VNS7NV04PTR-E](#)