


Datasheet

Snubberless™, logic level and standard 16 A Triacs



Features

- · Medium current Triac
- · Low thermal resistance with clip bonding
- · Low thermal resistance insulation ceramic for insulated BTA
- High commutation (4Q) or very high commutation (3Q, Snubberless™) capability
- BTA series UL1557 certified (file ref: 81734)
- Packages are RoHS (2002/95/EC) compliant
- Insulated tab (BTA series, rated at 2500 V_{RMS})

Applications

- Snubberless versions (BTA/BTB...W and T1635) especially recommended for use on inductive loads, because of their high commutation performances
- On/off or phase angle function in applications such as static relays, light dimmers and appliance motor speed controllers

Description

lectronics sales office

Available either in through-hole or surface mount packages, the BTA16, BTB16 and T1610, T1635 and T1650 Triac series are suitable for general purpose mains power AC switching. They can be used as ON/OFF function in applications such as static relays, heating regulation or induction motor starting circuit. They are also recommended for phase control operations in light dimmers and appliance motors speed controllers.

The Snubberless™ versions (W suffix and T1610, T1635, T1650) are especially recommended for use on inductive loads, because of their high commutation performance.

By using an internal ceramic pad, the Snubberless™ series provide an insulated tab (rated at 2500 V_{RMS}) complying with UL standards (file reference: E81734).

Product status link					
BTA16					
BTB16					
T1610					
T1635					
T1650					

Product summary						
I _{T(RMS)} 16 A						
V _{DRM} /V _{RRM}	600, 800 V					
I _{GT} Snubberless™	10, 35, 50 mA					
I _{GT} standard	25, 50 mA					



1 Characteristics

Table 1. Absolute maximum ratings

Symbol	Parameters	Value	Unit		
1	DMC on state surrent (full sine verse)	TO-220AB, D ² PAK	T _c = 100 °C	40	
I _{T(RMS)}	RMS on-state current (full sine wave)	TO-220AB Ins.	T _c = 86 °C	16	Α
l	Non repetitive surge peak on-state current (full cycle,	F = 50 Hz	t _p = 20 ms	160	A
I _{TSM}	T _j initial = 25 °C)	F = 60 Hz	t _p = 16.7 ms	168	
I ² t	I ² t value for fusing	144	A ² s		
dl/dt	Critical rate of rise of on-state current $I_G = 2 \times I_{GT}$, $t_r \le 100 \text{ ns}$	F = 120 Hz	T _j = 125 °C	50	A/µs
V _{DSM} /V _{RSM}	Non repetitive surge peak off-state voltage $t_p = 10 \text{ ms}$ $T_j = 25 \text{ °C}$				V
I _{GM}	Peak gate current	4	Α		
P _{G(AV)}	Average gate power dissipation	1	W		
T _{stg}	Storage junction temperature range	-40 to +150	°C		
Tj	Operating junction temperature range	-40 to +125	°C		

Table 2. Static electrical characteristics

Symbol	Test conditions	Tj		Value	Unit
V _T ⁽¹⁾	$I_{TM} = 22.5 \text{ A}, t_p = 380 \ \mu\text{s}$	25 °C	Max.	1.55	V
V _{TO} ⁽¹⁾	threshold on-state voltage	125 °C	Max.	0.85	V
R _D ⁽¹⁾	Dynamic resistance	125 °C	Max.	25	mΩ
I _{DRM} /I _{RRM}	$V_{DRM} = V_{RRM}$	25 °C	Max.	5	μA
'DRM' 'RRM		125 °C		2	mA

^{1.} For both polarities of A2 referenced to A1

Table 3. Electrical characteristics (T_j = 25 °C, unless otherwise specified) - standard (4 quadrants)

Symbol	Parameters	Quadrant		BT/ BTI	Unit	
				С	В]
I _{GT} ⁽¹⁾		1 - 11 - 111	Max.	25	50	mA
'GT'	$V_D = 12 \text{ V}, R_L = 33 \Omega$	IV	IVIAX.	50	100	IIIA
V _{GT}		All	Max.	1	.3	V
V _{GD}	$V_D = V_{DRM}, R_L = 3.3 \text{ k}\Omega, T_j = 125 \text{ °C}$	All	Min.	0	.2	V
IH ⁽²⁾	I _T = 500 mA		Max.	25	50	mA
IL	I _G = 1.2 I _{GT}	I - III - IV	Max.	40	60	m 1
		Ш	Max.	80	120	mA

DS2114 - Rev 11 page 2/18



Symbol	Parameters	Quadrant		BTA16 BTB16		Unit
				С	В	
dV/dt ⁽²⁾	V _D = 67 % V _{DRM} gate open, T _j = 125 °C			200	400	V/µs
(dV/dt)c ⁽²⁾	(dl/dt)c = 7 A/ms, T _j = 125 °C			5	10	V/µs

^{1.} Minimum I_{GT} is guaranteed at 5 % of I_{GT} max.

Table 4. Electrical characteristics (T_j = 25 °C, unless otherwise specified) - Snubberless and logic level (3 quadrants)

Symbol	Parameters	Quadrant		T1610 / BTA16- SW / BTB16- SW	T1635 / BTA16-CW / BTB16-CW	T1650 / BTA16-BW / BTB16-BW	Unit
I _{GT} ⁽¹⁾	$V_D = 12 \text{ V, R}_1 = 30 \Omega$		Max.	10	35	50	mA
V _{GT}	VD = 12 V, IVL = 50 32	1 - 11 - 111	Max.		1.3		V
V_{GD}	$V_D = V_{DRM}, R_L = 3.3 \text{ k}\Omega, T_j = 125 \text{ °C}$		Min.		0.2		V
IH ⁽²⁾	I _T = 500 mA			15	35	50	mA
I _I	I _I I _G = 1.2 I _{GT}		Max.	25	50	70	mA
'L	IG - 1.2 IG	II	Max.	30	60	80	IIIA
(dV/dt) ⁽²⁾	$VD = 67 \% V_{DRM}$ gate open, $T_j = 125$	°C	Min.	40	500	1000	V/µs
	(dV/dt)c = 0.1 V/µs, T _j = 125 °C			8.5			
(dl/dt)c(2)	(dV/dt)c = 10 V/µs, T _j = 125 °C		Min.	3.0			A/ms
	Without snubber, T _j = 125 °C				8.5	14	

^{1.} Minimum I_{GT} is guaranteed at 5 % of I_{GT} max.

Table 5. Thermal resistance

Symbol	Paramete	Value	Unit	
Page 3	TO-220AB / D²PAK Max. junction to case (AC)		1.2	
R _{th(j-c)}	TO-220AB insulated		2.1	°C/W
D.,	Junction to ambient (S = 2 cm²)	D²PAK	45	C/VV
R _{th(j-a)}	Junction to ambient	TO-220AB / TO-220AB ins	60	

1. Copper surface under tab.

DS2114 - Rev 11 page 3/18

^{2.} For both polarities of A2 referenced to A1

^{2.} For both polarities of A2 referenced to A1




Characteristics (curves) 1.1

Figure 2. Maximum power dissipation versus on-state RMS current (full cycle) P(W) 20 18 16

Figure 3. RMS on-state current versus case temperature (full cycle) I_{T(RMS)}(A) 18 16 -BTB/T16-14 - BŤA 12 10 8 6 4 2 T_C(°C) 0 50 25 75 125 0 100

14 12 10 I_{T(RMS)}(A) 10 12 14

Figure 4. On-state rms current versus ambient temperature (full cycle) I_{T(RMS)}(A) 4.0 3.5 D²PAK (S = 1 cm²) Printed circuit board FR4, copper thickness: 35 um 3.0 2.5 2.0 1.5 1.0 0.5 T_C(°C) 0.0 25 50 75 100 125 0



page 4/18



Figure 6. On-state characteristics (maximum values)




Figure 7. Surge peak on-state current versus number of cycles




Figure 8. Non-repetitive surge peak on-state current for a sinusoidal




Figure 9. Relative variation of gate trigger current




Figure 10. Relative variation of critical rate of decrease of main current versus (dV/dt)c (typical values)






Figure 11. Relative variation of critical rate of decrease of main current versus (junction temperature (typical values)



DS2114 - Rev 11 page 5/18





DS2114 - Rev 11 page 6/18



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

DS2114 - Rev 11 page 7/18




2.1 TO-220AB Insulated and non Insulated package information

Epoxy meets UL 94,V0

Cooling method: by conduction (C)
 Recommended torque value: 0.55 N·m

Maximum torque value: 0.70 N⋅m

Figure 13. TO-220AB Insulated and non Insulated package outline



(1)Resin gate position accepted in one of the two positions or in the symmetrical opposites.

DS2114 - Rev 11 page 8/18



Table 6. TO-220ABInsulated and non Insulated package mechanical data

			Di	mensions		
Ref.	Millimeters				Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	15.20		15.90	0.5984		0.6260
a1		3.75			0.1476	
a2	13.00		14.00	0.5118		0.5512
В	10.00		10.40	0.3937		0.4094
b1	0.61		0.88	0.0240		0.0346
b2	1.23		1.32	0.0484		0.0520
С	4.40		4.60	0.1732		0.1811
c1	0.49		0.70	0.0193		0.0276
c2	2.40		2.72	0.0945		0.1071
е	2.40		2.70	0.0945		0.1063
F	6.20		6.60	0.2441		0.2598
I	3.73		3.88	0.1469		0.1528
L	2.65		2.95	0.1043		0.1161
12	1.14		1.70	0.0449		0.0669
13	1.14		1.70	0.0449		0.0669
14	15.80	16.40	16.80	0.6220	0.6457	0.6614
M		2.6			0.1024	


^{1.} Inch dimensions are for reference only.

DS2114 - Rev 11 page 9/18



2.2 D²PAK package information

Figure 14. D²PAK package outline



(1) Resin gate position accepted in one of the two positions or in the symmetrical opposites

DS2114 - Rev 11 page 10/18



Table 7. D²PAK package mechanical data


	Dimensions						
Ref.		Millimeters			Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	4.30		4.60	0.1693		0.1811	
A1	2.49		2.69	0.0980		0.1059	
A2	0.03		0.23	0.0012		0.0091	
А3		0.25			0.0098		
b	0.70		0.93	0.0276		0.0366	
b2	1.25		1.7	0.0492		0.0669	
С	0.45		0.60	0.0177		0.0236	
c2	1.21		1.36	0.0476		0.0535	
D	8.95		9.35	0.3524		0.3681	
D1	7.50		8.00	0.2953		0.3150	
D2	1.30		1.70	0.0512		0.0669	
е	2.54			0.1			
Е	10.00		10.28	0.3937		0.4047	
E1	8.30		8.70	0.3268		0.3425	
E2	6.85		7.25	0.2697		0.2854	
G	4.88		5.28	0.1921		0.2079	
Н	15		15.85	0.5906		0.6240	
L	1.78		2.28	0.0701		0.0898	
L2	1.27		1.40	0.0500		0.0551	
L3	1.40		1.75	0.0551		0.0689	
R		0.40			0.0157		
V2	0°		8°	0°		8°	

^{1.} Dimensions in inches are given for reference only

DS2114 - Rev 11 page 11/18



Figure 15. D²PAK recommended footprint (dimensions are in mm)




DS2114 - Rev 11 page 12/18



3 Ordering information


Figure 16. Ordering information scheme (BTA16 and BTB16 series)



DS2114 - Rev 11 page 13/18



Figure 17. Ordering information scheme (T8 series)



Downloaded from Arrow.com.

page 14/18



3.1 Product selector

Table 8. Product selector

Part N	umber	Sensitivity	Type	Backago
600	800	- Sensitivity	Type	Package
BTB16-600C		35 mA	Standard	TO-220AB
BTB16-600B	BTB16-800B	50 mA	Standard	TO-220AB
BTB16-600SW	BTB16-800SW	10 mA	Snubberless™	TO-220AB
BTB16-600CW	BTB16-800CW	35 mA	Snubberless™	TO-220AB
BTB16-600BW	BTB16-800BW	50 mA	Snubberless™	TO-220AB
BTA16-600C		35 mA	Standard	TO-220AB Ins.
BTA16-600B	BTA16-800B	50 mA	Standard	TO-220AB Ins.
BTA16-600SW	BTA16-800SW	10 mA	Snubberless™	TO-220AB Ins.
BTA16-600CW	BTA16-800CW	35 mA	Snubberless™	TO-220AB Ins.
BTA16-600BW	BTA16-800BW	50 mA	Snubberless™	TO-220AB Ins.
T1610-600G	T1610-800G	10 mA	Snubberless™	D ² PAK
T1635-600G	T1635-800G	35 mA	Snubberless™	D ² PAK
T1650-600G		50 mA	Snubberless™	D ² PAK



3.2 Ordering information

Table 9. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode	
BTA16-600BRG	BTA16-600B					
BTA16-600BWRG	BTA16-600BW					
BTA16-600CRG	BTA16-600C					
BTA16-600CWRG	BTA16-600CW					
BTA16-600SWRG	BTA16-600SW	TO-220AB Ins.			Tube	
BTA16-800BRG	BTA16-800B					
BTA16-800BWRG	BTA16-800BW					
BTA16-800CWRG	BTA16-800CW					
BTA16-800SWRG	BTA16-800SW		2.30	50	50	
BTB16-600BRG	BTB16-600B		2.50 50			
BTB16-600BWRG	BTB16-600BW					
BTB16-600CRG	BTB16-600C					
BTB16-600CWRG	BTB16-600CW					
BTB16-600SWRG	BTB16-600SW	TO-220AB	Т		Tube	
BTB16-800BRG	BTB16-800B					
BTB16-800BWRG	BTB16-800BW					
BTB16-800CWRG	BTB16-800CW					
BTB16-800SWRG	BTB16-800SW	-				
T1610-600G-TR	T1610-600G					
T1610-800G-TR	T1610-800G					
T1635-600G-TR	T1635-600G	D²PAK	1.50	1000	Tape and reel	
T1635-800G-TR	T1635-800G	D-PAK				
T1650-600G-TR	T1650-600G					
T1635-600G	T1635-600G			50	Tube	

DS2114 - Rev 11 page 16/18



Revision history

Table 10. Document revision history

Date	Revision	Changes
Oct-2002	6A	Last update.
13-Feb-2006	7	TO-220AB delivery mode changed from bulk to tube. ECOPACK statement added.
03-Jul-2009	8	Added part number T1610.
04-Dec-2009	9	Updated value for V_{DSM} / V_{RSM} in Table 2. Updated temperature in Table 2 from 15 $^{\circ}C$ to 86 $^{\circ}C.$
11-Mar-2010	10	Updated value for V_{DSM} / V_{RSM} in Table 2. Updated temperature in Table 2 from 15 $^{\circ}C$ to 86 $^{\circ}C.$
30-May-2018	11	Updated Section • Product status / summary. Added T1650 package information.

DS2114 - Rev 11 page 17/18



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics - All rights reserved

DS2114 - Rev 11 page 18/18