

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD






C

REVISED (ECR-13-003844)

04JUN13

JL

WK



NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC(LCP),
UL 94V-0, COLOR: NATURE.
ACTUATOR: THERMOPLASTIC, UL 94 V-0,
COLOR: IVORY.
HOLD DOWN: PHOSPHOR BRONZE.
CONTACT: PHOSPHOR BRONZE.
- FINISH:
CONTACT: GOLD FLASH OVER ALL,
50u" MIN. NICKEL UNDERPLATED ALL OVER.
HOLD DOWN: 100u" MIN. BRIGHT TIN PLATING OVER,
50u" MIN. NICKEL UNDERPLATED ALL OVER.
WITHOUT AMP LOGO FOR 12 POSITION UNDER

24.50	25.60	30.43	50	5-1734592-0
24.00	25.10	29.93	49	4-1734592-9
23.50	24.60	29.43	48	4-1734592-8
23.00	24.10	28.93	47	4-1734592-7
22.50	23.60	28.43	46	4-1734592-6
22.00	23.10	27.63	45	4-1734592-5
21.50	22.60	27.43	44	4-1734592-4
21.00	22.10	26.93	43	4-1734592-3
20.50	21.60	26.43	42	4-1734592-2
20.00	21.10	25.93	41	4-1734592-1
19.50	20.60	25.43	40	4-1734592-0
19.00	20.10	24.93	39	3-1734592-9
18.50	19.60	24.43	38	3-1734592-8
18.00	19.10	23.93	37	3-1734592-7
17.50	18.60	23.43	36	3-1734592-6
17.00	18.10	22.93	35	3-1734592-5
16.50	17.60	22.43	34	3-1734592-4
16.00	17.10	21.93	33	3-1734592-3
15.50	16.60	21.43	32	3-1734592-2
15.00	16.10	20.93	31	3-1734592-1
14.50	15.60	20.43	30	3-1734592-0
14.00	15.10	19.93	29	2-1734592-9
13.50	14.60	19.43	28	2-1734592-8
13.00	14.10	18.93	27	2-1734592-7
12.50	13.60	18.43	26	2-1734592-6
12.00	13.10	17.93	25	2-1734592-5
11.50	12.60	17.43	24	2-1734592-4
11.00	12.10	16.93	23	2-1734592-3
10.50	11.60	16.43	22	2-1734592-2
10.00	11.10	15.93	21	2-1734592-1
9.50	10.60	15.43	20	2-1734592-0
9.00	10.10	14.93	19	1-1734592-9
8.50	9.60	14.43	18	1-1734592-8
8.00	9.10	13.93	17	1-1734592-7
7.50	8.60	13.43	16	1-1734592-6
7.00	8.10	12.93	15	1-1734592-5
6.50	7.60	12.43	14	1-1734592-4
6.00	7.10	11.93	13	1-1734592-3
5.50	6.60	11.43	12	1-1734592-2
5.00	6.10	10.93	11	1-1734592-1
4.50	5.60	10.43	10	1-1734592-0
4.00	5.10	9.93	09	0-1734592-9
3.50	4.60	9.43	08	0-1734592-8
3.00	4.10	8.93	07	0-1734592-7
2.50	3.60	8.43	06	0-1734592-6
2.00	3.10	7.93	05	0-1734592-5
C	B	A	POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. LAI 15APR2009

CHK S. CHIEN

15APR2009

APVD W. KODAMA 15APR2009

PRODUCT SPEC

108-57523

QUALIFICATION TEST REPORT

501-57598

WEIGHT - GRAMS

CUSTOMER DRAWING

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.35
2 PLC	± 0.25
3 PLC	± -
4 PLC	± -
ANGLES	± 3°

MATERIAL

SEE NOTE

FINISH

SEE NOTE

STE

TE Connectivity

NAME

FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT, SMT TYPE.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734592

SCALE


SHEET

1 OF 3

REV


C

P	LTR	DESCRIPTION	DATE	DWN	APV
		SEE SHEET 1.			



RECOMMENDED PCB DIMENSIONS DIAGRAM

TOLERANCE ± 0.05



TOLERANCE ± 0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity	
		CHK			
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD		FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT, SMT TYPE.	
		PRODUCT SPEC			
		APPLICATION SPEC		SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
MATERIAL		FINISH		WEIGHT	
				A3 00779 C=1734592	
				CUSTOMER DRAWING	
				SCALE	
				SHEET	
				2 OF 3	
				REV C	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

C

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR



DESCRIPTION

DATE

DWN


APVD

SEE SHEET 1.



NOTE :

1. TAPE REEL:
DIAMETER: 13", THICKNESS : 0.35±0.05mm.
2. CARTON:
SIZE: 350mm(L)X 350mm(W)X 340mm(H).



12000	2000	44.00	26.70	30.55	31.50	50	
		44.00	26.20	30.05	31.00	49	
		44.00	25.70	29.55	30.50	48	
		44.00	25.20	29.05	30.00	47	
		44.00	24.70	28.55	29.50	46	
		44.00	24.20	28.05	29.00	45	
		44.00	23.70	27.55	28.50	44	
		44.00	23.20	27.05	28.00	43	
		44.00	22.70	26.55	27.50	42	
		44.00	22.20	26.05	27.00	41	
		44.00	21.70	25.55	26.50	40	
		44.00	21.20	25.05	26.00	39	
		44.00	20.70	24.55	25.50	38	
		44.00	20.20	24.05	25.00	37	
		44.00	19.70	23.55	24.50	36	
		44.00	19.20	23.05	24.00	35	
		44.00	18.70	22.55	23.50	34	
		44.00	18.20	22.05	23.00	33	
		44.00	17.70	21.55	22.50	32	
		44.00	17.20	21.05	22.00	31	
16000		32.00	16.70	20.55	21.50	30	
		32.00	16.20	20.05	21.00	29	
		32.00	15.70	19.55	20.50	28	
		32.00	15.20	19.05	20.00	27	
		32.00	14.70	18.55	19.50	26	
		32.00	14.20	18.05	19.00	25	
		32.00	13.70	17.55	18.50	24	
		32.00	13.20	17.05	18.00	23	
		32.00	12.70	16.55	17.50	22	
		32.00	12.20	16.05	17.00	21	
20000		24.00	11.70	15.55	16.50	20	
		24.00	11.20	15.05	16.00	19	
		24.00	10.70	14.55	15.50	18	
		24.00	10.20	14.05	15.00	17	
		24.00	9.70	13.55	14.50	16	
		24.00	9.20	13.05	14.00	15	
		24.00	8.70	12.55	13.50	14	
		24.00	8.20	12.05	13.00	13	
		24.00	7.70	11.55	12.50	12	
		24.00	7.20	11.05	12.00	11	
	24.00	6.70	10.55	11.50	10		
	24.00	6.20	10.05	11.00	09		
	24.00	5.70	9.55	10.50	08		
	24.00	5.20	9.05	10.00	07		
	24.00	4.70	8.55	9.50	06		
	24.00	4.20	8.05	9.00	05		
	APQ (PCS/CARTON)	PPQ (PCS/REEL)	D	C	B	A	POS
	DIMENSIONS						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity	
DIMENSIONS: MM		CHK		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD		
0 PLC ± -		PRODUCT SPEC		
1 PLC ± -		APPLICATION SPEC	NAME	
2 PLC ± -		WEIGHT	FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT, SMT TYPE.	
3 PLC ± -		CUSTOMER DRAWING	SIZE	
4 PLC ± -			CAGE CODE	
ANGLES ± -			DRAWING NO	
FINISH			RESTRICTED TO	
			A3 00779 C=1734592	
			SCALE	
			SHEET 3 OF 3	
			REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1734592-8](#)