

CHISEL


SKUS	DESCRIPTION
263.G19	CHISEL




Cutting angle: 60°

HARDNESS

Tip hardened to 57 - 60 HRc
Head hardened to 36 - 44 HRc



	A [MM]	A [IN]	DIAMETER [MM]	LENGTH L [MM]	LENGTH L1 [MM]	WEIGHT [KG]
263.G19	15.0	12.0	190.0	15.0	0.165	
263.G20	20.0	16.0	200.0	0.305		
263.G22	25.0	18.0	20.0	0.415		